

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219533

Luminaire Tested: **LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2044.1 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219533

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219533

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20683	20683	20683
5°	45764	19556	13741
10°	183224	16988	11480
15°	422333	13519	10089
20°	630443	9588	9000
25°	826892	6392	8017
30°	949206	4027	7003
35°	870322	2578	6067
40°	713713	1682	5160
45°	413775	1165	4165
50°	117253	859	3436
55°	10725	811	2888
60°	1647	930	2383
65°	436	871	1742
70°	538	1076	1360
75°	711	1422	1422
80°	0	2120	1060
85°	0	4224	1112



TEST NUMBER: P1219533

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.3	1.5
10°-20°	271.8	13.3
20°-30°	662.3	32.4
30°-40°	717.8	35.1
40°-50°	325.2	15.9
50°-60°	25.2	1.2
60°-70°	5.2	0.3
70°-80°	3.8	0.2
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	964.5	47.2
0°-40°	1682.3	82.3
0°-60°	2032.7	99.4
0°-90°	2044.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2044.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	214	214	214	214	214	
5°	471	347	201	152	141	85
15°	4211	1378	135	98	101	1224
25°	7736	1978	60	59	75	3526
35°	7359	503	22	34	51	4527
45°	3020	64	8	19	30	2384
55°	64	8	5	11	17	145
65°	2	3	4	8	8	3
75°	2	3	4	6	4	1
85°	0	3	4	3	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1219533

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5
2.5°	319.7	314.1	316.9	309.3	304.6	300.8	302.6	300.8	288.5	285.6	276.1
5°	470.6	462.1	462.1	446.0	428.8	418.5	418.5	406.2	379.6	367.2	347.3
7.5°	843.5	826.4	812.2	761.9	696.5	659.5	650.0	597.8	530.4	487.8	437.4
10°	1862.6	1791.5	1741.2	1610.1	1434.6	1325.6	1279.0	1098.9	884.3	723.0	576.9
12.5°	3132.1	3035.3	2947.2	2732.6	2480.2	2308.6	2216.6	1950.8	1534.2	1236.4	925.1
15°	4211.0	4106.5	4002.2	3741.3	3474.6	3325.7	3156.8	2804.9	2254.5	1831.2	1377.7
17.5°	5096.2	5037.3	4930.2	4547.8	4211.8	3979.5	3803.9	3343.6	2777.2	2294.3	1781.0
20°	6115.3	5970.1	5778.4	5314.5	4855.2	4563.9	4317.2	3756.5	3101.7	2546.8	1994.5
22.5°	6973.0	6869.6	6594.4	5982.4	5306.8	5058.2	4756.5	4081.9	3310.4	2653.9	2019.1
25°	7735.9	7573.6	7228.2	6500.5	5808.8	5385.6	5015.6	4258.4	3387.3	2661.5	1978.3
27.5°	8182.7	7971.2	7565.2	6771.9	5982.4	5514.7	5104.7	4288.8	3339.0	2560.9	1829.4
30°	8485.5	8064.2	7615.3	6774.8	5927.4	5449.2	5024.1	4136.1	3137.8	2331.3	1578.9
32.5°	7986.5	7742.5	7313.7	6505.2	5627.5	5160.7	4738.4	3804.8	2823.7	1990.7	1098.9
35°	7359.2	7161.9	6788.9	5986.2	5177.8	4737.5	4289.7	3379.8	2414.8	1368.2	502.8
37.5°	6630.5	6475.9	6074.5	5341.0	4629.4	4198.7	3749.8	2880.6	1700.3	678.4	305.6
40°	5643.7	5512.6	5183.5	4594.3	3938.7	3528.7	3115.0	2154.8	923.3	378.6	199.3
42.5°	4638.9	4528.8	4229.0	3719.4	3143.5	2805.7	2441.4	1313.1	459.3	238.2	111.0
45°	3020.2	2882.6	2721.3	2487.9	2203.2	1995.4	1565.6	633.8	272.3	132.8	63.5
47.5°	1731.6	1640.5	1375.8	1085.6	881.5	804.6	585.5	295.0	150.0	76.9	38.9
50°	778.0	719.3	603.4	491.5	355.9	278.0	236.2	148.1	73.9	41.8	26.6
52.5°	191.7	195.4	185.0	162.2	144.1	122.5	106.3	69.3	38.9	25.6	17.1
55°	63.5	64.6	58.9	56.0	51.3	47.5	43.7	31.3	23.7	22.8	8.5
57.5°	22.8	22.8	23.7	21.8	20.9	19.9	18.9	16.1	14.4	8.5	4.8
60°	8.5	8.5	8.5	9.5	9.5	9.5	10.4	9.5	6.6	4.8	3.8
62.5°	3.8	3.8	3.8	3.8	4.8	4.8	5.7	4.8	3.8	3.8	2.8
65°	1.9	1.9	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
67.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8	2.8
70°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8	2.8
72.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8	2.8
75°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.8
77.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.8
80°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.8
82.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.8
85°	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	2.8
87.5°	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219533

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5
2.5°	266.6	260.9	249.5	241.0	234.4	233.4	227.8	218.2	214.4	207.8	202.2
5°	328.3	314.1	296.0	278.9	266.6	260.0	240.0	222.0	211.5	201.1	191.7
7.5°	394.7	362.4	331.2	303.6	286.5	276.1	252.3	223.1	204.0	188.9	176.6
10°	478.2	411.7	357.7	315.0	292.2	278.0	249.5	214.4	190.7	172.7	160.4
12.5°	669.0	487.8	382.4	320.6	292.2	272.3	238.2	203.0	176.6	154.6	141.3
15°	995.3	681.3	453.5	323.4	282.7	260.0	221.1	184.1	157.5	134.8	122.5
17.5°	1302.8	896.7	566.4	343.5	277.2	241.9	198.2	162.2	134.8	112.9	102.4
20°	1462.0	1003.8	629.1	358.7	267.6	219.1	171.7	138.5	112.0	93.0	84.4
22.5°	1466.0	994.4	598.7	323.4	232.4	187.8	147.1	113.9	91.1	75.0	68.4
25°	1375.8	879.6	492.4	252.3	187.8	157.5	122.5	93.0	71.1	59.8	55.1
27.5°	1206.0	711.6	363.4	182.1	147.1	125.2	95.9	71.1	54.1	46.5	43.7
30°	932.7	440.2	201.1	134.8	111.0	93.8	69.3	47.5	40.8	36.0	34.2
32.5°	463.0	215.3	142.4	95.9	75.9	59.8	43.7	35.2	31.3	28.5	27.5
35°	251.5	154.6	89.2	57.9	45.6	38.0	29.4	24.6	22.8	21.8	21.8
37.5°	175.6	92.0	54.1	35.2	28.5	25.6	20.9	18.1	17.1	17.1	17.1
40°	96.8	55.1	33.2	22.8	18.9	17.1	14.4	13.3	13.3	13.3	14.4
42.5°	56.0	34.2	22.8	16.1	13.3	12.3	10.4	9.5	10.4	10.4	11.3
45°	36.0	25.6	15.2	11.3	9.5	8.5	7.6	7.6	8.5	8.5	9.5
47.5°	25.6	18.1	10.4	7.6	5.7	5.7	5.7	5.7	6.6	7.6	8.5
50°	15.2	9.5	5.7	4.8	3.8	3.8	3.8	4.8	5.7	5.7	6.6
52.5°	8.5	5.7	3.8	3.8	2.8	2.8	3.8	3.8	4.8	5.7	6.6
55°	4.8	3.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	4.8	5.7
57.5°	3.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	4.8	4.8
60°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	4.8	4.8
62.5°	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	4.8
65°	2.8	2.8	2.8	3.8	2.8	3.8	3.8	3.8	3.8	3.8	4.8
67.5°	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	4.8
70°	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	4.8
72.5°	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	4.8
75°	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
77.5°	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
80°	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
85°	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
87.5°	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219533

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5
2.5°	200.2	193.6	188.9	186.9	183.1	184.1	181.3	179.3	173.6	173.6	169.8
5°	185.0	176.6	170.8	168.0	164.1	163.3	160.4	157.5	151.8	150.9	148.1
7.5°	169.0	160.4	153.7	150.9	147.1	146.1	142.4	140.4	135.6	134.8	131.9
10°	151.8	142.4	136.7	133.7	130.0	130.0	127.2	125.2	121.5	121.5	119.5
12.5°	133.7	125.2	121.5	117.6	115.8	115.8	113.9	112.0	109.2	110.0	109.2
15°	114.7	108.2	104.3	102.4	101.6	101.6	100.6	99.6	97.8	99.6	97.8
17.5°	96.8	92.0	89.2	88.3	87.3	87.3	87.3	88.3	87.3	89.2	89.2
20°	79.7	75.9	73.9	73.9	73.0	75.0	75.0	76.9	76.9	79.7	80.7
22.5°	65.4	62.6	61.7	61.7	61.7	63.5	64.6	66.4	67.4	70.2	72.2
25°	52.2	51.3	51.3	51.3	52.2	54.1	56.0	57.9	58.9	62.6	63.5
27.5°	42.7	41.8	42.7	42.7	43.7	46.5	48.4	50.2	52.2	55.1	56.9
30°	34.2	34.2	35.2	36.0	37.0	38.9	41.8	43.7	45.6	48.4	50.2
32.5°	27.5	28.5	29.4	30.4	30.4	33.2	35.2	38.0	38.9	41.8	43.7
35°	22.8	23.7	24.6	25.6	25.6	28.5	30.4	32.2	34.2	36.0	38.0
37.5°	18.1	18.9	20.9	21.8	21.8	24.6	25.6	27.5	29.4	31.3	33.2
40°	15.2	16.1	18.1	18.1	18.9	20.9	21.8	23.7	25.6	27.5	29.4
42.5°	12.3	13.3	15.2	16.1	16.1	18.1	18.9	20.9	21.8	23.7	24.6
45°	11.3	11.3	13.3	13.3	14.4	15.2	17.1	18.1	18.9	20.9	21.8
47.5°	9.5	10.4	11.3	12.3	12.3	13.3	14.4	15.2	16.1	18.1	18.9
50°	7.6	8.5	10.4	10.4	10.4	12.3	13.3	14.4	14.4	15.2	16.1
52.5°	7.6	7.6	8.5	9.5	9.5	10.4	11.3	12.3	12.3	13.3	14.4
55°	6.6	6.6	7.6	8.5	8.5	9.5	10.4	10.4	11.3	11.3	12.3
57.5°	5.7	6.6	7.6	7.6	7.6	8.5	9.5	9.5	10.4	10.4	11.3
60°	5.7	6.6	6.6	7.6	7.6	8.5	8.5	8.5	9.5	9.5	9.5
62.5°	5.7	5.7	6.6	6.6	6.6	7.6	7.6	8.5	8.5	8.5	8.5
65°	5.7	5.7	6.6	6.6	6.6	7.6	7.6	7.6	7.6	7.6	7.6
67.5°	4.8	5.7	5.7	5.7	6.6	6.6	6.6	6.6	6.6	6.6	6.6
70°	4.8	4.8	5.7	5.7	5.7	6.6	6.6	6.6	6.6	6.6	6.6
72.5°	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
75°	4.8	4.8	4.8	4.8	4.8	5.7	5.7	5.7	5.7	4.8	4.8
77.5°	3.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	3.8
80°	3.8	3.8	4.8	3.8	4.8	4.8	4.8	4.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	2.8	2.8
85°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	2.8	2.8	2.8	1.9
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	2.8	2.8	2.8	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219533

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	213.5	213.5	213.5	213.5	213.5	213.5	213.5	213.5
2.5°	168.0	169.8	168.0	169.8	165.0	167.0	169.0	164.1
5°	146.1	144.1	145.2	147.1	143.3	144.1	145.2	141.3
7.5°	130.9	131.9	130.0	131.9	129.1	130.0	130.9	128.0
10°	118.7	119.5	118.7	119.5	116.7	118.7	119.5	116.7
12.5°	107.1	109.2	108.2	110.0	107.1	109.2	111.0	107.1
15°	98.7	100.6	99.6	101.6	99.6	101.6	103.4	100.6
17.5°	90.1	92.0	92.0	93.8	93.0	94.8	96.8	93.8
20°	81.5	84.4	84.4	86.3	86.3	87.3	90.1	87.3
22.5°	73.9	76.9	76.9	78.7	78.7	80.7	82.6	80.7
25°	65.4	69.3	70.2	72.2	72.2	73.9	76.9	75.0
27.5°	59.8	62.6	63.5	65.4	66.4	68.4	70.2	68.4
30°	52.2	56.0	56.9	58.9	59.8	62.6	63.5	62.6
32.5°	46.5	49.3	50.2	52.2	54.1	56.0	57.9	56.9
35°	40.8	43.7	44.6	46.5	47.5	50.2	52.2	51.3
37.5°	36.0	38.9	39.7	40.8	41.8	44.6	46.5	45.6
40°	31.3	33.2	34.2	36.0	37.0	38.9	40.8	40.8
42.5°	27.5	29.4	30.4	31.3	32.2	34.2	36.0	35.2
45°	23.7	25.6	26.6	27.5	28.5	29.4	31.3	30.4
47.5°	19.9	21.8	22.8	23.7	24.6	25.6	27.5	26.6
50°	17.1	18.9	18.9	19.9	20.9	21.8	23.7	22.8
52.5°	15.2	16.1	17.1	17.1	18.1	18.9	20.9	19.9
55°	13.3	14.4	14.4	15.2	15.2	16.1	17.1	17.1
57.5°	11.3	12.3	12.3	13.3	13.3	14.4	15.2	15.2
60°	10.4	10.4	11.3	11.3	11.3	12.3	12.3	12.3
62.5°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
65°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
67.5°	6.6	6.6	6.6	6.6	6.6	5.7	5.7	5.7
70°	5.7	5.7	5.7	5.7	5.7	4.8	4.8	4.8
72.5°	5.7	5.7	4.8	4.8	4.8	4.8	4.8	3.8
75°	4.8	4.8	4.8	4.8	3.8	3.8	3.8	3.8
77.5°	3.8	3.8	3.8	3.8	2.8	2.8	2.8	2.8
80°	3.8	2.8	2.8	2.8	2.8	2.8	2.8	1.9
82.5°	2.8	2.8	2.8	1.9	1.9	1.9	1.9	1.9
85°	1.9	1.9	1.9	1.9	1.0	1.0	1.0	1.0
87.5°	1.9	1.0	1.0	1.0	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)