

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212258

Luminaire Tested: **LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1930.2 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212258

CATALOG NUMBER: LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212258

CATALOG NUMBER: LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	73	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	57	67	61	57	66	61	57	64	60	56	54		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20189	20189	20189
5°	38665	19225	15608
10°	126415	17038	13290
15°	309594	14081	11734
20°	583319	10732	10515
25°	976474	7611	9203
30°	1237005	5235	7853
35°	1127142	3394	6658
40°	742319	2415	5640
45°	321559	1603	4658
50°	57029	1115	3843
55°	9154	895	3226
60°	2267	833	2461
65°	734	986	1926
70°	595	1218	1501
75°	786	1198	1198
80°	0	1785	1172
85°	0	3557	1223



TEST NUMBER: P1212258

CATALOG NUMBER: LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.7	1.4
10°-20°	214.7	11.1
20°-30°	646.7	33.5
30°-40°	736.1	38.1
40°-50°	272.2	14.1
50°-60°	21.6	1.1
60°-70°	5.8	0.3
70°-80°	4.1	0.2
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.1	46.0
0°-40°	1624.2	84.1
0°-60°	1918.0	99.4
0°-90°	1930.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1930.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	208	208	208	208	208	
5°	398	292	198	166	160	64
15°	3087	1043	140	111	117	968
25°	9135	1524	71	69	86	4170
35°	9531	534	29	39	56	5666
45°	2347	63	12	21	34	1987
55°	54	12	5	13	19	89
65°	3	3	4	8	8	4
75°	2	3	3	5	3	1
85°	0	2	3	3	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212258

CATALOG NUMBER: LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4
2.5°	267.9	270.0	267.9	263.6	263.6	258.3	256.2	254.1	248.7	245.5	241.2
5°	397.6	391.2	385.9	373.2	368.9	357.1	348.6	336.9	321.0	307.2	292.3
7.5°	680.3	670.7	650.6	612.3	588.9	560.2	537.8	500.6	452.8	413.5	374.2
10°	1285.1	1243.7	1195.8	1109.8	1047.1	980.1	926.9	827.0	706.8	608.0	512.4
12.5°	2070.7	2073.9	1984.6	1839.0	1723.2	1605.1	1513.7	1328.8	1116.1	930.1	746.2
15°	3086.9	3028.5	2935.9	2712.8	2481.0	2309.9	2164.2	1883.7	1582.8	1310.7	1042.8
17.5°	4157.4	4181.8	3966.0	3601.5	3234.7	2978.5	2758.4	2333.3	1976.0	1639.1	1311.7
20°	5658.2	5490.3	5182.1	4591.1	4021.3	3650.3	3324.0	2772.3	2273.7	1845.3	1477.6
22.5°	7388.9	7117.8	6490.6	5658.2	4796.2	4282.8	3827.8	3068.8	2463.0	1950.6	1533.9
25°	9135.3	8928.1	7928.8	6685.2	5450.0	4784.5	4195.6	3269.8	2553.3	1975.0	1524.4
27.5°	10483.2	10145.2	9006.7	7385.7	5840.0	5054.5	4366.8	3331.4	2534.2	1915.5	1433.9
30°	11058.3	10631.0	9369.1	7545.1	5843.2	5009.9	4281.8	3209.2	2398.1	1764.5	1263.9
32.5°	10703.2	10210.0	8937.6	7104.0	5443.5	4661.2	3953.3	2944.5	2172.7	1527.5	949.2
35°	9530.8	9039.6	7860.9	6233.4	4805.8	4122.3	3506.8	2599.0	1850.6	1132.1	533.6
37.5°	7804.4	7385.7	6542.8	5224.6	4050.0	3495.1	2982.8	2189.8	1378.7	649.5	267.9
40°	5869.9	5575.4	5069.4	4143.6	3278.2	2856.3	2443.9	1677.4	837.6	326.4	151.9
42.5°	4069.1	3877.8	3623.7	3065.7	2528.9	2238.7	1908.0	1120.4	430.5	179.6	94.6
45°	2347.1	2226.9	2156.9	1918.7	1709.4	1567.9	1275.6	603.7	217.9	107.4	62.8
47.5°	1036.5	956.7	922.7	822.8	765.3	727.1	577.2	257.3	117.0	69.1	52.1
50°	378.4	378.4	379.5	333.8	273.2	245.5	192.4	113.8	65.9	54.2	38.3
52.5°	133.9	131.8	137.1	129.7	113.8	102.0	85.0	57.4	40.4	34.0	21.3
55°	54.2	52.1	54.2	51.1	47.8	44.6	39.4	30.8	25.5	21.3	11.7
57.5°	24.5	24.5	25.5	24.5	24.5	22.4	20.2	23.4	18.1	11.7	7.4
60°	11.7	11.7	12.7	12.7	12.7	11.7	11.7	12.7	10.7	7.4	5.3
62.5°	5.3	5.3	6.4	6.4	6.4	6.4	6.4	7.4	5.3	4.3	3.2
65°	3.2	2.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
67.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2	3.2
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	3.2
80°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
82.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212258

CATALOG NUMBER: LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4
2.5°	237.1	233.8	227.4	224.3	220.1	216.8	214.7	210.4	206.3	203.1	200.9
5°	278.6	266.8	253.0	242.4	233.8	228.5	220.1	212.6	204.1	197.7	192.4
7.5°	339.1	310.4	279.6	258.3	246.6	236.0	221.1	208.4	196.6	188.2	180.7
10°	433.7	372.0	317.8	276.3	256.2	241.2	217.9	199.8	185.0	173.2	165.9
12.5°	591.0	464.5	368.9	298.7	267.9	245.5	212.6	188.2	170.1	158.4	148.8
15°	806.8	600.6	439.1	325.3	281.6	249.8	204.1	174.3	154.2	140.4	131.8
17.5°	1009.8	743.1	518.7	357.1	295.6	251.9	192.4	156.2	135.1	122.2	113.8
20°	1137.4	835.5	571.9	375.2	299.7	245.5	176.5	137.1	115.8	104.1	95.7
22.5°	1167.2	846.1	567.6	358.2	281.6	226.4	154.2	118.0	97.7	87.2	79.7
25°	1123.6	786.6	508.1	309.3	240.2	190.3	128.6	95.7	80.8	71.2	65.9
27.5°	1014.1	669.7	401.8	232.8	179.6	140.4	97.7	74.4	64.9	57.4	54.2
30°	817.5	470.9	251.9	144.6	114.8	92.5	70.2	57.4	49.9	46.8	43.5
32.5°	495.4	242.4	132.8	86.1	72.3	62.8	51.1	42.5	38.3	36.1	35.1
35°	236.0	127.6	81.9	58.5	51.1	44.6	37.2	31.9	29.7	28.7	28.7
37.5°	133.9	82.9	55.3	39.4	35.1	30.8	27.7	24.5	23.4	23.4	23.4
40°	85.0	53.1	36.1	28.7	25.5	23.4	21.3	19.1	19.1	19.1	19.1
42.5°	55.3	38.3	27.7	21.3	19.1	18.1	15.9	14.8	14.8	14.8	15.9
45°	43.5	31.9	22.4	17.0	14.8	13.8	12.7	11.7	11.7	11.7	12.7
47.5°	37.2	22.4	14.8	11.7	9.6	9.6	8.4	8.4	8.4	9.6	10.7
50°	22.4	13.8	9.6	7.4	6.4	6.4	6.4	6.4	6.4	7.4	8.4
52.5°	12.7	8.4	6.4	5.3	4.3	4.3	4.3	4.3	5.3	6.4	6.4
55°	8.4	6.4	4.3	4.3	3.2	3.2	3.2	4.3	4.3	5.3	6.4
57.5°	5.3	4.3	3.2	3.2	3.2	3.2	3.2	3.2	4.3	5.3	5.3
60°	4.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3
62.5°	3.2	3.2	4.3	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3
65°	3.2	3.2	4.3	4.3	3.2	3.2	3.2	3.2	3.2	4.3	5.3
67.5°	3.2	3.2	4.3	4.3	4.3	4.3	3.2	3.2	3.2	4.3	4.3
70°	3.2	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2	4.3	4.3
72.5°	3.2	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2	4.3	4.3
75°	3.2	3.2	4.3	4.3	4.3	4.3	4.3	3.2	3.2	3.2	4.3
77.5°	3.2	3.2	4.3	4.3	4.3	4.3	4.3	3.2	3.2	3.2	4.3
80°	3.2	3.2	3.2	4.3	3.2	4.3	3.2	3.2	3.2	3.2	3.2
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212258

CATALOG NUMBER: LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4
2.5°	197.7	195.6	192.4	191.3	192.4	191.3	186.0	185.0	182.9	182.9	182.9
5°	187.0	183.9	179.6	177.5	177.5	175.4	170.1	169.0	165.9	165.9	164.8
7.5°	174.3	170.1	164.8	162.6	162.6	160.5	155.2	153.1	150.9	150.9	149.9
10°	159.4	154.2	148.8	147.8	146.7	143.5	140.4	139.2	136.1	137.1	136.1
12.5°	142.4	138.1	133.9	131.8	131.8	128.6	126.5	125.4	124.4	124.4	124.4
15°	126.5	121.1	117.0	115.8	115.8	114.8	112.7	112.7	110.6	112.7	112.7
17.5°	108.4	104.1	103.1	101.0	102.0	101.0	98.9	100.0	100.0	101.0	102.0
20°	91.4	88.2	87.2	86.1	87.2	87.2	86.1	87.2	88.2	91.4	93.6
22.5°	76.6	74.4	74.4	73.3	74.4	75.5	74.4	76.6	78.6	80.8	83.9
25°	63.8	62.8	62.8	62.8	63.8	64.9	65.9	68.0	69.1	72.3	74.4
27.5°	52.1	52.1	52.1	53.1	54.2	55.3	56.3	59.6	60.6	63.8	65.9
30°	43.5	42.5	43.5	44.6	45.8	47.8	48.9	51.1	52.1	55.3	57.4
32.5°	35.1	36.1	37.2	38.3	39.4	40.4	41.5	43.5	45.8	47.8	49.9
35°	29.7	29.7	30.8	31.9	33.0	35.1	36.1	37.2	39.4	41.5	42.5
37.5°	24.5	25.5	26.5	27.7	28.7	29.7	30.8	31.9	33.0	35.1	37.2
40°	20.2	21.3	22.4	23.4	23.4	25.5	25.5	27.7	28.7	30.8	33.0
42.5°	17.0	18.1	19.1	20.2	20.2	21.3	22.4	23.4	24.5	26.5	28.7
45°	13.8	14.8	15.9	17.0	17.0	18.1	19.1	20.2	21.3	23.4	24.5
47.5°	11.7	12.7	13.8	14.8	14.8	15.9	17.0	18.1	18.1	20.2	21.3
50°	9.6	10.7	11.7	12.7	12.7	13.8	14.8	15.9	15.9	17.0	18.1
52.5°	7.4	8.4	10.7	10.7	11.7	12.7	12.7	13.8	13.8	14.8	15.9
55°	7.4	8.4	9.6	9.6	10.7	11.7	11.7	12.7	12.7	12.7	13.8
57.5°	6.4	7.4	8.4	9.6	9.6	10.7	10.7	10.7	10.7	11.7	11.7
60°	6.4	7.4	7.4	8.4	8.4	9.6	9.6	9.6	9.6	10.7	10.7
62.5°	6.4	6.4	7.4	7.4	8.4	8.4	8.4	9.6	9.6	9.6	9.6
65°	5.3	6.4	7.4	7.4	7.4	8.4	8.4	8.4	8.4	8.4	8.4
67.5°	5.3	6.4	6.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
70°	5.3	5.3	6.4	6.4	6.4	7.4	7.4	7.4	6.4	7.4	6.4
72.5°	4.3	5.3	5.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
75°	4.3	5.3	5.3	5.3	5.3	6.4	6.4	5.3	5.3	5.3	5.3
77.5°	4.3	4.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	4.3
80°	4.3	4.3	4.3	4.3	5.3	5.3	4.3	4.3	4.3	4.3	4.3
82.5°	3.2	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2	3.2
85°	3.2	3.2	4.3	4.3	4.3	4.3	3.2	3.2	3.2	3.2	2.1
87.5°	3.2	3.2	3.2	4.3	3.2	3.2	3.2	3.2	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212258

CATALOG NUMBER: LDSQA4A25935D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	208.4	208.4	208.4	208.4	208.4	208.4	208.4	208.4
2.5°	179.6	178.6	179.6	178.6	178.6	179.6	176.5	178.6
5°	162.6	160.5	161.6	160.5	159.4	160.5	158.4	160.5
7.5°	147.8	146.7	146.7	146.7	145.6	146.7	144.6	146.7
10°	135.1	133.9	133.9	133.9	133.9	135.1	132.8	135.1
12.5°	122.2	122.2	123.3	122.2	123.3	124.4	122.2	124.4
15°	111.6	112.7	113.8	113.8	114.8	115.8	114.8	117.0
17.5°	103.1	104.1	106.3	106.3	107.4	109.5	108.4	110.6
20°	94.6	95.7	97.7	97.7	98.9	101.0	100.0	102.0
22.5°	85.0	87.2	88.2	89.3	90.4	92.5	91.4	93.6
25°	75.5	78.6	79.7	80.8	81.9	83.9	83.9	86.1
27.5°	68.0	70.2	71.2	72.3	74.4	76.6	76.6	77.6
30°	59.6	61.6	63.8	64.9	65.9	68.0	68.0	70.2
32.5°	52.1	54.2	55.3	56.3	58.5	60.6	61.6	62.8
35°	44.6	47.8	48.9	51.1	52.1	55.3	55.3	56.3
37.5°	39.4	41.5	43.5	44.6	46.8	48.9	48.9	51.1
40°	35.1	37.2	38.3	39.4	41.5	43.5	43.5	44.6
42.5°	29.7	33.0	34.0	35.1	36.1	38.3	39.4	40.4
45°	26.5	27.7	28.7	29.7	30.8	33.0	33.0	34.0
47.5°	22.4	23.4	24.5	25.5	26.5	27.7	28.7	29.7
50°	19.1	20.2	21.3	21.3	22.4	24.5	24.5	25.5
52.5°	15.9	17.0	18.1	18.1	19.1	21.3	21.3	22.4
55°	13.8	14.8	15.9	15.9	17.0	18.1	18.1	19.1
57.5°	12.7	12.7	13.8	13.8	14.8	14.8	15.9	15.9
60°	10.7	11.7	11.7	11.7	12.7	12.7	12.7	12.7
62.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	10.7
65°	8.4	8.4	8.4	8.4	8.4	8.4	7.4	8.4
67.5°	7.4	7.4	7.4	7.4	6.4	6.4	6.4	6.4
70°	6.4	6.4	6.4	6.4	6.4	5.3	5.3	5.3
72.5°	5.3	5.3	5.3	5.3	5.3	4.3	4.3	4.3
75°	5.3	5.3	4.3	4.3	4.3	4.3	4.3	3.2
77.5°	4.3	4.3	4.3	4.3	3.2	3.2	3.2	3.2
80°	3.2	3.2	3.2	3.2	3.2	3.2	2.1	2.1
82.5°	3.2	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	2.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
87.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)