

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219535

Luminaire Tested: **LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219535
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1898.3 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219535

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219535

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	20489	20489	20489
5°	45880	19274	13819
10°	179919	16880	10880
15°	390590	13660	9458
20°	582680	10124	8557
25°	757884	7140	7440
30°	847836	4810	6499
35°	762998	2815	5535
40°	622686	1922	4818
45°	357536	1302	3905
50°	104579	1025	3301
55°	12059	811	2736
60°	2577	930	2209
65°	871	871	1559
70°	793	1076	1076
75°	711	1422	1048
80°	0	2120	1060
85°	0	4224	1112



TEST NUMBER: P1219535

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.3	1.6
10°-20°	259.9	13.7
20°-30°	619.9	32.7
30°-40°	654.2	34.5
40°-50°	296.7	15.6
50°-60°	26.0	1.4
60°-70°	5.5	0.3
70°-80°	3.6	0.2
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	910.1	47.9
0°-40°	1564.4	82.4
0°-60°	1887.1	99.4
0°-90°	1898.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1898.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	212	212	212	212	212	
5°	472	346	198	152	142	85
15°	3894	1370	136	93	94	1133
25°	7090	1885	67	57	70	3221
35°	6452	520	24	32	47	3984
45°	2610	73	10	18	28	2069
55°	71	11	5	10	16	143
65°	4	4	4	8	7	5
75°	2	2	4	5	3	2
85°	0	2	4	3	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219535

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5
2.5°	314.5	316.5	307.8	308.9	300.2	304.0	301.2	293.5	287.8	278.3	274.5
5°	471.8	474.6	455.6	449.9	429.8	429.8	421.3	401.2	383.2	361.3	346.0
7.5°	862.6	874.0	816.8	774.0	711.0	695.8	666.2	597.6	541.3	484.2	441.3
10°	1829.0	1808.1	1689.9	1592.7	1430.6	1370.6	1290.6	1093.2	912.1	732.0	590.9
12.5°	2884.2	2951.7	2724.0	2644.9	2388.5	2334.2	2163.6	1841.4	1535.5	1217.1	935.1
15°	3894.5	3914.6	3715.3	3586.5	3274.0	3203.4	2993.7	2615.4	2203.7	1759.5	1369.7
17.5°	4705.6	4785.7	4493.0	4354.9	3948.9	3835.3	3588.5	3128.2	2669.7	2184.6	1722.3
20°	5652.0	5673.0	5326.2	5060.1	4529.3	4356.8	4061.3	3490.3	2944.2	2390.4	1913.0
22.5°	6512.7	6508.0	6062.0	5686.4	5014.4	4808.5	4443.5	3766.8	3132.0	2482.0	1931.1
25°	7090.3	7105.6	6628.0	6183.9	5359.4	5081.1	4669.4	3910.6	3195.8	2479.2	1885.3
27.5°	7398.1	7383.0	6871.1	6396.5	5486.2	5174.4	4727.4	3915.4	3137.7	2381.9	1748.1
30°	7579.3	7375.4	6829.2	6336.3	5400.4	5080.2	4625.6	3764.8	2944.2	2164.6	1503.1
32.5°	7095.1	7016.0	6540.4	6017.0	5104.9	4787.5	4338.7	3444.6	2637.2	1831.9	1077.0
35°	6451.7	6454.6	5990.4	5501.4	4641.7	4365.3	3902.1	3054.8	2262.7	1273.4	520.3
37.5°	5776.9	5786.5	5345.2	4890.5	4125.2	3834.4	3400.8	2610.6	1627.9	648.1	313.6
40°	4923.9	4944.0	4563.6	4198.5	3492.2	3212.0	2825.1	1975.8	910.3	362.2	212.5
42.5°	4023.1	4047.9	3710.5	3386.4	2786.0	2555.3	2212.2	1223.9	451.8	234.4	124.8
45°	2609.7	2681.2	2430.5	2294.1	1946.4	1809.1	1443.9	624.3	272.6	137.3	73.4
47.5°	1493.6	1494.5	1282.8	1027.5	842.6	733.0	572.8	284.0	159.2	77.2	44.7
50°	693.9	711.0	563.3	469.0	335.5	284.0	233.6	153.5	83.8	44.7	27.7
52.5°	202.0	213.5	193.5	175.3	148.7	132.5	113.5	75.3	43.8	26.7	17.3
55°	71.4	76.2	71.4	66.8	60.1	54.3	48.6	36.3	24.8	16.2	11.4
57.5°	29.5	30.6	29.5	28.5	26.7	26.7	23.8	20.0	15.2	10.5	7.6
60°	13.3	14.4	13.3	14.4	13.3	13.3	13.3	14.4	9.5	6.8	5.7
62.5°	5.7	6.8	6.8	6.8	6.8	7.6	7.6	6.8	5.7	4.8	3.8
65°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
67.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
70°	2.8	2.8	2.8	2.8	2.8	2.8	1.9	1.9	2.8	2.8	2.8
72.5°	2.8	2.8	2.8	2.8	1.9	1.9	1.9	1.9	1.9	2.8	2.8
75°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
77.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
80°	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
82.5°	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
85°	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
87.5°	0.0	0.0	0.0	0.0	1.0	1.0	1.0	1.0	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219535

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5
2.5°	269.8	261.2	247.7	239.3	235.5	229.7	225.8	216.3	212.5	205.0	202.0
5°	331.8	314.5	294.5	278.3	267.8	256.4	239.3	220.3	210.6	198.2	191.6
7.5°	402.3	365.0	329.8	301.2	287.8	272.6	250.6	221.1	203.0	186.8	177.3
10°	491.8	415.6	360.3	314.5	294.5	274.5	247.7	213.5	190.6	171.6	161.1
12.5°	701.6	501.4	387.9	322.2	296.4	271.5	238.3	203.0	176.3	154.4	143.0
15°	1009.4	700.5	462.3	328.8	289.7	259.3	221.1	185.7	158.3	136.2	124.8
17.5°	1281.9	893.0	565.2	353.6	287.8	244.9	200.2	164.0	137.3	116.3	106.7
20°	1430.6	994.0	633.8	368.8	279.3	223.1	176.3	142.1	116.3	98.2	89.5
22.5°	1433.5	988.3	609.0	335.5	246.0	193.5	152.5	120.0	97.2	81.0	74.3
25°	1347.6	881.6	508.0	264.0	201.1	164.0	127.7	100.0	79.0	66.8	60.9
27.5°	1187.6	716.8	373.6	190.6	157.2	132.5	103.0	80.1	62.0	54.3	49.5
30°	934.1	467.0	218.2	142.1	122.0	102.0	78.2	56.3	48.6	43.0	39.0
32.5°	501.4	226.8	152.5	104.8	86.7	71.4	51.5	41.0	35.3	31.4	30.6
35°	262.1	165.8	102.0	66.8	55.2	46.8	35.3	28.5	25.7	23.8	23.8
37.5°	187.8	103.9	64.8	43.0	36.3	29.5	24.8	21.0	19.0	19.0	19.0
40°	111.5	63.9	39.0	27.7	23.8	21.0	18.1	15.2	15.2	15.2	15.2
42.5°	67.7	40.0	27.7	19.0	17.3	15.2	13.3	12.5	11.4	11.4	12.5
45°	41.9	27.7	18.1	14.4	13.3	11.4	10.5	9.5	9.5	9.5	10.5
47.5°	26.7	20.0	13.3	9.5	8.5	7.6	6.8	6.8	7.6	7.6	8.5
50°	20.0	12.5	8.5	6.8	5.7	5.7	4.8	5.7	5.7	6.8	7.6
52.5°	11.4	7.6	5.7	4.8	4.8	3.8	3.8	4.8	4.8	5.7	6.8
55°	7.6	5.7	4.8	3.8	3.8	3.8	3.8	3.8	4.8	4.8	5.7
57.5°	5.7	4.8	3.8	3.8	3.8	2.8	3.8	3.8	3.8	4.8	5.7
60°	4.8	3.8	3.8	3.8	3.8	2.8	2.8	3.8	3.8	4.8	4.8
62.5°	3.8	3.8	3.8	3.8	3.8	2.8	3.8	3.8	3.8	3.8	4.8
65°	2.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	4.8
67.5°	2.8	2.8	3.8	3.8	3.8	2.8	3.8	3.8	3.8	3.8	4.8
70°	2.8	2.8	2.8	3.8	3.8	2.8	3.8	3.8	3.8	3.8	3.8
72.5°	2.8	2.8	2.8	3.8	3.8	2.8	3.8	3.8	3.8	3.8	3.8
75°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8
77.5°	2.8	2.8	2.8	2.8	3.8	2.8	3.8	3.8	3.8	3.8	3.8
80°	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8	3.8
82.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8
85°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8	3.8
87.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219535

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5
2.5°	194.5	191.6	185.7	184.9	184.0	180.2	177.3	174.5	174.5	171.6	169.7
5°	180.2	175.3	168.7	165.8	164.9	160.1	156.2	153.5	152.5	149.7	146.7
7.5°	164.9	159.2	151.5	148.7	147.8	143.0	139.2	136.2	134.5	131.6	129.6
10°	148.7	142.1	135.3	132.5	131.6	126.8	124.0	121.1	119.2	117.2	115.3
12.5°	131.6	125.8	119.2	116.3	115.3	111.5	108.7	106.7	105.8	103.9	103.0
15°	114.3	108.7	103.0	101.0	100.0	97.2	95.3	94.3	93.4	93.4	92.6
17.5°	97.2	92.6	87.7	86.7	85.8	83.8	83.0	82.0	83.0	83.0	83.8
20°	81.0	77.2	73.4	73.4	72.5	71.4	71.4	71.4	73.4	74.3	76.2
22.5°	66.8	63.9	60.9	60.9	60.9	60.9	60.9	63.0	64.8	66.8	67.7
25°	55.2	52.4	51.5	51.5	51.5	52.4	53.4	55.2	57.2	59.1	60.9
27.5°	44.7	43.0	43.0	43.0	43.8	44.7	45.8	47.6	50.5	52.4	54.3
30°	36.3	35.3	35.3	36.3	37.2	38.1	40.0	41.9	43.8	45.8	47.6
32.5°	28.5	29.5	29.5	30.6	31.4	32.4	34.3	36.3	38.1	40.0	41.0
35°	23.8	23.8	24.8	25.7	26.7	27.7	29.5	31.4	32.4	34.3	36.3
37.5°	19.0	20.0	21.0	21.9	22.8	23.8	24.8	26.7	27.7	29.5	31.4
40°	16.2	17.3	18.1	19.0	19.0	21.0	21.0	22.8	23.8	25.7	27.7
42.5°	13.3	14.4	15.2	16.2	16.2	17.3	18.1	19.0	21.0	21.9	23.8
45°	10.5	11.4	12.5	13.3	14.4	15.2	15.2	17.3	18.1	19.0	21.0
47.5°	9.5	10.5	11.4	11.4	12.5	13.3	13.3	15.2	16.2	17.3	18.1
50°	7.6	8.5	9.5	10.5	10.5	11.4	12.5	13.3	14.4	15.2	15.2
52.5°	6.8	7.6	8.5	8.5	9.5	10.5	10.5	11.4	12.5	12.5	13.3
55°	6.8	7.6	7.6	8.5	8.5	9.5	9.5	10.5	10.5	11.4	11.4
57.5°	5.7	6.8	6.8	7.6	7.6	8.5	8.5	9.5	9.5	9.5	10.5
60°	5.7	5.7	6.8	6.8	7.6	7.6	7.6	8.5	8.5	8.5	9.5
62.5°	4.8	5.7	5.7	6.8	6.8	6.8	7.6	7.6	7.6	8.5	8.5
65°	4.8	5.7	5.7	6.8	6.8	6.8	6.8	6.8	7.6	7.6	7.6
67.5°	4.8	4.8	5.7	5.7	5.7	5.7	6.8	6.8	6.8	6.8	6.8
70°	4.8	4.8	4.8	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
72.5°	3.8	4.8	4.8	4.8	4.8	5.7	5.7	5.7	5.7	5.7	4.8
75°	3.8	3.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8
77.5°	3.8	3.8	3.8	4.8	4.8	4.8	4.8	4.8	4.8	3.8	3.8
80°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	2.8
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	2.8	2.8	2.8
85°	3.8	2.8	3.8	3.8	3.8	2.8	2.8	2.8	2.8	2.8	1.9
87.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219535

CATALOG NUMBER: LDSQA4A20950D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	211.5	211.5	211.5	211.5	211.5	211.5	211.5	211.5
2.5°	167.8	165.8	166.8	166.8	164.9	164.0	164.0	164.9
5°	144.9	143.0	143.9	143.9	142.1	141.0	141.0	142.1
7.5°	127.7	125.8	126.8	126.8	124.8	124.8	124.8	124.8
10°	114.3	113.5	113.5	113.5	111.5	112.5	111.5	110.6
12.5°	102.0	102.0	102.0	102.0	101.0	102.0	101.0	101.0
15°	92.6	92.6	93.4	93.4	93.4	94.3	94.3	94.3
17.5°	84.8	85.8	86.7	87.7	87.7	88.7	88.7	88.7
20°	77.2	79.0	80.1	81.0	81.0	83.0	82.0	83.0
22.5°	69.6	71.4	72.5	73.4	74.3	75.3	75.3	76.2
25°	63.0	64.8	65.7	66.8	67.7	69.6	69.6	69.6
27.5°	56.3	58.1	59.1	60.9	62.0	63.9	63.9	63.9
30°	49.5	51.5	52.4	53.4	55.2	57.2	57.2	58.1
32.5°	43.0	45.8	46.8	47.6	49.5	51.5	52.4	52.4
35°	38.1	40.0	41.0	43.0	43.8	46.8	46.8	46.8
37.5°	33.3	35.3	37.2	38.1	39.0	41.0	41.9	43.0
40°	29.5	31.4	32.4	33.3	35.3	37.2	38.1	38.1
42.5°	25.7	27.7	28.5	29.5	30.6	32.4	32.4	32.4
45°	22.8	23.8	24.8	25.7	26.7	27.7	28.5	28.5
47.5°	19.0	21.0	21.0	21.9	22.8	24.8	24.8	25.7
50°	16.2	18.1	18.1	19.0	20.0	21.0	21.9	21.9
52.5°	14.4	15.2	16.2	16.2	17.3	18.1	19.0	19.0
55°	12.5	13.3	13.3	14.4	14.4	15.2	16.2	16.2
57.5°	10.5	11.4	12.5	12.5	12.5	13.3	13.3	14.4
60°	9.5	10.5	10.5	10.5	10.5	11.4	11.4	11.4
62.5°	8.5	8.5	8.5	8.5	8.5	8.5	8.5	8.5
65°	7.6	7.6	7.6	7.6	6.8	6.8	6.8	6.8
67.5°	6.8	6.8	6.8	6.8	5.7	5.7	5.7	5.7
70°	5.7	5.7	5.7	5.7	4.8	4.8	4.8	3.8
72.5°	4.8	4.8	4.8	4.8	4.8	3.8	3.8	3.8
75°	4.8	3.8	3.8	3.8	3.8	3.8	2.8	2.8
77.5°	3.8	3.8	3.8	2.8	2.8	2.8	2.8	2.8
80°	2.8	2.8	2.8	2.8	2.8	1.9	1.9	1.9
82.5°	2.8	1.9	1.9	1.9	1.9	1.9	1.9	1.9
85°	1.9	1.9	1.9	1.9	1.0	1.0	1.0	1.0
87.5°	1.9	1.0	1.0	1.0	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)