

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212264

Luminaire Tested: **LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2279.8 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212264

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212264

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	23066	23066	23066
5°	51054	21812	15336
10°	204354	18936	12808
15°	471025	15064	11253
20°	703133	10691	10041
25°	922238	7119	8936
30°	1058652	4508	7808
35°	970680	2874	6753
40°	796002	1872	5754
45°	461479	1302	4631
50°	130772	965	3828
55°	11975	895	3209
60°	1841	1027	2674
65°	481	986	1926
70°	595	1218	1501
75°	786	1609	1609
80°	0	2399	1172
85°	0	4780	1223



TEST NUMBER: P1212264

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.8	1.5
10°-20°	303.2	13.3
20°-30°	738.7	32.4
30°-40°	800.6	35.1
40°-50°	362.7	15.9
50°-60°	28.1	1.2
60°-70°	5.8	0.3
70°-80°	4.3	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.7	47.2
0°-40°	1876.3	82.3
0°-60°	2267.1	99.4
0°-90°	2279.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2279.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	238	238	238	238	238	
5°	525	387	224	169	158	94
15°	4696	1536	150	109	112	1365
25°	8628	2206	67	66	84	3933
35°	8208	561	24	38	57	5049
45°	3368	71	10	21	34	2659
55°	71	10	5	13	19	162
65°	2	3	4	8	8	4
75°	2	3	4	6	4	1
85°	0	3	4	3	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212264

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1
2.5°	356.6	350.2	353.5	345.0	339.7	335.5	337.6	335.5	321.7	318.6	308.0
5°	525.0	515.3	515.3	497.4	478.3	466.8	466.8	453.0	423.3	409.6	387.3
7.5°	940.8	921.8	905.9	849.8	776.7	735.4	724.9	666.7	591.6	544.0	487.8
10°	2077.4	1997.9	1941.9	1795.9	1600.1	1478.3	1426.5	1225.5	986.3	806.4	643.4
12.5°	3493.2	3385.3	3286.9	3047.7	2766.2	2574.7	2472.1	2175.7	1711.1	1378.9	1031.8
15°	4696.5	4580.1	4463.7	4172.7	3875.3	3709.2	3520.8	3128.1	2514.4	2042.5	1536.5
17.5°	5683.8	5618.2	5498.6	5072.2	4697.5	4438.3	4242.5	3729.2	3097.5	2558.8	1986.3
20°	6820.4	6658.4	6444.7	5927.2	5415.0	5090.2	4815.0	4189.6	3459.4	2840.3	2224.4
22.5°	7777.1	7661.7	7354.8	6672.2	5918.7	5641.5	5304.9	4552.5	3692.3	2960.0	2252.0
25°	8627.9	8446.9	8061.7	7250.0	6478.5	6006.6	5593.9	4749.5	3777.9	2968.4	2206.4
27.5°	9126.3	8890.3	8437.4	7552.6	6672.2	6150.6	5693.3	4783.3	3723.9	2856.2	2040.3
30°	9463.9	8994.0	8493.4	7555.8	6610.8	6077.5	5603.4	4612.9	3499.6	2600.1	1760.9
32.5°	8907.3	8635.3	8156.9	7255.2	6276.5	5755.8	5284.9	4243.5	3149.4	2220.2	1225.5
35°	8207.8	7987.6	7571.8	6676.5	5774.8	5283.8	4784.4	3769.5	2693.2	1526.0	560.8
37.5°	7395.0	7222.5	6774.8	5956.9	5163.2	4682.7	4182.2	3212.8	1896.4	756.7	340.7
40°	6294.4	6148.4	5781.2	5124.0	4392.7	3935.6	3474.2	2403.3	1029.7	422.2	222.2
42.5°	5173.7	5051.0	4716.6	4148.4	3505.9	3129.2	2722.9	1464.7	512.2	265.6	123.8
45°	3368.4	3215.0	3035.0	2774.7	2457.2	2225.5	1746.1	706.9	303.7	148.1	70.9
47.5°	1931.3	1829.8	1534.5	1210.6	983.1	897.4	652.9	329.1	167.2	85.7	43.3
50°	867.7	802.2	673.1	548.1	396.8	310.1	263.5	165.1	82.5	46.6	29.7
52.5°	213.8	217.9	206.3	181.0	160.8	136.6	118.5	77.2	43.3	28.5	19.0
55°	70.9	72.0	65.6	62.5	57.1	52.8	48.7	34.9	26.5	25.4	9.5
57.5°	25.4	25.4	26.5	24.3	23.3	22.2	21.2	17.9	15.9	9.5	5.3
60°	9.5	9.5	9.5	10.6	10.6	10.6	11.6	10.6	7.4	5.3	4.3
62.5°	4.3	4.3	4.3	4.3	5.3	5.3	6.4	5.3	4.3	4.3	3.1
65°	2.1	2.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
67.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.1
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1
80°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.1
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	3.1
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212264

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1
2.5°	297.4	291.0	278.3	268.8	261.4	260.4	254.0	243.5	239.2	231.7	225.4
5°	366.2	350.2	330.2	311.2	297.4	289.9	267.7	247.6	236.0	224.3	213.8
7.5°	440.2	404.3	369.4	338.6	319.6	308.0	281.5	248.7	227.6	210.6	196.8
10°	533.4	459.3	398.9	351.4	326.0	310.1	278.3	239.2	212.7	192.5	178.9
12.5°	746.0	544.0	426.5	357.6	326.0	303.7	265.6	226.4	196.8	172.5	157.7
15°	1110.1	759.8	505.8	360.9	315.3	289.9	246.6	205.3	175.7	150.2	136.6
17.5°	1453.0	1000.0	631.8	383.0	309.0	269.9	221.2	181.0	150.2	125.9	114.3
20°	1630.8	1119.6	701.6	400.0	298.4	244.5	191.5	154.5	124.8	103.7	94.2
22.5°	1635.0	1109.0	667.7	360.9	259.3	209.5	164.0	127.0	101.5	83.6	76.1
25°	1534.5	981.0	549.3	281.5	209.5	175.7	136.6	103.7	79.4	66.6	61.3
27.5°	1345.1	793.6	405.3	203.2	164.0	139.7	106.9	79.4	60.3	51.8	48.7
30°	1040.3	491.1	224.3	150.2	123.8	104.8	77.2	52.8	45.5	40.3	38.1
32.5°	516.4	240.2	158.7	106.9	84.7	66.6	48.7	39.2	34.9	31.7	30.7
35°	280.4	172.5	99.5	64.6	50.8	42.3	32.8	27.5	25.4	24.3	24.3
37.5°	195.8	102.6	60.3	39.2	31.7	28.5	23.3	20.1	19.0	19.0	19.0
40°	108.0	61.3	37.0	25.4	21.2	19.0	15.9	14.8	14.8	14.8	15.9
42.5°	62.5	38.1	25.4	17.9	14.8	13.8	11.6	10.6	11.6	11.6	12.7
45°	40.3	28.5	16.9	12.7	10.6	9.5	8.4	8.4	9.5	9.5	10.6
47.5°	28.5	20.1	11.6	8.4	6.4	6.4	6.4	6.4	7.4	8.4	9.5
50°	16.9	10.6	6.4	5.3	4.3	4.3	4.3	5.3	6.4	6.4	7.4
52.5°	9.5	6.4	4.3	4.3	3.1	3.1	4.3	4.3	5.3	6.4	7.4
55°	5.3	4.3	3.1	3.1	3.1	3.1	3.1	4.3	4.3	5.3	6.4
57.5°	4.3	3.1	3.1	3.1	3.1	3.1	3.1	4.3	4.3	5.3	5.3
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.3	4.3	5.3	5.3
62.5°	3.1	3.1	3.1	3.1	3.1	3.1	4.3	4.3	4.3	4.3	5.3
65°	3.1	3.1	3.1	4.3	3.1	4.3	4.3	4.3	4.3	4.3	5.3
67.5°	3.1	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3	5.3
70°	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	5.3
72.5°	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	5.3
75°	3.1	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
77.5°	3.1	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
80°	3.1	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
82.5°	3.1	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
85°	3.1	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
87.5°	3.1	3.1	3.1	3.1	4.3	4.3	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212264

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1
2.5°	223.3	215.9	210.6	208.4	204.3	205.3	202.1	200.0	193.6	193.6	189.4
5°	206.3	196.8	190.5	187.3	183.0	182.0	178.9	175.7	169.4	168.2	165.1
7.5°	188.4	178.9	171.5	168.2	164.0	163.0	158.7	156.7	151.3	150.2	147.1
10°	169.4	158.7	152.4	149.2	145.0	145.0	141.8	139.7	135.4	135.4	133.3
12.5°	149.2	139.7	135.4	131.2	129.1	129.1	127.0	124.8	121.7	122.8	121.7
15°	128.1	120.7	116.4	114.3	113.3	113.3	112.2	111.0	109.0	111.0	109.0
17.5°	108.0	102.6	99.5	98.5	97.4	97.4	97.4	98.5	97.4	99.5	99.5
20°	88.9	84.7	82.5	82.5	81.5	83.6	83.6	85.7	85.7	88.9	89.9
22.5°	73.0	69.8	68.8	68.8	68.8	70.9	72.0	74.1	75.1	78.3	80.4
25°	58.2	57.1	57.1	57.1	58.2	60.3	62.5	64.6	65.6	69.8	70.9
27.5°	47.6	46.6	47.6	47.6	48.7	51.8	54.0	56.1	58.2	61.3	63.5
30°	38.1	38.1	39.2	40.3	41.3	43.3	46.6	48.7	50.8	54.0	56.1
32.5°	30.7	31.7	32.8	33.8	33.8	37.0	39.2	42.3	43.3	46.6	48.7
35°	25.4	26.5	27.5	28.5	28.5	31.7	33.8	36.0	38.1	40.3	42.3
37.5°	20.1	21.2	23.3	24.3	24.3	27.5	28.5	30.7	32.8	34.9	37.0
40°	16.9	17.9	20.1	20.1	21.2	23.3	24.3	26.5	28.5	30.7	32.8
42.5°	13.8	14.8	16.9	17.9	17.9	20.1	21.2	23.3	24.3	26.5	27.5
45°	12.7	12.7	14.8	14.8	15.9	16.9	19.0	20.1	21.2	23.3	24.3
47.5°	10.6	11.6	12.7	13.8	13.8	14.8	15.9	16.9	17.9	20.1	21.2
50°	8.4	9.5	11.6	11.6	11.6	13.8	14.8	15.9	15.9	16.9	17.9
52.5°	8.4	8.4	9.5	10.6	10.6	11.6	12.7	13.8	13.8	14.8	15.9
55°	7.4	7.4	8.4	9.5	9.5	10.6	11.6	11.6	12.7	12.7	13.8
57.5°	6.4	7.4	8.4	8.4	8.4	9.5	10.6	10.6	11.6	11.6	12.7
60°	6.4	7.4	7.4	8.4	8.4	9.5	9.5	9.5	10.6	10.6	10.6
62.5°	6.4	6.4	7.4	7.4	7.4	8.4	8.4	9.5	9.5	9.5	9.5
65°	6.4	6.4	7.4	7.4	7.4	8.4	8.4	8.4	8.4	8.4	8.4
67.5°	5.3	6.4	6.4	6.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
70°	5.3	5.3	6.4	6.4	6.4	7.4	7.4	7.4	7.4	7.4	7.4
72.5°	5.3	5.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
75°	5.3	5.3	5.3	5.3	5.3	6.4	6.4	6.4	6.4	5.3	5.3
77.5°	4.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	4.3
80°	4.3	4.3	5.3	4.3	5.3	5.3	5.3	5.3	4.3	4.3	4.3
82.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.1	3.1
85°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.1	3.1	3.1	2.1
87.5°	4.3	4.3	4.3	4.3	4.3	4.3	3.1	3.1	3.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212264

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	238.1	238.1	238.1	238.1	238.1	238.1	238.1	238.1
2.5°	187.3	189.4	187.3	189.4	184.1	186.3	188.4	183.0
5°	163.0	160.8	161.9	164.0	159.7	160.8	161.9	157.7
7.5°	146.1	147.1	145.0	147.1	143.9	145.0	146.1	142.9
10°	132.3	133.3	132.3	133.3	130.2	132.3	133.3	130.2
12.5°	119.5	121.7	120.7	122.8	119.5	121.7	123.8	119.5
15°	110.0	112.2	111.0	113.3	111.0	113.3	115.3	112.2
17.5°	100.5	102.6	102.6	104.8	103.7	105.8	108.0	104.8
20°	91.0	94.2	94.2	96.3	96.3	97.4	100.5	97.4
22.5°	82.5	85.7	85.7	87.9	87.9	89.9	92.0	89.9
25°	73.0	77.2	78.3	80.4	80.4	82.5	85.7	83.6
27.5°	66.6	69.8	70.9	73.0	74.1	76.1	78.3	76.1
30°	58.2	62.5	63.5	65.6	66.6	69.8	70.9	69.8
32.5°	51.8	55.1	56.1	58.2	60.3	62.5	64.6	63.5
35°	45.5	48.7	49.8	51.8	52.8	56.1	58.2	57.1
37.5°	40.3	43.3	44.4	45.5	46.6	49.8	51.8	50.8
40°	34.9	37.0	38.1	40.3	41.3	43.3	45.5	45.5
42.5°	30.7	32.8	33.8	34.9	36.0	38.1	40.3	39.2
45°	26.5	28.5	29.7	30.7	31.7	32.8	34.9	33.8
47.5°	22.2	24.3	25.4	26.5	27.5	28.5	30.7	29.7
50°	19.0	21.2	21.2	22.2	23.3	24.3	26.5	25.4
52.5°	16.9	17.9	19.0	19.0	20.1	21.2	23.3	22.2
55°	14.8	15.9	15.9	16.9	16.9	17.9	19.0	19.0
57.5°	12.7	13.8	13.8	14.8	14.8	15.9	16.9	16.9
60°	11.6	11.6	12.7	12.7	12.7	13.8	13.8	13.8
62.5°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
65°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
67.5°	7.4	7.4	7.4	7.4	7.4	6.4	6.4	6.4
70°	6.4	6.4	6.4	6.4	6.4	5.3	5.3	5.3
72.5°	6.4	6.4	5.3	5.3	5.3	5.3	5.3	4.3
75°	5.3	5.3	5.3	5.3	4.3	4.3	4.3	4.3
77.5°	4.3	4.3	4.3	4.3	3.1	3.1	3.1	3.1
80°	4.3	3.1	3.1	3.1	3.1	3.1	3.1	2.1
82.5°	3.1	3.1	3.1	2.1	2.1	2.1	2.1	2.1
85°	2.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
87.5°	2.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)