

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212266

Luminaire Tested: **LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2117.2 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212266

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212266

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	22863	22863	22863
5°	51171	21501	15404
10°	200675	18818	12129
15°	435632	15255	10551
20°	649865	11289	9536
25°	845266	7953	8295
30°	945593	5347	7260
35°	850974	3134	6162
40°	694478	2150	5375
45°	398760	1466	4370
50°	116636	1115	3692
55°	13461	895	3057
60°	2868	1027	2461
65°	986	986	1696
70°	906	1218	1218
75°	786	1609	1198
80°	0	2399	1172
85°	0	4780	1223



TEST NUMBER: P1212266

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.8	1.6
10°-20°	289.8	13.7
20°-30°	691.4	32.7
30°-40°	729.7	34.5
40°-50°	330.9	15.6
50°-60°	29.0	1.4
60°-70°	6.1	0.3
70°-80°	4.0	0.2
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1015.1	47.9
0°-40°	1744.8	82.4
0°-60°	2104.7	99.4
0°-90°	2117.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2117.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	236	236	236	236	236	
5°	526	386	221	170	158	94
15°	4344	1528	152	104	105	1264
25°	7908	2103	74	64	78	3592
35°	7196	580	26	36	52	4444
45°	2911	82	11	20	32	2308
55°	80	13	5	12	18	159
65°	4	4	4	8	7	6
75°	2	2	4	5	3	2
85°	0	2	4	3	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212266

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0
2.5°	350.8	352.9	343.4	344.4	334.8	339.1	335.9	327.4	321.0	310.4	306.1
5°	526.2	529.4	508.1	501.7	479.5	479.5	469.9	447.5	427.4	402.9	385.9
7.5°	962.1	974.8	911.0	863.1	793.0	776.0	743.1	666.5	603.7	540.0	492.2
10°	2040.0	2016.6	1884.8	1776.3	1595.6	1528.7	1439.4	1219.3	1017.3	816.4	659.1
12.5°	3216.7	3292.2	3038.1	2949.9	2663.9	2603.3	2413.1	2053.8	1712.6	1357.5	1042.8
15°	4343.6	4365.8	4143.6	4000.1	3651.4	3572.8	3339.0	2916.9	2457.7	1962.4	1527.6
17.5°	5248.2	5337.5	5011.1	4857.0	4404.1	4277.6	4002.3	3488.8	2977.5	2436.4	1920.9
20°	6303.7	6327.2	5940.2	5643.6	5051.5	4859.1	4529.6	3892.8	3283.7	2666.1	2133.5
22.5°	7263.6	7258.3	6760.9	6342.0	5592.5	5363.0	4955.8	4201.1	3493.1	2768.1	2153.7
25°	7907.8	7924.8	7392.3	6897.0	5977.4	5667.0	5207.8	4361.6	3564.3	2764.9	2102.7
27.5°	8251.2	8234.2	7663.3	7133.9	6118.8	5771.1	5272.6	4366.9	3499.5	2656.5	1949.5
30°	8453.2	8225.7	7616.5	7067.0	6023.2	5665.9	5158.9	4198.9	3283.7	2414.2	1676.5
32.5°	7913.1	7824.9	7294.4	6710.8	5693.5	5339.6	4838.9	3841.8	2941.4	2043.1	1201.3
35°	7195.6	7198.8	6681.1	6135.8	5177.0	4868.6	4352.0	3407.0	2523.7	1420.3	580.4
37.5°	6442.9	6453.6	5961.4	5454.4	4600.8	4276.5	3792.9	2911.6	1815.7	722.8	349.8
40°	5491.6	5513.9	5089.8	4682.7	3894.9	3582.4	3150.8	2203.6	1015.2	404.0	237.1
42.5°	4487.1	4514.7	4138.3	3776.9	3107.2	2850.0	2467.3	1364.9	503.9	261.5	139.2
45°	2910.6	2990.3	2710.7	2558.7	2170.7	2017.7	1610.5	696.3	304.0	153.1	81.9
47.5°	1665.8	1666.8	1430.8	1145.9	939.7	817.5	638.9	316.7	177.5	86.1	49.9
50°	773.9	793.0	628.3	523.0	374.2	316.7	260.5	171.2	93.6	49.9	30.8
52.5°	225.4	238.1	215.8	195.6	165.9	147.8	126.5	83.9	48.9	29.7	19.1
55°	79.7	85.0	79.7	74.4	66.9	60.6	54.2	40.4	27.7	18.1	12.7
57.5°	33.0	34.0	33.0	31.9	29.7	29.7	26.5	22.4	17.0	11.7	8.4
60°	14.8	15.9	14.8	15.9	14.8	14.8	14.8	15.9	10.7	7.4	6.4
62.5°	6.4	7.4	7.4	7.4	7.4	8.4	8.4	7.4	6.4	5.3	4.3
65°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
67.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
70°	3.2	3.2	3.2	3.2	3.2	3.2	2.1	2.1	3.2	3.2	3.2
72.5°	3.2	3.2	3.2	3.2	2.1	2.1	2.1	2.1	2.1	3.2	3.2
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
80°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212266

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0
2.5°	300.9	291.3	276.3	266.8	262.5	256.2	251.9	241.4	237.1	228.5	225.4
5°	369.9	350.8	328.5	310.4	298.7	285.9	266.8	245.5	234.9	221.1	213.7
7.5°	448.6	407.1	367.8	335.9	321.0	304.0	279.6	246.6	226.4	208.4	197.7
10°	548.5	463.5	401.8	350.8	328.5	306.1	276.3	238.1	212.6	191.3	179.6
12.5°	782.4	559.1	432.7	359.3	330.6	302.9	265.8	226.4	196.6	172.2	159.4
15°	1125.8	781.3	515.6	366.8	323.1	289.2	246.6	207.3	176.5	152.1	139.2
17.5°	1429.8	996.0	630.4	394.4	321.0	273.2	223.2	182.9	153.1	129.7	119.0
20°	1595.6	1108.7	706.9	411.4	311.5	248.7	196.6	158.4	129.7	109.5	100.0
22.5°	1598.8	1102.3	679.2	374.2	274.3	215.8	170.1	133.9	108.4	90.4	82.9
25°	1503.1	983.3	566.6	294.4	224.3	182.9	142.4	111.6	88.2	74.4	68.0
27.5°	1324.5	799.4	416.7	212.6	175.4	147.8	114.8	89.3	69.1	60.6	55.3
30°	1041.8	520.8	243.5	158.4	136.1	113.8	87.2	62.8	54.2	47.8	43.5
32.5°	559.1	253.0	170.1	117.0	96.7	79.7	57.4	45.8	39.4	35.1	34.0
35°	292.3	185.0	113.8	74.4	61.6	52.1	39.4	31.9	28.7	26.5	26.5
37.5°	209.4	115.8	72.3	47.8	40.4	33.0	27.7	23.4	21.3	21.3	21.3
40°	124.4	71.2	43.5	30.8	26.5	23.4	20.2	17.0	17.0	17.0	17.0
42.5°	75.5	44.6	30.8	21.3	19.1	17.0	14.8	13.8	12.7	12.7	13.8
45°	46.8	30.8	20.2	15.9	14.8	12.7	11.7	10.7	10.7	10.7	11.7
47.5°	29.7	22.4	14.8	10.7	9.6	8.4	7.4	7.4	8.4	8.4	9.6
50°	22.4	13.8	9.6	7.4	6.4	6.4	5.3	6.4	6.4	7.4	8.4
52.5°	12.7	8.4	6.4	5.3	5.3	4.3	4.3	5.3	5.3	6.4	7.4
55°	8.4	6.4	5.3	4.3	4.3	4.3	4.3	4.3	5.3	5.3	6.4
57.5°	6.4	5.3	4.3	4.3	4.3	3.2	4.3	4.3	4.3	5.3	6.4
60°	5.3	4.3	4.3	4.3	4.3	3.2	3.2	4.3	4.3	5.3	5.3
62.5°	4.3	4.3	4.3	4.3	4.3	3.2	4.3	4.3	4.3	4.3	5.3
65°	3.2	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	5.3
67.5°	3.2	3.2	4.3	4.3	4.3	3.2	4.3	4.3	4.3	4.3	5.3
70°	3.2	3.2	3.2	4.3	4.3	3.2	4.3	4.3	4.3	4.3	4.3
72.5°	3.2	3.2	3.2	4.3	4.3	3.2	4.3	4.3	4.3	4.3	4.3
75°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3
77.5°	3.2	3.2	3.2	3.2	4.3	3.2	4.3	4.3	4.3	4.3	4.3
80°	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3	4.3
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3
87.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212266

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0
2.5°	216.8	213.7	207.3	206.3	205.1	200.9	197.7	194.6	194.6	191.3	189.3
5°	200.9	195.6	188.2	185.0	183.9	178.6	174.3	171.2	170.1	166.9	163.7
7.5°	183.9	177.5	169.0	165.9	164.8	159.4	155.2	152.1	149.9	146.7	144.6
10°	165.9	158.4	150.9	147.8	146.7	141.4	138.1	135.1	132.8	130.8	128.6
12.5°	146.7	140.4	132.8	129.7	128.6	124.4	121.1	119.0	118.0	115.8	114.8
15°	127.6	121.1	114.8	112.7	111.6	108.4	106.3	105.2	104.1	104.1	103.1
17.5°	108.4	103.1	97.7	96.7	95.7	93.6	92.5	91.4	92.5	92.5	93.6
20°	90.4	86.1	81.9	81.9	80.8	79.7	79.7	79.7	81.9	82.9	85.0
22.5°	74.4	71.2	68.0	68.0	68.0	68.0	68.0	70.2	72.3	74.4	75.5
25°	61.6	58.5	57.4	57.4	57.4	58.5	59.6	61.6	63.8	65.9	68.0
27.5°	49.9	47.8	47.8	47.8	48.9	49.9	51.1	53.1	56.3	58.5	60.6
30°	40.4	39.4	39.4	40.4	41.5	42.5	44.6	46.8	48.9	51.1	53.1
32.5°	31.9	33.0	33.0	34.0	35.1	36.1	38.3	40.4	42.5	44.6	45.8
35°	26.5	26.5	27.7	28.7	29.7	30.8	33.0	35.1	36.1	38.3	40.4
37.5°	21.3	22.4	23.4	24.5	25.5	26.5	27.7	29.7	30.8	33.0	35.1
40°	18.1	19.1	20.2	21.3	21.3	23.4	23.4	25.5	26.5	28.7	30.8
42.5°	14.8	15.9	17.0	18.1	18.1	19.1	20.2	21.3	23.4	24.5	26.5
45°	11.7	12.7	13.8	14.8	15.9	17.0	17.0	19.1	20.2	21.3	23.4
47.5°	10.7	11.7	12.7	12.7	13.8	14.8	14.8	17.0	18.1	19.1	20.2
50°	8.4	9.6	10.7	11.7	11.7	12.7	13.8	14.8	15.9	17.0	17.0
52.5°	7.4	8.4	9.6	9.6	10.7	11.7	11.7	12.7	13.8	13.8	14.8
55°	7.4	8.4	8.4	9.6	9.6	10.7	10.7	11.7	11.7	12.7	12.7
57.5°	6.4	7.4	7.4	8.4	8.4	9.6	9.6	10.7	10.7	10.7	11.7
60°	6.4	6.4	7.4	7.4	8.4	8.4	8.4	9.6	9.6	9.6	10.7
62.5°	5.3	6.4	6.4	7.4	7.4	7.4	8.4	8.4	8.4	9.6	9.6
65°	5.3	6.4	6.4	7.4	7.4	7.4	7.4	7.4	8.4	8.4	8.4
67.5°	5.3	5.3	6.4	6.4	6.4	6.4	7.4	7.4	7.4	7.4	7.4
70°	5.3	5.3	5.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4
72.5°	4.3	5.3	5.3	5.3	5.3	6.4	6.4	6.4	6.4	6.4	5.3
75°	4.3	4.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
77.5°	4.3	4.3	4.3	5.3	5.3	5.3	5.3	5.3	5.3	4.3	4.3
80°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2
82.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2	3.2
85°	4.3	3.2	4.3	4.3	4.3	3.2	3.2	3.2	3.2	3.2	2.1
87.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212266

CATALOG NUMBER: LDSQA4A25935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	236.0	236.0	236.0	236.0	236.0	236.0	236.0	236.0
2.5°	187.0	185.0	186.0	186.0	183.9	182.9	182.9	183.9
5°	161.6	159.4	160.5	160.5	158.4	157.3	157.3	158.4
7.5°	142.4	140.4	141.4	141.4	139.2	139.2	139.2	139.2
10°	127.6	126.5	126.5	126.5	124.4	125.4	124.4	123.3
12.5°	113.8	113.8	113.8	113.8	112.7	113.8	112.7	112.7
15°	103.1	103.1	104.1	104.1	104.1	105.2	105.2	105.2
17.5°	94.6	95.7	96.7	97.7	97.7	98.9	98.9	98.9
20°	86.1	88.2	89.3	90.4	90.4	92.5	91.4	92.5
22.5°	77.6	79.7	80.8	81.9	82.9	83.9	83.9	85.0
25°	70.2	72.3	73.3	74.4	75.5	77.6	77.6	77.6
27.5°	62.8	64.9	65.9	68.0	69.1	71.2	71.2	71.2
30°	55.3	57.4	58.5	59.6	61.6	63.8	63.8	64.9
32.5°	47.8	51.1	52.1	53.1	55.3	57.4	58.5	58.5
35°	42.5	44.6	45.8	47.8	48.9	52.1	52.1	52.1
37.5°	37.2	39.4	41.5	42.5	43.5	45.8	46.8	47.8
40°	33.0	35.1	36.1	37.2	39.4	41.5	42.5	42.5
42.5°	28.7	30.8	31.9	33.0	34.0	36.1	36.1	36.1
45°	25.5	26.5	27.7	28.7	29.7	30.8	31.9	31.9
47.5°	21.3	23.4	23.4	24.5	25.5	27.7	27.7	28.7
50°	18.1	20.2	20.2	21.3	22.4	23.4	24.5	24.5
52.5°	15.9	17.0	18.1	18.1	19.1	20.2	21.3	21.3
55°	13.8	14.8	14.8	15.9	15.9	17.0	18.1	18.1
57.5°	11.7	12.7	13.8	13.8	13.8	14.8	14.8	15.9
60°	10.7	11.7	11.7	11.7	11.7	12.7	12.7	12.7
62.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6
65°	8.4	8.4	8.4	8.4	7.4	7.4	7.4	7.4
67.5°	7.4	7.4	7.4	7.4	6.4	6.4	6.4	6.4
70°	6.4	6.4	6.4	6.4	5.3	5.3	5.3	4.3
72.5°	5.3	5.3	5.3	5.3	5.3	4.3	4.3	4.3
75°	5.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2
77.5°	4.3	4.3	4.3	3.2	3.2	3.2	3.2	3.2
80°	3.2	3.2	3.2	3.2	3.2	2.1	2.1	2.1
82.5°	3.2	2.1	2.1	2.1	2.1	2.1	2.1	2.1
85°	2.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
87.5°	2.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)