

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212236

Luminaire Tested: **LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2158.3 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212236

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212236

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	21836	21836	21836
5°	48321	20655	14519
10°	193444	17933	12129
15°	445912	14272	10651
20°	665638	10124	9505
25°	873058	6745	8466
30°	1002195	4251	7394
35°	918904	2720	6398
40°	753548	1770	5438
45°	436874	1233	4384
50°	123809	904	3617
55°	11333	844	3057
60°	1744	969	2519
65°	458	917	1834
70°	566	1133	1416
75°	749	1497	1497
80°	0	2232	1116
85°	0	4446	1223

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212236

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.0	1.5
10°-20°	287.0	13.3
20°-30°	699.3	32.4
30°-40°	757.9	35.1
40°-50°	343.4	15.9
50°-60°	26.6	1.2
60°-70°	5.5	0.3
70°-80°	4.0	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1018.3	47.2
0°-40°	1776.2	82.3
0°-60°	2146.2	99.4
0°-90°	2158.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2158.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	225	225	225	225	225	
5°	497	367	212	160	149	89
15°	4446	1455	142	103	106	1292
25°	8168	2089	63	62	79	3723
35°	7770	531	23	36	54	4779
45°	3189	67	9	20	32	2517
55°	67	9	5	12	18	153
65°	2	3	4	8	8	3
75°	2	3	4	6	4	1
85°	0	3	4	3	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212236

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4
2.5°	337.6	331.6	334.6	326.5	321.6	317.6	319.6	317.6	304.6	301.5	291.6
5°	496.9	487.8	487.8	470.8	452.8	441.8	441.8	428.8	400.8	387.7	366.7
7.5°	890.5	872.6	857.6	804.4	735.4	696.3	686.2	631.1	560.0	514.9	461.9
10°	1966.5	1891.5	1838.3	1700.1	1514.8	1399.5	1350.4	1160.1	933.6	763.4	609.1
12.5°	3307.0	3204.8	3111.6	2885.2	2618.8	2437.4	2340.2	2059.8	1620.0	1305.4	976.7
15°	4446.1	4335.8	4225.6	3950.2	3668.7	3511.4	3333.0	2961.4	2380.3	1933.5	1454.7
17.5°	5380.7	5318.6	5205.4	4801.7	4447.0	4201.6	4016.2	3530.4	2932.3	2422.3	1880.4
20°	6456.7	6303.4	6101.0	5611.2	5126.3	4818.7	4558.3	3966.1	3274.9	2688.9	2105.8
22.5°	7362.4	7253.1	6962.6	6316.4	5603.1	5340.6	5022.1	4309.8	3495.3	2802.1	2131.8
25°	8167.8	7996.4	7631.8	6863.4	6133.1	5686.3	5295.6	4496.1	3576.4	2810.1	2088.7
27.5°	8639.6	8416.2	7987.4	7149.9	6316.4	5822.5	5389.7	4528.2	3525.4	2703.9	1931.5
30°	8959.2	8514.4	8040.5	7152.9	6258.3	5753.5	5304.6	4366.9	3313.0	2461.5	1667.0
32.5°	8432.3	8174.7	7722.0	6868.4	5941.7	5448.9	5003.1	4017.3	2981.4	2101.8	1160.1
35°	7770.0	7561.7	7167.9	6320.4	5466.9	5002.0	4529.2	3568.4	2549.6	1444.6	530.9
37.5°	7000.6	6837.3	6413.6	5639.2	4887.8	4433.1	3959.2	3041.5	1795.2	716.3	322.5
40°	5958.7	5820.5	5472.9	4850.8	4158.5	3725.7	3288.9	2275.1	974.7	399.7	210.4
42.5°	4897.9	4781.6	4465.1	3927.1	3319.0	2962.4	2577.6	1386.5	484.9	251.5	117.3
45°	3188.8	3043.5	2873.2	2626.7	2326.2	2106.8	1652.9	669.2	287.5	140.3	67.1
47.5°	1828.3	1732.2	1452.7	1146.1	930.7	849.6	618.1	311.5	158.3	81.1	41.1
50°	821.5	759.3	637.1	518.9	375.7	293.6	249.5	156.2	78.1	44.1	28.0
52.5°	202.3	206.3	195.3	171.2	152.2	129.2	112.2	73.1	41.1	27.0	18.1
55°	67.1	68.1	62.1	59.1	54.1	50.1	46.1	33.1	25.0	24.0	9.0
57.5°	24.0	24.0	25.0	23.0	22.1	21.0	20.1	17.0	15.0	9.0	5.0
60°	9.0	9.0	9.0	10.0	10.0	10.0	11.0	10.0	7.0	5.0	4.0
62.5°	4.0	4.0	4.0	4.0	5.0	5.0	6.0	5.0	4.0	4.0	3.1
65°	2.0	2.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
67.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	3.1	3.1
70°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	3.1	3.1
72.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	3.1	3.1
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	3.1
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0	3.1
80°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0	3.1
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0	3.1
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	3.1
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212236

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4
2.5°	281.5	275.5	263.5	254.5	247.5	246.5	240.4	230.4	226.4	219.4	213.4
5°	346.6	331.6	312.6	294.5	281.5	274.6	253.4	234.4	223.4	212.4	202.3
7.5°	416.7	382.7	349.6	320.5	302.6	291.6	266.5	235.4	215.4	199.3	186.3
10°	504.9	434.8	377.7	332.6	308.6	293.6	263.5	226.4	201.4	182.3	169.2
12.5°	706.3	514.9	403.8	338.6	308.6	287.5	251.5	214.4	186.3	163.3	149.3
15°	1050.9	719.3	478.9	341.6	298.5	274.6	233.4	194.4	166.3	142.3	129.2
17.5°	1375.4	946.7	598.0	362.7	292.5	255.4	209.4	171.2	142.3	119.3	108.3
20°	1543.8	1059.9	664.2	378.7	282.5	231.4	181.3	146.3	118.2	98.2	89.2
22.5°	1547.8	1050.0	632.1	341.6	245.5	198.3	155.3	120.2	96.2	79.2	72.1
25°	1452.7	928.7	519.9	266.5	198.3	166.3	129.2	98.2	75.1	63.1	58.1
27.5°	1273.3	751.3	383.7	192.4	155.3	132.3	101.2	75.1	57.1	49.0	46.1
30°	984.8	464.8	212.4	142.3	117.3	99.2	73.1	50.1	43.0	38.0	36.0
32.5°	488.9	227.4	150.2	101.2	80.2	63.1	46.1	37.1	33.1	30.0	29.1
35°	265.5	163.3	94.2	61.1	48.1	40.0	31.1	26.0	24.0	23.0	23.0
37.5°	185.3	97.2	57.1	37.1	30.0	27.0	22.1	19.0	18.1	18.1	18.1
40°	102.2	58.1	35.1	24.0	20.1	18.1	15.0	14.0	14.0	14.0	15.0
42.5°	59.1	36.0	24.0	17.0	14.0	13.0	11.0	10.0	11.0	11.0	12.0
45°	38.0	27.0	16.1	12.0	10.0	9.0	8.0	8.0	9.0	9.0	10.0
47.5°	27.0	19.0	11.0	8.0	6.0	6.0	6.0	6.0	7.0	8.0	9.0
50°	16.1	10.0	6.0	5.0	4.0	4.0	4.0	5.0	6.0	6.0	7.0
52.5°	9.0	6.0	4.0	4.0	3.1	3.1	4.0	4.0	5.0	6.0	7.0
55°	5.0	4.0	3.1	3.1	3.1	3.1	3.1	4.0	4.0	5.0	6.0
57.5°	4.0	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	5.0	5.0
60°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	5.0	5.0
62.5°	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0	5.0
65°	3.1	3.1	3.1	4.0	3.1	4.0	4.0	4.0	4.0	4.0	5.0
67.5°	3.1	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	5.0
70°	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	5.0
72.5°	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	5.0
75°	3.1	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
77.5°	3.1	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
80°	3.1	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
82.5°	3.1	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
85°	3.1	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
87.5°	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0	4.0	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212236

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4
2.5°	211.4	204.3	199.3	197.3	193.3	194.4	191.3	189.3	183.3	183.3	179.3
5°	195.3	186.3	180.3	177.3	173.4	172.3	169.2	166.3	160.3	159.3	156.2
7.5°	178.3	169.2	162.3	159.3	155.3	154.2	150.2	148.2	143.2	142.3	139.2
10°	160.3	150.2	144.3	141.2	137.2	137.2	134.3	132.3	128.2	128.2	126.2
12.5°	141.2	132.3	128.2	124.2	122.2	122.2	120.2	118.2	115.3	116.2	115.3
15°	121.3	114.2	110.2	108.3	107.2	107.2	106.2	105.2	103.2	105.2	103.2
17.5°	102.2	97.2	94.2	93.2	92.2	92.2	92.2	93.2	92.2	94.2	94.2
20°	84.2	80.2	78.1	78.1	77.1	79.2	79.2	81.1	81.1	84.2	85.1
22.5°	69.1	66.1	65.1	65.1	65.1	67.1	68.1	70.1	71.1	74.1	76.1
25°	55.1	54.1	54.1	54.1	55.1	57.1	59.1	61.1	62.1	66.1	67.1
27.5°	45.0	44.1	45.0	45.0	46.1	49.0	51.1	53.1	55.1	58.1	60.1
30°	36.0	36.0	37.1	38.0	39.1	41.1	44.1	46.1	48.1	51.1	53.1
32.5°	29.1	30.0	31.1	32.0	32.0	35.1	37.1	40.0	41.1	44.1	46.1
35°	24.0	25.0	26.0	27.0	27.0	30.0	32.0	34.0	36.0	38.0	40.0
37.5°	19.0	20.1	22.1	23.0	23.0	26.0	27.0	29.1	31.1	33.1	35.1
40°	16.1	17.0	19.0	19.0	20.1	22.1	23.0	25.0	27.0	29.1	31.1
42.5°	13.0	14.0	16.1	17.0	17.0	19.0	20.1	22.1	23.0	25.0	26.0
45°	12.0	12.0	14.0	14.0	15.0	16.1	18.1	19.0	20.1	22.1	23.0
47.5°	10.0	11.0	12.0	13.0	13.0	14.0	15.0	16.1	17.0	19.0	20.1
50°	8.0	9.0	11.0	11.0	11.0	13.0	14.0	15.0	15.0	16.1	17.0
52.5°	8.0	8.0	9.0	10.0	10.0	11.0	12.0	13.0	13.0	14.0	15.0
55°	7.0	7.0	8.0	9.0	9.0	10.0	11.0	11.0	12.0	12.0	13.0
57.5°	6.0	7.0	8.0	8.0	8.0	9.0	10.0	10.0	11.0	11.0	12.0
60°	6.0	7.0	7.0	8.0	8.0	9.0	9.0	9.0	10.0	10.0	10.0
62.5°	6.0	6.0	7.0	7.0	7.0	8.0	8.0	9.0	9.0	9.0	9.0
65°	6.0	6.0	7.0	7.0	7.0	8.0	8.0	8.0	8.0	8.0	8.0
67.5°	5.0	6.0	6.0	6.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
70°	5.0	5.0	6.0	6.0	6.0	7.0	7.0	7.0	7.0	7.0	7.0
72.5°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
75°	5.0	5.0	5.0	5.0	5.0	6.0	6.0	6.0	6.0	5.0	5.0
77.5°	4.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	4.0
80°	4.0	4.0	5.0	4.0	5.0	5.0	5.0	5.0	4.0	4.0	4.0
82.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	3.1	3.1
85°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	3.1	3.1	3.1	2.0
87.5°	4.0	4.0	4.0	4.0	4.0	4.0	3.1	3.1	3.1	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212236

CATALOG NUMBER: LDSQA4A25927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	225.4	225.4	225.4	225.4	225.4	225.4	225.4	225.4
2.5°	177.3	179.3	177.3	179.3	174.3	176.3	178.3	173.4
5°	154.2	152.2	153.3	155.3	151.3	152.2	153.3	149.3
7.5°	138.3	139.2	137.2	139.2	136.3	137.2	138.3	135.2
10°	125.3	126.2	125.3	126.2	123.3	125.3	126.2	123.3
12.5°	113.2	115.3	114.2	116.2	113.2	115.3	117.3	113.2
15°	104.2	106.2	105.2	107.2	105.2	107.2	109.2	106.2
17.5°	95.2	97.2	97.2	99.2	98.2	100.1	102.2	99.2
20°	86.2	89.2	89.2	91.2	91.2	92.2	95.2	92.2
22.5°	78.1	81.1	81.1	83.1	83.1	85.1	87.2	85.1
25°	69.1	73.1	74.1	76.1	76.1	78.1	81.1	79.2
27.5°	63.1	66.1	67.1	69.1	70.1	72.1	74.1	72.1
30°	55.1	59.1	60.1	62.1	63.1	66.1	67.1	66.1
32.5°	49.0	52.1	53.1	55.1	57.1	59.1	61.1	60.1
35°	43.0	46.1	47.0	49.0	50.1	53.1	55.1	54.1
37.5°	38.0	41.1	42.0	43.0	44.1	47.0	49.0	48.1
40°	33.1	35.1	36.0	38.0	39.1	41.1	43.0	43.0
42.5°	29.1	31.1	32.0	33.1	34.0	36.0	38.0	37.1
45°	25.0	27.0	28.0	29.1	30.0	31.1	33.1	32.0
47.5°	21.0	23.0	24.0	25.0	26.0	27.0	29.1	28.0
50°	18.1	20.1	20.1	21.0	22.1	23.0	25.0	24.0
52.5°	16.1	17.0	18.1	18.1	19.0	20.1	22.1	21.0
55°	14.0	15.0	15.0	16.1	16.1	17.0	18.1	18.1
57.5°	12.0	13.0	13.0	14.0	14.0	15.0	16.1	16.1
60°	11.0	11.0	12.0	12.0	12.0	13.0	13.0	13.0
62.5°	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0
65°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
67.5°	7.0	7.0	7.0	7.0	7.0	6.0	6.0	6.0
70°	6.0	6.0	6.0	6.0	6.0	5.0	5.0	5.0
72.5°	6.0	6.0	5.0	5.0	5.0	5.0	5.0	4.0
75°	5.0	5.0	5.0	5.0	4.0	4.0	4.0	4.0
77.5°	4.0	4.0	4.0	4.0	3.1	3.1	3.1	3.1
80°	4.0	3.1	3.1	3.1	3.1	3.1	3.1	2.0
82.5°	3.1	3.1	3.1	2.0	2.0	2.0	2.0	2.0
85°	2.0	2.0	2.0	2.0	1.1	1.1	1.1	1.1
87.5°	2.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)