

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212242

Luminaire Tested: **LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212242
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2042.6 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212242

CATALOG NUMBER: LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212242

CATALOG NUMBER: LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	24461	24461	24461
5°	57346	23096	16143
10°	226566	20294	13467
15°	419304	16247	11814
20°	537649	11825	10691
25°	643287	8380	9460
30°	684014	5515	8323
35°	701016	3335	7250
40°	641718	2162	6235
45°	463055	1507	5110
50°	202149	1221	4250
55°	13934	1013	3564
60°	2558	969	2926
65°	917	917	2063
70°	878	1133	1416
75°	749	1497	1497
80°	0	2232	1729
85°	0	4446	1223

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212242

CATALOG NUMBER: LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.8	1.8
10°-20°	289.1	14.2
20°-30°	605.3	29.6
30°-40°	673.7	33.0
40°-50°	386.8	18.9
50°-60°	38.6	1.9
60°-70°	6.1	0.3
70°-80°	3.8	0.2
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	931.2	45.6
0°-40°	1604.9	78.6
0°-60°	2030.3	99.4
0°-90°	2042.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2042.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	252	252	252	252	252	
5°	590	406	238	173	166	108
15°	4181	1669	162	114	118	1182
25°	6018	2297	78	69	88	2725
35°	5928	701	28	40	61	3619
45°	3380	84	11	22	37	2581
55°	82	12	6	13	21	246
65°	4	3	4	8	9	5
75°	2	2	4	5	4	1
85°	0	2	4	3	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212242

CATALOG NUMBER: LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5
2.5°	377.3	369.2	361.3	356.2	351.2	358.2	353.2	351.2	337.1	330.0	324.0
5°	589.7	574.6	552.4	534.3	516.2	520.2	506.1	489.0	453.8	428.7	406.5
7.5°	1138.0	1100.8	1032.3	966.0	899.6	887.5	843.2	766.8	668.2	593.7	529.3
10°	2303.2	2190.5	2064.8	1928.9	1769.9	1725.7	1616.0	1408.8	1182.3	923.6	736.5
12.5°	3400.0	3348.7	3200.8	3024.7	2852.6	2747.0	2633.3	2291.1	1931.9	1515.4	1167.2
15°	4180.8	4149.6	4019.9	3859.8	3674.7	3606.3	3467.5	3126.3	2672.5	2174.5	1669.3
17.5°	4759.4	4706.1	4570.3	4396.2	4176.7	4118.5	3952.4	3613.3	3142.4	2642.3	2081.8
20°	5215.2	5182.0	5005.9	4796.6	4534.0	4463.6	4269.4	3916.2	3404.0	2872.7	2302.2
22.5°	5624.8	5568.3	5352.1	5102.5	4802.7	4727.2	4510.9	4123.5	3573.1	2981.4	2341.4
25°	6018.2	5932.6	5670.0	5343.0	4990.8	4888.2	4650.7	4240.2	3635.5	2990.5	2297.2
27.5°	6132.8	6089.6	5847.1	5466.7	5059.3	4943.5	4696.0	4266.3	3612.3	2908.0	2138.2
30°	6114.8	6078.6	5876.3	5478.8	5047.2	4925.4	4673.8	4185.9	3477.4	2692.6	1857.5
32.5°	6057.3	6043.3	5798.8	5374.2	4934.5	4801.7	4530.0	3985.6	3224.9	2364.6	1357.4
35°	5927.6	5872.3	5567.3	5167.9	4745.3	4599.4	4292.5	3698.8	2891.8	1721.6	701.3
37.5°	5547.3	5504.0	5263.5	4913.3	4501.8	4314.7	3990.6	3328.5	2238.8	979.0	419.6
40°	5074.4	5053.3	4864.0	4551.1	4111.5	3900.1	3547.9	2723.8	1366.4	556.4	276.7
42.5°	4589.4	4583.3	4381.0	4054.0	3577.1	3334.6	2969.3	1837.3	726.5	336.0	159.9
45°	3379.9	3416.1	3275.3	3079.0	2714.8	2538.7	2064.8	946.9	418.6	186.2	84.5
47.5°	2370.7	2330.4	2080.9	1737.7	1404.6	1189.3	899.6	447.8	223.4	97.6	48.3
50°	1341.3	1348.3	1123.0	908.6	595.7	472.0	358.2	225.4	107.7	51.3	29.2
52.5°	350.1	366.3	315.9	271.7	231.4	188.2	151.9	97.6	51.3	30.2	19.1
55°	82.5	85.5	79.5	74.4	70.5	62.3	55.3	42.3	28.2	19.1	12.1
57.5°	29.2	30.2	29.2	29.2	28.2	27.2	25.2	22.2	17.1	12.1	8.1
60°	13.2	14.1	13.2	14.1	14.1	14.1	14.1	14.1	10.1	7.0	5.0
62.5°	6.0	6.0	6.0	6.0	7.0	7.0	8.1	8.1	6.0	5.0	4.0
65°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	3.1
67.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
70°	3.1	3.1	3.1	2.0	2.0	2.0	2.0	2.0	2.0	2.0	3.1
72.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
75°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0	2.0
80°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.0	2.0	2.0
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.0	2.0	2.0
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212242

CATALOG NUMBER: LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5
2.5°	313.0	311.9	300.9	292.8	288.8	282.7	275.7	265.6	254.5	244.5	240.5
5°	380.4	367.2	344.1	325.0	315.9	306.9	290.8	272.6	255.6	237.5	228.4
7.5°	467.9	429.6	384.4	349.2	334.0	319.0	295.9	270.6	247.5	223.4	210.3
10°	587.6	499.1	420.6	364.2	342.1	322.0	288.8	257.6	232.4	206.3	189.1
12.5°	840.2	620.9	458.8	371.2	342.1	315.9	275.7	239.5	211.3	184.1	168.0
15°	1210.5	838.2	542.3	378.4	335.1	301.8	255.6	216.4	186.2	162.0	146.9
17.5°	1509.4	1038.5	646.0	396.5	326.0	282.7	229.4	188.2	159.9	137.9	125.8
20°	1660.2	1123.0	693.3	399.5	303.9	252.5	198.2	159.0	133.8	114.7	104.6
22.5°	1657.2	1095.8	651.0	350.1	266.6	218.4	167.0	130.8	110.7	95.6	87.6
25°	1552.6	970.0	543.4	279.8	215.3	181.2	135.8	105.7	89.6	78.4	71.4
27.5°	1356.4	787.9	405.5	207.3	168.0	142.9	105.7	84.5	71.4	63.4	58.4
30°	1064.6	527.3	255.6	153.9	127.8	107.7	81.5	65.4	56.4	49.3	46.3
32.5°	586.7	274.7	172.0	112.7	93.6	78.4	60.4	47.3	41.3	36.3	35.2
35°	324.0	194.2	122.8	75.5	62.3	53.3	41.3	34.2	30.2	28.2	28.2
37.5°	229.4	124.8	73.4	47.3	40.3	35.2	28.2	24.2	23.1	22.2	22.2
40°	137.9	73.4	44.3	31.2	27.2	24.2	21.1	18.1	18.1	17.1	18.1
42.5°	75.5	44.3	30.2	22.2	19.1	18.1	15.1	14.1	14.1	14.1	15.1
45°	45.3	29.2	21.1	16.1	14.1	12.1	11.0	10.1	11.0	11.0	12.1
47.5°	29.2	21.1	14.1	10.1	9.0	8.1	7.0	8.1	8.1	9.0	10.1
50°	20.2	13.2	9.0	6.0	6.0	5.0	6.0	6.0	7.0	8.1	9.0
52.5°	13.2	9.0	6.0	5.0	4.0	4.0	4.0	5.0	6.0	7.0	8.1
55°	8.1	6.0	5.0	4.0	4.0	4.0	4.0	4.0	5.0	6.0	7.0
57.5°	6.0	5.0	4.0	3.1	3.1	3.1	4.0	4.0	5.0	5.0	6.0
60°	4.0	4.0	3.1	3.1	3.1	3.1	3.1	4.0	4.0	5.0	6.0
62.5°	4.0	4.0	3.1	3.1	3.1	3.1	4.0	4.0	4.0	5.0	5.0
65°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	5.0
67.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	5.0
70°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	5.0
72.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0
75°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0
77.5°	2.0	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0
80°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0
82.5°	2.0	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0
85°	2.0	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0	4.0
87.5°	2.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	4.0	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212242

CATALOG NUMBER: LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5
2.5°	235.4	228.4	222.4	224.4	220.4	213.3	211.3	206.3	200.3	199.2	199.2
5°	218.4	207.3	198.2	197.2	193.3	185.2	183.2	178.1	173.1	172.0	171.1
7.5°	197.2	185.2	177.0	175.1	172.0	165.0	164.0	159.0	155.9	153.9	153.9
10°	176.1	165.0	157.9	157.0	154.9	148.9	147.9	143.9	140.9	139.9	138.9
12.5°	155.9	146.9	140.9	139.9	137.9	132.8	131.8	128.8	126.8	125.8	125.8
15°	136.9	128.8	123.7	122.8	121.7	116.7	116.7	114.7	113.8	113.8	114.7
17.5°	117.8	110.7	106.7	105.7	105.7	101.7	102.6	101.7	101.7	101.7	103.7
20°	98.6	92.5	89.6	90.5	88.5	87.6	88.5	88.5	88.5	90.5	93.6
22.5°	82.5	77.5	74.4	75.5	75.5	74.4	75.5	76.4	78.4	81.5	84.5
25°	67.4	63.4	62.3	63.4	63.4	63.4	65.4	67.4	69.4	72.4	75.5
27.5°	54.3	51.3	51.3	52.3	53.3	53.3	56.4	58.4	61.3	64.4	67.4
30°	43.3	42.3	42.3	44.3	44.3	45.3	49.3	51.3	53.3	56.4	59.3
32.5°	34.2	34.2	35.2	37.3	37.3	39.3	42.3	44.3	46.3	49.3	52.3
35°	28.2	29.2	30.2	31.2	32.2	33.2	36.3	38.3	40.3	43.3	45.3
37.5°	23.1	24.2	25.2	27.2	27.2	28.2	31.2	33.2	34.2	37.3	40.3
40°	19.1	20.2	21.1	23.1	23.1	24.2	27.2	28.2	29.2	32.2	35.2
42.5°	16.1	17.1	18.1	19.1	20.2	21.1	23.1	24.2	26.2	28.2	30.2
45°	13.2	14.1	15.1	16.1	17.1	18.1	19.1	21.1	22.2	24.2	26.2
47.5°	11.0	12.1	13.2	14.1	15.1	15.1	17.1	18.1	19.1	21.1	23.1
50°	10.1	11.0	12.1	12.1	13.2	14.1	15.1	16.1	17.1	18.1	20.2
52.5°	8.1	9.0	10.1	11.0	11.0	12.1	13.2	14.1	15.1	16.1	17.1
55°	8.1	8.1	9.0	10.1	10.1	11.0	12.1	13.2	13.2	14.1	15.1
57.5°	7.0	8.1	8.1	9.0	9.0	10.1	11.0	11.0	12.1	12.1	13.2
60°	6.0	7.0	8.1	8.1	8.1	9.0	9.0	10.1	10.1	11.0	11.0
62.5°	6.0	7.0	7.0	8.1	8.1	8.1	9.0	9.0	9.0	10.1	10.1
65°	6.0	6.0	7.0	7.0	7.0	7.0	8.1	8.1	8.1	9.0	9.0
67.5°	5.0	6.0	6.0	6.0	7.0	7.0	7.0	7.0	7.0	8.1	8.1
70°	5.0	5.0	6.0	6.0	6.0	6.0	6.0	7.0	7.0	7.0	7.0
72.5°	5.0	5.0	5.0	5.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
75°	4.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
77.5°	4.0	4.0	4.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
80°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
82.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	3.1	3.1
85°	4.0	4.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
87.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212242

CATALOG NUMBER: LDSQA4A25927D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	252.5	252.5	252.5	252.5	252.5	252.5	252.5	252.5
2.5°	195.2	193.3	192.2	195.2	191.1	193.3	192.2	193.3
5°	168.0	166.0	165.0	168.0	164.0	166.0	164.0	166.0
7.5°	150.9	149.9	148.9	150.9	147.9	149.9	148.9	149.9
10°	136.9	135.8	134.8	137.9	134.8	136.9	135.8	136.9
12.5°	124.8	124.8	123.7	125.8	123.7	125.8	124.8	125.8
15°	113.8	114.7	113.8	115.8	114.7	116.7	115.8	117.8
17.5°	104.6	105.7	105.7	108.7	107.7	110.7	109.6	110.7
20°	95.6	96.6	97.6	99.7	99.7	102.6	101.7	103.7
22.5°	86.5	88.5	88.5	91.6	91.6	94.6	94.6	95.6
25°	77.5	80.4	81.5	83.5	84.5	87.6	87.6	88.5
27.5°	70.5	72.4	73.4	76.4	77.5	80.4	80.4	82.5
30°	62.3	65.4	66.4	68.5	69.4	72.4	72.4	74.4
32.5°	55.3	57.3	59.3	61.3	62.3	65.4	65.4	67.4
35°	48.3	51.3	52.3	54.3	56.4	59.3	59.3	61.3
37.5°	42.3	45.3	46.3	48.3	50.3	53.3	53.3	55.3
40°	37.3	40.3	41.3	43.3	44.3	48.3	48.3	49.3
42.5°	33.2	35.2	36.3	38.3	39.3	41.3	41.3	43.3
45°	28.2	30.2	31.2	32.2	34.2	36.3	36.3	37.3
47.5°	24.2	26.2	27.2	28.2	29.2	31.2	31.2	33.2
50°	21.1	22.2	23.1	24.2	25.2	27.2	27.2	28.2
52.5°	18.1	19.1	20.2	21.1	22.2	23.1	24.2	25.2
55°	16.1	17.1	17.1	18.1	19.1	20.2	20.2	21.1
57.5°	14.1	15.1	15.1	15.1	16.1	17.1	17.1	18.1
60°	12.1	13.2	13.2	13.2	14.1	14.1	14.1	15.1
62.5°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0
65°	9.0	9.0	9.0	9.0	9.0	9.0	8.1	9.0
67.5°	8.1	8.1	8.1	7.0	7.0	7.0	7.0	7.0
70°	7.0	7.0	7.0	6.0	6.0	6.0	5.0	5.0
72.5°	6.0	6.0	6.0	5.0	5.0	5.0	4.0	4.0
75°	5.0	5.0	5.0	5.0	4.0	4.0	4.0	4.0
77.5°	4.0	4.0	4.0	4.0	4.0	4.0	3.1	3.1
80°	4.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1
82.5°	3.1	3.1	3.1	3.1	2.0	2.0	2.0	2.0
85°	2.0	2.0	2.0	2.0	2.0	2.0	1.1	1.1
87.5°	2.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)