

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212282

Luminaire Tested: **LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212282
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2507.5 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212282

CATALOG NUMBER: LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212282

CATALOG NUMBER: LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	28346	28346	28346
5°	74539	27005	17631
10°	292227	23363	14677
15°	537991	18414	12998
20°	676041	13010	11835
25°	808624	8594	10550
30°	850342	5392	9251
35°	857206	3264	8006
40°	788793	2175	6816
45°	561204	1576	5658
50°	231915	1206	4672
55°	13377	1165	4054
60°	1550	1104	3333
65°	527	1307	2384
70°	651	1303	1614
75°	861	1722	1722
80°	0	2566	1897
85°	0	5113	2556



TEST NUMBER: P1212282

CATALOG NUMBER: LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	1.8
10°-20°	367.4	14.7
20°-30°	760.0	30.3
30°-40°	827.3	33.0
40°-50°	453.6	18.1
50°-60°	39.3	1.6
60°-70°	6.4	0.3
70°-80°	4.6	0.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1173.4	46.8
0°-40°	2000.7	79.8
0°-60°	2493.6	99.4
0°-90°	2507.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2507.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	293	293	293	293	293	
5°	766	524	278	192	181	140
15°	5364	2255	184	124	130	1498
25°	7565	2999	80	76	99	3416
35°	7248	820	28	44	68	4448
45°	4096	84	12	24	41	3127
55°	79	9	7	15	24	271
65°	2	3	6	9	10	3
75°	2	3	5	7	5	2
85°	0	2	5	3	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212282

CATALOG NUMBER: LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6
2.5°	460.2	444.1	441.7	444.1	432.6	431.4	433.7	424.5	416.5	408.6	401.6
5°	766.5	733.2	722.9	709.1	674.7	663.2	660.9	624.2	588.7	555.3	524.4
7.5°	1489.3	1422.8	1387.2	1318.4	1212.9	1165.7	1140.6	1020.1	907.6	805.4	712.6
10°	2970.7	2796.3	2711.4	2581.7	2351.1	2237.5	2154.9	1852.0	1553.7	1266.8	1014.3
12.5°	4335.0	4238.6	4113.5	4044.7	3670.7	3527.2	3390.6	2970.7	2516.3	2052.7	1592.7
15°	5364.2	5223.1	5089.9	5057.9	4764.2	4596.6	4445.2	4010.2	3469.8	2880.0	2254.7
17.5°	5968.9	5867.9	5741.7	5680.9	5336.8	5201.3	5029.2	4608.1	4082.5	3495.0	2768.8
20°	6557.6	6408.3	6230.5	6138.8	5757.8	5601.7	5406.7	4963.7	4407.3	3783.1	3056.8
22.5°	7095.7	6903.0	6650.5	6508.2	6080.2	5908.2	5690.1	5210.4	4608.1	3894.3	3080.9
25°	7565.0	7390.6	7054.4	6805.4	6300.5	6097.4	5843.8	5342.4	4680.4	3885.2	2999.4
27.5°	7654.5	7537.4	7235.7	6947.7	6377.4	6151.4	5888.6	5369.9	4629.9	3757.9	2780.2
30°	7601.7	7475.5	7233.4	6939.6	6345.3	6117.0	5843.8	5253.0	4432.5	3460.6	2378.6
32.5°	7474.4	7365.3	7076.2	6766.4	6187.0	5949.4	5661.4	4978.7	4094.0	2987.9	1749.8
35°	7248.3	7084.2	6735.4	6480.8	5935.6	5691.3	5339.0	4612.7	3588.0	2148.0	820.4
37.5°	6788.1	6628.7	6377.4	6142.2	5610.9	5323.0	4951.1	4103.2	2659.7	1171.6	507.1
40°	6237.4	6099.8	5880.6	5652.3	5104.9	4773.3	4363.6	3207.1	1565.1	659.8	312.1
42.5°	5638.5	5496.2	5248.3	4982.1	4385.5	4035.5	3592.6	2075.7	825.0	389.0	169.8
45°	4096.3	3969.0	3788.8	3597.2	3251.7	2999.4	2416.5	1090.1	456.7	206.6	83.8
47.5°	2803.2	2651.7	2319.0	1916.2	1553.7	1328.8	999.4	472.7	234.0	103.2	49.3
50°	1538.8	1378.0	1208.3	940.9	629.9	517.5	402.8	228.3	105.5	51.6	27.6
52.5°	377.5	333.9	305.2	281.1	222.7	200.8	169.8	95.2	48.2	28.7	19.5
55°	79.2	73.4	70.0	68.9	63.1	60.8	52.8	36.7	26.5	18.4	9.2
57.5°	23.0	21.8	23.0	23.0	23.0	21.8	21.8	16.1	14.9	9.2	5.7
60°	8.0	8.0	8.0	9.2	9.2	9.2	10.4	10.4	8.0	5.7	4.6
62.5°	3.4	3.4	3.4	4.6	4.6	5.7	5.7	5.7	4.6	4.6	3.4
65°	2.3	2.3	2.3	2.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4
67.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4
70°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4
72.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4
75°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4
80°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.3	2.3	2.3	2.3
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3
85°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3
87.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212282

CATALOG NUMBER: LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6
2.5°	382.1	370.6	356.9	342.0	339.7	331.6	320.1	304.1	298.3	286.9	276.6
5°	479.7	448.7	416.5	387.8	378.7	366.0	345.4	316.7	298.3	277.7	260.5
7.5°	610.4	539.3	473.8	422.2	406.1	385.5	353.4	316.7	289.2	260.5	237.5
10°	784.8	640.3	527.8	444.1	417.6	390.1	347.6	302.9	270.8	237.5	213.4
12.5°	1121.0	788.2	578.3	455.5	418.8	383.2	329.3	281.1	244.4	211.1	187.0
15°	1593.8	1069.4	680.4	463.6	407.3	363.7	300.6	251.3	214.5	183.6	160.6
17.5°	1993.1	1335.6	817.0	486.5	399.3	338.6	267.3	216.8	181.3	153.8	135.4
20°	2188.1	1455.0	878.9	489.9	376.4	300.6	228.3	180.1	149.2	126.2	110.1
22.5°	2165.2	1414.8	821.5	429.1	317.8	253.6	189.3	145.7	119.3	101.0	89.5
25°	2011.4	1240.3	670.2	328.2	247.8	205.4	148.1	113.6	92.9	80.4	71.1
27.5°	1753.3	995.9	488.8	231.7	188.2	156.1	110.1	87.2	71.1	62.0	56.2
30°	1350.6	636.9	281.1	166.5	136.6	111.3	82.7	63.1	53.9	48.2	43.6
32.5°	696.5	309.8	187.0	119.3	96.5	80.4	57.3	45.9	40.1	36.7	34.4
35°	382.1	220.4	129.6	76.9	62.0	51.6	39.0	32.2	29.9	27.6	27.6
37.5°	262.8	136.6	72.3	45.9	37.8	32.2	26.5	23.0	21.8	21.8	21.8
40°	151.5	72.3	41.3	28.7	24.0	21.8	18.4	17.2	17.2	17.2	18.4
42.5°	78.0	42.4	27.6	19.5	17.2	14.9	12.7	12.7	12.7	13.8	14.9
45°	45.9	28.7	18.4	12.7	11.5	10.4	9.2	9.2	10.4	11.5	12.7
47.5°	28.7	19.5	11.5	8.0	6.9	6.9	6.9	6.9	8.0	9.2	10.4
50°	19.5	10.4	6.9	4.6	4.6	4.6	4.6	5.7	6.9	8.0	9.2
52.5°	10.4	5.7	4.6	3.4	3.4	3.4	4.6	4.6	5.7	6.9	8.0
55°	5.7	4.6	3.4	3.4	3.4	3.4	3.4	4.6	5.7	6.9	8.0
57.5°	4.6	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	5.7	6.9
60°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	5.7	6.9
62.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	5.7	5.7
65°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	5.7	5.7
67.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	5.7
70°	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6	5.7
72.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6
75°	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6	4.6	5.7
77.5°	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6	4.6
80°	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6	4.6
82.5°	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6	4.6
85°	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6	4.6	4.6
87.5°	3.4	3.4	3.4	3.4	3.4	3.4	4.6	4.6	4.6	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212282

CATALOG NUMBER: LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6
2.5°	270.8	261.6	252.5	252.5	247.8	241.0	238.7	231.7	227.2	224.9	222.7
5°	247.8	234.0	221.5	220.4	214.5	206.6	203.1	196.2	191.6	189.3	188.2
7.5°	221.5	207.7	195.1	192.8	188.2	182.5	179.0	173.2	171.0	168.7	167.5
10°	196.2	182.5	173.2	171.0	167.5	162.9	159.4	156.1	153.8	152.7	152.7
12.5°	171.0	160.6	152.7	150.4	148.1	144.6	142.3	140.0	138.9	138.9	138.9
15°	148.1	138.9	132.0	132.0	129.6	127.3	127.3	125.1	123.9	125.1	126.2
17.5°	125.1	118.2	112.4	112.4	111.3	110.1	110.1	110.1	111.3	112.4	114.8
20°	103.2	97.6	95.2	95.2	94.0	95.2	95.2	96.5	97.6	101.0	104.4
22.5°	83.8	80.4	78.0	79.2	79.2	80.4	81.5	83.8	86.1	89.5	92.9
25°	67.7	65.4	64.3	65.4	66.6	67.7	70.0	72.3	75.7	79.2	83.8
27.5°	53.9	52.8	52.8	53.9	55.1	57.3	60.8	63.1	66.6	70.0	74.6
30°	43.6	42.4	43.6	45.9	47.0	49.3	51.6	55.1	58.5	62.0	66.6
32.5°	34.4	35.5	36.7	37.8	39.0	42.4	44.8	47.0	50.5	53.9	58.5
35°	28.7	29.9	31.0	32.2	33.3	35.5	37.8	40.1	43.6	47.0	51.6
37.5°	23.0	24.0	25.2	27.6	28.7	29.9	33.3	34.4	37.8	40.1	44.8
40°	19.5	20.7	21.8	23.0	24.0	26.5	28.7	29.9	32.2	35.5	39.0
42.5°	16.1	17.2	18.4	19.5	20.7	23.0	24.0	26.5	28.7	31.0	33.3
45°	13.8	14.9	16.1	17.2	18.4	19.5	20.7	23.0	24.0	26.5	28.7
47.5°	11.5	12.7	14.9	14.9	16.1	17.2	18.4	19.5	21.8	23.0	25.2
50°	10.4	11.5	12.7	13.8	13.8	14.9	16.1	17.2	18.4	19.5	21.8
52.5°	9.2	10.4	11.5	11.5	12.7	13.8	14.9	14.9	16.1	17.2	18.4
55°	8.0	9.2	10.4	10.4	11.5	12.7	12.7	13.8	14.9	14.9	16.1
57.5°	8.0	8.0	9.2	9.2	10.4	10.4	11.5	12.7	12.7	13.8	14.9
60°	6.9	8.0	8.0	9.2	9.2	10.4	10.4	11.5	11.5	12.7	12.7
62.5°	6.9	6.9	8.0	8.0	9.2	9.2	10.4	10.4	10.4	11.5	11.5
65°	6.9	6.9	8.0	8.0	8.0	9.2	9.2	9.2	9.2	10.4	10.4
67.5°	5.7	6.9	6.9	8.0	8.0	8.0	8.0	8.0	9.2	9.2	9.2
70°	5.7	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.0	8.0	8.0
72.5°	5.7	5.7	5.7	5.7	6.9	6.9	6.9	6.9	6.9	6.9	6.9
75°	5.7	5.7	5.7	5.7	5.7	6.9	6.9	6.9	6.9	6.9	6.9
77.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
80°	4.6	4.6	4.6	4.6	4.6	5.7	4.6	4.6	4.6	4.6	4.6
82.5°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	3.4	3.4
85°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	3.4	3.4	3.4	3.4
87.5°	4.6	4.6	4.6	3.4	3.4	3.4	3.4	3.4	3.4	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212282

CATALOG NUMBER: LDSQA4A25940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	292.6	292.6	292.6	292.6	292.6	292.6	292.6	292.6
2.5°	219.2	216.8	219.2	216.8	216.8	212.3	215.6	213.4
5°	184.8	182.5	184.8	183.6	181.3	180.1	182.5	181.3
7.5°	165.3	162.9	165.3	165.3	162.9	161.7	164.0	162.9
10°	150.4	149.2	150.4	150.4	149.2	148.1	150.4	149.2
12.5°	137.7	136.6	138.9	138.9	137.7	137.7	140.0	137.7
15°	126.2	126.2	128.5	128.5	128.5	128.5	130.8	129.6
17.5°	114.8	117.0	119.3	120.5	120.5	120.5	122.8	122.8
20°	105.5	107.8	110.1	111.3	112.4	112.4	114.8	114.8
22.5°	95.2	97.6	101.0	102.1	103.2	104.4	106.7	106.7
25°	86.1	88.4	91.7	92.9	95.2	96.5	98.7	98.7
27.5°	76.9	80.4	82.7	84.9	86.1	88.4	90.6	90.6
30°	68.9	72.3	74.6	76.9	78.0	80.4	82.7	82.7
32.5°	60.8	64.3	66.6	68.9	71.1	72.3	75.7	75.7
35°	53.9	56.2	59.6	60.8	63.1	65.4	67.7	67.7
37.5°	47.0	49.3	51.6	53.9	56.2	57.3	59.6	60.8
40°	41.3	43.6	45.9	47.0	49.3	51.6	52.8	53.9
42.5°	35.5	37.8	40.1	41.3	43.6	44.8	47.0	47.0
45°	31.0	33.3	34.4	35.5	37.8	39.0	41.3	41.3
47.5°	26.5	28.7	29.9	31.0	32.2	33.3	35.5	35.5
50°	23.0	24.0	25.2	26.5	27.6	29.9	31.0	31.0
52.5°	19.5	21.8	21.8	23.0	24.0	25.2	26.5	27.6
55°	17.2	18.4	19.5	19.5	20.7	21.8	23.0	24.0
57.5°	14.9	16.1	17.2	17.2	18.4	18.4	19.5	20.7
60°	13.8	13.8	14.9	14.9	14.9	16.1	16.1	17.2
62.5°	11.5	11.5	12.7	12.7	12.7	12.7	12.7	12.7
65°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
67.5°	9.2	9.2	9.2	9.2	8.0	8.0	8.0	8.0
70°	8.0	8.0	8.0	8.0	6.9	6.9	6.9	5.7
72.5°	6.9	6.9	6.9	6.9	5.7	5.7	4.6	4.6
75°	5.7	5.7	5.7	5.7	5.7	4.6	4.6	4.6
77.5°	5.7	4.6	4.6	4.6	4.6	4.6	4.6	3.4
80°	4.6	4.6	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	3.4	3.4	3.4	2.3	2.3	2.3	2.3
85°	3.4	2.3	2.3	2.3	2.3	2.3	2.3	2.3
87.5°	2.3	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)