

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212268

Luminaire Tested: **LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2322.4 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212268

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212268

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	26253	26253	26253
5°	69035	25002	16337
10°	270655	21632	13585
15°	498275	17050	12045
20°	626123	12052	10959
25°	748916	7953	9770
30°	787565	4989	8569
35°	793912	3016	7403
40°	730545	2011	6310
45°	519760	1466	5247
50°	214779	1115	4325
55°	12380	1081	3783
60°	1434	1027	3081
65°	481	1215	2201
70°	595	1218	1501
75°	786	1609	1609
80°	0	2399	1785
85°	0	4780	2334



TEST NUMBER: P1212268

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.6	1.8
10°-20°	340.3	14.7
20°-30°	703.9	30.3
30°-40°	766.2	33.0
40°-50°	420.1	18.1
50°-60°	36.4	1.6
60°-70°	5.9	0.3
70°-80°	4.3	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1086.8	46.8
0°-40°	1853.0	79.8
0°-60°	2309.5	99.4
0°-90°	2322.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2322.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	271	271	271	271	271	
5°	710	486	257	178	168	130
15°	4968	2088	170	115	120	1387
25°	7006	2778	74	70	91	3164
35°	6713	760	26	40	63	4120
45°	3794	78	11	22	38	2896
55°	73	8	6	14	22	251
65°	2	3	5	8	10	3
75°	2	3	4	6	4	1
85°	0	2	4	3	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1212268

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0
2.5°	426.1	411.3	409.1	411.3	400.6	399.6	401.7	393.2	385.8	378.3	371.9
5°	709.9	679.1	669.5	656.7	624.8	614.2	612.1	578.1	545.2	514.4	485.6
7.5°	1379.4	1317.7	1284.9	1221.0	1123.3	1079.7	1056.3	944.8	840.6	746.0	659.9
10°	2751.4	2589.8	2511.2	2391.1	2177.5	2072.3	1995.8	1715.2	1438.9	1173.2	939.4
12.5°	4014.9	3925.6	3809.8	3746.1	3399.5	3266.8	3140.4	2751.4	2330.5	1901.1	1475.0
15°	4968.2	4837.4	4714.1	4684.4	4412.3	4257.2	4117.0	3714.1	3213.6	2667.4	2088.2
17.5°	5528.2	5434.7	5317.8	5261.4	4942.7	4817.2	4657.9	4267.8	3781.1	3237.0	2564.3
20°	6073.4	5935.1	5770.5	5685.5	5332.6	5188.1	5007.4	4597.3	4081.9	3503.8	2831.0
22.5°	6571.7	6393.2	6159.4	6027.7	5631.3	5471.9	5270.0	4825.8	4267.8	3606.9	2853.4
25°	7006.4	6844.8	6533.5	6302.9	5835.3	5647.2	5412.3	4948.0	4334.8	3598.3	2777.9
27.5°	7089.4	6980.9	6701.4	6434.7	5906.5	5697.1	5453.8	4973.5	4288.0	3480.4	2574.9
30°	7040.5	6923.5	6699.3	6427.3	5876.8	5665.3	5412.3	4865.1	4105.2	3205.1	2203.0
32.5°	6922.4	6821.5	6553.7	6266.8	5730.2	5510.1	5243.4	4611.0	3791.7	2767.3	1620.6
35°	6713.1	6561.2	6238.0	6002.1	5497.3	5271.1	4944.7	4272.1	3323.1	1989.4	759.8
37.5°	6286.9	6139.2	5906.5	5688.7	5196.7	4929.9	4585.6	3800.2	2463.3	1085.0	469.7
40°	5776.8	5649.3	5446.4	5234.9	4727.9	4420.8	4041.5	2970.3	1449.5	611.1	289.1
42.5°	5222.1	5090.4	4860.8	4614.3	4061.7	3737.5	3327.4	1922.4	764.1	360.2	157.3
45°	3793.8	3675.9	3509.0	3331.5	3011.7	2777.9	2238.1	1009.5	423.0	191.3	77.6
47.5°	2596.2	2456.0	2147.7	1774.8	1438.9	1230.7	925.6	437.8	216.8	95.7	45.8
50°	1425.1	1276.3	1119.0	871.4	583.4	479.3	372.9	211.5	97.7	47.8	25.5
52.5°	349.6	309.2	282.7	260.4	206.1	186.0	157.3	88.2	44.6	26.5	18.1
55°	73.3	68.0	64.9	63.8	58.5	56.3	48.9	34.0	24.5	17.0	8.4
57.5°	21.3	20.2	21.3	21.3	21.3	20.2	20.2	14.8	13.8	8.4	5.3
60°	7.4	7.4	7.4	8.4	8.4	8.4	9.6	9.6	7.4	5.3	4.3
62.5°	3.2	3.2	3.2	4.3	4.3	5.3	5.3	5.3	4.3	4.3	3.2
65°	2.1	2.1	2.1	2.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2
67.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2
80°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	2.1
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
85°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
87.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212268

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0
2.5°	353.9	343.3	330.5	316.7	314.6	307.2	296.5	281.6	276.3	265.7	256.1
5°	444.2	415.5	385.8	359.1	350.7	339.0	319.9	293.3	276.3	257.1	241.2
7.5°	565.4	499.4	438.9	391.0	376.2	357.1	327.3	293.3	267.8	241.2	219.9
10°	726.9	593.0	488.9	411.3	386.8	361.4	322.0	280.6	250.8	219.9	197.7
12.5°	1038.3	730.0	535.6	421.9	387.9	355.0	304.9	260.4	226.3	195.5	173.2
15°	1476.0	990.4	630.2	429.4	377.2	336.9	278.4	232.7	198.8	170.0	148.8
17.5°	1845.9	1237.0	756.7	450.6	369.8	313.5	247.6	200.8	168.0	142.4	125.4
20°	2026.6	1347.5	814.0	453.8	348.5	278.4	211.5	166.9	138.1	116.9	102.0
22.5°	2005.4	1310.3	760.8	397.5	294.4	234.9	175.4	134.9	110.5	93.5	82.9
25°	1862.9	1148.7	620.6	303.9	229.6	190.2	137.1	105.2	86.1	74.4	65.9
27.5°	1623.8	922.4	452.7	214.6	174.3	144.6	102.0	80.7	65.9	57.3	52.1
30°	1250.7	589.8	260.4	154.1	126.5	103.1	76.6	58.5	49.9	44.6	40.4
32.5°	645.0	286.9	173.2	110.5	89.3	74.4	53.1	42.5	37.2	34.0	31.9
35°	353.9	204.1	120.1	71.2	57.3	47.8	36.1	29.7	27.7	25.5	25.5
37.5°	243.3	126.5	66.9	42.5	35.1	29.7	24.5	21.3	20.2	20.2	20.2
40°	140.3	66.9	38.3	26.5	22.4	20.2	17.0	15.9	15.9	15.9	17.0
42.5°	72.3	39.3	25.5	18.1	15.9	13.8	11.7	11.7	11.7	12.7	13.8
45°	42.5	26.5	17.0	11.7	10.7	9.6	8.4	8.4	9.6	10.7	11.7
47.5°	26.5	18.1	10.7	7.4	6.4	6.4	6.4	6.4	7.4	8.4	9.6
50°	18.1	9.6	6.4	4.3	4.3	4.3	4.3	5.3	6.4	7.4	8.4
52.5°	9.6	5.3	4.3	3.2	3.2	3.2	4.3	4.3	5.3	6.4	7.4
55°	5.3	4.3	3.2	3.2	3.2	3.2	3.2	4.3	5.3	6.4	7.4
57.5°	4.3	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3	6.4
60°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3	6.4
62.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3	5.3
65°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3	5.3
67.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	5.3
70°	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3	5.3
72.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3
75°	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3	4.3	5.3
77.5°	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3	4.3
80°	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3	4.3
82.5°	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3	4.3
85°	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3	4.3	4.3
87.5°	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212268

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0
2.5°	250.8	242.3	233.8	233.8	229.6	223.2	221.0	214.6	210.4	208.3	206.1
5°	229.6	216.8	205.1	204.1	198.8	191.3	188.1	181.8	177.5	175.4	174.3
7.5°	205.1	192.4	180.7	178.5	174.3	169.0	165.7	160.4	158.3	156.2	155.2
10°	181.8	169.0	160.4	158.3	155.2	150.9	147.6	144.6	142.4	141.3	141.3
12.5°	158.3	148.8	141.3	139.2	137.1	133.9	131.8	129.6	128.6	128.6	128.6
15°	137.1	128.6	122.2	122.2	120.1	117.9	117.9	115.8	114.8	115.8	116.9
17.5°	115.8	109.5	104.1	104.1	103.1	102.0	102.0	102.0	103.1	104.1	106.3
20°	95.7	90.4	88.2	88.2	87.1	88.2	88.2	89.3	90.4	93.5	96.7
22.5°	77.6	74.4	72.3	73.3	73.3	74.4	75.4	77.6	79.7	82.9	86.1
25°	62.6	60.6	59.6	60.6	61.6	62.6	64.9	66.9	70.2	73.3	77.6
27.5°	49.9	48.9	48.9	49.9	51.0	53.1	56.3	58.5	61.6	64.9	69.1
30°	40.4	39.3	40.4	42.5	43.5	45.8	47.8	51.0	54.2	57.3	61.6
32.5°	31.9	32.9	34.0	35.1	36.1	39.3	41.5	43.5	46.8	49.9	54.2
35°	26.5	27.7	28.7	29.7	30.8	32.9	35.1	37.2	40.4	43.5	47.8
37.5°	21.3	22.4	23.4	25.5	26.5	27.7	30.8	31.9	35.1	37.2	41.5
40°	18.1	19.1	20.2	21.3	22.4	24.5	26.5	27.7	29.7	32.9	36.1
42.5°	14.8	15.9	17.0	18.1	19.1	21.3	22.4	24.5	26.5	28.7	30.8
45°	12.7	13.8	14.8	15.9	17.0	18.1	19.1	21.3	22.4	24.5	26.5
47.5°	10.7	11.7	13.8	13.8	14.8	15.9	17.0	18.1	20.2	21.3	23.4
50°	9.6	10.7	11.7	12.7	12.7	13.8	14.8	15.9	17.0	18.1	20.2
52.5°	8.4	9.6	10.7	10.7	11.7	12.7	13.8	13.8	14.8	15.9	17.0
55°	7.4	8.4	9.6	9.6	10.7	11.7	11.7	12.7	13.8	13.8	14.8
57.5°	7.4	7.4	8.4	8.4	9.6	9.6	10.7	11.7	11.7	12.7	13.8
60°	6.4	7.4	7.4	8.4	8.4	9.6	9.6	10.7	10.7	11.7	11.7
62.5°	6.4	6.4	7.4	7.4	8.4	8.4	9.6	9.6	9.6	10.7	10.7
65°	6.4	6.4	7.4	7.4	7.4	8.4	8.4	8.4	8.4	9.6	9.6
67.5°	5.3	6.4	6.4	7.4	7.4	7.4	7.4	7.4	8.4	8.4	8.4
70°	5.3	6.4	6.4	6.4	6.4	7.4	7.4	7.4	7.4	7.4	7.4
72.5°	5.3	5.3	5.3	5.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4
75°	5.3	5.3	5.3	5.3	5.3	6.4	6.4	6.4	6.4	6.4	6.4
77.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
80°	4.3	4.3	4.3	4.3	4.3	5.3	4.3	4.3	4.3	4.3	4.3
82.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2
85°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2	3.2	3.2
87.5°	4.3	4.3	4.3	3.2	3.2	3.2	3.2	3.2	3.2	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212268

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	271.0	271.0	271.0	271.0	271.0	271.0	271.0	271.0
2.5°	202.9	200.8	202.9	200.8	200.8	196.6	199.8	197.7
5°	171.1	169.0	171.1	170.0	168.0	166.9	169.0	168.0
7.5°	153.0	150.9	153.0	153.0	150.9	149.9	151.9	150.9
10°	139.2	138.1	139.2	139.2	138.1	137.1	139.2	138.1
12.5°	127.6	126.5	128.6	128.6	127.6	127.6	129.6	127.6
15°	116.9	116.9	119.0	119.0	119.0	119.0	121.1	120.1
17.5°	106.3	108.4	110.5	111.5	111.5	111.5	113.8	113.8
20°	97.7	99.8	102.0	103.1	104.1	104.1	106.3	106.3
22.5°	88.2	90.4	93.5	94.6	95.7	96.7	98.8	98.8
25°	79.7	81.8	85.0	86.1	88.2	89.3	91.4	91.4
27.5°	71.2	74.4	76.6	78.6	79.7	81.8	83.9	83.9
30°	63.8	66.9	69.1	71.2	72.3	74.4	76.6	76.6
32.5°	56.3	59.6	61.6	63.8	65.9	66.9	70.2	70.2
35°	49.9	52.1	55.3	56.3	58.5	60.6	62.6	62.6
37.5°	43.5	45.8	47.8	49.9	52.1	53.1	55.3	56.3
40°	38.3	40.4	42.5	43.5	45.8	47.8	48.9	49.9
42.5°	32.9	35.1	37.2	38.3	40.4	41.5	43.5	43.5
45°	28.7	30.8	31.9	32.9	35.1	36.1	38.3	38.3
47.5°	24.5	26.5	27.7	28.7	29.7	30.8	32.9	32.9
50°	21.3	22.4	23.4	24.5	25.5	27.7	28.7	28.7
52.5°	18.1	20.2	20.2	21.3	22.4	23.4	24.5	25.5
55°	15.9	17.0	18.1	18.1	19.1	20.2	21.3	22.4
57.5°	13.8	14.8	15.9	15.9	17.0	17.0	18.1	19.1
60°	12.7	12.7	13.8	13.8	13.8	14.8	14.8	15.9
62.5°	10.7	10.7	11.7	11.7	11.7	11.7	11.7	11.7
65°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6
67.5°	8.4	8.4	8.4	8.4	7.4	7.4	7.4	7.4
70°	7.4	7.4	7.4	7.4	6.4	6.4	6.4	5.3
72.5°	6.4	6.4	6.4	6.4	5.3	5.3	4.3	4.3
75°	5.3	5.3	5.3	5.3	5.3	4.3	4.3	4.3
77.5°	5.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2
80°	4.3	4.3	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	3.2	3.2	3.2	3.2	2.1	2.1	2.1	2.1
85°	3.2	2.1	2.1	2.1	2.1	2.1	2.1	2.1
87.5°	2.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)