

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212270

Luminaire Tested: **LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212270
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2157.6 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 30.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212270

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1212270

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	71	90	82	76	71	80	74	70		78	73	69		76
5	86	76	69	64	84	75	68	64	73	67	63		71	66	62		70
6	80	70	62	57	79	69	62	57	67	61	57		66	60	56		64
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59
8	70	59	52	47	69	58	51	46	57	51	46		56	50	46		55
9	66	54	47	42	64	54	47	42	53	46	42		52	46	42		51
10	62	50	43	38	60	50	43	38	49	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	25846	25846	25846
5°	60574	24399	17057
10°	239334	21435	14224
15°	442923	17170	12476
20°	567927	12485	11289
25°	679522	8861	10005
30°	722540	5828	8792
35°	740504	3512	7675
40°	677861	2289	6589
45°	489140	1603	5398
50°	213528	1266	4476
55°	14728	1081	3783
60°	2674	1027	3081
65°	986	986	2201
70°	906	1218	1501
75°	786	1609	1609
80°	0	2399	1785
85°	0	4780	1223

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212270

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.9	1.8
10°-20°	305.4	14.2
20°-30°	639.4	29.6
30°-40°	711.7	33.0
40°-50°	408.5	18.9
50°-60°	40.8	1.9
60°-70°	6.4	0.3
70°-80°	4.1	0.2
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	983.6	45.6
0°-40°	1695.3	78.6
0°-60°	2144.7	99.4
0°-90°	2157.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2157.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	267	267	267	267	267	
5°	623	429	251	183	175	114
15°	4416	1763	171	120	124	1248
25°	6357	2427	83	73	94	2879
35°	6262	741	30	42	65	3823
45°	3570	89	12	23	39	2726
55°	87	13	6	14	22	260
65°	4	3	4	8	10	6
75°	2	2	4	5	4	2
85°	0	2	4	3	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212270

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8
2.5°	398.5	390.1	381.6	376.3	370.9	378.4	373.1	370.9	356.1	348.6	342.3
5°	622.9	606.9	583.5	564.4	545.3	549.5	534.6	516.6	479.4	452.7	429.4
7.5°	1202.1	1162.8	1090.5	1020.4	950.2	937.4	890.7	810.0	705.8	627.1	559.1
10°	2433.0	2314.0	2181.1	2037.6	1869.7	1822.9	1707.1	1488.1	1248.9	975.8	778.1
12.5°	3591.5	3537.3	3381.1	3195.1	3013.3	2901.8	2781.6	2420.1	2040.8	1600.7	1233.0
15°	4416.3	4383.4	4246.2	4077.3	3881.7	3809.4	3662.8	3302.4	2823.1	2296.9	1763.3
17.5°	5027.5	4971.2	4827.7	4643.8	4412.1	4350.4	4175.0	3816.8	3319.4	2791.1	2199.2
20°	5508.9	5473.8	5287.9	5066.8	4789.4	4715.0	4509.9	4136.8	3595.7	3034.6	2431.9
22.5°	5941.5	5882.1	5653.5	5389.9	5073.2	4993.4	4764.9	4355.7	3774.3	3149.4	2473.3
25°	6357.2	6266.8	5989.3	5644.0	5272.0	5163.6	4912.7	4479.0	3840.2	3158.9	2426.6
27.5°	6478.3	6432.6	6176.5	5774.8	5344.3	5222.1	4960.5	4506.6	3815.8	3071.8	2258.7
30°	6459.2	6420.9	6207.3	5787.5	5331.5	5202.8	4937.1	4421.6	3673.3	2844.3	1962.1
32.5°	6398.7	6383.7	6125.5	5676.9	5212.4	5072.2	4785.2	4210.1	3406.6	2497.8	1433.9
35°	6261.5	6203.1	5880.9	5459.0	5012.7	4858.5	4534.3	3907.2	3054.8	1818.6	740.8
37.5°	5859.8	5814.0	5560.0	5190.1	4755.4	4557.7	4215.5	3516.0	2364.9	1034.2	443.2
40°	5360.2	5337.9	5138.1	4807.4	4343.0	4119.8	3747.8	2877.3	1443.4	587.8	292.3
42.5°	4847.8	4841.5	4627.8	4282.4	3778.6	3522.4	3136.6	1940.9	767.4	355.0	169.0
45°	3570.3	3608.6	3459.7	3252.5	2867.7	2681.7	2181.1	1000.2	442.2	196.6	89.3
47.5°	2504.1	2461.6	2198.1	1835.6	1483.8	1256.3	950.2	473.0	236.0	103.1	51.1
50°	1416.8	1424.2	1186.2	959.8	629.3	498.5	378.4	238.1	113.8	54.2	30.8
52.5°	369.9	386.8	333.8	287.0	244.5	198.8	160.5	103.1	54.2	31.9	20.2
55°	87.2	90.4	83.9	78.6	74.4	65.9	58.5	44.6	29.7	20.2	12.7
57.5°	30.8	31.9	30.8	30.8	29.7	28.7	26.5	23.4	18.1	12.7	8.4
60°	13.8	14.8	13.8	14.8	14.8	14.8	14.8	14.8	10.7	7.4	5.3
62.5°	6.4	6.4	6.4	6.4	7.4	7.4	8.4	8.4	6.4	5.3	4.3
65°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2
67.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
70°	3.2	3.2	3.2	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
75°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
77.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1	2.1
80°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
82.5°	0.0	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1
85°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
87.5°	0.0	0.0	0.0	0.0	1.1	1.1	1.1	1.1	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212270

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8
2.5°	330.5	329.5	317.8	309.3	305.1	298.7	291.3	280.6	268.9	258.3	254.0
5°	401.8	388.0	363.6	343.3	333.8	324.2	307.2	288.1	270.0	250.9	241.2
7.5°	494.2	453.9	406.0	368.8	352.9	336.9	312.5	285.9	261.5	236.0	222.2
10°	620.7	527.2	444.3	384.7	361.4	340.1	305.1	272.1	245.5	217.9	199.8
12.5°	887.5	655.8	484.7	392.2	361.4	333.8	291.3	253.0	223.2	194.5	177.5
15°	1278.6	885.5	572.9	399.7	353.9	318.8	270.0	228.5	196.6	171.2	155.2
17.5°	1594.4	1097.0	682.4	418.8	344.3	298.7	242.3	198.8	169.0	145.6	132.8
20°	1753.8	1186.2	732.3	421.9	321.0	266.8	209.4	168.0	141.4	121.1	110.5
22.5°	1750.6	1157.5	687.8	369.9	281.6	230.6	176.4	138.1	116.9	101.0	92.4
25°	1640.0	1024.7	574.0	295.4	227.4	191.3	143.5	111.6	94.6	82.9	75.5
27.5°	1432.8	832.3	428.3	218.9	177.5	150.9	111.6	89.3	75.5	66.9	61.6
30°	1124.5	557.0	270.0	162.6	135.1	113.8	86.1	69.1	59.6	52.1	48.9
32.5°	619.6	290.1	181.8	119.0	98.8	82.9	63.8	49.9	43.5	38.3	37.2
35°	342.3	205.1	129.7	79.7	65.9	56.3	43.5	36.1	31.9	29.7	29.7
37.5°	242.3	131.8	77.6	49.9	42.5	37.2	29.7	25.5	24.5	23.4	23.4
40°	145.6	77.6	46.8	32.9	28.7	25.5	22.4	19.1	19.1	18.1	19.1
42.5°	79.7	46.8	31.9	23.4	20.2	19.1	15.9	14.8	14.8	14.8	15.9
45°	47.8	30.8	22.4	17.0	14.8	12.7	11.7	10.7	11.7	11.7	12.7
47.5°	30.8	22.4	14.8	10.7	9.6	8.4	7.4	8.4	8.4	9.6	10.7
50°	21.3	13.8	9.6	6.4	6.4	5.3	6.4	6.4	7.4	8.4	9.6
52.5°	13.8	9.6	6.4	5.3	4.3	4.3	4.3	5.3	6.4	7.4	8.4
55°	8.4	6.4	5.3	4.3	4.3	4.3	4.3	4.3	5.3	6.4	7.4
57.5°	6.4	5.3	4.3	3.2	3.2	3.2	4.3	4.3	5.3	5.3	6.4
60°	4.3	4.3	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3	6.4
62.5°	4.3	4.3	3.2	3.2	3.2	3.2	4.3	4.3	4.3	5.3	5.3
65°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	5.3
67.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3
72.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3
75°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3
77.5°	2.1	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3
80°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3
82.5°	2.1	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3
85°	2.1	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3	4.3
87.5°	2.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212270

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8
2.5°	248.7	241.2	234.9	237.1	232.8	225.4	223.2	217.9	211.5	210.4	210.4
5°	230.6	218.9	209.4	208.4	204.1	195.6	193.4	188.1	182.8	181.8	180.7
7.5°	208.4	195.6	187.0	185.0	181.8	174.3	173.2	168.0	164.7	162.6	162.6
10°	186.0	174.3	166.9	165.9	163.7	157.3	156.2	151.9	148.8	147.8	146.6
12.5°	164.7	155.2	148.8	147.8	145.6	140.3	139.2	136.1	133.9	132.8	132.8
15°	144.6	136.1	130.8	129.7	128.6	123.3	123.3	121.1	120.1	120.1	121.1
17.5°	124.4	116.9	112.7	111.6	111.6	107.4	108.4	107.4	107.4	107.4	109.5
20°	104.1	97.7	94.6	95.7	93.6	92.4	93.6	93.6	93.6	95.7	98.8
22.5°	87.2	81.9	78.6	79.7	79.7	78.6	79.7	80.7	82.9	86.1	89.3
25°	71.2	66.9	65.9	66.9	66.9	66.9	69.1	71.2	73.3	76.6	79.7
27.5°	57.4	54.2	54.2	55.3	56.3	56.3	59.6	61.6	64.9	68.0	71.2
30°	45.8	44.6	44.6	46.8	46.8	47.8	52.1	54.2	56.3	59.6	62.6
32.5°	36.1	36.1	37.2	39.4	39.4	41.5	44.6	46.8	48.9	52.1	55.3
35°	29.7	30.8	31.9	32.9	34.0	35.1	38.3	40.4	42.5	45.8	47.8
37.5°	24.5	25.5	26.5	28.7	28.7	29.7	32.9	35.1	36.1	39.4	42.5
40°	20.2	21.3	22.4	24.5	24.5	25.5	28.7	29.7	30.8	34.0	37.2
42.5°	17.0	18.1	19.1	20.2	21.3	22.4	24.5	25.5	27.7	29.7	31.9
45°	13.8	14.8	15.9	17.0	18.1	19.1	20.2	22.4	23.4	25.5	27.7
47.5°	11.7	12.7	13.8	14.8	15.9	15.9	18.1	19.1	20.2	22.4	24.5
50°	10.7	11.7	12.7	12.7	13.8	14.8	15.9	17.0	18.1	19.1	21.3
52.5°	8.4	9.6	10.7	11.7	11.7	12.7	13.8	14.8	15.9	17.0	18.1
55°	8.4	8.4	9.6	10.7	10.7	11.7	12.7	13.8	13.8	14.8	15.9
57.5°	7.4	8.4	8.4	9.6	9.6	10.7	11.7	11.7	12.7	12.7	13.8
60°	6.4	7.4	8.4	8.4	8.4	9.6	9.6	10.7	10.7	11.7	11.7
62.5°	6.4	7.4	7.4	8.4	8.4	8.4	9.6	9.6	9.6	10.7	10.7
65°	6.4	6.4	7.4	7.4	7.4	7.4	8.4	8.4	8.4	9.6	9.6
67.5°	5.3	6.4	6.4	6.4	7.4	7.4	7.4	7.4	7.4	8.4	8.4
70°	5.3	5.3	6.4	6.4	6.4	6.4	6.4	7.4	7.4	7.4	7.4
72.5°	5.3	5.3	5.3	5.3	6.4	6.4	6.4	6.4	6.4	6.4	6.4
75°	4.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
77.5°	4.3	4.3	4.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
80°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
82.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2
85°	4.3	4.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212270

CATALOG NUMBER: LDSQA4A25935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	266.8	266.8	266.8	266.8	266.8	266.8	266.8	266.8
2.5°	206.1	204.1	203.1	206.1	202.0	204.1	203.1	204.1
5°	177.5	175.4	174.3	177.5	173.2	175.4	173.2	175.4
7.5°	159.4	158.3	157.3	159.4	156.2	158.3	157.3	158.3
10°	144.6	143.5	142.4	145.6	142.4	144.6	143.5	144.6
12.5°	131.8	131.8	130.8	132.8	130.8	132.8	131.8	132.8
15°	120.1	121.1	120.1	122.2	121.1	123.3	122.2	124.4
17.5°	110.5	111.6	111.6	114.8	113.8	116.9	115.8	116.9
20°	101.0	102.0	103.1	105.2	105.2	108.4	107.4	109.5
22.5°	91.4	93.6	93.6	96.7	96.7	100.0	100.0	101.0
25°	81.9	85.0	86.1	88.2	89.3	92.4	92.4	93.6
27.5°	74.4	76.6	77.6	80.7	81.9	85.0	85.0	87.2
30°	65.9	69.1	70.2	72.3	73.3	76.6	76.6	78.6
32.5°	58.5	60.6	62.6	64.9	65.9	69.1	69.1	71.2
35°	51.1	54.2	55.3	57.4	59.6	62.6	62.6	64.9
37.5°	44.6	47.8	48.9	51.1	53.1	56.3	56.3	58.5
40°	39.4	42.5	43.5	45.8	46.8	51.1	51.1	52.1
42.5°	35.1	37.2	38.3	40.4	41.5	43.5	43.5	45.8
45°	29.7	31.9	32.9	34.0	36.1	38.3	38.3	39.4
47.5°	25.5	27.7	28.7	29.7	30.8	32.9	32.9	35.1
50°	22.4	23.4	24.5	25.5	26.5	28.7	28.7	29.7
52.5°	19.1	20.2	21.3	22.4	23.4	24.5	25.5	26.5
55°	17.0	18.1	18.1	19.1	20.2	21.3	21.3	22.4
57.5°	14.8	15.9	15.9	15.9	17.0	18.1	18.1	19.1
60°	12.7	13.8	13.8	13.8	14.8	14.8	14.8	15.9
62.5°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7
65°	9.6	9.6	9.6	9.6	9.6	9.6	8.4	9.6
67.5°	8.4	8.4	8.4	7.4	7.4	7.4	7.4	7.4
70°	7.4	7.4	7.4	6.4	6.4	6.4	5.3	5.3
72.5°	6.4	6.4	6.4	5.3	5.3	5.3	4.3	4.3
75°	5.3	5.3	5.3	5.3	4.3	4.3	4.3	4.3
77.5°	4.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2
80°	4.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2
82.5°	3.2	3.2	3.2	3.2	2.1	2.1	2.1	2.1
85°	2.1	2.1	2.1	2.1	2.1	2.1	1.1	1.1
87.5°	2.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)