

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212310

Luminaire Tested: **LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2733.3 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212310

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212310

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	30903	30903	30903
5°	81249	29436	19216
10°	318561	25468	15995
15°	586452	20069	14181
20°	736937	14186	12897
25°	881470	9364	11501
30°	926945	5873	10079
35°	934432	3560	8728
40°	859852	2377	7436
45°	611757	1713	6165
50°	252803	1311	5094
55°	14576	1267	4425
60°	1686	1201	3643
65°	573	1421	2590
70°	708	1416	1756
75°	936	1871	1871
80°	0	2789	2064
85°	0	5558	2779



TEST NUMBER: P1212310

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.1	1.8
10°-20°	400.5	14.7
20°-30°	828.5	30.3
30°-40°	901.9	33.0
40°-50°	494.5	18.1
50°-60°	42.8	1.6
60°-70°	7.0	0.3
70°-80°	5.0	0.2
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1279.1	46.8
0°-40°	2181.0	79.8
0°-60°	2718.3	99.4
0°-90°	2733.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2733.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	319	319	319	319	319	
5°	836	572	303	209	198	153
15°	5847	2458	200	135	141	1633
25°	8246	3270	88	83	108	3724
35°	7901	894	30	48	74	4849
45°	4465	91	12	26	45	3408
55°	86	10	8	16	26	295
65°	2	4	6	10	11	4
75°	2	4	5	8	5	2
85°	0	2	5	4	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212310

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0
2.5°	501.6	484.1	481.6	484.1	471.5	470.3	472.8	462.8	454.0	445.3	437.8
5°	835.5	799.2	787.9	773.0	735.5	723.0	720.5	680.5	641.6	605.3	571.7
7.5°	1623.6	1551.0	1512.2	1437.1	1322.1	1270.8	1243.3	1111.9	989.4	878.0	776.8
10°	3238.4	3048.2	2955.6	2814.3	2562.8	2439.1	2349.0	2018.7	1693.5	1380.9	1105.7
12.5°	4725.5	4620.5	4484.1	4409.0	4001.3	3844.9	3696.1	3238.4	2743.0	2237.6	1736.1
15°	5847.4	5693.6	5548.5	5513.5	5193.3	5010.6	4845.6	4371.5	3782.4	3139.5	2457.9
17.5°	6506.7	6396.6	6259.0	6192.7	5817.5	5669.9	5482.2	5023.2	4450.3	3809.9	3018.1
20°	7148.3	6985.7	6791.9	6691.7	6276.5	6106.4	5893.7	5410.9	4804.3	4123.8	3332.1
22.5°	7735.0	7524.8	7249.6	7094.5	6628.0	6440.3	6202.7	5679.8	5023.2	4245.2	3358.4
25°	8246.5	8056.3	7689.9	7418.4	6868.1	6646.8	6370.3	5823.7	5102.0	4235.2	3269.5
27.5°	8344.0	8216.5	7887.5	7573.6	6951.9	6705.5	6419.1	5853.7	5046.9	4096.4	3030.7
30°	8286.5	8148.9	7885.0	7564.8	6916.8	6668.0	6370.3	5726.2	4831.8	3772.4	2592.9
32.5°	8147.6	8028.9	7713.6	7376.0	6744.3	6485.4	6171.4	5427.2	4462.8	3257.1	1907.4
35°	7901.3	7722.4	7342.2	7064.5	6470.4	6203.9	5820.0	5028.2	3911.3	2341.5	894.3
37.5°	7399.7	7225.8	6951.9	6695.5	6116.4	5802.4	5397.2	4472.9	2899.4	1277.0	552.8
40°	6799.3	6649.3	6410.4	6161.4	5564.8	5203.3	4756.7	3496.0	1706.1	719.2	340.2
42.5°	6146.4	5991.3	5721.2	5431.0	4780.6	4399.1	3916.2	2262.7	899.4	424.0	185.1
45°	4465.3	4326.5	4130.2	3921.2	3544.7	3269.5	2634.1	1188.3	497.8	225.1	91.3
47.5°	3055.7	2890.5	2527.8	2088.8	1693.5	1448.4	1089.4	515.3	255.2	112.5	53.8
50°	1677.4	1502.2	1317.1	1025.7	686.7	564.1	439.0	248.9	115.0	56.3	30.1
52.5°	411.5	364.0	332.7	306.5	242.6	218.9	185.1	103.8	52.5	31.3	21.2
55°	86.3	80.0	76.3	75.0	68.8	66.3	57.5	40.0	28.8	20.0	10.1
57.5°	25.0	23.7	25.0	25.0	25.0	23.7	23.7	17.5	16.3	10.1	6.2
60°	8.7	8.7	8.7	10.1	10.1	10.1	11.3	11.3	8.7	6.2	5.0
62.5°	3.7	3.7	3.7	5.0	5.0	6.2	6.2	6.2	5.0	5.0	3.7
65°	2.5	2.5	2.5	2.5	3.7	3.7	3.7	3.7	3.7	3.7	3.7
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7
70°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7
77.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7
80°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5	2.5
82.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
85°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
87.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212310

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0
2.5°	416.5	404.0	388.9	372.8	370.2	361.5	348.9	331.4	325.2	312.7	301.5
5°	522.9	489.1	454.0	422.7	412.8	399.0	376.5	345.2	325.2	302.7	284.0
7.5°	665.5	587.8	516.5	460.2	442.7	420.2	385.2	345.2	315.2	284.0	258.9
10°	855.5	697.9	575.4	484.1	455.3	425.2	379.0	330.2	295.2	258.9	232.7
12.5°	1222.0	859.3	630.4	496.5	456.5	417.8	359.0	306.5	266.5	230.2	203.9
15°	1737.4	1165.7	741.7	505.3	444.0	396.5	327.7	273.9	233.9	200.1	175.1
17.5°	2172.7	1455.9	890.6	530.3	435.3	368.9	291.4	236.4	197.6	167.6	147.6
20°	2385.3	1586.0	958.1	534.0	410.3	327.7	248.9	196.4	162.6	137.6	120.1
22.5°	2360.2	1542.2	895.5	467.8	346.5	276.4	206.3	158.9	130.1	110.1	97.5
25°	2192.7	1352.2	730.4	357.8	270.2	223.9	161.4	123.8	101.4	87.6	77.5
27.5°	1911.2	1085.7	532.8	252.7	205.1	170.1	120.1	95.0	77.5	67.6	61.2
30°	1472.2	694.2	306.5	181.4	148.8	121.4	90.1	68.8	58.8	52.5	47.6
32.5°	759.2	337.8	203.9	130.1	105.1	87.6	62.5	50.1	43.7	40.0	37.5
35°	416.5	240.1	141.4	83.8	67.6	56.3	42.5	35.0	32.5	30.1	30.1
37.5°	286.5	148.8	78.8	50.1	41.2	35.0	28.8	25.0	23.7	23.7	23.7
40°	165.1	78.8	45.0	31.3	26.2	23.7	20.0	18.8	18.8	18.8	20.0
42.5°	85.1	46.3	30.1	21.2	18.8	16.3	13.8	13.8	13.8	15.0	16.3
45°	50.1	31.3	20.0	13.8	12.5	11.3	10.1	10.1	11.3	12.5	13.8
47.5°	31.3	21.2	12.5	8.7	7.5	7.5	7.5	7.5	8.7	10.1	11.3
50°	21.2	11.3	7.5	5.0	5.0	5.0	5.0	6.2	7.5	8.7	10.1
52.5°	11.3	6.2	5.0	3.7	3.7	3.7	5.0	5.0	6.2	7.5	8.7
55°	6.2	5.0	3.7	3.7	3.7	3.7	3.7	5.0	6.2	7.5	8.7
57.5°	5.0	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2	7.5
60°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2	7.5
62.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2	6.2
65°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2	6.2
67.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	6.2
70°	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0	6.2
72.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0
75°	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0	5.0	6.2
77.5°	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0	5.0
80°	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0	5.0
82.5°	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0	5.0
85°	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0	5.0	5.0
87.5°	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212310

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0
2.5°	295.2	285.2	275.2	275.2	270.2	262.6	260.1	252.7	247.7	245.2	242.6
5°	270.2	255.2	241.4	240.1	233.9	225.1	221.4	213.9	208.9	206.3	205.1
7.5°	241.4	226.3	212.7	210.2	205.1	198.9	195.2	188.8	186.3	183.9	182.6
10°	213.9	198.9	188.8	186.3	182.6	177.6	173.9	170.1	167.6	166.3	166.3
12.5°	186.3	175.1	166.3	163.8	161.4	157.6	155.1	152.5	151.3	151.3	151.3
15°	161.4	151.3	143.8	143.8	141.4	138.9	138.9	136.4	135.0	136.4	137.6
17.5°	136.4	128.8	122.6	122.6	121.4	120.1	120.1	120.1	121.4	122.6	125.1
20°	112.5	106.3	103.8	103.8	102.6	103.8	103.8	105.1	106.3	110.1	113.8
22.5°	91.3	87.6	85.1	86.3	86.3	87.6	88.8	91.3	93.8	97.5	101.4
25°	73.8	71.3	70.1	71.3	72.5	73.8	76.3	78.8	82.6	86.3	91.3
27.5°	58.8	57.5	57.5	58.8	60.0	62.5	66.3	68.8	72.5	76.3	81.2
30°	47.6	46.3	47.6	50.1	51.3	53.8	56.3	60.0	63.8	67.6	72.5
32.5°	37.5	38.8	40.0	41.2	42.5	46.3	48.8	51.3	55.0	58.8	63.8
35°	31.3	32.5	33.8	35.0	36.3	38.8	41.2	43.7	47.6	51.3	56.3
37.5°	25.0	26.2	27.6	30.1	31.3	32.5	36.3	37.5	41.2	43.7	48.8
40°	21.2	22.5	23.7	25.0	26.2	28.8	31.3	32.5	35.0	38.8	42.5
42.5°	17.5	18.8	20.0	21.2	22.5	25.0	26.2	28.8	31.3	33.8	36.3
45°	15.0	16.3	17.5	18.8	20.0	21.2	22.5	25.0	26.2	28.8	31.3
47.5°	12.5	13.8	16.3	16.3	17.5	18.8	20.0	21.2	23.7	25.0	27.6
50°	11.3	12.5	13.8	15.0	15.0	16.3	17.5	18.8	20.0	21.2	23.7
52.5°	10.1	11.3	12.5	12.5	13.8	15.0	16.3	16.3	17.5	18.8	20.0
55°	8.7	10.1	11.3	11.3	12.5	13.8	13.8	15.0	16.3	16.3	17.5
57.5°	8.7	8.7	10.1	10.1	11.3	11.3	12.5	13.8	13.8	15.0	16.3
60°	7.5	8.7	8.7	10.1	10.1	11.3	11.3	12.5	12.5	13.8	13.8
62.5°	7.5	7.5	8.7	8.7	10.1	10.1	11.3	11.3	11.3	12.5	12.5
65°	7.5	7.5	8.7	8.7	8.7	10.1	10.1	10.1	10.1	11.3	11.3
67.5°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	8.7	10.1	10.1	10.1
70°	6.2	7.5	7.5	7.5	7.5	8.7	8.7	8.7	8.7	8.7	8.7
72.5°	6.2	6.2	6.2	6.2	7.5	7.5	7.5	7.5	7.5	7.5	7.5
75°	6.2	6.2	6.2	6.2	6.2	7.5	7.5	7.5	7.5	7.5	7.5
77.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
80°	5.0	5.0	5.0	5.0	5.0	6.2	5.0	5.0	5.0	5.0	5.0
82.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	3.7	3.7
85°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	3.7	3.7	3.7	3.7
87.5°	5.0	5.0	5.0	3.7	3.7	3.7	3.7	3.7	3.7	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212310

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	319.0	319.0	319.0	319.0	319.0	319.0	319.0	319.0
2.5°	238.9	236.4	238.9	236.4	236.4	231.4	235.2	232.7
5°	201.4	198.9	201.4	200.1	197.6	196.4	198.9	197.6
7.5°	180.1	177.6	180.1	180.1	177.6	176.4	178.9	177.6
10°	163.8	162.6	163.8	163.8	162.6	161.4	163.8	162.6
12.5°	150.1	148.8	151.3	151.3	150.1	150.1	152.5	150.1
15°	137.6	137.6	140.1	140.1	140.1	140.1	142.6	141.4
17.5°	125.1	127.6	130.1	131.3	131.3	131.3	133.8	133.8
20°	115.0	117.5	120.1	121.4	122.6	122.6	125.1	125.1
22.5°	103.8	106.3	110.1	111.3	112.5	113.8	116.3	116.3
25°	93.8	96.3	100.1	101.4	103.8	105.1	107.6	107.6
27.5°	83.8	87.6	90.1	92.5	93.8	96.3	98.8	98.8
30°	75.0	78.8	81.2	83.8	85.1	87.6	90.1	90.1
32.5°	66.3	70.1	72.5	75.0	77.5	78.8	82.6	82.6
35°	58.8	61.2	65.1	66.3	68.8	71.3	73.8	73.8
37.5°	51.3	53.8	56.3	58.8	61.2	62.5	65.1	66.3
40°	45.0	47.6	50.1	51.3	53.8	56.3	57.5	58.8
42.5°	38.8	41.2	43.7	45.0	47.6	48.8	51.3	51.3
45°	33.8	36.3	37.5	38.8	41.2	42.5	45.0	45.0
47.5°	28.8	31.3	32.5	33.8	35.0	36.3	38.8	38.8
50°	25.0	26.2	27.6	28.8	30.1	32.5	33.8	33.8
52.5°	21.2	23.7	23.7	25.0	26.2	27.6	28.8	30.1
55°	18.8	20.0	21.2	21.2	22.5	23.7	25.0	26.2
57.5°	16.3	17.5	18.8	18.8	20.0	20.0	21.2	22.5
60°	15.0	15.0	16.3	16.3	16.3	17.5	17.5	18.8
62.5°	12.5	12.5	13.8	13.8	13.8	13.8	13.8	13.8
65°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3
67.5°	10.1	10.1	10.1	10.1	8.7	8.7	8.7	8.7
70°	8.7	8.7	8.7	8.7	7.5	7.5	7.5	6.2
72.5°	7.5	7.5	7.5	7.5	6.2	6.2	5.0	5.0
75°	6.2	6.2	6.2	6.2	6.2	5.0	5.0	5.0
77.5°	6.2	5.0	5.0	5.0	5.0	5.0	5.0	3.7
80°	5.0	5.0	3.7	3.7	3.7	3.7	3.7	3.7
82.5°	3.7	3.7	3.7	3.7	2.5	2.5	2.5	2.5
85°	3.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	1.2	1.2	1.2	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)