

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212312

Luminaire Tested: **LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212312
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2539.4 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212312

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212312

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	30419	30419	30419
5°	71291	28717	20081
10°	281682	25232	16743
15°	521322	20199	14673
20°	668463	14701	13278
25°	799785	10432	11769
30°	850421	6846	10347
35°	871563	4139	9023
40°	797835	2681	7739
45°	575698	1891	6343
50°	251341	1522	5275
55°	17329	1267	4425
60°	3158	1201	3643
65°	1146	1146	2590
70°	1048	1416	1756
75°	936	1871	1871
80°	0	2789	2064
85°	0	5558	1334



TEST NUMBER: P1212312

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	1.8
10°-20°	359.5	14.2
20°-30°	752.5	29.6
30°-40°	837.7	33.0
40°-50°	480.8	18.9
50°-60°	48.0	1.9
60°-70°	7.5	0.3
70°-80°	4.7	0.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1157.7	45.6
0°-40°	1995.4	78.6
0°-60°	2524.2	99.4
0°-90°	2539.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2539.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	314	314	314	314	314	
5°	733	505	295	215	206	134
15°	5198	2076	201	141	146	1469
25°	7482	2856	98	86	110	3388
35°	7370	872	35	50	76	4500
45°	4202	105	14	28	46	3208
55°	103	15	8	16	26	306
65°	5	4	5	10	11	6
75°	2	2	5	6	5	2
85°	0	2	5	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212312

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0
2.5°	469.2	459.1	449.1	442.8	436.6	445.3	439.1	436.6	419.1	410.3	402.8
5°	733.1	714.4	686.8	664.3	641.7	646.8	629.3	607.9	564.2	532.9	505.4
7.5°	1414.9	1368.7	1283.6	1201.0	1118.4	1103.4	1048.3	953.3	830.7	738.1	658.0
10°	2863.5	2723.4	2567.1	2398.2	2200.6	2145.5	2009.1	1751.4	1469.9	1148.4	915.8
12.5°	4227.2	4163.4	3979.5	3760.5	3546.6	3415.3	3273.9	2848.6	2401.9	1884.0	1451.1
15°	5198.0	5159.2	4997.8	4798.9	4568.7	4483.6	4311.1	3886.9	3322.7	2703.4	2075.5
17.5°	5917.4	5851.0	5682.1	5465.7	5193.0	5120.4	4914.0	4492.4	3907.0	3285.1	2588.4
20°	6484.1	6442.7	6223.8	5963.6	5637.1	5549.5	5308.1	4868.9	4232.2	3571.7	2862.3
22.5°	6993.2	6923.2	6654.1	6343.9	5971.1	5877.2	5608.3	5126.7	4442.4	3706.7	2911.1
25°	7482.3	7376.0	7049.5	6642.9	6205.1	6077.5	5782.2	5271.8	4519.9	3718.0	2856.1
27.5°	7624.9	7571.1	7269.6	6796.8	6290.1	6146.3	5838.5	5304.3	4491.2	3615.4	2658.4
30°	7602.4	7557.4	7305.9	6811.8	6275.1	6123.7	5811.0	5204.2	4323.5	3347.7	2309.4
32.5°	7531.1	7513.6	7209.6	6681.7	6135.0	5969.9	5632.0	4955.3	4009.5	2939.9	1687.7
35°	7369.7	7300.9	6921.9	6425.2	5899.8	5718.4	5336.9	4598.8	3595.4	2140.4	871.9
37.5°	6896.8	6843.1	6544.1	6108.7	5597.0	5364.3	4961.5	4138.4	2783.5	1217.2	521.7
40°	6308.9	6282.6	6047.4	5658.4	5111.7	4848.9	4411.1	3386.5	1698.8	691.8	344.1
42.5°	5705.9	5698.4	5446.9	5040.4	4447.3	4145.9	3691.7	2284.4	903.2	417.9	198.9
45°	4202.1	4247.2	4072.1	3828.1	3375.2	3156.3	2567.1	1177.2	520.5	231.4	105.1
47.5°	2947.4	2897.3	2587.1	2160.6	1746.4	1478.7	1118.4	556.8	277.8	121.4	60.0
50°	1667.7	1676.4	1396.1	1129.7	740.6	586.7	445.3	280.2	133.9	63.8	36.3
52.5°	435.4	455.4	392.8	337.8	287.7	233.9	188.9	121.4	63.8	37.5	23.7
55°	102.6	106.3	98.9	92.5	87.6	77.5	68.8	52.5	35.0	23.7	15.0
57.5°	36.3	37.5	36.3	36.3	35.0	33.8	31.3	27.6	21.2	15.0	10.1
60°	16.3	17.5	16.3	17.5	17.5	17.5	17.5	17.5	12.5	8.7	6.2
62.5°	7.5	7.5	7.5	7.5	8.7	8.7	10.1	10.1	7.5	6.2	5.0
65°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	3.7
67.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
70°	3.7	3.7	3.7	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
77.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5	2.5
80°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
82.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
85°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5
87.5°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212312

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0
2.5°	389.1	387.8	374.0	364.1	359.0	351.5	342.7	330.3	316.5	304.0	299.0
5°	472.9	456.6	427.8	404.1	392.8	381.6	361.6	339.0	317.8	295.3	284.0
7.5°	581.7	534.2	477.9	434.1	415.4	396.5	367.8	336.5	307.7	277.8	261.5
10°	730.5	620.5	523.0	452.9	425.3	400.4	359.0	320.2	288.9	256.5	235.2
12.5°	1044.6	771.9	570.4	461.6	425.3	392.8	342.7	297.8	262.7	228.9	208.9
15°	1504.9	1042.1	674.3	470.4	416.6	375.3	317.8	268.9	231.4	201.4	182.6
17.5°	1876.5	1291.0	803.2	492.9	405.3	351.5	285.2	233.9	198.9	171.4	156.4
20°	2064.2	1396.1	862.0	496.6	377.8	314.0	246.5	197.6	166.3	142.6	130.1
22.5°	2060.4	1362.3	809.4	435.4	331.5	271.4	207.7	162.6	137.6	118.9	108.8
25°	1930.3	1205.9	675.5	347.8	267.7	225.2	168.9	131.3	111.3	97.6	88.8
27.5°	1686.4	979.6	504.2	257.8	208.9	177.6	131.3	105.1	88.8	78.8	72.5
30°	1323.6	655.5	317.8	191.4	158.9	133.9	101.4	81.4	70.1	61.2	57.5
32.5°	729.3	341.5	213.9	140.1	116.4	97.6	75.0	58.8	51.3	45.1	43.7
35°	402.8	241.5	152.7	93.8	77.5	66.3	51.3	42.5	37.5	35.0	35.0
37.5°	285.2	155.1	91.3	58.8	50.1	43.7	35.0	30.1	28.8	27.6	27.6
40°	171.4	91.3	55.0	38.8	33.8	30.1	26.2	22.5	22.5	21.2	22.5
42.5°	93.8	55.0	37.5	27.6	23.7	22.5	18.8	17.5	17.5	17.5	18.8
45°	56.3	36.3	26.2	20.0	17.5	15.0	13.8	12.5	13.8	13.8	15.0
47.5°	36.3	26.2	17.5	12.5	11.3	10.1	8.7	10.1	10.1	11.3	12.5
50°	25.0	16.3	11.3	7.5	7.5	6.2	7.5	7.5	8.7	10.1	11.3
52.5°	16.3	11.3	7.5	6.2	5.0	5.0	5.0	6.2	7.5	8.7	10.1
55°	10.1	7.5	6.2	5.0	5.0	5.0	5.0	5.0	6.2	7.5	8.7
57.5°	7.5	6.2	5.0	3.7	3.7	3.7	5.0	5.0	6.2	6.2	7.5
60°	5.0	5.0	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2	7.5
62.5°	5.0	5.0	3.7	3.7	3.7	3.7	5.0	5.0	5.0	6.2	6.2
65°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	6.2
67.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2
70°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2
72.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0
75°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0
77.5°	2.5	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0
80°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0
82.5°	2.5	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0
85°	2.5	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0	5.0
87.5°	2.5	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212312

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0
2.5°	292.8	284.0	276.5	279.0	274.0	265.2	262.7	256.5	248.9	247.7	247.7
5°	271.4	257.8	246.5	245.2	240.2	230.2	227.7	221.5	215.2	213.9	212.7
7.5°	245.2	230.2	220.1	217.6	213.9	205.2	204.0	197.6	193.9	191.4	191.4
10°	218.9	205.2	196.4	195.2	192.7	185.2	183.9	178.9	175.1	173.9	172.7
12.5°	193.9	182.6	175.1	173.9	171.4	165.1	163.8	160.1	157.6	156.4	156.4
15°	170.2	160.1	153.9	152.7	151.4	145.1	145.1	142.6	141.4	141.4	142.6
17.5°	146.3	137.6	132.7	131.3	131.3	126.3	127.6	126.3	126.3	126.3	128.8
20°	122.6	115.1	111.3	112.5	110.1	108.8	110.1	110.1	110.1	112.5	116.4
22.5°	102.6	96.3	92.5	93.8	93.8	92.5	93.8	95.0	97.6	101.4	105.1
25°	83.8	78.8	77.5	78.8	78.8	78.8	81.4	83.8	86.3	90.1	93.8
27.5°	67.6	63.8	63.8	65.1	66.3	66.3	70.1	72.5	76.3	80.1	83.8
30°	53.8	52.5	52.5	55.0	55.0	56.3	61.2	63.8	66.3	70.1	73.8
32.5°	42.5	42.5	43.7	46.3	46.3	48.8	52.5	55.0	57.5	61.2	65.1
35°	35.0	36.3	37.5	38.8	40.0	41.2	45.1	47.6	50.1	53.8	56.3
37.5°	28.8	30.1	31.3	33.8	33.8	35.0	38.8	41.2	42.5	46.3	50.1
40°	23.7	25.0	26.2	28.8	28.8	30.1	33.8	35.0	36.3	40.0	43.7
42.5°	20.0	21.2	22.5	23.7	25.0	26.2	28.8	30.1	32.5	35.0	37.5
45°	16.3	17.5	18.8	20.0	21.2	22.5	23.7	26.2	27.6	30.1	32.5
47.5°	13.8	15.0	16.3	17.5	18.8	18.8	21.2	22.5	23.7	26.2	28.8
50°	12.5	13.8	15.0	15.0	16.3	17.5	18.8	20.0	21.2	22.5	25.0
52.5°	10.1	11.3	12.5	13.8	13.8	15.0	16.3	17.5	18.8	20.0	21.2
55°	10.1	10.1	11.3	12.5	12.5	13.8	15.0	16.3	16.3	17.5	18.8
57.5°	8.7	10.1	10.1	11.3	11.3	12.5	13.8	13.8	15.0	15.0	16.3
60°	7.5	8.7	10.1	10.1	10.1	11.3	11.3	12.5	12.5	13.8	13.8
62.5°	7.5	8.7	8.7	10.1	10.1	10.1	11.3	11.3	11.3	12.5	12.5
65°	7.5	7.5	8.7	8.7	8.7	8.7	10.1	10.1	10.1	11.3	11.3
67.5°	6.2	7.5	7.5	7.5	8.7	8.7	8.7	8.7	8.7	10.1	10.1
70°	6.2	6.2	7.5	7.5	7.5	7.5	7.5	8.7	8.7	8.7	8.7
72.5°	6.2	6.2	6.2	6.2	7.5	7.5	7.5	7.5	7.5	7.5	7.5
75°	5.0	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
77.5°	5.0	5.0	5.0	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
80°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
82.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	3.7	3.7
85°	5.0	5.0	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
87.5°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212312

CATALOG NUMBER: LDSQA4A30930D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	314.0	314.0	314.0	314.0	314.0	314.0	314.0	314.0
2.5°	242.7	240.2	239.0	242.7	237.6	240.2	239.0	240.2
5°	208.9	206.5	205.2	208.9	204.0	206.5	204.0	206.5
7.5°	187.7	186.4	185.2	187.7	183.9	186.4	185.2	186.4
10°	170.2	168.9	167.7	171.4	167.7	170.2	168.9	170.2
12.5°	155.1	155.1	153.9	156.4	153.9	156.4	155.1	156.4
15°	141.4	142.6	141.4	143.8	142.6	145.1	143.8	146.3
17.5°	130.1	131.3	131.3	135.1	133.9	137.6	136.4	137.6
20°	118.9	120.1	121.4	123.8	123.8	127.6	126.3	128.8
22.5°	107.6	110.1	110.1	113.8	113.8	117.6	117.6	118.9
25°	96.3	100.1	101.4	103.8	105.1	108.8	108.8	110.1
27.5°	87.6	90.1	91.3	95.0	96.3	100.1	100.1	102.6
30°	77.5	81.4	82.6	85.1	86.3	90.1	90.1	92.5
32.5°	68.8	71.3	73.8	76.3	77.5	81.4	81.4	83.8
35°	60.0	63.8	65.1	67.6	70.1	73.8	73.8	76.3
37.5°	52.5	56.3	57.5	60.0	62.6	66.3	66.3	68.8
40°	46.3	50.1	51.3	53.8	55.0	60.0	60.0	61.2
42.5°	41.2	43.7	45.1	47.6	48.8	51.3	51.3	53.8
45°	35.0	37.5	38.8	40.0	42.5	45.1	45.1	46.3
47.5°	30.1	32.5	33.8	35.0	36.3	38.8	38.8	41.2
50°	26.2	27.6	28.8	30.1	31.3	33.8	33.8	35.0
52.5°	22.5	23.7	25.0	26.2	27.6	28.8	30.1	31.3
55°	20.0	21.2	21.2	22.5	23.7	25.0	25.0	26.2
57.5°	17.5	18.8	18.8	18.8	20.0	21.2	21.2	22.5
60°	15.0	16.3	16.3	16.3	17.5	17.5	17.5	18.8
62.5°	13.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8
65°	11.3	11.3	11.3	11.3	11.3	11.3	10.1	11.3
67.5°	10.1	10.1	10.1	8.7	8.7	8.7	8.7	8.7
70°	8.7	8.7	8.7	7.5	7.5	7.5	6.2	6.2
72.5°	7.5	7.5	7.5	6.2	6.2	6.2	5.0	5.0
75°	6.2	6.2	6.2	6.2	5.0	5.0	5.0	5.0
77.5°	5.0	5.0	5.0	5.0	5.0	5.0	3.7	3.7
80°	5.0	3.7	3.7	3.7	3.7	3.7	3.7	3.7
82.5°	3.7	3.7	3.7	3.7	2.5	2.5	2.5	2.5
85°	2.5	2.5	2.5	2.5	2.5	2.5	1.2	1.2
87.5°	2.5	1.2	1.2	1.2	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)