

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212320

Luminaire Tested: **LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212320
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2709.1 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212320

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212320

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	27416	27416	27416
5°	60662	25926	18224
10°	242826	22507	15218
15°	559704	17902	13369
20°	835525	12711	11928
25°	1095881	8466	10614
30°	1257979	5347	9273
35°	1153431	3418	8030
40°	945884	2226	6842
45°	548366	1548	5508
50°	155399	1145	4551
55°	14238	1064	3817
60°	2189	1221	3178
65°	573	1169	2315
70°	708	1445	1784
75°	936	1909	1909
80°	0	2845	1395
85°	0	5669	1334

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212320

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.2	1.5
10°-20°	360.3	13.3
20°-30°	877.8	32.4
30°-40°	951.3	35.1
40°-50°	431.0	15.9
50°-60°	33.3	1.2
60°-70°	6.9	0.3
70°-80°	5.1	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1278.2	47.2
0°-40°	2229.6	82.3
0°-60°	2694.0	99.4
0°-90°	2709.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2709.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	283	283	283	283	283	
5°	624	460	267	201	187	112
15°	5581	1826	178	130	133	1622
25°	10252	2622	79	78	99	4673
35°	9753	666	29	45	68	5999
45°	4003	84	11	25	40	3160
55°	84	11	6	15	23	193
65°	2	4	5	10	10	4
75°	2	4	5	8	5	2
85°	0	4	5	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212320

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0
2.5°	423.7	416.2	420.0	410.0	403.6	398.7	401.2	398.7	382.3	378.5	365.9
5°	623.8	612.3	612.3	591.0	568.4	554.6	554.6	538.2	503.0	486.7	460.2
7.5°	1117.9	1095.3	1076.4	1009.8	923.0	873.9	861.4	792.2	703.0	646.4	579.7
10°	2468.5	2374.1	2307.5	2134.0	1901.3	1756.7	1695.1	1456.2	1172.0	958.2	764.6
12.5°	4150.9	4022.7	3905.7	3621.5	3287.1	3059.5	2937.5	2585.4	2033.3	1638.5	1226.0
15°	5580.7	5442.4	5304.1	4958.3	4605.0	4407.6	4183.7	3717.1	2987.8	2427.0	1825.9
17.5°	6754.0	6676.0	6533.9	6027.2	5582.0	5273.9	5041.3	4431.4	3680.6	3040.6	2360.3
20°	8104.6	7912.1	7658.1	7043.2	6434.6	6048.6	5721.6	4978.4	4110.7	3375.1	2643.3
22.5°	9241.4	9104.3	8739.5	7928.5	7033.1	6703.7	6303.8	5409.8	4387.5	3517.2	2676.0
25°	10252.4	10037.3	9579.6	8615.1	7698.4	7137.5	6647.1	5643.7	4489.3	3527.3	2621.8
27.5°	10844.6	10564.3	10026.0	8974.7	7928.5	7308.6	6765.3	5683.9	4425.1	3394.0	2424.4
30°	11245.8	10687.4	10092.6	8978.5	7855.5	7221.8	6658.4	5481.4	4158.5	3089.6	2092.4
32.5°	10584.4	10261.2	9692.8	8621.3	7458.2	6839.6	6280.0	5042.5	3742.3	2638.2	1456.2
35°	9753.1	9491.5	8997.4	7933.5	6862.2	6278.6	5685.1	4479.2	3200.3	1813.3	666.5
37.5°	8787.3	8582.3	8050.5	7078.4	6135.3	5564.5	4969.6	3817.7	2253.4	899.1	404.9
40°	7479.6	7306.0	6869.7	6088.8	5219.8	4676.6	4128.3	2855.7	1223.6	501.7	264.1
42.5°	6147.9	6002.0	5604.7	4929.4	4166.1	3718.4	3235.5	1740.4	608.6	315.6	147.1
45°	4002.6	3820.3	3606.5	3297.1	2919.9	2644.5	2074.9	840.0	360.9	176.1	84.3
47.5°	2294.9	2174.2	1823.4	1438.6	1168.2	1066.4	775.9	391.1	198.7	101.8	51.5
50°	1031.1	953.2	799.8	651.3	471.5	368.5	313.1	196.2	98.1	55.4	35.3
52.5°	254.0	259.0	245.2	215.0	191.1	162.3	140.8	91.8	51.5	33.9	22.6
55°	84.3	85.5	78.0	74.2	67.9	62.8	57.9	41.5	31.4	30.2	11.3
57.5°	30.2	30.2	31.4	28.9	27.7	26.4	25.2	21.4	18.9	11.3	6.3
60°	11.3	11.3	11.3	12.5	12.5	12.5	13.8	12.5	8.8	6.3	5.1
62.5°	5.1	5.1	5.1	5.1	6.3	6.3	7.6	6.3	5.1	5.1	3.7
65°	2.5	2.5	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7	3.7
70°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7	3.7
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7	3.7
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.7
77.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7
80°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7
82.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7
85°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	3.7
87.5°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212320

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0
2.5°	353.4	345.8	330.8	319.5	310.6	309.4	301.8	289.3	284.2	275.4	267.8
5°	435.0	416.2	392.3	369.7	353.4	344.5	318.1	294.3	280.5	266.6	254.0
7.5°	523.1	480.4	438.9	402.4	379.8	365.9	334.5	295.5	270.4	250.3	233.9
10°	633.8	545.8	474.0	417.5	387.4	368.5	330.8	284.2	252.8	228.8	212.6
12.5°	886.5	646.4	506.8	425.0	387.4	360.9	315.6	269.1	233.9	205.0	187.4
15°	1319.2	902.9	601.0	428.8	374.7	344.5	293.0	244.0	208.7	178.5	162.3
17.5°	1726.5	1188.3	750.8	455.2	367.1	320.7	262.8	215.0	178.5	149.6	135.8
20°	1937.8	1330.5	833.7	475.3	354.6	290.5	227.6	183.6	148.4	123.3	111.9
22.5°	1942.8	1317.8	793.5	428.8	308.0	248.9	194.9	150.9	120.7	99.3	90.5
25°	1823.4	1165.7	652.7	334.5	248.9	208.7	162.3	123.3	94.4	79.2	72.9
27.5°	1598.3	943.1	481.6	241.5	194.9	166.0	127.0	94.4	71.6	61.6	57.9
30°	1236.1	583.5	266.6	178.5	147.1	124.5	91.8	62.8	54.1	47.8	45.3
32.5°	613.7	285.4	188.6	127.0	100.6	79.2	57.9	46.6	41.5	37.7	36.5
35°	333.2	205.0	118.2	76.7	60.3	50.3	39.0	32.7	30.2	28.9	28.9
37.5°	232.7	121.9	71.6	46.6	37.7	33.9	27.7	23.8	22.6	22.6	22.6
40°	128.3	72.9	44.0	30.2	25.2	22.6	18.9	17.6	17.6	17.6	18.9
42.5°	74.2	45.3	30.2	21.4	17.6	16.4	13.8	12.5	13.8	13.8	15.1
45°	47.8	33.9	20.1	15.1	12.5	11.3	10.1	10.1	11.3	11.3	12.5
47.5°	33.9	23.8	13.8	10.1	7.6	7.6	7.6	7.6	8.8	10.1	11.3
50°	20.1	12.5	7.6	6.3	5.1	5.1	5.1	6.3	7.6	7.6	8.8
52.5°	11.3	7.6	5.1	5.1	3.7	3.7	5.1	5.1	6.3	7.6	8.8
55°	6.3	5.1	3.7	3.7	3.7	3.7	3.7	5.1	5.1	6.3	7.6
57.5°	5.1	3.7	3.7	3.7	3.7	3.7	3.7	5.1	5.1	6.3	6.3
60°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.1	5.1	6.3	6.3
62.5°	3.7	3.7	3.7	3.7	3.7	3.7	5.1	5.1	5.1	5.1	6.3
65°	3.7	3.7	3.7	5.1	3.7	5.1	5.1	5.1	5.1	5.1	6.3
67.5°	3.7	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1	6.3
70°	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	6.3
72.5°	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	6.3
75°	3.7	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
77.5°	3.7	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
80°	3.7	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
82.5°	3.7	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
85°	3.7	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
87.5°	3.7	3.7	3.7	3.7	5.1	5.1	5.1	5.1	5.1	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212320

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0
2.5°	265.3	256.5	250.3	247.7	242.7	244.0	240.1	237.6	230.1	230.1	225.1
5°	245.2	233.9	226.3	222.6	217.5	216.3	212.6	208.7	201.3	199.9	196.2
7.5°	223.9	212.6	203.7	199.9	194.9	193.7	188.6	186.1	179.8	178.5	174.8
10°	201.3	188.6	181.0	177.3	172.3	172.3	168.5	166.0	160.9	160.9	158.4
12.5°	177.3	166.0	160.9	155.9	153.5	153.5	150.9	148.4	144.6	145.9	144.6
15°	152.2	143.4	138.3	135.8	134.6	134.6	133.3	132.0	129.5	132.0	129.5
17.5°	128.3	121.9	118.2	117.0	115.7	115.7	115.7	117.0	115.7	118.2	118.2
20°	105.7	100.6	98.1	98.1	96.8	99.3	99.3	101.8	101.8	105.7	106.9
22.5°	86.8	82.9	81.7	81.7	81.7	84.3	85.5	88.0	89.3	93.0	95.6
25°	69.2	67.9	67.9	67.9	69.2	71.6	74.2	76.7	78.0	82.9	84.3
27.5°	56.6	55.4	56.6	56.6	57.9	61.6	64.2	66.7	69.2	72.9	75.5
30°	45.3	45.3	46.6	47.8	49.0	51.5	55.4	57.9	60.3	64.2	66.7
32.5°	36.5	37.7	39.0	40.2	40.2	44.0	46.6	50.3	51.5	55.4	57.9
35°	30.2	31.4	32.7	33.9	33.9	37.7	40.2	42.7	45.3	47.8	50.3
37.5°	23.8	25.2	27.7	28.9	28.9	32.7	33.9	36.5	39.0	41.5	44.0
40°	20.1	21.4	23.8	23.8	25.2	27.7	28.9	31.4	33.9	36.5	39.0
42.5°	16.4	17.6	20.1	21.4	21.4	23.8	25.2	27.7	28.9	31.4	32.7
45°	15.1	15.1	17.6	17.6	18.9	20.1	22.6	23.8	25.2	27.7	28.9
47.5°	12.5	13.8	15.1	16.4	16.4	17.6	18.9	20.1	21.4	23.8	25.2
50°	10.1	11.3	13.8	13.8	13.8	16.4	17.6	18.9	18.9	20.1	21.4
52.5°	10.1	10.1	11.3	12.5	12.5	13.8	15.1	16.4	16.4	17.6	18.9
55°	8.8	8.8	10.1	11.3	11.3	12.5	13.8	13.8	15.1	15.1	16.4
57.5°	7.6	8.8	10.1	10.1	10.1	11.3	12.5	12.5	13.8	13.8	15.1
60°	7.6	8.8	8.8	10.1	10.1	11.3	11.3	11.3	12.5	12.5	12.5
62.5°	7.6	7.6	8.8	8.8	8.8	10.1	10.1	11.3	11.3	11.3	11.3
65°	7.6	7.6	8.8	8.8	8.8	10.1	10.1	10.1	10.1	10.1	10.1
67.5°	6.3	7.6	7.6	7.6	8.8	8.8	8.8	8.8	8.8	8.8	8.8
70°	6.3	6.3	7.6	7.6	7.6	8.8	8.8	8.8	8.8	8.8	8.8
72.5°	6.3	6.3	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
75°	6.3	6.3	6.3	6.3	6.3	7.6	7.6	7.6	7.6	6.3	6.3
77.5°	5.1	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	5.1
80°	5.1	5.1	6.3	5.1	6.3	6.3	6.3	6.3	5.1	5.1	5.1
82.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	3.7	3.7
85°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	3.7	3.7	3.7	2.5
87.5°	5.1	5.1	5.1	5.1	5.1	5.1	3.7	3.7	3.7	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212320

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	283.0	283.0	283.0	283.0	283.0	283.0	283.0	283.0
2.5°	222.6	225.1	222.6	225.1	218.8	221.4	223.9	217.5
5°	193.7	191.1	192.4	194.9	189.8	191.1	192.4	187.4
7.5°	173.6	174.8	172.3	174.8	171.0	172.3	173.6	169.7
10°	157.2	158.4	157.2	158.4	154.7	157.2	158.4	154.7
12.5°	142.0	144.6	143.4	145.9	142.0	144.6	147.1	142.0
15°	130.7	133.3	132.0	134.6	132.0	134.6	137.1	133.3
17.5°	119.4	121.9	121.9	124.5	123.3	125.8	128.3	124.5
20°	108.1	111.9	111.9	114.5	114.5	115.7	119.4	115.7
22.5°	98.1	101.8	101.8	104.4	104.4	106.9	109.4	106.9
25°	86.8	91.8	93.0	95.6	95.6	98.1	101.8	99.3
27.5°	79.2	82.9	84.3	86.8	88.0	90.5	93.0	90.5
30°	69.2	74.2	75.5	78.0	79.2	82.9	84.3	82.9
32.5°	61.6	65.4	66.7	69.2	71.6	74.2	76.7	75.5
35°	54.1	57.9	59.1	61.6	62.8	66.7	69.2	67.9
37.5°	47.8	51.5	52.8	54.1	55.4	59.1	61.6	60.3
40°	41.5	44.0	45.3	47.8	49.0	51.5	54.1	54.1
42.5°	36.5	39.0	40.2	41.5	42.7	45.3	47.8	46.6
45°	31.4	33.9	35.3	36.5	37.7	39.0	41.5	40.2
47.5°	26.4	28.9	30.2	31.4	32.7	33.9	36.5	35.3
50°	22.6	25.2	25.2	26.4	27.7	28.9	31.4	30.2
52.5°	20.1	21.4	22.6	22.6	23.8	25.2	27.7	26.4
55°	17.6	18.9	18.9	20.1	20.1	21.4	22.6	22.6
57.5°	15.1	16.4	16.4	17.6	17.6	18.9	20.1	20.1
60°	13.8	13.8	15.1	15.1	15.1	16.4	16.4	16.4
62.5°	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5
65°	10.1	10.1	10.1	10.1	10.1	10.1	10.1	10.1
67.5°	8.8	8.8	8.8	8.8	8.8	7.6	7.6	7.6
70°	7.6	7.6	7.6	7.6	7.6	6.3	6.3	6.3
72.5°	7.6	7.6	6.3	6.3	6.3	6.3	6.3	5.1
75°	6.3	6.3	6.3	6.3	5.1	5.1	5.1	5.1
77.5°	5.1	5.1	5.1	5.1	3.7	3.7	3.7	3.7
80°	5.1	3.7	3.7	3.7	3.7	3.7	3.7	2.5
82.5°	3.7	3.7	3.7	2.5	2.5	2.5	2.5	2.5
85°	2.5	2.5	2.5	2.5	1.2	1.2	1.2	1.2
87.5°	2.5	1.2	1.2	1.2	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)