

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212322

Luminaire Tested: **LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2515.9 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212322

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212322

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	27174	27174	27174
5°	60798	25546	18311
10°	238458	22369	14421
15°	517651	18123	12547
20°	772236	13412	11330
25°	1004415	9449	9855
30°	1123633	6354	8625
35°	1011208	3725	7320
40°	825227	2555	6386
45°	473837	1740	5192
50°	138594	1326	4371
55°	15995	1064	3631
60°	3410	1221	2926
65°	1169	1169	2017
70°	1076	1445	1445
75°	936	1909	1422
80°	0	2845	1395
85°	0	5669	1334

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P1212322

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.2	1.6
10°-20°	344.4	13.7
20°-30°	821.6	32.7
30°-40°	867.1	34.5
40°-50°	393.2	15.6
50°-60°	34.5	1.4
60°-70°	7.2	0.3
70°-80°	4.7	0.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1206.2	47.9
0°-40°	2073.3	82.4
0°-60°	2501.0	99.4
0°-90°	2515.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2515.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	280	280	280	280	280	
5°	625	459	263	202	188	112
15°	5161	1815	181	124	125	1502
25°	9397	2498	88	76	92	4269
35°	8550	690	32	43	62	5280
45°	3459	97	13	24	38	2742
55°	95	15	6	14	22	189
65°	5	5	5	10	9	7
75°	2	2	5	6	4	2
85°	0	2	5	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212322

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5
2.5°	416.9	419.3	408.0	409.3	397.9	403.0	399.1	389.1	381.5	368.8	363.7
5°	625.2	629.1	603.8	596.2	569.7	569.7	558.3	531.8	507.8	478.8	458.6
7.5°	1143.2	1158.4	1082.5	1025.7	942.3	922.1	883.0	792.0	717.4	641.7	584.9
10°	2424.1	2396.3	2239.7	2110.7	1896.0	1816.5	1710.4	1448.9	1208.9	970.1	783.2
12.5°	3822.3	3912.1	3610.1	3505.4	3165.5	3093.5	2867.4	2440.5	2035.0	1613.1	1239.2
15°	5161.4	5187.8	4923.9	4753.3	4339.0	4245.5	3967.7	3466.2	2920.5	2331.9	1815.2
17.5°	6236.4	6342.5	5954.6	5771.5	5233.4	5083.1	4755.8	4145.7	3538.1	2895.2	2282.6
20°	7490.7	7518.5	7058.7	6706.2	6002.7	5774.0	5382.4	4625.8	3902.0	3168.1	2535.2
22.5°	8631.3	8625.0	8033.8	7536.1	6645.5	6372.7	5888.9	4992.1	4150.8	3289.3	2559.2
25°	9396.7	9417.0	8784.2	8195.6	7102.8	6734.0	6188.3	5182.9	4235.5	3285.5	2498.5
27.5°	9804.8	9784.6	9106.2	8477.1	7270.9	6857.7	6265.4	5189.2	4158.4	3156.7	2316.6
30°	10044.8	9774.5	9050.6	8397.6	7157.2	6732.8	6130.2	4989.5	3902.0	2868.7	1992.1
32.5°	9403.1	9298.2	8667.9	7974.4	6765.5	6345.0	5750.0	4565.1	3495.2	2427.8	1427.4
35°	8550.5	8554.2	7939.0	7291.1	6151.7	5785.4	5171.4	4048.5	2998.8	1687.7	689.6
37.5°	7656.1	7668.7	7083.9	6481.3	5467.1	5081.7	4507.0	3459.8	2157.5	858.9	415.6
40°	6525.5	6552.1	6048.1	5564.3	4628.3	4256.9	3744.0	2618.5	1206.4	480.0	281.7
42.5°	5331.9	5364.7	4917.5	4488.0	3692.3	3386.6	2931.8	1621.9	598.8	310.7	165.4
45°	3458.6	3553.3	3221.1	3040.5	2579.5	2397.5	1913.8	827.4	361.3	181.9	97.3
47.5°	1979.4	1980.7	1700.2	1361.6	1116.7	971.3	759.1	376.4	211.0	102.3	59.3
50°	919.6	942.3	746.6	621.5	444.7	376.4	309.5	203.4	111.2	59.3	36.6
52.5°	267.8	283.0	256.4	232.4	197.1	175.6	150.3	99.8	58.1	35.4	22.7
55°	94.7	101.0	94.7	88.4	79.6	72.0	64.4	48.0	32.9	21.5	15.1
57.5°	39.2	40.5	39.2	37.9	35.4	35.4	31.5	26.6	20.2	13.9	10.1
60°	17.6	19.0	17.6	19.0	17.6	17.6	17.6	19.0	12.7	8.8	7.6
62.5°	7.6	8.8	8.8	8.8	8.8	10.1	10.1	8.8	7.6	6.3	5.1
65°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
70°	3.8	3.8	3.8	3.8	3.8	3.8	2.5	2.5	3.8	3.8	3.8
72.5°	3.8	3.8	3.8	3.8	2.5	2.5	2.5	2.5	2.5	3.8	3.8
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
77.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
80°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5
82.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
85°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5
87.5°	0.0	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212322

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5
2.5°	357.5	346.1	328.4	317.1	312.0	304.4	299.3	286.8	281.7	271.5	267.8
5°	439.6	416.9	390.3	368.8	354.9	339.8	317.1	291.8	279.1	262.7	253.9
7.5°	533.0	483.8	437.1	399.1	381.5	361.3	332.2	293.0	269.1	247.6	234.9
10°	651.8	550.8	477.4	416.9	390.3	363.7	328.4	283.0	252.7	227.4	213.5
12.5°	929.7	664.4	514.2	426.9	392.9	360.0	315.8	269.1	233.7	204.6	189.5
15°	1337.7	928.4	612.7	435.8	384.0	343.6	293.0	246.3	209.7	180.7	165.4
17.5°	1699.0	1183.6	749.1	468.6	381.5	324.6	265.2	217.3	181.9	154.1	141.5
20°	1896.0	1317.5	840.0	488.8	370.1	295.6	233.7	188.3	154.1	130.1	118.8
22.5°	1899.9	1309.9	807.2	444.7	325.9	256.4	202.2	159.1	128.8	107.4	98.5
25°	1786.1	1168.4	673.3	349.8	266.6	217.3	169.3	132.7	104.9	88.4	80.8
27.5°	1573.9	949.9	495.2	252.7	208.4	175.6	136.4	106.1	82.2	72.0	65.7
30°	1237.9	618.9	289.3	188.3	161.7	135.1	103.6	74.6	64.4	56.8	51.8
32.5°	664.4	300.6	202.2	139.0	114.9	94.7	68.3	54.4	46.8	41.7	40.5
35°	347.4	219.8	135.1	88.4	73.2	61.9	46.8	37.9	34.1	31.5	31.5
37.5°	248.8	137.6	85.9	56.8	48.0	39.2	32.9	27.8	25.3	25.3	25.3
40°	147.8	84.6	51.8	36.6	31.5	27.8	24.0	20.2	20.2	20.2	20.2
42.5°	89.7	53.0	36.6	25.3	22.7	20.2	17.6	16.4	15.1	15.1	16.4
45°	55.6	36.6	24.0	19.0	17.6	15.1	13.9	12.7	12.7	12.7	13.9
47.5°	35.4	26.6	17.6	12.7	11.4	10.1	8.8	8.8	10.1	10.1	11.4
50°	26.6	16.4	11.4	8.8	7.6	7.6	6.3	7.6	7.6	8.8	10.1
52.5°	15.1	10.1	7.6	6.3	6.3	5.1	5.1	6.3	6.3	7.6	8.8
55°	10.1	7.6	6.3	5.1	5.1	5.1	5.1	5.1	6.3	6.3	7.6
57.5°	7.6	6.3	5.1	5.1	5.1	3.8	5.1	5.1	5.1	6.3	7.6
60°	6.3	5.1	5.1	5.1	5.1	3.8	3.8	5.1	5.1	6.3	6.3
62.5°	5.1	5.1	5.1	5.1	5.1	3.8	5.1	5.1	5.1	5.1	6.3
65°	3.8	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	6.3
67.5°	3.8	3.8	5.1	5.1	5.1	3.8	5.1	5.1	5.1	5.1	6.3
70°	3.8	3.8	3.8	5.1	5.1	3.8	5.1	5.1	5.1	5.1	5.1
72.5°	3.8	3.8	3.8	5.1	5.1	3.8	5.1	5.1	5.1	5.1	5.1
75°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1
77.5°	3.8	3.8	3.8	3.8	5.1	3.8	5.1	5.1	5.1	5.1	5.1
80°	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1	5.1
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1
85°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212322

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5
2.5°	257.6	253.9	246.3	245.1	243.7	238.8	234.9	231.2	231.2	227.4	224.9
5°	238.8	232.4	223.6	219.8	218.5	212.2	207.1	203.4	202.2	198.3	194.5
7.5°	218.5	211.0	200.8	197.1	195.8	189.5	184.4	180.7	178.1	174.4	171.8
10°	197.1	188.3	179.3	175.6	174.4	168.0	164.2	160.5	157.9	155.4	152.9
12.5°	174.4	166.8	157.9	154.1	152.9	147.8	144.0	141.5	140.2	137.6	136.4
15°	151.5	144.0	136.4	133.9	132.7	128.8	126.3	125.1	123.7	123.7	122.5
17.5°	128.8	122.5	116.2	114.9	113.7	111.2	109.9	108.6	109.9	109.9	111.2
20°	107.4	102.3	97.3	97.3	96.0	94.7	94.7	94.7	97.3	98.5	101.0
22.5°	88.4	84.6	80.8	80.8	80.8	80.8	80.8	83.4	85.9	88.4	89.7
25°	73.2	69.5	68.3	68.3	68.3	69.5	70.7	73.2	75.8	78.3	80.8
27.5°	59.3	56.8	56.8	56.8	58.1	59.3	60.7	63.2	66.9	69.5	72.0
30°	48.0	46.8	46.8	48.0	49.3	50.5	53.0	55.6	58.1	60.7	63.2
32.5°	37.9	39.2	39.2	40.5	41.7	42.9	45.4	48.0	50.5	53.0	54.4
35°	31.5	31.5	32.9	34.1	35.4	36.6	39.2	41.7	42.9	45.4	48.0
37.5°	25.3	26.6	27.8	29.0	30.3	31.5	32.9	35.4	36.6	39.2	41.7
40°	21.5	22.7	24.0	25.3	25.3	27.8	27.8	30.3	31.5	34.1	36.6
42.5°	17.6	19.0	20.2	21.5	21.5	22.7	24.0	25.3	27.8	29.0	31.5
45°	13.9	15.1	16.4	17.6	19.0	20.2	20.2	22.7	24.0	25.3	27.8
47.5°	12.7	13.9	15.1	15.1	16.4	17.6	17.6	20.2	21.5	22.7	24.0
50°	10.1	11.4	12.7	13.9	13.9	15.1	16.4	17.6	19.0	20.2	20.2
52.5°	8.8	10.1	11.4	11.4	12.7	13.9	13.9	15.1	16.4	16.4	17.6
55°	8.8	10.1	10.1	11.4	11.4	12.7	12.7	13.9	13.9	15.1	15.1
57.5°	7.6	8.8	8.8	10.1	10.1	11.4	11.4	12.7	12.7	12.7	13.9
60°	7.6	7.6	8.8	8.8	10.1	10.1	10.1	11.4	11.4	11.4	12.7
62.5°	6.3	7.6	7.6	8.8	8.8	8.8	10.1	10.1	10.1	11.4	11.4
65°	6.3	7.6	7.6	8.8	8.8	8.8	8.8	8.8	10.1	10.1	10.1
67.5°	6.3	6.3	7.6	7.6	7.6	7.6	8.8	8.8	8.8	8.8	8.8
70°	6.3	6.3	6.3	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
72.5°	5.1	6.3	6.3	6.3	6.3	7.6	7.6	7.6	7.6	7.6	6.3
75°	5.1	5.1	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
77.5°	5.1	5.1	5.1	6.3	6.3	6.3	6.3	6.3	6.3	5.1	5.1
80°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	3.8
82.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	3.8	3.8	3.8
85°	5.1	3.8	5.1	5.1	5.1	3.8	3.8	3.8	3.8	3.8	2.5
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212322

CATALOG NUMBER: LDSQA4A30935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	280.5	280.5	280.5	280.5	280.5	280.5	280.5	280.5
2.5°	222.3	219.8	221.0	221.0	218.5	217.3	217.3	218.5
5°	192.0	189.5	190.7	190.7	188.3	186.9	186.9	188.3
7.5°	169.3	166.8	168.0	168.0	165.4	165.4	165.4	165.4
10°	151.5	150.3	150.3	150.3	147.8	149.0	147.8	146.6
12.5°	135.1	135.1	135.1	135.1	133.9	135.1	133.9	133.9
15°	122.5	122.5	123.7	123.7	123.7	125.1	125.1	125.1
17.5°	112.4	113.7	114.9	116.2	116.2	117.5	117.5	117.5
20°	102.3	104.9	106.1	107.4	107.4	109.9	108.6	109.9
22.5°	92.2	94.7	96.0	97.3	98.5	99.8	99.8	101.0
25°	83.4	85.9	87.1	88.4	89.7	92.2	92.2	92.2
27.5°	74.6	77.1	78.3	80.8	82.2	84.6	84.6	84.6
30°	65.7	68.3	69.5	70.7	73.2	75.8	75.8	77.1
32.5°	56.8	60.7	61.9	63.2	65.7	68.3	69.5	69.5
35°	50.5	53.0	54.4	56.8	58.1	61.9	61.9	61.9
37.5°	44.2	46.8	49.3	50.5	51.8	54.4	55.6	56.8
40°	39.2	41.7	42.9	44.2	46.8	49.3	50.5	50.5
42.5°	34.1	36.6	37.9	39.2	40.5	42.9	42.9	42.9
45°	30.3	31.5	32.9	34.1	35.4	36.6	37.9	37.9
47.5°	25.3	27.8	27.8	29.0	30.3	32.9	32.9	34.1
50°	21.5	24.0	24.0	25.3	26.6	27.8	29.0	29.0
52.5°	19.0	20.2	21.5	21.5	22.7	24.0	25.3	25.3
55°	16.4	17.6	17.6	19.0	19.0	20.2	21.5	21.5
57.5°	13.9	15.1	16.4	16.4	16.4	17.6	17.6	19.0
60°	12.7	13.9	13.9	13.9	13.9	15.1	15.1	15.1
62.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
65°	10.1	10.1	10.1	10.1	8.8	8.8	8.8	8.8
67.5°	8.8	8.8	8.8	8.8	7.6	7.6	7.6	7.6
70°	7.6	7.6	7.6	7.6	6.3	6.3	6.3	5.1
72.5°	6.3	6.3	6.3	6.3	6.3	5.1	5.1	5.1
75°	6.3	5.1	5.1	5.1	5.1	5.1	3.8	3.8
77.5°	5.1	5.1	5.1	3.8	3.8	3.8	3.8	3.8
80°	3.8	3.8	3.8	3.8	3.8	2.5	2.5	2.5
82.5°	3.8	2.5	2.5	2.5	2.5	2.5	2.5	2.5
85°	2.5	2.5	2.5	2.5	1.2	1.2	1.2	1.2
87.5°	2.5	1.2	1.2	1.2	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)