

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212324

Luminaire Tested: **LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2759.7 lumens
Efficiency: N/A
Efficacy: 69.3 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212324

CATALOG NUMBER: LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212324

CATALOG NUMBER: LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	31194	31194	31194
5°	82027	29718	19410
10°	321611	25714	16152
15°	592089	20259	14312
20°	744010	14320	13021
25°	889925	9449	11608
30°	935850	5929	10179
35°	943396	3583	8811
40°	868098	2403	7499
45°	617621	1740	6220
50°	255215	1326	5139
55°	14711	1284	4493
60°	1705	1221	3681
65°	573	1444	2613
70°	708	1445	1784
75°	936	1909	1909
80°	0	2845	2120
85°	0	5669	2779

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212324

CATALOG NUMBER: LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	1.8
10°-20°	404.4	14.7
20°-30°	836.4	30.3
30°-40°	910.5	33.0
40°-50°	499.2	18.1
50°-60°	43.2	1.6
60°-70°	7.1	0.3
70°-80°	5.1	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.4	46.8
0°-40°	2201.9	79.8
0°-60°	2744.4	99.4
0°-90°	2759.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2759.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	322	322	322	322	322	
5°	844	577	306	211	200	154
15°	5904	2481	202	136	143	1649
25°	8326	3301	88	83	109	3760
35°	7977	903	30	48	74	4896
45°	4508	92	13	27	45	3441
55°	87	10	8	16	27	298
65°	2	4	6	10	11	4
75°	2	4	5	8	5	2
85°	0	2	5	4	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212324

CATALOG NUMBER: LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0
2.5°	506.4	488.7	486.1	488.7	476.1	474.8	477.3	467.3	458.4	449.5	441.9
5°	843.5	806.9	795.5	780.4	742.5	729.9	727.4	686.9	647.8	611.2	577.1
7.5°	1639.1	1565.8	1526.7	1450.9	1334.8	1283.0	1255.2	1122.7	998.9	886.5	784.2
10°	3269.4	3077.4	2984.0	2841.3	2587.5	2462.5	2371.5	2038.2	1709.8	1394.1	1116.3
12.5°	4770.9	4664.8	4527.1	4451.4	4039.6	3881.9	3731.6	3269.4	2769.3	2259.1	1752.7
15°	5903.6	5748.2	5601.7	5566.4	5243.1	5058.8	4892.1	4413.4	3818.7	3169.6	2481.4
17.5°	6569.0	6458.0	6319.1	6252.1	5873.3	5724.2	5534.9	5071.4	4493.0	3846.5	3047.2
20°	7216.9	7052.7	6857.0	6755.9	6336.7	6164.9	5950.2	5462.9	4850.4	4163.5	3364.1
22.5°	7809.1	7597.0	7319.1	7162.6	6691.5	6502.1	6262.2	5734.4	5071.4	4286.0	3390.6
25°	8325.6	8133.6	7763.7	7489.6	6934.0	6710.5	6431.4	5879.6	5151.0	4275.8	3301.0
27.5°	8424.2	8295.3	7963.2	7646.3	7018.7	6769.8	6480.7	5909.9	5095.4	4135.7	3059.7
30°	8366.1	8227.1	7960.6	7637.4	6983.3	6732.0	6431.4	5781.1	4878.2	3808.6	2617.8
32.5°	8225.8	8105.9	7787.6	7446.7	6809.0	6547.6	6230.6	5479.3	4505.6	3288.3	1925.7
35°	7977.1	7796.5	7412.6	7132.2	6532.4	6263.5	5875.8	5076.4	3948.8	2364.0	902.9
37.5°	7470.7	7295.2	7018.7	6759.8	6175.1	5858.1	5449.0	4515.7	2927.2	1289.3	558.1
40°	6864.5	6713.0	6471.8	6220.5	5618.1	5253.3	4802.4	3529.6	1722.5	726.1	343.5
42.5°	6205.4	6048.8	5776.0	5483.1	4826.5	4441.2	3953.9	2284.4	908.0	428.0	186.9
45°	4508.1	4368.0	4169.7	3958.8	3578.7	3301.0	2659.5	1199.6	502.6	227.4	92.2
47.5°	3085.0	2918.3	2552.1	2108.9	1709.8	1462.3	1099.9	520.3	257.6	113.7	54.4
50°	1693.4	1516.6	1329.7	1035.5	693.3	569.5	443.2	251.3	116.2	56.8	30.3
52.5°	415.5	367.5	335.9	309.4	245.0	221.0	186.9	104.9	53.0	31.5	21.5
55°	87.1	80.8	77.1	75.8	69.5	66.9	58.1	40.5	29.0	20.2	10.1
57.5°	25.3	24.0	25.3	25.3	25.3	24.0	24.0	17.6	16.4	10.1	6.3
60°	8.8	8.8	8.8	10.1	10.1	10.1	11.4	11.4	8.8	6.3	5.1
62.5°	3.8	3.8	3.8	5.1	5.1	6.3	6.3	6.3	5.1	5.1	3.8
65°	2.5	2.5	2.5	2.5	3.8	3.8	3.8	3.8	3.8	3.8	3.8
67.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.8
70°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.8
72.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.8
75°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.8
77.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.8
80°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	2.5	2.5	2.5	2.5
82.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
85°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
87.5°	0.0	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212324

CATALOG NUMBER: LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0
2.5°	420.5	407.9	392.7	376.3	373.8	365.0	352.3	334.6	328.4	315.7	304.3
5°	527.8	493.7	458.4	426.8	416.7	402.8	380.1	348.5	328.4	305.6	286.7
7.5°	671.8	593.5	521.5	464.7	447.0	424.3	388.9	348.5	318.2	286.7	261.4
10°	863.8	704.7	580.9	488.7	459.7	429.4	382.6	333.3	298.0	261.4	234.9
12.5°	1233.7	867.5	636.4	501.4	460.9	421.8	362.4	309.4	268.9	232.3	205.9
15°	1754.0	1176.9	748.9	510.2	448.3	400.4	330.9	276.5	236.2	202.0	176.8
17.5°	2193.4	1469.9	899.1	535.4	439.5	372.6	294.3	238.7	199.6	169.2	149.0
20°	2408.1	1601.2	967.3	539.2	414.1	330.9	251.3	198.3	164.2	138.9	121.2
22.5°	2382.9	1557.0	904.1	472.3	349.8	279.1	208.4	160.3	131.3	111.1	98.5
25°	2213.7	1365.0	737.4	361.1	272.8	226.0	162.9	125.0	102.3	88.4	78.3
27.5°	1929.6	1096.1	538.0	255.0	207.1	171.8	121.2	95.9	78.3	68.1	61.9
30°	1486.3	700.8	309.4	183.1	150.3	122.5	91.0	69.5	59.3	53.0	48.0
32.5°	766.5	340.9	205.9	131.3	106.1	88.4	63.2	50.5	44.2	40.5	37.9
35°	420.5	242.5	142.7	84.6	68.1	56.8	42.9	35.4	32.9	30.3	30.3
37.5°	289.2	150.3	79.6	50.5	41.7	35.4	29.0	25.3	24.0	24.0	24.0
40°	166.7	79.6	45.4	31.5	26.6	24.0	20.2	19.0	19.0	19.0	20.2
42.5°	85.9	46.7	30.3	21.5	19.0	16.4	13.9	13.9	13.9	15.1	16.4
45°	50.5	31.5	20.2	13.9	12.7	11.4	10.1	10.1	11.4	12.7	13.9
47.5°	31.5	21.5	12.7	8.8	7.6	7.6	7.6	7.6	8.8	10.1	11.4
50°	21.5	11.4	7.6	5.1	5.1	5.1	5.1	6.3	7.6	8.8	10.1
52.5°	11.4	6.3	5.1	3.8	3.8	3.8	5.1	5.1	6.3	7.6	8.8
55°	6.3	5.1	3.8	3.8	3.8	3.8	3.8	5.1	6.3	7.6	8.8
57.5°	5.1	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	6.3	7.6
60°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	6.3	7.6
62.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	6.3	6.3
65°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	6.3	6.3
67.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	6.3
70°	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1	6.3
72.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1
75°	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1	5.1	6.3
77.5°	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1	5.1
80°	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1	5.1
82.5°	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1	5.1
85°	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1	5.1	5.1
87.5°	3.8	3.8	3.8	3.8	3.8	3.8	5.1	5.1	5.1	5.1	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212324

CATALOG NUMBER: LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0
2.5°	298.0	287.9	277.9	277.9	272.8	265.2	262.6	255.0	250.1	247.5	245.0
5°	272.8	257.6	243.7	242.5	236.2	227.4	223.5	215.9	210.9	208.4	207.1
7.5°	243.7	228.6	214.7	212.1	207.1	200.8	197.0	190.6	188.1	185.7	184.4
10°	215.9	200.8	190.6	188.1	184.4	179.3	175.5	171.8	169.2	167.9	167.9
12.5°	188.1	176.8	167.9	165.4	162.9	159.1	156.6	154.0	152.8	152.8	152.8
15°	162.9	152.8	145.2	145.2	142.7	140.1	140.1	137.6	136.4	137.6	138.9
17.5°	137.6	130.1	123.7	123.7	122.5	121.2	121.2	121.2	122.5	123.7	126.3
20°	113.7	107.4	104.9	104.9	103.5	104.9	104.9	106.1	107.4	111.1	114.9
22.5°	92.2	88.4	85.9	87.1	87.1	88.4	89.6	92.2	94.7	98.5	102.3
25°	74.5	72.0	70.7	72.0	73.2	74.5	77.1	79.6	83.4	87.1	92.2
27.5°	59.3	58.1	58.1	59.3	60.6	63.2	66.9	69.5	73.2	77.1	82.0
30°	48.0	46.7	48.0	50.5	51.8	54.4	56.8	60.6	64.4	68.1	73.2
32.5°	37.9	39.1	40.5	41.7	42.9	46.7	49.3	51.8	55.6	59.3	64.4
35°	31.5	32.9	34.1	35.4	36.6	39.1	41.7	44.2	48.0	51.8	56.8
37.5°	25.3	26.6	27.8	30.3	31.5	32.9	36.6	37.9	41.7	44.2	49.3
40°	21.5	22.7	24.0	25.3	26.6	29.0	31.5	32.9	35.4	39.1	42.9
42.5°	17.6	19.0	20.2	21.5	22.7	25.3	26.6	29.0	31.5	34.1	36.6
45°	15.1	16.4	17.6	19.0	20.2	21.5	22.7	25.3	26.6	29.0	31.5
47.5°	12.7	13.9	16.4	16.4	17.6	19.0	20.2	21.5	24.0	25.3	27.8
50°	11.4	12.7	13.9	15.1	15.1	16.4	17.6	19.0	20.2	21.5	24.0
52.5°	10.1	11.4	12.7	12.7	13.9	15.1	16.4	16.4	17.6	19.0	20.2
55°	8.8	10.1	11.4	11.4	12.7	13.9	13.9	15.1	16.4	16.4	17.6
57.5°	8.8	8.8	10.1	10.1	11.4	11.4	12.7	13.9	13.9	15.1	16.4
60°	7.6	8.8	8.8	10.1	10.1	11.4	11.4	12.7	12.7	13.9	13.9
62.5°	7.6	7.6	8.8	8.8	10.1	10.1	11.4	11.4	11.4	12.7	12.7
65°	7.6	7.6	8.8	8.8	8.8	10.1	10.1	10.1	10.1	11.4	11.4
67.5°	6.3	7.6	7.6	8.8	8.8	8.8	8.8	8.8	10.1	10.1	10.1
70°	6.3	7.6	7.6	7.6	7.6	8.8	8.8	8.8	8.8	8.8	8.8
72.5°	6.3	6.3	6.3	6.3	7.6	7.6	7.6	7.6	7.6	7.6	7.6
75°	6.3	6.3	6.3	6.3	6.3	7.6	7.6	7.6	7.6	7.6	7.6
77.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
80°	5.1	5.1	5.1	5.1	5.1	6.3	5.1	5.1	5.1	5.1	5.1
82.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	3.8	3.8
85°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	3.8	3.8	3.8	3.8
87.5°	5.1	5.1	5.1	3.8	3.8	3.8	3.8	3.8	3.8	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212324

CATALOG NUMBER: LDSQA4A30935D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0
2.5°	241.1	238.7	241.1	238.7	238.7	233.6	237.4	234.9
5°	203.3	200.8	203.3	202.0	199.6	198.3	200.8	199.6
7.5°	181.8	179.3	181.8	181.8	179.3	178.1	180.6	179.3
10°	165.4	164.2	165.4	165.4	164.2	162.9	165.4	164.2
12.5°	151.5	150.3	152.8	152.8	151.5	151.5	154.0	151.5
15°	138.9	138.9	141.5	141.5	141.5	141.5	144.0	142.7
17.5°	126.3	128.8	131.3	132.5	132.5	132.5	135.1	135.1
20°	116.2	118.6	121.2	122.5	123.7	123.7	126.3	126.3
22.5°	104.9	107.4	111.1	112.4	113.7	114.9	117.4	117.4
25°	94.7	97.2	101.0	102.3	104.9	106.1	108.6	108.6
27.5°	84.6	88.4	91.0	93.5	94.7	97.2	99.8	99.8
30°	75.8	79.6	82.0	84.6	85.9	88.4	91.0	91.0
32.5°	66.9	70.7	73.2	75.8	78.3	79.6	83.4	83.4
35°	59.3	61.9	65.7	66.9	69.5	72.0	74.5	74.5
37.5°	51.8	54.4	56.8	59.3	61.9	63.2	65.7	66.9
40°	45.4	48.0	50.5	51.8	54.4	56.8	58.1	59.3
42.5°	39.1	41.7	44.2	45.4	48.0	49.3	51.8	51.8
45°	34.1	36.6	37.9	39.1	41.7	42.9	45.4	45.4
47.5°	29.0	31.5	32.9	34.1	35.4	36.6	39.1	39.1
50°	25.3	26.6	27.8	29.0	30.3	32.9	34.1	34.1
52.5°	21.5	24.0	24.0	25.3	26.6	27.8	29.0	30.3
55°	19.0	20.2	21.5	21.5	22.7	24.0	25.3	26.6
57.5°	16.4	17.6	19.0	19.0	20.2	20.2	21.5	22.7
60°	15.1	15.1	16.4	16.4	16.4	17.6	17.6	19.0
62.5°	12.7	12.7	13.9	13.9	13.9	13.9	13.9	13.9
65°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
67.5°	10.1	10.1	10.1	10.1	8.8	8.8	8.8	8.8
70°	8.8	8.8	8.8	8.8	7.6	7.6	7.6	6.3
72.5°	7.6	7.6	7.6	7.6	6.3	6.3	5.1	5.1
75°	6.3	6.3	6.3	6.3	6.3	5.1	5.1	5.1
77.5°	6.3	5.1	5.1	5.1	5.1	5.1	5.1	3.8
80°	5.1	5.1	3.8	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	2.5	2.5	2.5	2.5
85°	3.8	2.5	2.5	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	1.2	1.2	1.2	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)