

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212338

Luminaire Tested: **LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26801)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2979.6 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.59 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212338

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212338

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74		
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	60		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33684	33684	33684
5°	88571	32091	20947
10°	347246	27770	17441
15°	639287	21884	15445
20°	803329	15464	14062
25°	960879	10208	12538
30°	1010450	6410	10985
35°	1018612	3879	9520
40°	937310	2592	8106
45°	666874	1877	6713
50°	275576	1432	5546
55°	15893	1368	4830
60°	1841	1318	3972
65°	619	1559	2819
70°	765	1530	1926
75°	1011	2021	2021
80°	0	3013	2287
85°	0	6002	3001



TEST NUMBER: P1212338

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.6	1.8
10°-20°	436.6	14.7
20°-30°	903.1	30.3
30°-40°	983.1	33.0
40°-50°	539.0	18.1
50°-60°	46.7	1.6
60°-70°	7.6	0.3
70°-80°	5.4	0.2
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1394.3	46.8
0°-40°	2377.4	79.8
0°-60°	2963.1	99.4
0°-90°	2979.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2979.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	348	348	348	348	348	
5°	911	623	330	228	215	166
15°	6374	2679	218	147	154	1780
25°	8989	3564	96	90	117	4059
35°	8613	975	33	52	80	5286
45°	4868	100	14	29	49	3715
55°	94	11	8	18	29	322
65°	3	4	7	11	12	4
75°	3	4	5	8	5	2
85°	0	3	5	4	3	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212338

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7
2.5°	546.8	527.7	524.9	527.7	514.0	512.7	515.4	504.4	494.9	485.4	477.2
5°	910.8	871.2	859.0	842.6	801.7	788.1	785.3	741.7	699.5	659.9	623.1
7.5°	1769.8	1690.7	1648.4	1566.6	1441.2	1385.3	1355.3	1212.2	1078.5	957.1	846.7
10°	3530.0	3322.8	3221.9	3067.8	2793.8	2658.8	2560.6	2200.7	1846.2	1505.3	1205.3
12.5°	5151.2	5036.6	4888.0	4806.2	4361.8	4191.3	4029.0	3530.0	2990.1	2439.2	1892.5
15°	6374.2	6206.5	6048.3	6010.2	5661.2	5462.1	5282.1	4765.3	4123.1	3422.3	2679.2
17.5°	7092.8	6972.8	6822.8	6750.5	6341.6	6180.6	5976.1	5475.8	4851.2	4153.1	3290.1
20°	7792.3	7615.0	7403.6	7294.6	6841.9	6656.5	6424.7	5898.4	5237.1	4495.4	3632.3
22.5°	8431.7	8202.7	7902.7	7733.6	7225.0	7020.6	6761.5	6191.5	5475.8	4627.6	3661.0
25°	8989.4	8782.1	8382.7	8086.7	7486.8	7245.4	6944.2	6348.3	5561.6	4616.7	3564.1
27.5°	9095.7	8956.6	8598.1	8255.8	7578.2	7309.6	6997.3	6381.0	5501.6	4465.4	3303.7
30°	9033.0	8883.0	8595.3	8246.3	7540.0	7268.7	6944.2	6242.0	5267.0	4112.2	2826.5
32.5°	8881.7	8752.1	8408.6	8040.4	7351.9	7069.6	6727.3	5916.1	4864.9	3550.5	2079.3
35°	8613.1	8418.0	8003.6	7700.9	7053.2	6762.8	6344.3	5481.2	4263.6	2552.4	974.9
37.5°	8066.3	7876.8	7578.2	7298.7	6667.3	6325.2	5883.3	4875.7	3160.5	1392.2	602.6
40°	7411.8	7248.3	6987.8	6716.5	6066.1	5672.0	5185.2	3810.9	1859.8	784.0	370.9
42.5°	6700.1	6531.1	6236.5	5920.2	5211.2	4795.4	4269.0	2466.6	980.4	462.2	201.8
45°	4867.6	4716.3	4502.1	4274.5	3864.0	3564.1	2871.4	1295.3	542.6	245.4	99.6
47.5°	3331.0	3151.0	2755.6	2277.0	1846.2	1578.9	1187.6	561.7	278.1	122.7	58.6
50°	1828.5	1637.5	1435.8	1118.0	748.5	614.9	478.6	271.3	125.4	61.4	32.8
52.5°	448.6	396.7	362.7	334.0	264.5	238.7	201.8	113.1	57.3	34.1	23.2
55°	94.1	87.2	83.2	81.8	75.0	72.3	62.7	43.6	31.4	21.8	11.0
57.5°	27.2	25.9	27.2	27.2	27.2	25.9	25.9	19.1	17.7	11.0	6.8
60°	9.5	9.5	9.5	11.0	11.0	11.0	12.3	12.3	9.5	6.8	5.4
62.5°	4.1	4.1	4.1	5.4	5.4	6.8	6.8	6.8	5.4	5.4	4.1
65°	2.7	2.7	2.7	2.7	4.1	4.1	4.1	4.1	4.1	4.1	4.1
67.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	4.1
70°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	4.1
72.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	4.1
75°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	4.1
77.5°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	2.7	2.7	2.7	4.1
80°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	2.7	2.7	2.7	2.7
82.5°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.7	2.7	2.7
85°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.7	2.7	2.7
87.5°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212338

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7
2.5°	454.0	440.4	424.1	406.3	403.6	394.0	380.4	361.4	354.5	340.9	328.6
5°	570.0	533.1	494.9	460.8	450.0	434.9	410.4	376.3	354.5	330.0	309.5
7.5°	725.3	640.8	563.1	501.7	482.6	458.1	419.9	376.3	343.6	309.5	282.3
10°	932.6	760.8	627.2	527.7	496.3	463.5	413.1	359.9	321.8	282.3	253.6
12.5°	1332.2	936.7	687.2	541.3	497.7	455.4	391.3	334.0	290.4	250.9	222.3
15°	1893.9	1270.8	808.5	550.9	484.0	432.2	357.2	298.5	254.9	218.2	190.9
17.5°	2368.4	1587.1	970.8	578.1	474.5	402.3	317.6	257.6	215.4	182.7	160.9
20°	2600.1	1728.9	1044.5	582.2	447.3	357.2	271.3	214.0	177.3	150.0	130.9
22.5°	2572.9	1681.2	976.2	510.0	377.6	301.4	225.0	173.1	141.8	120.0	106.3
25°	2390.2	1473.9	796.3	390.0	294.5	244.1	175.9	135.0	110.4	95.5	84.5
27.5°	2083.4	1183.4	580.8	275.4	223.6	185.4	130.9	103.6	84.5	73.7	66.8
30°	1604.8	756.8	334.0	197.7	162.3	132.2	98.2	75.0	64.1	57.3	51.9
32.5°	827.6	368.2	222.3	141.8	114.6	95.5	68.1	54.6	47.7	43.6	40.9
35°	454.0	261.8	154.0	91.3	73.7	61.4	46.3	38.2	35.5	32.8	32.8
37.5°	312.2	162.3	85.9	54.6	45.0	38.2	31.4	27.2	25.9	25.9	25.9
40°	180.0	85.9	49.0	34.1	28.6	25.9	21.8	20.5	20.5	20.5	21.8
42.5°	92.7	50.4	32.8	23.2	20.5	17.7	15.0	15.0	15.0	16.4	17.7
45°	54.6	34.1	21.8	15.0	13.7	12.3	11.0	11.0	12.3	13.7	15.0
47.5°	34.1	23.2	13.7	9.5	8.1	8.1	8.1	8.1	9.5	11.0	12.3
50°	23.2	12.3	8.1	5.4	5.4	5.4	5.4	6.8	8.1	9.5	11.0
52.5°	12.3	6.8	5.4	4.1	4.1	4.1	5.4	5.4	6.8	8.1	9.5
55°	6.8	5.4	4.1	4.1	4.1	4.1	4.1	5.4	6.8	8.1	9.5
57.5°	5.4	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	6.8	8.1
60°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	6.8	8.1
62.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	6.8	6.8
65°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	6.8	6.8
67.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	6.8
70°	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4	6.8
72.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4
75°	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4	5.4	6.8
77.5°	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4	5.4
80°	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4	5.4
82.5°	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4	5.4
85°	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4	5.4	5.4
87.5°	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212338

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7
2.5°	321.8	310.9	300.0	300.0	294.5	286.3	283.6	275.4	270.0	267.2	264.5
5°	294.5	278.1	263.2	261.8	254.9	245.4	241.4	233.1	227.7	225.0	223.6
7.5°	263.2	246.8	231.8	229.1	223.6	216.8	212.7	205.9	203.2	200.5	199.1
10°	233.1	216.8	205.9	203.2	199.1	193.6	189.5	185.4	182.7	181.4	181.4
12.5°	203.2	190.9	181.4	178.7	175.9	171.8	169.0	166.3	165.0	165.0	165.0
15°	175.9	165.0	156.8	156.8	154.0	151.3	151.3	148.6	147.2	148.6	150.0
17.5°	148.6	140.5	133.6	133.6	132.2	130.9	130.9	130.9	132.2	133.6	136.4
20°	122.7	115.9	113.1	113.1	111.8	113.1	113.1	114.6	115.9	120.0	124.1
22.5°	99.6	95.5	92.7	94.1	94.1	95.5	96.8	99.6	102.3	106.3	110.4
25°	80.5	77.7	76.4	77.7	79.1	80.5	83.2	85.9	89.9	94.1	99.6
27.5°	64.1	62.7	62.7	64.1	65.4	68.1	72.3	75.0	79.1	83.2	88.6
30°	51.9	50.4	51.9	54.6	55.9	58.6	61.4	65.4	69.5	73.7	79.1
32.5°	40.9	42.3	43.6	45.0	46.3	50.4	53.2	55.9	60.0	64.1	69.5
35°	34.1	35.5	36.8	38.2	39.6	42.3	45.0	47.7	51.9	55.9	61.4
37.5°	27.2	28.6	29.9	32.8	34.1	35.5	39.6	40.9	45.0	47.7	53.2
40°	23.2	24.5	25.9	27.2	28.6	31.4	34.1	35.5	38.2	42.3	46.3
42.5°	19.1	20.5	21.8	23.2	24.5	27.2	28.6	31.4	34.1	36.8	39.6
45°	16.4	17.7	19.1	20.5	21.8	23.2	24.5	27.2	28.6	31.4	34.1
47.5°	13.7	15.0	17.7	17.7	19.1	20.5	21.8	23.2	25.9	27.2	29.9
50°	12.3	13.7	15.0	16.4	16.4	17.7	19.1	20.5	21.8	23.2	25.9
52.5°	11.0	12.3	13.7	13.7	15.0	16.4	17.7	17.7	19.1	20.5	21.8
55°	9.5	11.0	12.3	12.3	13.7	15.0	15.0	16.4	17.7	17.7	19.1
57.5°	9.5	9.5	11.0	11.0	12.3	12.3	13.7	15.0	15.0	16.4	17.7
60°	8.1	9.5	9.5	11.0	11.0	12.3	12.3	13.7	13.7	15.0	15.0
62.5°	8.1	8.1	9.5	9.5	11.0	11.0	12.3	12.3	12.3	13.7	13.7
65°	8.1	8.1	9.5	9.5	9.5	11.0	11.0	11.0	11.0	12.3	12.3
67.5°	6.8	8.1	8.1	9.5	9.5	9.5	9.5	9.5	11.0	11.0	11.0
70°	6.8	8.1	8.1	8.1	8.1	9.5	9.5	9.5	9.5	9.5	9.5
72.5°	6.8	6.8	6.8	6.8	8.1	8.1	8.1	8.1	8.1	8.1	8.1
75°	6.8	6.8	6.8	6.8	6.8	8.1	8.1	8.1	8.1	8.1	8.1
77.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
80°	5.4	5.4	5.4	5.4	5.4	6.8	5.4	5.4	5.4	5.4	5.4
82.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	4.1	4.1
85°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	4.1	4.1	4.1	4.1
87.5°	5.4	5.4	5.4	4.1	4.1	4.1	4.1	4.1	4.1	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212338

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	347.7	347.7	347.7	347.7	347.7	347.7	347.7	347.7
2.5°	260.5	257.6	260.5	257.6	257.6	252.2	256.3	253.6
5°	219.6	216.8	219.6	218.2	215.4	214.0	216.8	215.4
7.5°	196.4	193.6	196.4	196.4	193.6	192.2	194.9	193.6
10°	178.7	177.3	178.7	178.7	177.3	175.9	178.7	177.3
12.5°	163.6	162.3	165.0	165.0	163.6	163.6	166.3	163.6
15°	150.0	150.0	152.7	152.7	152.7	152.7	155.5	154.0
17.5°	136.4	139.1	141.8	143.2	143.2	143.2	145.9	145.9
20°	125.4	128.1	130.9	132.2	133.6	133.6	136.4	136.4
22.5°	113.1	115.9	120.0	121.4	122.7	124.1	126.8	126.8
25°	102.3	105.0	109.0	110.4	113.1	114.6	117.3	117.3
27.5°	91.3	95.5	98.2	100.9	102.3	105.0	107.7	107.7
30°	81.8	85.9	88.6	91.3	92.7	95.5	98.2	98.2
32.5°	72.3	76.4	79.1	81.8	84.5	85.9	89.9	89.9
35°	64.1	66.8	70.9	72.3	75.0	77.7	80.5	80.5
37.5°	55.9	58.6	61.4	64.1	66.8	68.1	70.9	72.3
40°	49.0	51.9	54.6	55.9	58.6	61.4	62.7	64.1
42.5°	42.3	45.0	47.7	49.0	51.9	53.2	55.9	55.9
45°	36.8	39.6	40.9	42.3	45.0	46.3	49.0	49.0
47.5°	31.4	34.1	35.5	36.8	38.2	39.6	42.3	42.3
50°	27.2	28.6	29.9	31.4	32.8	35.5	36.8	36.8
52.5°	23.2	25.9	25.9	27.2	28.6	29.9	31.4	32.8
55°	20.5	21.8	23.2	23.2	24.5	25.9	27.2	28.6
57.5°	17.7	19.1	20.5	20.5	21.8	21.8	23.2	24.5
60°	16.4	16.4	17.7	17.7	17.7	19.1	19.1	20.5
62.5°	13.7	13.7	15.0	15.0	15.0	15.0	15.0	15.0
65°	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
67.5°	11.0	11.0	11.0	11.0	9.5	9.5	9.5	9.5
70°	9.5	9.5	9.5	9.5	8.1	8.1	8.1	6.8
72.5°	8.1	8.1	8.1	8.1	6.8	6.8	5.4	5.4
75°	6.8	6.8	6.8	6.8	6.8	5.4	5.4	5.4
77.5°	6.8	5.4	5.4	5.4	5.4	5.4	5.4	4.1
80°	5.4	5.4	4.1	4.1	4.1	4.1	4.1	4.1
82.5°	4.1	4.1	4.1	4.1	2.7	2.7	2.7	2.7
85°	4.1	2.7	2.7	2.7	2.7	2.7	2.7	2.7
87.5°	2.7	1.4	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)