

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212340

Luminaire Tested: **LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1212340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2768.2 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212340

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212340

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	104	102		103	101	99		99	97	96		96	94	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	91	85	80	97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	71	90	82	76	71		80	74	70		78	73	69		76	72	68
5	86	76	69	64	84	75	68	64		73	67	63		71	66	62		70	65	62
6	80	70	62	57	79	69	62	57		67	61	57		66	60	56		64	59	56
7	75	64	57	52	74	63	56	51		62	56	51		60	55	51		59	54	50
8	70	59	52	47	69	58	51	46		57	51	46		56	50	46		55	50	46
9	66	54	47	42	64	54	47	42		53	46	42		52	46	42		51	45	42
10	62	50	43	38	60	50	43	38		49	42	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33160	33160	33160
5°	77709	31294	21880
10°	307062	27504	18238
15°	568289	22024	16007
20°	728680	16031	14485
25°	871829	11362	12827
30°	927035	7472	11287
35°	950078	4518	9839
40°	869704	2934	8448
45°	627568	2055	6919
50°	273963	1658	5757
55°	18900	1368	4830
60°	3429	1318	3972
65°	1238	1238	2819
70°	1161	1530	1926
75°	1011	2021	2021
80°	0	3013	2287
85°	0	6002	1556



TEST NUMBER: P1212340

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.9	1.8
10°-20°	391.8	14.2
20°-30°	820.3	29.6
30°-40°	913.1	33.0
40°-50°	524.2	18.9
50°-60°	52.4	1.9
60°-70°	8.2	0.3
70°-80°	5.2	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1262.0	45.6
0°-40°	2175.1	78.6
0°-60°	2751.7	99.4
0°-90°	2768.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2768.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	342	342	342	342	342	
5°	799	551	322	235	225	146
15°	5666	2262	220	154	160	1602
25°	8156	3113	106	94	120	3694
35°	8034	951	38	55	83	4905
45°	4581	115	15	30	50	3497
55°	112	16	8	18	29	334
65°	5	4	5	11	12	7
75°	3	3	5	7	5	2
85°	0	3	5	4	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1212340

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3
2.5°	511.4	500.5	489.6	482.7	476.0	485.4	478.7	476.0	456.9	447.3	439.1
5°	799.1	778.7	748.6	724.1	699.6	705.0	685.9	662.7	615.1	580.9	551.0
7.5°	1542.3	1491.9	1399.2	1309.2	1219.2	1202.8	1142.8	1039.1	905.5	804.6	717.3
10°	3121.5	2968.8	2798.3	2614.3	2398.8	2338.8	2190.2	1909.2	1602.3	1251.9	998.2
12.5°	4608.0	4538.4	4338.0	4099.3	3866.2	3722.9	3568.9	3105.1	2618.3	2053.8	1581.9
15°	5666.3	5624.0	5448.1	5231.2	4980.2	4887.6	4699.3	4237.0	3622.0	2947.0	2262.4
17.5°	6450.4	6378.1	6194.0	5958.0	5660.7	5581.7	5356.7	4897.1	4258.9	3581.1	2821.5
20°	7068.2	7023.2	6784.5	6500.9	6144.9	6049.5	5786.3	5307.6	4613.5	3893.4	3120.2
22.5°	7623.2	7546.8	7253.6	6915.4	6509.0	6406.8	6113.5	5588.5	4842.5	4040.7	3173.4
25°	8156.3	8040.5	7684.6	7241.4	6764.1	6625.0	6303.1	5746.7	4927.1	4053.0	3113.4
27.5°	8311.8	8253.2	7924.6	7409.1	6856.7	6700.0	6364.5	5782.2	4895.7	3941.1	2897.9
30°	8287.3	8238.3	7964.1	7425.5	6840.5	6675.4	6334.4	5673.1	4713.0	3649.3	2517.4
32.5°	8209.6	8190.5	7859.2	7283.6	6687.7	6507.7	6139.4	5401.6	4370.7	3204.7	1839.6
35°	8033.6	7958.7	7545.5	7004.1	6431.3	6233.5	5817.6	5013.0	3919.3	2333.3	950.6
37.5°	7518.1	7459.6	7133.6	6659.0	6101.3	5847.6	5408.5	4511.2	3034.3	1326.8	568.6
40°	6877.2	6848.6	6592.2	6168.1	5572.1	5285.8	4808.5	3691.6	1852.0	754.2	375.0
42.5°	6219.9	6211.7	5937.6	5494.4	4848.0	4519.3	4024.4	2490.2	984.6	455.5	216.8
45°	4580.7	4629.8	4438.9	4173.0	3679.3	3440.6	2798.3	1283.2	567.3	252.3	114.6
47.5°	3212.9	3158.4	2820.1	2355.1	1903.7	1611.9	1219.2	606.8	302.7	132.3	65.4
50°	1817.8	1827.4	1521.9	1231.5	807.3	639.6	485.4	305.4	145.9	69.5	39.6
52.5°	474.6	496.4	428.2	368.2	313.7	255.0	205.9	132.3	69.5	40.9	25.9
55°	111.9	115.9	107.7	100.9	95.5	84.5	75.0	57.3	38.2	25.9	16.4
57.5°	39.6	40.9	39.6	39.6	38.2	36.8	34.1	30.1	23.2	16.4	11.0
60°	17.7	19.1	17.7	19.1	19.1	19.1	19.1	19.1	13.7	9.5	6.8
62.5°	8.1	8.1	8.1	8.1	9.5	9.5	11.0	11.0	8.1	6.8	5.4
65°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	4.1
67.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
70°	4.1	4.1	4.1	2.7	2.7	2.7	2.7	2.7	2.7	2.7	4.1
72.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
75°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
77.5°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	2.7	2.7	2.7	2.7
80°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.7	2.7	2.7
82.5°	0.0	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.7	2.7	2.7
85°	0.0	0.0	0.0	0.0	1.4	1.4	1.4	1.4	2.7	2.7	2.7
87.5°	0.0	0.0	0.0	0.0	1.4	1.4	1.4	1.4	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212340

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3
2.5°	424.1	422.7	407.7	396.9	391.4	383.2	373.7	360.0	345.0	331.4	325.9
5°	515.5	497.8	466.4	440.5	428.2	416.0	394.1	369.6	346.3	321.8	309.6
7.5°	634.2	582.3	520.9	473.2	452.8	432.3	400.9	366.8	335.5	302.7	285.0
10°	796.4	676.4	570.1	493.7	463.6	436.4	391.4	349.1	315.0	279.6	256.4
12.5°	1138.7	841.4	621.8	503.2	463.6	428.2	373.7	324.5	286.3	249.5	227.7
15°	1640.5	1136.0	735.1	512.8	454.1	409.1	346.3	293.2	252.3	219.6	199.1
17.5°	2045.5	1407.3	875.5	537.3	441.8	383.2	311.0	255.0	216.8	186.8	170.5
20°	2250.2	1521.9	939.6	541.4	411.9	342.3	268.6	215.5	181.4	155.5	141.8
22.5°	2246.0	1485.0	882.3	474.6	361.4	295.9	226.3	177.3	150.1	129.5	118.6
25°	2104.2	1314.6	736.4	379.1	291.9	245.4	184.1	143.2	121.4	106.3	96.8
27.5°	1838.3	1067.7	549.6	280.9	227.7	193.7	143.2	114.6	96.8	85.9	79.1
30°	1442.8	714.6	346.3	208.6	173.2	145.9	110.5	88.6	76.4	66.8	62.7
32.5°	795.1	372.3	233.2	152.8	126.8	106.3	81.8	64.1	55.9	49.0	47.7
35°	439.1	263.2	166.3	102.3	84.5	72.3	55.9	46.3	40.9	38.2	38.2
37.5°	311.0	169.0	99.6	64.1	54.6	47.7	38.2	32.8	31.4	30.1	30.1
40°	186.8	99.6	60.0	42.3	36.8	32.8	28.6	24.5	24.5	23.2	24.5
42.5°	102.3	60.0	40.9	30.1	25.9	24.5	20.5	19.1	19.1	19.1	20.5
45°	61.4	39.6	28.6	21.8	19.1	16.4	15.0	13.7	15.0	15.0	16.4
47.5°	39.6	28.6	19.1	13.7	12.3	11.0	9.5	11.0	11.0	12.3	13.7
50°	27.2	17.7	12.3	8.1	8.1	6.8	8.1	8.1	9.5	11.0	12.3
52.5°	17.7	12.3	8.1	6.8	5.4	5.4	5.4	6.8	8.1	9.5	11.0
55°	11.0	8.1	6.8	5.4	5.4	5.4	5.4	5.4	6.8	8.1	9.5
57.5°	8.1	6.8	5.4	4.1	4.1	4.1	5.4	5.4	6.8	6.8	8.1
60°	5.4	5.4	4.1	4.1	4.1	4.1	4.1	5.4	5.4	6.8	8.1
62.5°	5.4	5.4	4.1	4.1	4.1	4.1	5.4	5.4	5.4	6.8	6.8
65°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	6.8
67.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	6.8
70°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	6.8
72.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4
75°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4
77.5°	2.7	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4
80°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4
82.5°	2.7	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4
85°	2.7	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4	5.4
87.5°	2.7	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212340

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3
2.5°	319.1	309.6	301.4	304.1	298.7	289.1	286.3	279.6	271.4	270.1	270.1
5°	295.9	280.9	268.6	267.2	261.8	251.0	248.1	241.4	234.6	233.2	231.9
7.5°	267.2	251.0	240.0	237.3	233.2	223.6	222.3	215.5	211.4	208.6	208.6
10°	238.7	223.6	214.1	212.8	210.1	201.8	200.5	195.0	191.0	189.5	188.1
12.5°	211.4	199.1	191.0	189.5	186.8	180.0	178.7	174.6	171.9	170.5	170.5
15°	185.4	174.6	167.7	166.3	165.0	158.2	158.2	155.5	154.1	154.1	155.5
17.5°	159.6	150.1	144.5	143.2	143.2	137.7	139.1	137.7	137.7	137.7	140.5
20°	133.7	125.4	121.4	122.7	120.0	118.6	120.0	120.0	120.0	122.7	126.8
22.5°	111.9	105.0	100.9	102.3	102.3	100.9	102.3	103.6	106.3	110.5	114.6
25°	91.4	85.9	84.5	85.9	85.9	85.9	88.6	91.4	94.1	98.2	102.3
27.5°	73.7	69.5	69.5	71.0	72.3	72.3	76.4	79.1	83.2	87.2	91.4
30°	58.6	57.3	57.3	60.0	60.0	61.4	66.8	69.5	72.3	76.4	80.5
32.5°	46.3	46.3	47.7	50.5	50.5	53.2	57.3	60.0	62.7	66.8	71.0
35°	38.2	39.6	40.9	42.3	43.6	45.0	49.0	51.9	54.6	58.6	61.4
37.5°	31.4	32.8	34.1	36.8	36.8	38.2	42.3	45.0	46.3	50.5	54.6
40°	25.9	27.2	28.6	31.4	31.4	32.8	36.8	38.2	39.6	43.6	47.7
42.5°	21.8	23.2	24.5	25.9	27.2	28.6	31.4	32.8	35.5	38.2	40.9
45°	17.7	19.1	20.5	21.8	23.2	24.5	25.9	28.6	30.1	32.8	35.5
47.5°	15.0	16.4	17.7	19.1	20.5	20.5	23.2	24.5	25.9	28.6	31.4
50°	13.7	15.0	16.4	16.4	17.7	19.1	20.5	21.8	23.2	24.5	27.2
52.5°	11.0	12.3	13.7	15.0	15.0	16.4	17.7	19.1	20.5	21.8	23.2
55°	11.0	11.0	12.3	13.7	13.7	15.0	16.4	17.7	17.7	19.1	20.5
57.5°	9.5	11.0	11.0	12.3	12.3	13.7	15.0	15.0	16.4	16.4	17.7
60°	8.1	9.5	11.0	11.0	11.0	12.3	12.3	13.7	13.7	15.0	15.0
62.5°	8.1	9.5	9.5	11.0	11.0	11.0	12.3	12.3	12.3	13.7	13.7
65°	8.1	8.1	9.5	9.5	9.5	9.5	11.0	11.0	11.0	12.3	12.3
67.5°	6.8	8.1	8.1	8.1	9.5	9.5	9.5	9.5	9.5	11.0	11.0
70°	6.8	6.8	8.1	8.1	8.1	8.1	8.1	9.5	9.5	9.5	9.5
72.5°	6.8	6.8	6.8	6.8	8.1	8.1	8.1	8.1	8.1	8.1	8.1
75°	5.4	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
77.5°	5.4	5.4	5.4	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
80°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
82.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	4.1	4.1
85°	5.4	5.4	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
87.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212340

CATALOG NUMBER: LDSQA4A30940D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	342.3	342.3	342.3	342.3	342.3	342.3	342.3	342.3
2.5°	264.5	261.8	260.5	264.5	259.1	261.8	260.5	261.8
5°	227.7	225.0	223.6	227.7	222.3	225.0	222.3	225.0
7.5°	204.5	203.2	201.8	204.5	200.5	203.2	201.8	203.2
10°	185.4	184.1	182.7	186.8	182.7	185.4	184.1	185.4
12.5°	169.0	169.0	167.7	170.5	167.7	170.5	169.0	170.5
15°	154.1	155.5	154.1	156.8	155.5	158.2	156.8	159.6
17.5°	141.8	143.2	143.2	147.2	145.9	150.1	148.6	150.1
20°	129.5	131.0	132.3	135.0	135.0	139.1	137.7	140.5
22.5°	117.3	120.0	120.0	124.1	124.1	128.1	128.1	129.5
25°	105.0	109.0	110.5	113.2	114.6	118.6	118.6	120.0
27.5°	95.5	98.2	99.6	103.6	105.0	109.0	109.0	111.9
30°	84.5	88.6	90.1	92.8	94.1	98.2	98.2	100.9
32.5°	75.0	77.7	80.5	83.2	84.5	88.6	88.6	91.4
35°	65.4	69.5	71.0	73.7	76.4	80.5	80.5	83.2
37.5°	57.3	61.4	62.7	65.4	68.1	72.3	72.3	75.0
40°	50.5	54.6	55.9	58.6	60.0	65.4	65.4	66.8
42.5°	45.0	47.7	49.0	51.9	53.2	55.9	55.9	58.6
45°	38.2	40.9	42.3	43.6	46.3	49.0	49.0	50.5
47.5°	32.8	35.5	36.8	38.2	39.6	42.3	42.3	45.0
50°	28.6	30.1	31.4	32.8	34.1	36.8	36.8	38.2
52.5°	24.5	25.9	27.2	28.6	30.1	31.4	32.8	34.1
55°	21.8	23.2	23.2	24.5	25.9	27.2	27.2	28.6
57.5°	19.1	20.5	20.5	20.5	21.8	23.2	23.2	24.5
60°	16.4	17.7	17.7	17.7	19.1	19.1	19.1	20.5
62.5°	15.0	15.0	15.0	15.0	15.0	15.0	15.0	15.0
65°	12.3	12.3	12.3	12.3	12.3	12.3	11.0	12.3
67.5°	11.0	11.0	11.0	9.5	9.5	9.5	9.5	9.5
70°	9.5	9.5	9.5	8.1	8.1	8.1	6.8	6.8
72.5°	8.1	8.1	8.1	6.8	6.8	6.8	5.4	5.4
75°	6.8	6.8	6.8	6.8	5.4	5.4	5.4	5.4
77.5°	5.4	5.4	5.4	5.4	5.4	5.4	4.1	4.1
80°	5.4	4.1	4.1	4.1	4.1	4.1	4.1	4.1
82.5°	4.1	4.1	4.1	4.1	2.7	2.7	2.7	2.7
85°	2.7	2.7	2.7	2.7	2.7	2.7	1.4	1.4
87.5°	2.7	1.4	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)