

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219555

Luminaire Tested: **LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2575.5 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219555

CATALOG NUMBER: LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219555

CATALOG NUMBER: LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	81	97	90	84	80	87	83	79		85	81	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	86	76	69	64	85	75	69	64	73	68	63		72	67	63		70
6	81	70	63	58	79	69	62	57	67	61	57		66	61	57		64
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		59
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51
10	62	50	43	38	60	50	43	38	49	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	26941	26941	26941
5°	51589	25653	20820
10°	168695	22743	17716
15°	413096	18775	15656
20°	778360	14330	14041
25°	1302949	10165	12282
30°	1650593	6980	10481
35°	1503987	4529	8893
40°	990487	3225	7537
45°	429065	2137	6206
50°	76109	1492	5139
55°	12228	1199	4307
60°	3023	1085	3313
65°	986	1284	2613
70°	793	1586	2011
75°	1048	1609	1609
80°	0	2399	1562
85°	0	4780	1667



TEST NUMBER: P1219555

CATALOG NUMBER: LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	1.4
10°-20°	286.5	11.1
20°-30°	862.9	33.5
30°-40°	982.2	38.1
40°-50°	363.1	14.1
50°-60°	28.8	1.1
60°-70°	7.8	0.3
70°-80°	5.4	0.2
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1185.1	46.0
0°-40°	2167.2	84.1
0°-60°	2559.2	99.4
0°-90°	2575.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2575.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	278	278	278	278	278	
5°	530	390	264	221	214	86
15°	4119	1391	187	148	156	1292
25°	12190	2034	95	92	115	5564
35°	12717	712	38	52	75	7561
45°	3132	84	16	28	45	2652
55°	72	16	7	17	26	119
65°	4	4	6	11	11	6
75°	3	4	4	7	4	2
85°	0	3	4	4	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1219555

CATALOG NUMBER: LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1
2.5°	357.3	360.4	357.3	351.7	351.7	344.7	341.8	339.0	331.9	327.6	322.0
5°	530.5	522.0	514.9	497.8	492.1	476.5	465.3	449.6	428.4	409.9	390.0
7.5°	907.7	895.0	868.0	817.0	785.7	747.6	717.7	668.1	604.2	551.7	499.2
10°	1714.9	1659.5	1595.7	1480.8	1397.0	1307.8	1236.8	1103.5	943.2	811.4	683.6
12.5°	2763.0	2767.2	2648.2	2453.8	2299.1	2141.8	2019.8	1773.0	1489.3	1241.1	995.7
15°	4118.9	4041.0	3917.7	3619.7	3310.5	3082.2	2887.8	2513.4	2111.9	1749.0	1391.4
17.5°	5547.3	5580.0	5292.0	4805.5	4316.2	3974.3	3680.8	3113.3	2636.8	2187.1	1750.3
20°	7550.1	7326.0	6914.6	6126.1	5365.8	4870.7	4435.3	3699.2	3033.9	2462.3	1971.5
22.5°	9859.2	9497.5	8660.7	7550.1	6399.7	5714.7	5107.6	4094.9	3286.4	2602.7	2046.7
25°	12189.6	11913.1	10579.7	8920.3	7272.1	6384.1	5598.4	4362.9	3407.0	2635.4	2033.9
27.5°	13988.2	13537.2	12018.0	9855.0	7792.6	6744.5	5826.8	4445.2	3381.4	2555.9	1913.5
30°	14755.6	14185.4	12501.6	10067.7	7796.9	6684.9	5713.2	4282.1	3199.9	2354.6	1686.5
32.5°	14281.7	13623.6	11925.8	9479.2	7263.6	6219.6	5275.0	3928.9	2899.2	2038.3	1266.6
35°	12717.3	12062.0	10489.0	8317.5	6412.6	5500.6	4679.3	3468.0	2469.5	1510.6	712.1
37.5°	10413.8	9855.0	8730.2	6971.4	5404.0	4663.7	3980.1	2921.9	1839.7	866.6	357.3
40°	7832.3	7439.5	6764.4	5528.8	4374.3	3811.2	3260.8	2238.2	1117.7	435.4	202.8
42.5°	5429.6	5174.3	4835.3	4090.6	3374.4	2987.1	2546.0	1495.0	574.4	239.7	126.3
45°	3131.8	2971.5	2878.0	2560.2	2280.8	2092.1	1702.1	805.6	290.8	143.2	83.7
47.5°	1383.0	1276.5	1231.2	1097.8	1021.3	970.1	770.2	343.3	156.1	92.2	69.5
50°	505.0	505.0	506.4	445.4	364.5	327.6	256.8	151.7	87.9	72.4	51.0
52.5°	178.8	176.0	182.9	173.0	151.7	136.2	113.6	76.6	54.0	45.3	28.3
55°	72.4	69.5	72.4	68.0	63.9	59.6	52.5	41.2	34.1	28.3	15.6
57.5°	32.7	32.7	34.1	32.7	32.7	29.7	26.9	31.3	24.1	15.6	9.9
60°	15.6	15.6	17.1	17.1	17.1	15.6	15.6	17.1	14.2	9.9	7.1
62.5°	7.1	7.1	8.4	8.4	8.4	8.4	8.4	9.9	7.1	5.6	4.3
65°	4.3	2.8	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
67.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.3	4.3
70°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.3
72.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.3
75°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.3
77.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.8	2.8	4.3
80°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8
82.5°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8
85°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.8	2.8
87.5°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219555

CATALOG NUMBER: LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1
2.5°	316.3	312.0	303.6	299.3	293.6	289.3	286.5	280.9	275.1	270.9	268.1
5°	371.6	356.0	337.6	323.4	312.0	304.9	293.6	283.7	272.3	263.8	256.8
7.5°	452.4	414.1	373.0	344.7	329.1	314.8	294.9	278.1	262.4	251.1	241.2
10°	578.7	496.4	424.1	368.8	341.8	322.0	290.8	266.7	246.8	231.2	221.3
12.5°	788.6	619.8	492.1	398.5	357.3	327.6	283.7	251.1	226.9	211.3	198.6
15°	1076.6	801.3	585.8	434.0	375.9	333.3	272.3	232.5	205.6	187.2	176.0
17.5°	1347.5	991.4	692.2	476.5	394.3	336.1	256.8	208.5	180.1	163.1	151.7
20°	1517.7	1114.9	763.0	500.7	400.1	327.6	235.6	182.9	154.6	139.0	127.6
22.5°	1557.4	1129.0	757.4	478.0	375.9	302.1	205.6	157.5	130.4	116.4	106.4
25°	1499.2	1049.6	678.0	412.8	320.6	253.9	171.6	127.6	107.7	95.1	87.9
27.5°	1353.1	893.7	536.1	310.6	239.7	187.2	130.4	99.3	86.5	76.6	72.4
30°	1090.8	628.4	336.1	192.8	153.1	123.3	93.7	76.6	66.7	62.4	58.1
32.5°	660.9	323.4	177.3	114.9	96.5	83.7	68.0	56.8	51.0	48.2	46.8
35°	314.8	170.1	109.2	78.0	68.0	59.6	49.6	42.5	39.7	38.3	38.3
37.5°	178.8	110.6	73.8	52.5	46.8	41.2	36.9	32.7	31.3	31.3	31.3
40°	113.6	70.8	48.2	38.3	34.1	31.3	28.3	25.5	25.5	25.5	25.5
42.5°	73.8	51.0	36.9	28.3	25.5	24.1	21.3	19.9	19.9	19.9	21.3
45°	58.1	42.5	29.7	22.7	19.9	18.4	17.1	15.6	15.6	15.6	17.1
47.5°	49.6	29.7	19.9	15.6	12.8	12.8	11.4	11.4	11.4	12.8	14.2
50°	29.7	18.4	12.8	9.9	8.4	8.4	8.4	8.4	8.4	9.9	11.4
52.5°	17.1	11.4	8.4	7.1	5.6	5.6	5.6	5.6	7.1	8.4	8.4
55°	11.4	8.4	5.6	5.6	4.3	4.3	4.3	5.6	5.6	7.1	8.4
57.5°	7.1	5.6	4.3	4.3	4.3	4.3	4.3	4.3	5.6	7.1	7.1
60°	5.6	4.3	4.3	4.3	4.3	4.3	4.3	4.3	5.6	5.6	7.1
62.5°	4.3	4.3	5.6	4.3	4.3	4.3	4.3	4.3	5.6	5.6	7.1
65°	4.3	4.3	5.6	5.6	4.3	4.3	4.3	4.3	4.3	5.6	7.1
67.5°	4.3	4.3	5.6	5.6	5.6	5.6	4.3	4.3	4.3	5.6	5.6
70°	4.3	5.6	5.6	5.6	5.6	5.6	5.6	4.3	4.3	5.6	5.6
72.5°	4.3	5.6	5.6	5.6	5.6	5.6	5.6	4.3	4.3	5.6	5.6
75°	4.3	4.3	5.6	5.6	5.6	5.6	5.6	4.3	4.3	4.3	5.6
77.5°	4.3	4.3	5.6	5.6	5.6	5.6	5.6	4.3	4.3	4.3	5.6
80°	4.3	4.3	4.3	5.6	4.3	5.6	4.3	4.3	4.3	4.3	4.3
82.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
85°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
87.5°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219555

CATALOG NUMBER: LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1
2.5°	263.8	261.0	256.8	255.2	256.8	255.2	248.2	246.8	244.0	244.0	244.0
5°	249.6	245.3	239.7	236.9	236.9	234.0	226.9	225.5	221.3	221.3	219.9
7.5°	232.5	226.9	219.9	217.0	217.0	214.1	207.1	204.3	201.4	201.4	200.0
10°	212.7	205.6	198.6	197.2	195.8	191.5	187.2	185.8	181.6	182.9	181.6
12.5°	190.0	184.4	178.8	176.0	176.0	171.6	168.8	167.3	166.0	166.0	166.0
15°	168.8	161.7	156.1	154.6	154.6	153.1	150.3	150.3	147.5	150.3	150.3
17.5°	144.7	139.0	137.6	134.8	136.2	134.8	131.9	133.4	133.4	134.8	136.2
20°	122.0	117.7	116.4	114.9	116.4	116.4	114.9	116.4	117.7	122.0	124.8
22.5°	102.1	99.3	99.3	97.9	99.3	100.7	99.3	102.1	104.9	107.7	112.0
25°	85.1	83.7	83.7	83.7	85.1	86.5	87.9	90.7	92.2	96.5	99.3
27.5°	69.5	69.5	69.5	70.8	72.4	73.8	75.2	79.5	80.8	85.1	87.9
30°	58.1	56.8	58.1	59.6	60.9	63.9	65.2	68.0	69.5	73.8	76.6
32.5°	46.8	48.2	49.6	51.0	52.5	54.0	55.3	58.1	60.9	63.9	66.7
35°	39.7	39.7	41.2	42.5	44.0	46.8	48.2	49.6	52.5	55.3	56.8
37.5°	32.7	34.1	35.5	36.9	38.3	39.7	41.2	42.5	44.0	46.8	49.6
40°	26.9	28.3	29.7	31.3	31.3	34.1	34.1	36.9	38.3	41.2	44.0
42.5°	22.7	24.1	25.5	26.9	26.9	28.3	29.7	31.3	32.7	35.5	38.3
45°	18.4	19.9	21.3	22.7	22.7	24.1	25.5	26.9	28.3	31.3	32.7
47.5°	15.6	17.1	18.4	19.9	19.9	21.3	22.7	24.1	24.1	26.9	28.3
50°	12.8	14.2	15.6	17.1	17.1	18.4	19.9	21.3	21.3	22.7	24.1
52.5°	9.9	11.4	14.2	14.2	15.6	17.1	17.1	18.4	18.4	19.9	21.3
55°	9.9	11.4	12.8	12.8	14.2	15.6	15.6	17.1	17.1	17.1	18.4
57.5°	8.4	9.9	11.4	12.8	12.8	14.2	14.2	14.2	14.2	15.6	15.6
60°	8.4	9.9	9.9	11.4	11.4	12.8	12.8	12.8	12.8	14.2	14.2
62.5°	8.4	8.4	9.9	9.9	11.4	11.4	11.4	12.8	12.8	12.8	12.8
65°	7.1	8.4	9.9	9.9	9.9	11.4	11.4	11.4	11.4	11.4	11.4
67.5°	7.1	8.4	8.4	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
70°	7.1	7.1	8.4	8.4	8.4	9.9	9.9	9.9	8.4	9.9	8.4
72.5°	5.6	7.1	7.1	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
75°	5.6	7.1	7.1	7.1	7.1	8.4	8.4	7.1	7.1	7.1	7.1
77.5°	5.6	5.6	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	5.6
80°	5.6	5.6	5.6	5.6	7.1	7.1	5.6	5.6	5.6	5.6	5.6
82.5°	4.3	5.6	5.6	5.6	5.6	5.6	5.6	5.6	4.3	4.3	4.3
85°	4.3	4.3	5.6	5.6	5.6	5.6	4.3	4.3	4.3	4.3	2.8
87.5°	4.3	4.3	4.3	5.6	4.3	4.3	4.3	4.3	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219555

CATALOG NUMBER: LDSQA4A30950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	278.1	278.1	278.1	278.1	278.1	278.1	278.1	278.1
2.5°	239.7	238.4	239.7	238.4	238.4	239.7	235.6	238.4
5°	217.0	214.1	215.7	214.1	212.7	214.1	211.3	214.1
7.5°	197.2	195.8	195.8	195.8	194.4	195.8	192.8	195.8
10°	180.1	178.8	178.8	178.8	178.8	180.1	177.3	180.1
12.5°	163.1	163.1	164.5	163.1	164.5	166.0	163.1	166.0
15°	148.9	150.3	151.7	151.7	153.1	154.6	153.1	156.1
17.5°	137.6	139.0	141.9	141.9	143.2	146.1	144.7	147.5
20°	126.3	127.6	130.4	130.4	131.9	134.8	133.4	136.2
22.5°	113.6	116.4	117.7	119.2	120.5	123.3	122.0	124.8
25°	100.7	104.9	106.4	107.7	109.2	112.0	112.0	114.9
27.5°	90.7	93.7	95.1	96.5	99.3	102.1	102.1	103.6
30°	79.5	82.3	85.1	86.5	87.9	90.7	90.7	93.7
32.5°	69.5	72.4	73.8	75.2	78.0	80.8	82.3	83.7
35°	59.6	63.9	65.2	68.0	69.5	73.8	73.8	75.2
37.5°	52.5	55.3	58.1	59.6	62.4	65.2	65.2	68.0
40°	46.8	49.6	51.0	52.5	55.3	58.1	58.1	59.6
42.5°	39.7	44.0	45.3	46.8	48.2	51.0	52.5	54.0
45°	35.5	36.9	38.3	39.7	41.2	44.0	44.0	45.3
47.5°	29.7	31.3	32.7	34.1	35.5	36.9	38.3	39.7
50°	25.5	26.9	28.3	28.3	29.7	32.7	32.7	34.1
52.5°	21.3	22.7	24.1	24.1	25.5	28.3	28.3	29.7
55°	18.4	19.9	21.3	21.3	22.7	24.1	24.1	25.5
57.5°	17.1	17.1	18.4	18.4	19.9	19.9	21.3	21.3
60°	14.2	15.6	15.6	15.6	17.1	17.1	17.1	17.1
62.5°	12.8	12.8	12.8	12.8	12.8	12.8	12.8	14.2
65°	11.4	11.4	11.4	11.4	11.4	11.4	9.9	11.4
67.5°	9.9	9.9	9.9	9.9	8.4	8.4	8.4	8.4
70°	8.4	8.4	8.4	8.4	8.4	7.1	7.1	7.1
72.5°	7.1	7.1	7.1	7.1	7.1	5.6	5.6	5.6
75°	7.1	7.1	5.6	5.6	5.6	5.6	5.6	4.3
77.5°	5.6	5.6	5.6	5.6	4.3	4.3	4.3	4.3
80°	4.3	4.3	4.3	4.3	4.3	4.3	2.8	2.8
82.5°	4.3	2.8	2.8	2.8	2.8	2.8	2.8	2.8
85°	2.8	2.8	2.8	2.8	1.5	1.5	1.5	1.5
87.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)