

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212350

Luminaire Tested: **LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212350
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2769.5 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212350

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212350

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	106	104	110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	87	85
3	99	91	86	81	97	90	85	80		87	83	79		85	81	78		82	79	76
4	93	84	77	72	91	83	76	72		80	75	71		78	74	70		76	72	69
5	87	77	70	65	85	76	69	64		74	68	64		72	67	63		70	66	63
6	81	70	63	58	79	69	63	58		68	62	57		66	61	57		65	60	57
7	76	65	57	52	74	64	57	52		62	56	52		61	56	52		60	55	51
8	71	59	52	47	69	59	52	47		58	51	47		57	51	47		55	50	47
9	66	55	48	43	65	54	48	43		53	47	43		52	47	43		51	46	42
10	62	51	44	39	61	50	44	39		49	43	39		48	43	39		48	42	39

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	29896	29896	29896
5°	66924	28123	20149
10°	262490	24622	15867
15°	569834	19938	13810
20°	850092	14763	12474
25°	1105694	10411	10849
30°	1236926	7003	9497
35°	1113151	4116	8066
40°	908439	2807	7031
45°	521610	1904	5713
50°	152565	1462	4808
55°	17616	1165	4003
60°	3759	1337	3236
65°	1261	1261	2223
70°	1190	1558	1558
75°	1048	2059	1572
80°	0	3068	1562
85°	0	6113	1667

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212350

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.2	1.6
10°-20°	379.1	13.7
20°-30°	904.4	32.7
30°-40°	954.5	34.5
40°-50°	432.9	15.6
50°-60°	38.0	1.4
60°-70°	7.9	0.3
70°-80°	5.2	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1327.8	47.9
0°-40°	2282.3	82.4
0°-60°	2753.1	99.4
0°-90°	2769.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2769.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	309	309	309	309	309	
5°	688	505	289	222	207	124
15°	5682	1998	199	136	138	1653
25°	10344	2750	97	83	102	4699
35°	9412	759	35	47	68	5813
45°	3807	107	14	26	42	3018
55°	104	17	7	15	24	208
65°	6	6	6	11	10	7
75°	3	3	6	7	4	2
85°	0	3	6	4	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1212350

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6
2.5°	458.9	461.6	449.1	450.6	437.9	443.6	439.4	428.2	420.0	406.0	400.5
5°	688.2	692.5	664.6	656.3	627.1	627.1	614.6	585.4	559.0	527.1	504.7
7.5°	1258.4	1275.1	1191.7	1129.1	1037.4	1015.1	972.0	871.8	789.9	706.4	643.9
10°	2668.4	2637.9	2465.4	2323.5	2087.1	1999.6	1882.8	1594.9	1330.7	1067.9	862.1
12.5°	4207.8	4306.5	3974.2	3858.7	3484.7	3405.4	3156.5	2686.5	2240.1	1775.7	1364.1
15°	5681.7	5710.9	5420.2	5232.6	4776.5	4673.6	4367.6	3815.6	3215.0	2566.9	1998.2
17.5°	6865.1	6981.9	6555.0	6353.3	5760.9	5595.5	5235.3	4563.8	3894.8	3187.1	2512.7
20°	8245.9	8276.5	7770.3	7382.3	6607.8	6356.1	5925.1	5092.1	4295.3	3487.5	2790.8
22.5°	9501.5	9494.6	8843.7	8295.9	7315.5	7015.2	6482.6	5495.4	4569.3	3621.0	2817.2
25°	10344.2	10366.4	9669.7	9021.8	7819.0	7412.9	6812.1	5705.4	4662.4	3616.8	2750.5
27.5°	10793.3	10771.2	10024.4	9331.9	8003.9	7549.2	6897.0	5712.3	4577.6	3475.0	2550.2
30°	11057.6	10760.0	9963.1	9244.3	7878.7	7411.5	6748.3	5492.7	4295.3	3157.9	2192.9
32.5°	10351.2	10235.7	9541.9	8778.5	7447.8	6984.7	6329.7	5025.4	3847.7	2672.5	1571.3
35°	9412.5	9416.6	8739.6	8026.2	6772.0	6368.7	5692.9	4456.7	3301.1	1857.7	759.2
37.5°	8428.0	8441.9	7798.1	7134.9	6018.3	5594.1	4961.4	3808.6	2375.1	945.6	457.6
40°	7183.5	7212.7	6657.9	6125.4	5094.9	4686.1	4121.5	2882.6	1327.9	528.4	310.1
42.5°	5869.5	5905.6	5413.3	4940.5	4064.6	3728.1	3227.5	1785.4	659.1	342.0	182.1
45°	3807.3	3911.5	3545.8	3347.0	2839.4	2639.2	2106.6	910.9	397.8	200.2	107.1
47.5°	2179.0	2180.3	1871.6	1499.0	1229.2	1069.3	835.7	414.4	232.2	112.6	65.3
50°	1012.3	1037.4	821.8	684.2	489.5	414.4	340.7	223.9	122.3	65.3	40.4
52.5°	294.7	311.4	282.2	255.9	217.0	193.3	165.4	109.9	64.0	38.9	25.0
55°	104.3	111.3	104.3	97.4	87.7	79.2	71.0	52.9	36.1	23.7	16.7
57.5°	43.1	44.5	43.1	41.7	38.9	38.9	34.8	29.2	22.2	15.3	11.2
60°	19.4	20.9	19.4	20.9	19.4	19.4	19.4	20.9	13.9	9.7	8.2
62.5°	8.2	9.7	9.7	9.7	9.7	11.2	11.2	9.7	8.2	6.9	5.5
65°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
67.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
70°	4.2	4.2	4.2	4.2	4.2	4.2	2.8	2.8	4.2	4.2	4.2
72.5°	4.2	4.2	4.2	4.2	2.8	2.8	2.8	2.8	2.8	4.2	4.2
75°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
77.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.8	2.8	2.8
80°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8
82.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.8	2.8	2.8
85°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8
87.5°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212350

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6
2.5°	393.5	381.1	361.5	349.0	343.5	335.1	329.5	315.7	310.1	298.9	294.7
5°	483.9	458.9	429.7	406.0	390.8	374.1	349.0	321.3	307.3	289.2	279.5
7.5°	586.8	532.5	481.2	439.4	420.0	397.8	365.7	322.6	296.2	272.5	258.6
10°	717.6	606.3	525.6	458.9	429.7	400.5	361.5	311.4	278.1	250.3	234.9
12.5°	1023.5	731.4	566.0	470.0	432.5	396.3	347.7	296.2	257.3	225.2	208.6
15°	1472.6	1022.0	674.4	479.8	422.7	378.1	322.6	271.2	230.9	198.8	182.1
17.5°	1870.2	1303.0	824.5	515.9	420.0	357.4	292.0	239.1	200.2	169.7	155.7
20°	2087.1	1450.4	924.7	538.1	407.5	325.4	257.3	207.2	169.7	143.2	130.7
22.5°	2091.4	1442.0	888.6	489.5	358.7	282.2	222.4	175.1	141.8	118.3	108.4
25°	1966.3	1286.3	741.1	385.1	293.4	239.1	186.3	146.0	115.3	97.4	89.0
27.5°	1732.7	1045.7	545.0	278.1	229.4	193.3	150.2	116.8	90.4	79.2	72.3
30°	1362.8	681.3	318.4	207.2	178.0	148.8	114.0	82.0	71.0	62.6	57.0
32.5°	731.4	331.0	222.4	152.9	126.5	104.3	75.0	59.8	51.5	45.8	44.5
35°	382.4	241.9	148.8	97.4	80.7	68.2	51.5	41.7	37.6	34.8	34.8
37.5°	274.0	151.5	94.6	62.6	52.9	43.1	36.1	30.6	27.9	27.9	27.9
40°	162.6	93.1	57.0	40.4	34.8	30.6	26.4	22.2	22.2	22.2	22.2
42.5°	98.7	58.3	40.4	27.9	25.0	22.2	19.4	18.1	16.7	16.7	18.1
45°	61.2	40.4	26.4	20.9	19.4	16.7	15.3	13.9	13.9	13.9	15.3
47.5°	38.9	29.2	19.4	13.9	12.5	11.2	9.7	9.7	11.2	11.2	12.5
50°	29.2	18.1	12.5	9.7	8.2	8.2	6.9	8.2	8.2	9.7	11.2
52.5°	16.7	11.2	8.2	6.9	6.9	5.5	5.5	6.9	6.9	8.2	9.7
55°	11.2	8.2	6.9	5.5	5.5	5.5	5.5	5.5	6.9	6.9	8.2
57.5°	8.2	6.9	5.5	5.5	5.5	4.2	5.5	5.5	5.5	6.9	8.2
60°	6.9	5.5	5.5	5.5	5.5	4.2	4.2	5.5	5.5	6.9	6.9
62.5°	5.5	5.5	5.5	5.5	5.5	4.2	5.5	5.5	5.5	5.5	6.9
65°	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.9
67.5°	4.2	4.2	5.5	5.5	5.5	4.2	5.5	5.5	5.5	5.5	6.9
70°	4.2	4.2	4.2	5.5	5.5	4.2	5.5	5.5	5.5	5.5	5.5
72.5°	4.2	4.2	4.2	5.5	5.5	4.2	5.5	5.5	5.5	5.5	5.5
75°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5
77.5°	4.2	4.2	4.2	4.2	5.5	4.2	5.5	5.5	5.5	5.5	5.5
80°	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5	5.5
82.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5
85°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5
87.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212350

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6
2.5°	283.7	279.5	271.2	269.7	268.3	262.8	258.6	254.6	254.6	250.3	247.5
5°	262.8	255.9	246.1	241.9	240.6	233.6	228.1	223.9	222.4	218.3	214.2
7.5°	240.6	232.2	221.1	217.0	215.5	208.6	203.0	198.8	196.1	191.8	189.1
10°	217.0	207.2	197.5	193.3	191.8	184.9	180.8	176.6	173.8	171.1	168.2
12.5°	191.8	183.6	173.8	169.7	168.2	162.6	158.5	155.7	154.4	151.5	150.2
15°	166.9	158.5	150.2	147.5	146.0	141.8	139.0	137.7	136.3	136.3	134.8
17.5°	141.8	134.8	128.0	126.5	125.1	122.3	121.0	119.6	121.0	121.0	122.3
20°	118.3	112.6	107.1	107.1	105.6	104.3	104.3	104.3	107.1	108.4	111.3
22.5°	97.4	93.1	89.0	89.0	89.0	89.0	89.0	91.7	94.6	97.4	98.7
25°	80.7	76.5	75.0	75.0	75.0	76.5	77.9	80.7	83.4	86.2	89.0
27.5°	65.3	62.6	62.6	62.6	64.0	65.3	66.7	69.5	73.7	76.5	79.2
30°	52.9	51.5	51.5	52.9	54.2	55.6	58.3	61.2	64.0	66.7	69.5
32.5°	41.7	43.1	43.1	44.5	45.8	47.3	50.1	52.9	55.6	58.3	59.8
35°	34.8	34.8	36.1	37.6	38.9	40.4	43.1	45.8	47.3	50.1	52.9
37.5°	27.9	29.2	30.6	31.9	33.4	34.8	36.1	38.9	40.4	43.1	45.8
40°	23.7	25.0	26.4	27.9	27.9	30.6	30.6	33.4	34.8	37.6	40.4
42.5°	19.4	20.9	22.2	23.7	23.7	25.0	26.4	27.9	30.6	31.9	34.8
45°	15.3	16.7	18.1	19.4	20.9	22.2	22.2	25.0	26.4	27.9	30.6
47.5°	13.9	15.3	16.7	16.7	18.1	19.4	19.4	22.2	23.7	25.0	26.4
50°	11.2	12.5	13.9	15.3	15.3	16.7	18.1	19.4	20.9	22.2	22.2
52.5°	9.7	11.2	12.5	12.5	13.9	15.3	15.3	16.7	18.1	18.1	19.4
55°	9.7	11.2	11.2	12.5	12.5	13.9	13.9	15.3	15.3	16.7	16.7
57.5°	8.2	9.7	9.7	11.2	11.2	12.5	12.5	13.9	13.9	13.9	15.3
60°	8.2	8.2	9.7	9.7	11.2	11.2	11.2	12.5	12.5	12.5	13.9
62.5°	6.9	8.2	8.2	9.7	9.7	9.7	11.2	11.2	11.2	12.5	12.5
65°	6.9	8.2	8.2	9.7	9.7	9.7	9.7	9.7	11.2	11.2	11.2
67.5°	6.9	6.9	8.2	8.2	8.2	8.2	9.7	9.7	9.7	9.7	9.7
70°	6.9	6.9	6.9	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
72.5°	5.5	6.9	6.9	6.9	6.9	8.2	8.2	8.2	8.2	8.2	6.9
75°	5.5	5.5	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
77.5°	5.5	5.5	5.5	6.9	6.9	6.9	6.9	6.9	6.9	5.5	5.5
80°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.2
82.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.2	4.2	4.2
85°	5.5	4.2	5.5	5.5	5.5	4.2	4.2	4.2	4.2	4.2	2.8
87.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212350

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	308.6	308.6	308.6	308.6	308.6	308.6	308.6	308.6
2.5°	244.8	241.9	243.4	243.4	240.6	239.1	239.1	240.6
5°	211.4	208.6	209.9	209.9	207.2	205.8	205.8	207.2
7.5°	186.3	183.6	184.9	184.9	182.1	182.1	182.1	182.1
10°	166.9	165.4	165.4	165.4	162.6	164.1	162.6	161.3
12.5°	148.8	148.8	148.8	148.8	147.5	148.8	147.5	147.5
15°	134.8	134.8	136.3	136.3	136.3	137.7	137.7	137.7
17.5°	123.8	125.1	126.5	128.0	128.0	129.3	129.3	129.3
20°	112.6	115.3	116.8	118.3	118.3	121.0	119.6	121.0
22.5°	101.5	104.3	105.6	107.1	108.4	109.9	109.9	111.3
25°	91.7	94.6	95.9	97.4	98.7	101.5	101.5	101.5
27.5°	82.0	84.9	86.2	89.0	90.4	93.1	93.1	93.1
30°	72.3	75.0	76.5	77.9	80.7	83.4	83.4	84.9
32.5°	62.6	66.7	68.2	69.5	72.3	75.0	76.5	76.5
35°	55.6	58.3	59.8	62.6	64.0	68.2	68.2	68.2
37.5°	48.6	51.5	54.2	55.6	57.0	59.8	61.2	62.6
40°	43.1	45.8	47.3	48.6	51.5	54.2	55.6	55.6
42.5°	37.6	40.4	41.7	43.1	44.5	47.3	47.3	47.3
45°	33.4	34.8	36.1	37.6	38.9	40.4	41.7	41.7
47.5°	27.9	30.6	30.6	31.9	33.4	36.1	36.1	37.6
50°	23.7	26.4	26.4	27.9	29.2	30.6	31.9	31.9
52.5°	20.9	22.2	23.7	23.7	25.0	26.4	27.9	27.9
55°	18.1	19.4	19.4	20.9	20.9	22.2	23.7	23.7
57.5°	15.3	16.7	18.1	18.1	18.1	19.4	19.4	20.9
60°	13.9	15.3	15.3	15.3	15.3	16.7	16.7	16.7
62.5°	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5
65°	11.2	11.2	11.2	11.2	9.7	9.7	9.7	9.7
67.5°	9.7	9.7	9.7	9.7	8.2	8.2	8.2	8.2
70°	8.2	8.2	8.2	8.2	6.9	6.9	6.9	5.5
72.5°	6.9	6.9	6.9	6.9	6.9	5.5	5.5	5.5
75°	6.9	5.5	5.5	5.5	5.5	5.5	4.2	4.2
77.5°	5.5	5.5	5.5	4.2	4.2	4.2	4.2	4.2
80°	4.2	4.2	4.2	4.2	4.2	2.8	2.8	2.8
82.5°	4.2	2.8	2.8	2.8	2.8	2.8	2.8	2.8
85°	2.8	2.8	2.8	2.8	1.5	1.5	1.5	1.5
87.5°	2.8	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)