

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212348

Luminaire Tested: **LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26800)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2982.2 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 2.38 / 0.59 / 1.18
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212348

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212348

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41		
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	30167	30167	30167
5°	66769	28532	20062
10°	267310	24779	16752
15°	616149	19718	14723
20°	919762	13979	13124
25°	1206374	9321	11694
30°	1384808	5884	10213
35°	1269720	3761	8846
40°	1041249	2441	7524
45°	603647	1713	6069
50°	171073	1236	5004
55°	15674	1165	4222
60°	2422	1337	3488
65°	642	1261	2521
70°	793	1558	1954
75°	1048	2059	2059
80°	0	3068	1562
85°	0	6113	1667



TEST NUMBER: P1212348

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.2	1.5
10°-20°	396.6	13.3
20°-30°	966.3	32.4
30°-40°	1047.2	35.1
40°-50°	474.5	15.9
50°-60°	36.7	1.2
60°-70°	7.6	0.3
70°-80°	5.6	0.2
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1407.1	47.2
0°-40°	2454.3	82.3
0°-60°	2965.6	99.4
0°-90°	2982.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2982.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	311	311	311	311	311	
5°	687	507	293	222	206	124
15°	6144	2010	197	143	147	1785
25°	11286	2886	87	86	109	5144
35°	10736	734	32	50	75	6604
45°	4406	93	12	28	44	3479
55°	93	12	7	17	25	212
65°	3	4	6	11	11	5
75°	3	4	6	8	6	2
85°	0	4	6	4	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1212348

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4
2.5°	466.5	458.2	462.4	451.2	444.4	438.9	441.6	438.9	420.8	416.7	402.9
5°	686.6	674.1	674.1	650.6	625.8	610.5	610.5	592.5	553.7	535.7	506.7
7.5°	1230.6	1205.7	1184.9	1111.5	1016.1	962.1	948.2	872.1	773.8	711.5	638.2
10°	2717.4	2613.5	2540.1	2349.1	2093.1	1933.8	1866.0	1602.9	1290.1	1054.8	841.6
12.5°	4569.6	4428.3	4299.6	3986.7	3618.5	3367.9	3233.6	2846.1	2238.4	1803.8	1349.6
15°	6143.5	5991.2	5838.9	5458.2	5069.3	4851.9	4605.4	4091.9	3289.1	2671.7	2010.1
17.5°	7435.0	7349.1	7192.7	6634.8	6144.8	5805.6	5549.5	4878.2	4051.7	3347.1	2598.3
20°	8921.7	8709.8	8430.3	7753.4	7083.4	6658.4	6298.5	5480.3	4525.1	3715.5	2909.7
22.5°	10173.1	10022.2	9620.7	8727.9	7742.2	7379.6	6939.4	5955.2	4829.8	3871.8	2945.7
25°	11286.1	11049.3	10545.4	9483.6	8474.5	7857.2	7317.3	6212.6	4941.8	3882.9	2886.2
27.5°	11938.0	11629.3	11036.8	9879.6	8727.9	8045.3	7447.4	6256.9	4871.3	3736.2	2668.9
30°	12379.6	11765.0	11110.2	9883.8	8647.6	7950.0	7329.8	6034.0	4577.8	3401.1	2303.4
32.5°	11651.5	11295.7	10670.0	9490.7	8210.2	7529.1	6913.1	5551.0	4119.7	2904.2	1602.9
35°	10736.4	10448.6	9904.6	8733.4	7554.0	6911.6	6258.3	4930.8	3523.0	1996.1	733.6
37.5°	9673.3	9447.7	8862.1	7792.2	6753.8	6125.5	5470.7	4202.7	2480.5	989.7	445.7
40°	8233.7	8042.6	7562.4	6702.7	5746.1	5148.1	4544.6	3143.7	1346.8	552.2	290.7
42.5°	6767.8	6607.2	6169.7	5426.5	4586.2	4093.4	3561.7	1915.8	670.0	347.4	162.0
45°	4406.1	4205.5	3970.1	3629.6	3214.3	2911.2	2284.0	924.7	397.2	193.8	92.8
47.5°	2526.3	2393.5	2007.3	1583.7	1286.0	1173.9	854.1	430.5	218.8	112.1	56.8
50°	1135.1	1049.2	880.4	717.1	519.2	405.7	344.6	215.9	108.0	61.0	38.8
52.5°	279.6	285.1	269.9	236.7	210.4	178.6	155.1	101.0	56.8	37.3	25.0
55°	92.8	94.1	85.8	81.8	74.8	69.3	63.7	45.7	34.5	33.2	12.5
57.5°	33.2	33.2	34.5	31.8	30.5	29.1	27.7	23.5	20.7	12.5	6.9
60°	12.5	12.5	12.5	13.8	13.8	13.8	15.3	13.8	9.7	6.9	5.5
62.5°	5.5	5.5	5.5	5.5	6.9	6.9	8.2	6.9	5.5	5.5	4.2
65°	2.8	2.8	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2
67.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.2	4.2
70°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.2	4.2
72.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.2	4.2
75°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	4.2
77.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8	4.2
80°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8	4.2
82.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8	4.2
85°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	4.2
87.5°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212348

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4
2.5°	388.9	380.7	364.1	351.6	341.9	340.6	332.2	318.4	312.9	303.2	294.8
5°	479.0	458.2	431.9	407.0	388.9	379.4	350.2	323.9	308.6	293.4	279.6
7.5°	575.8	528.7	483.2	443.0	418.1	402.9	368.2	325.4	297.6	275.4	257.4
10°	697.7	600.8	521.9	459.6	426.4	405.7	364.1	312.9	278.3	251.9	233.9
12.5°	975.9	711.5	557.9	467.9	426.4	397.2	347.4	296.2	257.4	225.6	206.3
15°	1452.1	993.9	661.7	472.0	412.4	379.4	322.6	268.6	229.8	196.6	178.6
17.5°	1900.6	1308.1	826.4	501.1	404.2	353.0	289.4	236.7	196.6	164.8	149.5
20°	2133.1	1464.6	917.8	523.3	390.4	319.8	250.6	202.1	163.3	135.6	123.2
22.5°	2138.7	1450.8	873.4	472.0	339.2	274.1	214.5	166.1	132.9	109.4	99.7
25°	2007.3	1283.3	718.5	368.2	274.1	229.8	178.6	135.6	103.8	87.2	80.3
27.5°	1759.4	1038.2	530.2	265.8	214.5	182.8	139.8	103.8	78.8	67.8	63.7
30°	1360.8	642.3	293.4	196.6	162.0	137.0	101.0	69.3	59.5	52.6	49.8
32.5°	675.5	314.2	207.6	139.8	110.7	87.2	63.7	51.2	45.7	41.5	40.2
35°	366.9	225.6	130.1	84.5	66.5	55.3	43.0	36.0	33.2	31.8	31.8
37.5°	256.1	134.3	78.8	51.2	41.5	37.3	30.5	26.3	25.0	25.0	25.0
40°	141.3	80.3	48.5	33.2	27.7	25.0	20.7	19.3	19.3	19.3	20.7
42.5°	81.8	49.8	33.2	23.5	19.3	18.0	15.3	13.8	15.3	15.3	16.6
45°	52.6	37.3	22.2	16.6	13.8	12.5	11.0	11.0	12.5	12.5	13.8
47.5°	37.3	26.3	15.3	11.0	8.2	8.2	8.2	8.2	9.7	11.0	12.5
50°	22.2	13.8	8.2	6.9	5.5	5.5	5.5	6.9	8.2	8.2	9.7
52.5°	12.5	8.2	5.5	5.5	4.2	4.2	5.5	5.5	6.9	8.2	9.7
55°	6.9	5.5	4.2	4.2	4.2	4.2	4.2	5.5	5.5	6.9	8.2
57.5°	5.5	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	6.9	6.9
60°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	6.9	6.9
62.5°	4.2	4.2	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5	6.9
65°	4.2	4.2	4.2	5.5	4.2	5.5	5.5	5.5	5.5	5.5	6.9
67.5°	4.2	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.9
70°	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.9
72.5°	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.9
75°	4.2	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
77.5°	4.2	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
80°	4.2	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
82.5°	4.2	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
85°	4.2	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
87.5°	4.2	4.2	4.2	4.2	5.5	5.5	5.5	5.5	5.5	5.5	5.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212348

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4
2.5°	292.1	282.4	275.4	272.7	267.1	268.6	264.4	261.6	253.3	253.3	247.8
5°	269.9	257.4	249.1	245.1	239.5	238.1	233.9	229.8	221.6	220.1	215.9
7.5°	246.4	233.9	224.3	220.1	214.5	213.2	207.6	204.8	197.9	196.6	192.4
10°	221.6	207.6	199.4	195.1	189.6	189.6	185.6	182.8	177.1	177.1	174.4
12.5°	195.1	182.8	177.1	171.6	168.8	168.8	166.1	163.3	159.3	160.6	159.3
15°	167.5	157.8	152.3	149.5	148.1	148.1	146.8	145.3	142.6	145.3	142.6
17.5°	141.3	134.3	130.1	128.8	127.3	127.3	127.3	128.8	127.3	130.1	130.1
20°	116.3	110.7	108.0	108.0	106.6	109.4	109.4	112.1	112.1	116.3	117.6
22.5°	95.6	91.3	90.0	90.0	90.0	92.8	94.1	96.9	98.3	102.5	105.3
25°	76.1	74.8	74.8	74.8	76.1	78.8	81.8	84.5	85.8	91.3	92.8
27.5°	62.3	61.0	62.3	62.3	63.7	67.8	70.6	73.3	76.1	80.3	83.1
30°	49.8	49.8	51.2	52.6	54.0	56.8	61.0	63.7	66.5	70.6	73.3
32.5°	40.2	41.5	43.0	44.3	44.3	48.5	51.2	55.3	56.8	61.0	63.7
35°	33.2	34.5	36.0	37.3	37.3	41.5	44.3	47.0	49.8	52.6	55.3
37.5°	26.3	27.7	30.5	31.8	31.8	36.0	37.3	40.2	43.0	45.7	48.5
40°	22.2	23.5	26.3	26.3	27.7	30.5	31.8	34.5	37.3	40.2	43.0
42.5°	18.0	19.3	22.2	23.5	23.5	26.3	27.7	30.5	31.8	34.5	36.0
45°	16.6	16.6	19.3	19.3	20.7	22.2	25.0	26.3	27.7	30.5	31.8
47.5°	13.8	15.3	16.6	18.0	18.0	19.3	20.7	22.2	23.5	26.3	27.7
50°	11.0	12.5	15.3	15.3	15.3	18.0	19.3	20.7	20.7	22.2	23.5
52.5°	11.0	11.0	12.5	13.8	13.8	15.3	16.6	18.0	18.0	19.3	20.7
55°	9.7	9.7	11.0	12.5	12.5	13.8	15.3	15.3	16.6	16.6	18.0
57.5°	8.2	9.7	11.0	11.0	11.0	12.5	13.8	13.8	15.3	15.3	16.6
60°	8.2	9.7	9.7	11.0	11.0	12.5	12.5	12.5	13.8	13.8	13.8
62.5°	8.2	8.2	9.7	9.7	9.7	11.0	11.0	12.5	12.5	12.5	12.5
65°	8.2	8.2	9.7	9.7	9.7	11.0	11.0	11.0	11.0	11.0	11.0
67.5°	6.9	8.2	8.2	8.2	9.7	9.7	9.7	9.7	9.7	9.7	9.7
70°	6.9	6.9	8.2	8.2	8.2	9.7	9.7	9.7	9.7	9.7	9.7
72.5°	6.9	6.9	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
75°	6.9	6.9	6.9	6.9	6.9	8.2	8.2	8.2	8.2	6.9	6.9
77.5°	5.5	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	5.5
80°	5.5	5.5	6.9	5.5	6.9	6.9	6.9	6.9	5.5	5.5	5.5
82.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.2	4.2
85°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.2	4.2	4.2	2.8
87.5°	5.5	5.5	5.5	5.5	5.5	5.5	4.2	4.2	4.2	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212348

CATALOG NUMBER: LDSQA4A35927D010TE LAR25NF 4LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	311.4	311.4	311.4	311.4	311.4	311.4	311.4	311.4
2.5°	245.1	247.8	245.1	247.8	240.8	243.6	246.4	239.5
5°	213.2	210.4	211.8	214.5	209.1	210.4	211.8	206.3
7.5°	191.0	192.4	189.6	192.4	188.3	189.6	191.0	186.9
10°	173.1	174.4	173.1	174.4	170.3	173.1	174.4	170.3
12.5°	156.4	159.3	157.8	160.6	156.4	159.3	162.0	156.4
15°	144.0	146.8	145.3	148.1	145.3	148.1	150.8	146.8
17.5°	131.5	134.3	134.3	137.0	135.6	138.3	141.3	137.0
20°	119.1	123.2	123.2	126.0	126.0	127.3	131.5	127.3
22.5°	108.0	112.1	112.1	114.8	114.8	117.6	120.5	117.6
25°	95.6	101.0	102.5	105.3	105.3	108.0	112.1	109.4
27.5°	87.2	91.3	92.8	95.6	96.9	99.7	102.5	99.7
30°	76.1	81.8	83.1	85.8	87.2	91.3	92.8	91.3
32.5°	67.8	72.0	73.3	76.1	78.8	81.8	84.5	83.1
35°	59.5	63.7	65.0	67.8	69.3	73.3	76.1	74.8
37.5°	52.6	56.8	58.1	59.5	61.0	65.0	67.8	66.5
40°	45.7	48.5	49.8	52.6	54.0	56.8	59.5	59.5
42.5°	40.2	43.0	44.3	45.7	47.0	49.8	52.6	51.2
45°	34.5	37.3	38.8	40.2	41.5	43.0	45.7	44.3
47.5°	29.1	31.8	33.2	34.5	36.0	37.3	40.2	38.8
50°	25.0	27.7	27.7	29.1	30.5	31.8	34.5	33.2
52.5°	22.2	23.5	25.0	25.0	26.3	27.7	30.5	29.1
55°	19.3	20.7	20.7	22.2	22.2	23.5	25.0	25.0
57.5°	16.6	18.0	18.0	19.3	19.3	20.7	22.2	22.2
60°	15.3	15.3	16.6	16.6	16.6	18.0	18.0	18.0
62.5°	13.8	13.8	13.8	13.8	13.8	13.8	13.8	13.8
65°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0
67.5°	9.7	9.7	9.7	9.7	9.7	8.2	8.2	8.2
70°	8.2	8.2	8.2	8.2	8.2	6.9	6.9	6.9
72.5°	8.2	8.2	6.9	6.9	6.9	6.9	6.9	5.5
75°	6.9	6.9	6.9	6.9	5.5	5.5	5.5	5.5
77.5°	5.5	5.5	5.5	5.5	4.2	4.2	4.2	4.2
80°	5.5	4.2	4.2	4.2	4.2	4.2	4.2	2.8
82.5°	4.2	4.2	4.2	2.8	2.8	2.8	2.8	2.8
85°	2.8	2.8	2.8	2.8	1.5	1.5	1.5	1.5
87.5°	2.8	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)