

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212382

Luminaire Tested: **LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212382
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2981.4 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212382

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212382

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	104	102		103	101	99		99	97	96		96	94	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	91	85	80	97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	71	90	82	76	71		80	74	70		78	73	69		76	72	68
5	86	76	69	64	84	75	68	64		73	67	63		71	66	62		70	65	62
6	80	70	62	57	79	69	62	57		67	61	57		66	60	56		64	59	56
7	75	64	57	52	74	63	56	51		62	56	51		60	55	51		59	54	50
8	70	59	52	47	69	58	51	46		57	51	46		56	50	46		55	50	46
9	66	54	47	42	64	54	47	42		53	46	42		52	46	42		51	45	42
10	62	50	43	38	60	50	43	38		49	42	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35708	35708	35708
5°	83699	33705	23563
10°	330710	29619	19644
15°	612027	23719	17230
20°	784752	17258	15598
25°	938945	12250	13821
30°	998392	8054	12159
35°	1023212	4861	10596
40°	936665	3162	9105
45°	675875	2206	7453
50°	295048	1763	6194
55°	20352	1486	5219
60°	3701	1434	4263
65°	1352	1352	3049
70°	1275	1671	2096
75°	1085	2208	2208
80°	0	3292	2510
85°	0	6558	1667

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212382

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.8
10°-20°	422.0	14.2
20°-30°	883.5	29.6
30°-40°	983.4	33.0
40°-50°	564.5	18.9
50°-60°	56.4	1.9
60°-70°	8.9	0.3
70°-80°	5.6	0.2
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1359.2	45.6
0°-40°	2342.6	78.6
0°-60°	2963.4	99.4
0°-90°	2981.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2981.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	369	369	369	369	369	
5°	861	593	347	253	242	158
15°	6102	2436	236	166	172	1725
25°	8784	3353	115	101	129	3978
35°	8652	1024	41	59	90	5283
45°	4933	123	16	32	54	3767
55°	120	18	9	19	31	360
65°	6	4	6	12	13	8
75°	3	3	6	7	6	2
85°	0	3	6	4	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1212382

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6
2.5°	550.7	539.0	527.3	520.0	512.6	522.8	515.5	512.6	491.9	481.7	472.9
5°	860.7	838.6	806.3	779.9	753.4	759.3	738.8	713.8	662.4	625.6	593.4
7.5°	1661.0	1606.7	1506.9	1409.9	1313.0	1295.3	1230.7	1119.2	975.3	866.6	772.5
10°	3361.9	3197.3	3013.8	2815.5	2583.5	2518.8	2358.8	2056.1	1725.6	1348.3	1075.1
12.5°	4962.7	4887.8	4671.9	4414.9	4163.7	4009.5	3843.6	3344.1	2819.8	2211.8	1703.7
15°	6102.4	6056.9	5867.4	5633.9	5363.6	5263.7	5061.2	4563.2	3900.9	3173.8	2436.5
17.5°	6946.8	6869.1	6670.8	6416.6	6096.4	6011.3	5769.0	5274.0	4586.7	3856.7	3038.8
20°	7612.1	7563.7	7306.6	7001.3	6617.8	6515.1	6231.6	5716.2	4968.5	4193.1	3360.3
22.5°	8209.9	8127.7	7811.9	7447.6	7010.0	6899.8	6584.1	6018.6	5215.3	4351.7	3417.6
25°	8784.2	8659.4	8275.9	7798.7	7284.7	7134.9	6788.3	6189.1	5306.3	4365.0	3353.0
27.5°	8951.6	8888.4	8534.6	7979.4	7384.5	7215.7	6854.3	6227.2	5272.6	4244.5	3121.0
30°	8925.2	8872.3	8577.1	7997.0	7366.9	7189.2	6822.0	6109.7	5075.7	3930.2	2711.1
32.5°	8841.5	8820.9	8464.0	7844.2	7202.4	7008.6	6612.0	5817.4	4707.1	3451.4	1981.2
35°	8652.0	8571.2	8126.1	7543.2	6926.4	6713.4	6265.4	5398.9	4220.9	2512.9	1023.6
37.5°	8096.9	8033.6	7682.7	7171.5	6570.9	6297.7	5824.8	4858.4	3267.8	1429.0	612.5
40°	7406.7	7375.8	7099.7	6642.8	6001.0	5692.6	5178.6	3975.8	1994.5	812.2	403.9
42.5°	6698.6	6689.9	6394.6	5917.3	5221.2	4867.2	4334.1	2681.9	1060.4	490.5	233.5
45°	4933.3	4986.3	4780.6	4494.2	3962.5	3705.5	3013.8	1382.0	611.0	271.7	123.4
47.5°	3460.1	3401.4	3037.2	2536.4	2050.2	1735.9	1313.0	653.6	326.0	142.4	70.6
50°	1957.7	1968.0	1639.1	1326.2	869.5	688.8	522.8	329.0	157.2	74.9	42.6
52.5°	511.1	534.5	461.2	396.5	337.8	274.6	221.8	142.4	74.9	44.0	27.9
55°	120.5	124.8	116.0	108.7	102.8	91.0	80.8	61.6	41.1	27.9	17.6
57.5°	42.6	44.0	42.6	42.6	41.1	39.7	36.6	32.3	25.0	17.6	11.7
60°	19.1	20.5	19.1	20.5	20.5	20.5	20.5	20.5	14.7	10.2	7.4
62.5°	8.8	8.8	8.8	8.8	10.2	10.2	11.7	11.7	8.8	7.4	5.9
65°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	4.5
67.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
70°	4.5	4.5	4.5	2.9	2.9	2.9	2.9	2.9	2.9	2.9	4.5
72.5°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
75°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
77.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.9	2.9	2.9	2.9
80°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.9	2.9	2.9
82.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.9	2.9	2.9
85°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.9	2.9	2.9
87.5°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.9	2.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212382

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6
2.5°	456.8	455.3	439.2	427.4	421.5	412.7	402.4	387.8	371.6	356.9	351.0
5°	555.2	536.1	502.3	474.4	461.2	447.9	424.4	398.0	373.0	346.6	333.4
7.5°	682.9	627.1	561.1	509.5	487.6	465.5	431.8	395.1	361.3	326.0	307.0
10°	857.7	728.5	613.9	531.7	499.3	470.0	421.5	376.0	339.3	301.1	276.1
12.5°	1226.3	906.1	669.8	541.9	499.3	461.2	402.4	349.5	308.4	268.7	245.4
15°	1766.8	1223.5	791.7	552.2	489.1	440.6	373.0	315.7	271.7	236.5	214.5
17.5°	2203.1	1515.7	942.9	578.7	475.8	412.7	334.8	274.6	233.5	201.2	183.6
20°	2423.3	1639.1	1011.9	583.1	443.6	368.6	289.4	232.1	195.4	167.4	152.7
22.5°	2418.9	1599.4	950.3	511.1	389.2	318.6	243.7	190.9	161.5	139.6	127.8
25°	2266.1	1415.8	793.1	408.3	314.3	264.4	198.3	154.2	130.7	114.6	104.3
27.5°	1979.8	1150.0	591.8	302.5	245.4	208.6	154.2	123.4	104.3	92.5	85.1
30°	1553.8	769.6	373.0	224.7	186.6	157.2	118.9	95.6	82.3	72.0	67.5
32.5°	856.2	400.9	251.1	164.5	136.5	114.6	88.2	69.0	60.2	52.9	51.4
35°	472.9	283.5	179.2	110.1	91.0	77.8	60.2	49.9	44.0	41.1	41.1
37.5°	334.8	182.1	107.2	69.0	58.8	51.4	41.1	35.2	33.8	32.3	32.3
40°	201.2	107.2	64.7	45.5	39.7	35.2	30.9	26.4	26.4	25.0	26.4
42.5°	110.1	64.7	44.0	32.3	27.9	26.4	22.0	20.5	20.5	20.5	22.0
45°	66.1	42.6	30.9	23.5	20.5	17.6	16.1	14.7	16.1	16.1	17.6
47.5°	42.6	30.9	20.5	14.7	13.3	11.7	10.2	11.7	11.7	13.3	14.7
50°	29.4	19.1	13.3	8.8	8.8	7.4	8.8	8.8	10.2	11.7	13.3
52.5°	19.1	13.3	8.8	7.4	5.9	5.9	5.9	7.4	8.8	10.2	11.7
55°	11.7	8.8	7.4	5.9	5.9	5.9	5.9	5.9	7.4	8.8	10.2
57.5°	8.8	7.4	5.9	4.5	4.5	4.5	5.9	5.9	7.4	7.4	8.8
60°	5.9	5.9	4.5	4.5	4.5	4.5	4.5	5.9	5.9	7.4	8.8
62.5°	5.9	5.9	4.5	4.5	4.5	4.5	5.9	5.9	5.9	7.4	7.4
65°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	7.4
67.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	7.4
70°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	7.4
72.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9
75°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9
77.5°	2.9	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9
80°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9
82.5°	2.9	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9
85°	2.9	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9
87.5°	2.9	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212382

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6
2.5°	343.6	333.4	324.6	327.6	321.6	311.4	308.4	301.1	292.2	290.8	290.8
5°	318.6	302.5	289.4	287.9	282.0	270.3	267.3	259.9	252.6	251.1	249.7
7.5°	287.9	270.3	258.5	255.6	251.1	240.8	239.4	232.1	227.6	224.7	224.7
10°	257.0	240.8	230.6	229.1	226.2	217.3	215.9	209.9	205.6	204.2	202.6
12.5°	227.6	214.5	205.6	204.2	201.2	193.8	192.4	188.0	185.0	183.6	183.6
15°	199.7	188.0	180.7	179.2	177.7	170.5	170.5	167.4	165.9	165.9	167.4
17.5°	171.8	161.5	155.7	154.2	154.2	148.3	149.8	148.3	148.3	148.3	151.3
20°	143.9	135.0	130.7	132.2	129.3	127.8	129.3	129.3	129.3	132.2	136.5
22.5°	120.5	113.2	108.7	110.1	110.1	108.7	110.1	111.5	114.6	118.9	123.4
25°	98.4	92.5	91.0	92.5	92.5	92.5	95.6	98.4	101.3	105.8	110.1
27.5°	79.4	74.9	74.9	76.4	77.8	77.8	82.3	85.1	89.6	94.0	98.4
30°	63.2	61.6	61.6	64.7	64.7	66.1	72.0	74.9	77.8	82.3	86.6
32.5°	49.9	49.9	51.4	54.4	54.4	57.3	61.6	64.7	67.5	72.0	76.4
35°	41.1	42.6	44.0	45.5	47.0	48.5	52.9	55.8	58.8	63.2	66.1
37.5°	33.8	35.2	36.6	39.7	39.7	41.1	45.5	48.5	49.9	54.4	58.8
40°	27.9	29.4	30.9	33.8	33.8	35.2	39.7	41.1	42.6	47.0	51.4
42.5°	23.5	25.0	26.4	27.9	29.4	30.9	33.8	35.2	38.3	41.1	44.0
45°	19.1	20.5	22.0	23.5	25.0	26.4	27.9	30.9	32.3	35.2	38.3
47.5°	16.1	17.6	19.1	20.5	22.0	22.0	25.0	26.4	27.9	30.9	33.8
50°	14.7	16.1	17.6	17.6	19.1	20.5	22.0	23.5	25.0	26.4	29.4
52.5°	11.7	13.3	14.7	16.1	16.1	17.6	19.1	20.5	22.0	23.5	25.0
55°	11.7	11.7	13.3	14.7	14.7	16.1	17.6	19.1	19.1	20.5	22.0
57.5°	10.2	11.7	11.7	13.3	13.3	14.7	16.1	16.1	17.6	17.6	19.1
60°	8.8	10.2	11.7	11.7	11.7	13.3	13.3	14.7	14.7	16.1	16.1
62.5°	8.8	10.2	10.2	11.7	11.7	11.7	13.3	13.3	13.3	14.7	14.7
65°	8.8	8.8	10.2	10.2	10.2	10.2	11.7	11.7	11.7	13.3	13.3
67.5°	7.4	8.8	8.8	8.8	10.2	10.2	10.2	10.2	10.2	11.7	11.7
70°	7.4	7.4	8.8	8.8	8.8	8.8	8.8	10.2	10.2	10.2	10.2
72.5°	7.4	7.4	7.4	7.4	8.8	8.8	8.8	8.8	8.8	8.8	8.8
75°	5.9	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
77.5°	5.9	5.9	5.9	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
80°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
82.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	4.5	4.5
85°	5.9	5.9	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
87.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	2.9	2.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212382

CATALOG NUMBER: LDSQA4A35935D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	368.6	368.6	368.6	368.6	368.6	368.6	368.6	368.6
2.5°	284.8	282.0	280.5	284.8	279.1	282.0	280.5	282.0
5°	245.4	242.3	240.8	245.4	239.4	242.3	239.4	242.3
7.5°	220.4	218.8	217.3	220.4	215.9	218.8	217.3	218.8
10°	199.7	198.3	196.8	201.2	196.8	199.7	198.3	199.7
12.5°	182.1	182.1	180.7	183.6	180.7	183.6	182.1	183.6
15°	165.9	167.4	165.9	168.8	167.4	170.5	168.8	171.8
17.5°	152.7	154.2	154.2	158.6	157.2	161.5	160.0	161.5
20°	139.6	141.0	142.4	145.5	145.5	149.8	148.3	151.3
22.5°	126.3	129.3	129.3	133.7	133.7	138.1	138.1	139.6
25°	113.2	117.5	118.9	121.9	123.4	127.8	127.8	129.3
27.5°	102.8	105.8	107.2	111.5	113.2	117.5	117.5	120.5
30°	91.0	95.6	96.9	99.9	101.3	105.8	105.8	108.7
32.5°	80.8	83.7	86.6	89.6	91.0	95.6	95.6	98.4
35°	70.6	74.9	76.4	79.4	82.3	86.6	86.6	89.6
37.5°	61.6	66.1	67.5	70.6	73.4	77.8	77.8	80.8
40°	54.4	58.8	60.2	63.2	64.7	70.6	70.6	72.0
42.5°	48.5	51.4	52.9	55.8	57.3	60.2	60.2	63.2
45°	41.1	44.0	45.5	47.0	49.9	52.9	52.9	54.4
47.5°	35.2	38.3	39.7	41.1	42.6	45.5	45.5	48.5
50°	30.9	32.3	33.8	35.2	36.6	39.7	39.7	41.1
52.5°	26.4	27.9	29.4	30.9	32.3	33.8	35.2	36.6
55°	23.5	25.0	25.0	26.4	27.9	29.4	29.4	30.9
57.5°	20.5	22.0	22.0	22.0	23.5	25.0	25.0	26.4
60°	17.6	19.1	19.1	19.1	20.5	20.5	20.5	22.0
62.5°	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1
65°	13.3	13.3	13.3	13.3	13.3	13.3	11.7	13.3
67.5°	11.7	11.7	11.7	10.2	10.2	10.2	10.2	10.2
70°	10.2	10.2	10.2	8.8	8.8	8.8	7.4	7.4
72.5°	8.8	8.8	8.8	7.4	7.4	7.4	5.9	5.9
75°	7.4	7.4	7.4	7.4	5.9	5.9	5.9	5.9
77.5°	5.9	5.9	5.9	5.9	5.9	5.9	4.5	4.5
80°	5.9	4.5	4.5	4.5	4.5	4.5	4.5	4.5
82.5°	4.5	4.5	4.5	4.5	2.9	2.9	2.9	2.9
85°	2.9	2.9	2.9	2.9	2.9	2.9	1.5	1.5
87.5°	2.9	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)