

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212392

Luminaire Tested: **LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3158.7 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212392

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212392

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34100	34100	34100
5°	76347	32091	22969
10°	299389	28085	18100
15°	649928	22746	15746
20°	969566	16835	14227
25°	1261091	11865	12378
30°	1410760	7976	10817
35°	1269601	4695	9189
40°	1036115	3199	8018
45°	594920	2178	6521
50°	174011	1658	5501
55°	20082	1334	4543
60°	4301	1531	3701
65°	1444	1444	2521
70°	1331	1784	1784
75°	1160	2358	1759
80°	0	3515	1729
85°	0	7003	1778

TEST NUMBER: P1212392

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	1.6
10°-20°	432.4	13.7
20°-30°	1031.5	32.7
30°-40°	1088.6	34.5
40°-50°	493.7	15.6
50°-60°	43.3	1.4
60°-70°	9.0	0.3
70°-80°	5.9	0.2
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1514.4	47.9
0°-40°	2603.1	82.4
0°-60°	3140.1	99.4
0°-90°	3158.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3158.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	352	352	352	352	352	
5°	785	576	330	254	236	141
15°	6480	2279	227	155	157	1885
25°	11798	3137	111	95	116	5360
35°	10735	866	40	54	78	6630
45°	4342	122	16	30	48	3443
55°	119	19	8	17	27	237
65°	6	6	6	13	11	8
75°	3	3	6	8	5	3
85°	0	3	6	5	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1212392

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0
2.5°	523.3	526.5	512.3	513.9	499.6	505.9	501.1	488.4	479.0	463.0	456.8
5°	785.1	789.9	758.0	748.6	715.2	715.2	701.0	667.7	637.6	601.0	575.7
7.5°	1435.3	1454.3	1359.2	1287.9	1183.1	1157.8	1108.7	994.4	900.9	805.6	734.2
10°	3043.5	3008.5	2812.0	2650.2	2380.6	2280.6	2147.4	1819.1	1517.8	1218.1	983.2
12.5°	4799.1	4911.7	4532.6	4401.1	3974.5	3884.0	3600.1	3064.1	2554.9	2025.2	1555.8
15°	6480.3	6513.6	6182.1	5968.0	5447.8	5330.5	4981.5	4351.8	3666.7	2927.7	2279.0
17.5°	7830.0	7963.1	7476.3	7246.3	6570.7	6382.0	5971.2	5205.1	4442.3	3635.0	2865.8
20°	9404.8	9439.6	8862.4	8419.8	7536.6	7249.5	6757.8	5807.9	4899.1	3977.6	3183.0
22.5°	10836.9	10829.0	10086.8	9461.8	8343.8	8001.2	7393.7	6267.8	5211.5	4129.9	3213.1
25°	11798.0	11823.4	11028.8	10289.8	8917.8	8454.8	7769.7	6507.2	5317.8	4125.2	3137.0
27.5°	12310.4	12285.0	11433.3	10643.4	9128.9	8610.3	7866.4	6515.2	5221.0	3963.3	2908.7
30°	12611.6	12272.2	11363.5	10543.5	8986.1	8453.3	7696.8	6264.6	4899.1	3601.7	2501.1
32.5°	11805.9	11674.4	10882.9	10012.3	8494.5	7966.4	7219.4	5731.7	4388.4	3048.2	1792.2
35°	10735.4	10740.3	9967.9	9154.3	7723.7	7263.8	6493.0	5083.1	3765.1	2118.8	865.9
37.5°	9612.6	9628.5	8894.1	8137.6	6864.0	6380.4	5658.7	4343.9	2708.8	1078.4	521.8
40°	8193.1	8226.4	7593.6	6986.2	5811.0	5344.7	4700.8	3287.8	1514.7	602.8	353.8
42.5°	6694.5	6735.6	6174.2	5634.9	4635.8	4252.0	3681.0	2036.4	751.8	390.1	207.8
45°	4342.4	4461.3	4044.2	3817.5	3238.5	3010.1	2402.8	1038.9	453.6	228.3	122.1
47.5°	2485.1	2486.7	2134.7	1709.7	1402.0	1219.7	953.2	472.7	264.9	128.5	74.5
50°	1154.6	1183.1	937.2	780.2	558.3	472.7	388.6	255.3	139.6	74.5	46.0
52.5°	336.2	355.3	321.9	291.9	247.4	220.5	188.7	125.3	72.9	44.4	28.5
55°	118.9	126.9	118.9	111.0	99.9	90.4	81.0	60.3	41.2	26.9	19.1
57.5°	49.1	50.7	49.1	47.6	44.4	44.4	39.7	33.2	25.3	17.4	12.8
60°	22.2	23.8	22.2	23.8	22.2	22.2	22.2	23.8	15.9	11.0	9.5
62.5°	9.5	11.0	11.0	11.0	11.0	12.8	12.8	11.0	9.5	7.9	6.3
65°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
67.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
70°	4.7	4.7	4.7	4.7	4.7	4.7	3.1	3.1	4.7	4.7	4.7
72.5°	4.7	4.7	4.7	4.7	3.1	3.1	3.1	3.1	3.1	4.7	4.7
75°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
77.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	1.6	3.1	3.1	3.1
80°	0.0	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1
82.5°	0.0	0.0	0.0	1.6	1.6	1.6	1.6	1.6	3.1	3.1	3.1
85°	0.0	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1
87.5°	0.0	0.0	0.0	0.0	1.6	1.6	1.6	1.6	3.1	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212392

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0
2.5°	448.9	434.6	412.3	398.1	391.7	382.2	376.0	360.0	353.8	341.0	336.2
5°	551.9	523.3	490.1	463.0	445.7	426.7	398.1	366.3	350.5	330.0	318.8
7.5°	669.2	607.4	548.7	501.1	479.0	453.6	417.0	367.9	337.8	310.9	295.0
10°	818.3	691.5	599.5	523.3	490.1	456.8	412.3	355.3	317.2	285.5	268.1
12.5°	1167.2	834.2	645.5	536.1	493.3	452.0	396.5	337.8	293.4	256.9	237.8
15°	1679.6	1165.7	769.2	547.1	482.1	431.4	367.9	309.3	263.3	226.8	207.8
17.5°	2133.1	1486.0	940.5	588.4	479.0	407.6	333.1	272.8	228.3	193.5	177.7
20°	2380.6	1654.2	1054.6	613.8	464.6	371.1	293.4	236.2	193.5	163.3	149.1
22.5°	2385.3	1644.6	1013.5	558.3	409.2	321.9	253.7	199.9	161.8	134.8	123.7
25°	2242.6	1467.1	845.3	439.2	334.7	272.8	212.5	166.5	131.7	111.0	101.5
27.5°	1976.1	1192.6	621.7	317.2	261.8	220.5	171.3	133.2	103.1	90.4	82.5
30°	1554.2	777.1	363.2	236.2	203.0	169.7	130.1	93.6	81.0	71.3	65.0
32.5°	834.2	377.5	253.7	174.5	144.2	118.9	85.7	68.2	58.8	52.3	50.7
35°	436.1	275.9	169.7	111.0	92.0	77.7	58.8	47.6	42.9	39.7	39.7
37.5°	312.4	172.9	107.9	71.3	60.3	49.1	41.2	35.0	31.7	31.7	31.7
40°	185.6	106.3	65.0	46.0	39.7	35.0	30.1	25.3	25.3	25.3	25.3
42.5°	112.6	66.6	46.0	31.7	28.5	25.3	22.2	20.7	19.1	19.1	20.7
45°	69.8	46.0	30.1	23.8	22.2	19.1	17.4	15.9	15.9	15.9	17.4
47.5°	44.4	33.2	22.2	15.9	14.3	12.8	11.0	11.0	12.8	12.8	14.3
50°	33.2	20.7	14.3	11.0	9.5	9.5	7.9	9.5	9.5	11.0	12.8
52.5°	19.1	12.8	9.5	7.9	7.9	6.3	6.3	7.9	7.9	9.5	11.0
55°	12.8	9.5	7.9	6.3	6.3	6.3	6.3	6.3	7.9	7.9	9.5
57.5°	9.5	7.9	6.3	6.3	6.3	4.7	6.3	6.3	6.3	7.9	9.5
60°	7.9	6.3	6.3	6.3	6.3	4.7	4.7	6.3	6.3	7.9	7.9
62.5°	6.3	6.3	6.3	6.3	6.3	4.7	6.3	6.3	6.3	6.3	7.9
65°	4.7	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.9
67.5°	4.7	4.7	6.3	6.3	6.3	4.7	6.3	6.3	6.3	6.3	7.9
70°	4.7	4.7	4.7	6.3	6.3	4.7	6.3	6.3	6.3	6.3	6.3
72.5°	4.7	4.7	4.7	6.3	6.3	4.7	6.3	6.3	6.3	6.3	6.3
75°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3
77.5°	4.7	4.7	4.7	4.7	6.3	4.7	6.3	6.3	6.3	6.3	6.3
80°	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3	6.3
82.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3
85°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3	6.3
87.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	6.3	6.3	6.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212392

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0
2.5°	323.5	318.8	309.3	307.8	306.0	299.7	295.0	290.2	290.2	285.5	282.2
5°	299.7	291.9	280.7	275.9	274.3	266.4	260.0	255.3	253.7	249.0	244.3
7.5°	274.3	264.9	252.1	247.4	245.9	237.8	231.6	226.8	223.7	218.9	215.6
10°	247.4	236.2	225.2	220.5	218.9	210.9	206.2	201.4	198.3	195.1	191.8
12.5°	218.9	209.3	198.3	193.5	191.8	185.6	180.8	177.7	176.1	172.9	171.3
15°	190.2	180.8	171.3	168.0	166.5	161.8	158.6	157.0	155.4	155.4	153.9
17.5°	161.8	153.9	145.9	144.2	142.7	139.6	138.0	136.4	138.0	138.0	139.6
20°	134.8	128.5	122.1	122.1	120.5	118.9	118.9	118.9	122.1	123.7	126.9
22.5°	111.0	106.3	101.5	101.5	101.5	101.5	101.5	104.8	107.9	111.0	112.6
25°	92.0	87.2	85.7	85.7	85.7	87.2	88.8	92.0	95.1	98.3	101.5
27.5°	74.5	71.3	71.3	71.3	72.9	74.5	76.1	79.2	84.1	87.2	90.4
30°	60.3	58.8	58.8	60.3	61.9	63.4	66.6	69.8	72.9	76.1	79.2
32.5°	47.6	49.1	49.1	50.7	52.3	53.9	57.2	60.3	63.4	66.6	68.2
35°	39.7	39.7	41.2	42.9	44.4	46.0	49.1	52.3	53.9	57.2	60.3
37.5°	31.7	33.2	35.0	36.5	38.1	39.7	41.2	44.4	46.0	49.1	52.3
40°	26.9	28.5	30.1	31.7	31.7	35.0	35.0	38.1	39.7	42.9	46.0
42.5°	22.2	23.8	25.3	26.9	26.9	28.5	30.1	31.7	35.0	36.5	39.7
45°	17.4	19.1	20.7	22.2	23.8	25.3	25.3	28.5	30.1	31.7	35.0
47.5°	15.9	17.4	19.1	19.1	20.7	22.2	22.2	25.3	26.9	28.5	30.1
50°	12.8	14.3	15.9	17.4	17.4	19.1	20.7	22.2	23.8	25.3	25.3
52.5°	11.0	12.8	14.3	14.3	15.9	17.4	17.4	19.1	20.7	20.7	22.2
55°	11.0	12.8	12.8	14.3	14.3	15.9	15.9	17.4	17.4	19.1	19.1
57.5°	9.5	11.0	11.0	12.8	12.8	14.3	14.3	15.9	15.9	15.9	17.4
60°	9.5	9.5	11.0	11.0	12.8	12.8	12.8	14.3	14.3	14.3	15.9
62.5°	7.9	9.5	9.5	11.0	11.0	11.0	12.8	12.8	12.8	14.3	14.3
65°	7.9	9.5	9.5	11.0	11.0	11.0	11.0	11.0	12.8	12.8	12.8
67.5°	7.9	7.9	9.5	9.5	9.5	9.5	11.0	11.0	11.0	11.0	11.0
70°	7.9	7.9	7.9	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
72.5°	6.3	7.9	7.9	7.9	7.9	9.5	9.5	9.5	9.5	9.5	7.9
75°	6.3	6.3	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
77.5°	6.3	6.3	6.3	7.9	7.9	7.9	7.9	7.9	7.9	6.3	6.3
80°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	4.7
82.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	4.7	4.7	4.7
85°	6.3	4.7	6.3	6.3	6.3	4.7	4.7	4.7	4.7	4.7	3.1
87.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	3.1	3.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212392

CATALOG NUMBER: LDSQA4A35940D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0
2.5°	279.1	275.9	277.5	277.5	274.3	272.8	272.8	274.3
5°	241.1	237.8	239.5	239.5	236.2	234.7	234.7	236.2
7.5°	212.5	209.3	210.9	210.9	207.8	207.8	207.8	207.8
10°	190.2	188.7	188.7	188.7	185.6	187.1	185.6	184.0
12.5°	169.7	169.7	169.7	169.7	168.0	169.7	168.0	168.0
15°	153.9	153.9	155.4	155.4	155.4	157.0	157.0	157.0
17.5°	141.1	142.7	144.2	145.9	145.9	147.5	147.5	147.5
20°	128.5	131.7	133.2	134.8	134.8	138.0	136.4	138.0
22.5°	115.8	118.9	120.5	122.1	123.7	125.3	125.3	126.9
25°	104.8	107.9	109.4	111.0	112.6	115.8	115.8	115.8
27.5°	93.6	96.7	98.3	101.5	103.1	106.3	106.3	106.3
30°	82.5	85.7	87.2	88.8	92.0	95.1	95.1	96.7
32.5°	71.3	76.1	77.7	79.2	82.5	85.7	87.2	87.2
35°	63.4	66.6	68.2	71.3	72.9	77.7	77.7	77.7
37.5°	55.5	58.8	61.9	63.4	65.0	68.2	69.8	71.3
40°	49.1	52.3	53.9	55.5	58.8	61.9	63.4	63.4
42.5°	42.9	46.0	47.6	49.1	50.7	53.9	53.9	53.9
45°	38.1	39.7	41.2	42.9	44.4	46.0	47.6	47.6
47.5°	31.7	35.0	35.0	36.5	38.1	41.2	41.2	42.9
50°	26.9	30.1	30.1	31.7	33.2	35.0	36.5	36.5
52.5°	23.8	25.3	26.9	26.9	28.5	30.1	31.7	31.7
55°	20.7	22.2	22.2	23.8	23.8	25.3	26.9	26.9
57.5°	17.4	19.1	20.7	20.7	20.7	22.2	22.2	23.8
60°	15.9	17.4	17.4	17.4	17.4	19.1	19.1	19.1
62.5°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
65°	12.8	12.8	12.8	12.8	11.0	11.0	11.0	11.0
67.5°	11.0	11.0	11.0	11.0	9.5	9.5	9.5	9.5
70°	9.5	9.5	9.5	9.5	7.9	7.9	7.9	6.3
72.5°	7.9	7.9	7.9	7.9	7.9	6.3	6.3	6.3
75°	7.9	6.3	6.3	6.3	6.3	6.3	4.7	4.7
77.5°	6.3	6.3	6.3	4.7	4.7	4.7	4.7	4.7
80°	4.7	4.7	4.7	4.7	4.7	3.1	3.1	3.1
82.5°	4.7	3.1	3.1	3.1	3.1	3.1	3.1	3.1
85°	3.1	3.1	3.1	3.1	1.6	1.6	1.6	1.6
87.5°	3.1	1.6	1.6	1.6	1.6	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)