

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219569

Luminaire Tested: **LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26830)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°
Description: PORTFOLIO 4" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 15° SPOT WITH SOLITE LENS, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2994.8 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.64 / 1.15
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219569

CATALOG NUMBER: LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219569

CATALOG NUMBER: LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69
5	86	76	69	64	85	75	69	64	73	68	63	72	67	63	70	66	62
6	81	70	63	58	79	69	62	57	67	61	57	66	61	57	64	60	56
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42
10	62	50	43	38	60	50	43	38	49	42	38	48	42	38	47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	31320	31320	31320
5°	59981	29835	24214
10°	196159	26442	20608
15°	480363	21834	18203
20°	905102	16660	16330
25°	1515115	11822	14281
30°	1919352	8121	12193
35°	1748886	5275	10348
40°	1151777	3743	8764
45°	498936	2480	7220
50°	88513	1718	5968
55°	14221	1385	4999
60°	3507	1279	3856
65°	1123	1513	3049
70°	906	1869	2323
75°	1198	1834	1834
80°	0	2734	1785
85°	0	5446	1890

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219569

CATALOG NUMBER: LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	1.4
10°-20°	333.1	11.1
20°-30°	1003.4	33.5
30°-40°	1142.1	38.1
40°-50°	422.3	14.1
50°-60°	33.5	1.1
60°-70°	9.0	0.3
70°-80°	6.3	0.2
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1378.0	46.0
0°-40°	2520.1	84.2
0°-60°	2975.9	99.4
0°-90°	2994.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2994.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	323	323	323	323	323	
5°	617	454	307	257	249	100
15°	4790	1618	218	172	182	1502
25°	14174	2365	111	107	134	6470
35°	14788	828	45	61	88	8792
45°	3642	97	18	33	53	3083
55°	84	18	8	20	30	138
65°	5	5	7	13	13	7
75°	3	5	5	8	5	2
85°	0	3	5	5	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1219569

CATALOG NUMBER: LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3
2.5°	415.6	419.0	415.6	409.0	409.0	400.8	397.5	394.3	385.9	381.0	374.4
5°	616.8	607.0	598.7	578.9	572.3	554.1	541.0	522.9	498.2	476.6	453.5
7.5°	1055.5	1040.8	1009.3	950.0	913.7	869.2	834.6	776.9	702.7	641.6	580.5
10°	1994.1	1929.7	1855.5	1721.8	1624.6	1520.7	1438.1	1283.2	1096.8	943.5	795.0
12.5°	3213.0	3217.9	3079.4	2853.3	2673.5	2490.6	2348.7	2061.8	1731.8	1443.2	1157.8
15°	4789.6	4699.0	4555.6	4209.2	3849.6	3584.2	3358.1	2922.7	2455.9	2033.7	1618.0
17.5°	6450.5	6488.6	6153.8	5588.0	5019.0	4621.4	4280.0	3620.3	3066.2	2543.3	2035.4
20°	8779.5	8518.8	8040.6	7123.6	6239.4	5663.8	5157.6	4301.5	3527.9	2863.2	2292.6
22.5°	11464.6	11044.0	10071.0	8779.5	7441.9	6645.2	5939.3	4761.6	3821.6	3026.5	2380.0
25°	14174.5	13853.0	12302.5	10372.8	8456.2	7423.7	6510.0	5073.3	3961.8	3064.5	2365.2
27.5°	16265.8	15741.4	13975.0	11459.7	9061.5	7842.6	6775.6	5169.0	3931.9	2972.1	2225.1
30°	17158.2	16495.2	14537.3	11707.0	9066.4	7773.4	6643.5	4979.4	3720.8	2737.9	1961.0
32.5°	16607.2	15842.0	13867.7	11022.6	8446.4	7232.4	6133.9	4568.7	3371.3	2370.2	1472.8
35°	14788.1	14026.1	12196.9	9671.8	7456.8	6396.2	5441.3	4032.7	2871.5	1756.6	827.9
37.5°	12109.4	11459.7	10151.8	8106.6	6284.0	5423.1	4628.2	3397.7	2139.2	1007.7	415.6
40°	9107.7	8650.8	7865.7	6429.2	5086.6	4431.8	3791.8	2602.6	1299.8	506.3	235.9
42.5°	6313.8	6016.8	5622.6	4756.6	3923.8	3473.5	2960.7	1738.5	668.0	278.8	146.7
45°	3641.8	3455.3	3346.5	2977.0	2652.2	2432.8	1979.1	936.7	338.1	166.6	97.3
47.5°	1608.2	1484.4	1431.7	1276.7	1187.6	1128.1	895.6	399.2	181.5	107.2	80.8
50°	587.3	587.3	588.8	517.9	423.9	381.0	298.6	176.5	102.2	84.2	59.3
52.5°	207.9	204.6	212.8	201.1	176.5	158.4	132.0	89.1	62.7	52.7	33.0
55°	84.2	80.8	84.2	79.1	74.2	69.3	61.2	47.8	39.6	33.0	18.1
57.5°	38.0	38.0	39.6	38.0	38.0	34.5	31.3	36.4	28.0	18.1	11.4
60°	18.1	18.1	19.9	19.9	19.9	18.1	18.1	19.9	16.5	11.4	8.2
62.5°	8.2	8.2	9.9	9.9	9.9	9.9	9.9	11.4	8.2	6.6	4.9
65°	4.9	3.2	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
67.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9	4.9
70°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9
72.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9
75°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9
77.5°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	1.7	3.2	3.2	4.9
80°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2
82.5°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2
85°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	1.7	3.2	3.2
87.5°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	1.7	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219569

CATALOG NUMBER: LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3
2.5°	367.7	362.9	353.0	348.1	341.3	336.4	333.1	326.6	319.9	315.0	311.7
5°	432.1	413.9	392.6	376.1	362.9	354.6	341.3	329.9	316.7	306.8	298.6
7.5°	526.1	481.5	433.7	400.8	382.6	366.1	343.0	323.3	305.1	291.9	280.5
10°	672.9	577.2	493.2	428.8	397.5	374.4	338.1	310.0	286.9	268.8	257.3
12.5°	917.1	720.7	572.3	463.4	415.6	381.0	329.9	291.9	263.8	245.6	231.0
15°	1252.0	931.8	681.2	504.6	437.0	387.6	316.7	270.4	239.2	217.7	204.6
17.5°	1566.9	1152.8	804.9	554.1	458.4	390.8	298.6	242.4	209.5	189.7	176.5
20°	1764.8	1296.5	887.3	582.2	465.2	381.0	273.8	212.8	179.8	161.6	148.4
22.5°	1811.0	1312.9	880.8	555.8	437.0	351.3	239.2	183.1	151.7	135.3	123.7
25°	1743.4	1220.4	788.3	480.0	372.7	295.2	199.5	148.4	125.3	110.6	102.2
27.5°	1573.4	1039.2	623.5	361.2	278.8	217.7	151.7	115.4	100.6	89.1	84.2
30°	1268.3	730.7	390.8	224.2	178.0	143.5	109.0	89.1	77.5	72.6	67.6
32.5°	768.6	376.1	206.2	133.6	112.2	97.3	79.1	65.9	59.3	56.1	54.4
35°	366.1	197.8	127.0	90.7	79.1	69.3	57.7	49.5	46.2	44.6	44.6
37.5°	207.9	128.6	85.8	61.2	54.4	47.8	42.8	38.0	36.4	36.4	36.4
40°	132.0	82.4	56.1	44.6	39.6	36.4	33.0	29.6	29.6	29.6	29.6
42.5°	85.8	59.3	42.8	33.0	29.6	28.0	24.8	23.1	23.1	23.1	24.8
45°	67.6	49.5	34.5	26.3	23.1	21.5	19.9	18.1	18.1	18.1	19.9
47.5°	57.7	34.5	23.1	18.1	14.9	14.9	13.3	13.3	13.3	14.9	16.5
50°	34.5	21.5	14.9	11.4	9.9	9.9	9.9	9.9	9.9	11.4	13.3
52.5°	19.9	13.3	9.9	8.2	6.6	6.6	6.6	6.6	8.2	9.9	9.9
55°	13.3	9.9	6.6	6.6	4.9	4.9	4.9	6.6	6.6	8.2	9.9
57.5°	8.2	6.6	4.9	4.9	4.9	4.9	4.9	4.9	6.6	8.2	8.2
60°	6.6	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	8.2
62.5°	4.9	4.9	6.6	4.9	4.9	4.9	4.9	4.9	6.6	6.6	8.2
65°	4.9	4.9	6.6	6.6	4.9	4.9	4.9	4.9	4.9	6.6	8.2
67.5°	4.9	4.9	6.6	6.6	6.6	6.6	4.9	4.9	4.9	6.6	6.6
70°	4.9	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9	6.6	6.6
72.5°	4.9	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9	6.6	6.6
75°	4.9	4.9	6.6	6.6	6.6	6.6	6.6	4.9	4.9	4.9	6.6
77.5°	4.9	4.9	6.6	6.6	6.6	6.6	6.6	4.9	4.9	4.9	6.6
80°	4.9	4.9	4.9	6.6	4.9	6.6	4.9	4.9	4.9	4.9	4.9
82.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
85°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
87.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219569

CATALOG NUMBER: LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3
2.5°	306.8	303.6	298.6	296.8	298.6	296.8	288.6	286.9	283.7	283.7	283.7
5°	290.3	285.3	278.8	275.5	275.5	272.1	263.8	262.2	257.3	257.3	255.7
7.5°	270.4	263.8	255.7	252.4	252.4	249.0	240.9	237.4	234.2	234.2	232.6
10°	247.3	239.2	231.0	229.3	227.7	222.6	217.7	216.1	211.1	212.8	211.1
12.5°	221.0	214.4	207.9	204.6	204.6	199.5	196.2	194.6	193.0	193.0	193.0
15°	196.2	188.0	181.5	179.8	179.8	178.0	174.7	174.7	171.5	174.7	174.7
17.5°	168.3	161.6	160.1	156.7	158.4	156.7	153.4	155.1	155.1	156.7	158.4
20°	141.9	137.0	135.3	133.6	135.3	135.3	133.6	135.3	137.0	141.9	145.2
22.5°	118.8	115.4	115.4	113.8	115.4	117.1	115.4	118.8	122.0	125.3	130.2
25°	98.9	97.3	97.3	97.3	98.9	100.6	102.2	105.6	107.2	112.2	115.4
27.5°	80.8	80.8	80.8	82.4	84.2	85.8	87.5	92.4	94.0	98.9	102.2
30°	67.6	65.9	67.6	69.3	70.9	74.2	75.8	79.1	80.8	85.8	89.1
32.5°	54.4	56.1	57.7	59.3	61.2	62.7	64.4	67.6	70.9	74.2	77.5
35°	46.2	46.2	47.8	49.5	51.1	54.4	56.1	57.7	61.2	64.4	65.9
37.5°	38.0	39.6	41.3	42.8	44.6	46.2	47.8	49.5	51.1	54.4	57.7
40°	31.3	33.0	34.5	36.4	36.4	39.6	39.6	42.8	44.6	47.8	51.1
42.5°	26.3	28.0	29.6	31.3	31.3	33.0	34.5	36.4	38.0	41.3	44.6
45°	21.5	23.1	24.8	26.3	26.3	28.0	29.6	31.3	33.0	36.4	38.0
47.5°	18.1	19.9	21.5	23.1	23.1	24.8	26.3	28.0	28.0	31.3	33.0
50°	14.9	16.5	18.1	19.9	19.9	21.5	23.1	24.8	24.8	26.3	28.0
52.5°	11.4	13.3	16.5	16.5	18.1	19.9	19.9	21.5	21.5	23.1	24.8
55°	11.4	13.3	14.9	14.9	16.5	18.1	18.1	19.9	19.9	19.9	21.5
57.5°	9.9	11.4	13.3	14.9	14.9	16.5	16.5	16.5	16.5	18.1	18.1
60°	9.9	11.4	11.4	13.3	13.3	14.9	14.9	14.9	14.9	16.5	16.5
62.5°	9.9	9.9	11.4	11.4	13.3	13.3	13.3	14.9	14.9	14.9	14.9
65°	8.2	9.9	11.4	11.4	11.4	13.3	13.3	13.3	13.3	13.3	13.3
67.5°	8.2	9.9	9.9	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
70°	8.2	8.2	9.9	9.9	9.9	11.4	11.4	11.4	9.9	11.4	9.9
72.5°	6.6	8.2	8.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
75°	6.6	8.2	8.2	8.2	8.2	9.9	9.9	8.2	8.2	8.2	8.2
77.5°	6.6	6.6	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	6.6
80°	6.6	6.6	6.6	6.6	8.2	8.2	6.6	6.6	6.6	6.6	6.6
82.5°	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9	4.9
85°	4.9	4.9	6.6	6.6	6.6	6.6	4.9	4.9	4.9	4.9	3.2
87.5°	4.9	4.9	4.9	6.6	4.9	4.9	4.9	4.9	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219569

CATALOG NUMBER: LDSQA4A35950D010TE LAR15SP 4LSQA1H-LSF-20 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	323.3	323.3	323.3	323.3	323.3	323.3	323.3	323.3
2.5°	278.8	277.1	278.8	277.1	277.1	278.8	273.8	277.1
5°	252.4	249.0	250.7	249.0	247.3	249.0	245.6	249.0
7.5°	229.3	227.7	227.7	227.7	226.0	227.7	224.2	227.7
10°	209.5	207.9	207.9	207.9	207.9	209.5	206.2	209.5
12.5°	189.7	189.7	191.4	189.7	191.4	193.0	189.7	193.0
15°	173.2	174.7	176.5	176.5	178.0	179.8	178.0	181.5
17.5°	160.1	161.6	164.9	164.9	166.6	169.8	168.3	171.5
20°	146.7	148.4	151.7	151.7	153.4	156.7	155.1	158.4
22.5°	132.0	135.3	137.0	138.5	140.2	143.5	141.9	145.2
25°	117.1	122.0	123.7	125.3	127.0	130.2	130.2	133.6
27.5°	105.6	109.0	110.6	112.2	115.4	118.8	118.8	120.4
30°	92.4	95.7	98.9	100.6	102.2	105.6	105.6	109.0
32.5°	80.8	84.2	85.8	87.5	90.7	94.0	95.7	97.3
35°	69.3	74.2	75.8	79.1	80.8	85.8	85.8	87.5
37.5°	61.2	64.4	67.6	69.3	72.6	75.8	75.8	79.1
40°	54.4	57.7	59.3	61.2	64.4	67.6	67.6	69.3
42.5°	46.2	51.1	52.7	54.4	56.1	59.3	61.2	62.7
45°	41.3	42.8	44.6	46.2	47.8	51.1	51.1	52.7
47.5°	34.5	36.4	38.0	39.6	41.3	42.8	44.6	46.2
50°	29.6	31.3	33.0	33.0	34.5	38.0	38.0	39.6
52.5°	24.8	26.3	28.0	28.0	29.6	33.0	33.0	34.5
55°	21.5	23.1	24.8	24.8	26.3	28.0	28.0	29.6
57.5°	19.9	19.9	21.5	21.5	23.1	23.1	24.8	24.8
60°	16.5	18.1	18.1	18.1	19.9	19.9	19.9	19.9
62.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	16.5
65°	13.3	13.3	13.3	13.3	13.3	13.3	11.4	13.3
67.5°	11.4	11.4	11.4	11.4	9.9	9.9	9.9	9.9
70°	9.9	9.9	9.9	9.9	9.9	8.2	8.2	8.2
72.5°	8.2	8.2	8.2	8.2	8.2	6.6	6.6	6.6
75°	8.2	8.2	6.6	6.6	6.6	6.6	6.6	4.9
77.5°	6.6	6.6	6.6	6.6	4.9	4.9	4.9	4.9
80°	4.9	4.9	4.9	4.9	4.9	4.9	3.2	3.2
82.5°	4.9	3.2	3.2	3.2	3.2	3.2	3.2	3.2
85°	3.2	3.2	3.2	3.2	1.7	1.7	1.7	1.7
87.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)