

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210833

Luminaire Tested: **LE_4B10D010 EC4B10209030 4LBCS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209030 4LBCS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1110.0 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210833

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBCS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P210833

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBCS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	108	104	100	97	100	97	94		96	93	91		92
2	101	94	87	82	99	92	86	81	88	84	79		85	81	78		82
3	93	83	75	70	90	81	74	69	79	73	68		76	71	67		73
4	85	74	66	60	83	73	65	59	70	64	58		68	62	58		66
5	79	66	58	52	77	65	57	51	63	56	51		61	55	50		60
6	73	60	52	45	71	59	51	45	57	50	45		56	49	44		54
7	68	55	46	40	66	54	46	40	52	45	40		51	44	40		50
8	63	50	42	36	61	49	41	36	48	41	36		47	40	36		46
9	59	46	38	33	57	45	38	32	44	37	32		43	37	32		42
10	55	42	35	30	54	42	34	30	41	34	29		40	34	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210833

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBCS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.0	3.9
10°-20°	122.3	11.0
20°-30°	184.0	16.6
30°-40°	218.0	19.6
40°-50°	217.0	19.5
50°-60°	174.9	15.8
60°-70°	105.8	9.5
70°-80°	39.3	3.5
80°-90°	5.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.2	31.5
0°-40°	567.2	51.1
0°-60°	959.0	86.4
0°-90°	1110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	453	
5°	451	43
15°	433	122
25°	400	184
35°	349	218
45°	282	217
55°	195	175
65°	106	106
75°	36	39
85°	5	6
90°	0	



TEST NUMBER: P210833

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBCS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	453.3
2.5°	453.3
5°	451.4
7.5°	450.0
10°	445.9
12.5°	439.2
15°	433.1
17.5°	426.4
20°	418.4
22.5°	410.3
25°	399.5
27.5°	388.1
30°	375.4
32.5°	363.2
35°	349.0
37.5°	334.3
40°	316.8
42.5°	300.0
45°	282.5
47.5°	263.0
50°	241.5
52.5°	219.2
55°	195.1
57.5°	173.5
60°	149.3
62.5°	127.8
65°	106.3
67.5°	86.1
70°	67.3
72.5°	50.5
75°	35.6
77.5°	22.9
80°	13.5
82.5°	8.1
85°	4.8
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)