

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211285

Luminaire Tested: **LE_4B15D010 EC4B10208035 4LBS1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208035 4LBS1LI
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1820.8 lumens
Efficiency: N/A
Efficacy: 127.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211285

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P211285

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20				20
RC	80				70					50					30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90	
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80	
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71	
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63	
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57	
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51	
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46	
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42	
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211285

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.9	6.5
10°-20°	300.7	16.5
20°-30°	389.6	21.4
30°-40°	381.7	21.0
40°-50°	323.5	17.8
50°-60°	212.1	11.6
60°-70°	85.2	4.7
70°-80°	9.8	0.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.1	44.4
0°-40°	1189.9	65.3
0°-60°	1725.5	94.8
0°-90°	1820.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1820.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1266	118
15°	1072	301
25°	851	390
35°	607	382
45°	421	324
55°	236	212
65°	83	85
75°	4	10
85°	0	0
90°	0	



TEST NUMBER: P211285

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1300.1
2.5°	1290.0
5°	1265.9
7.5°	1225.5
10°	1175.2
12.5°	1120.7
15°	1072.3
17.5°	1020.0
20°	967.6
22.5°	911.1
25°	850.6
27.5°	788.1
30°	723.6
32.5°	663.2
35°	606.7
37.5°	560.4
40°	509.9
42.5°	465.6
45°	421.3
47.5°	374.9
50°	328.5
52.5°	282.2
55°	235.8
57.5°	193.5
60°	153.2
62.5°	116.9
65°	82.6
67.5°	54.4
70°	32.2
72.5°	14.2
75°	4.1
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)