

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212378

Luminaire Tested: **LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2925.6 lumens
Efficiency: N/A
Efficacy: 61.3 lumens/watt
Spacing Criteria (0/90/45): 2.36 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212378

CATALOG NUMBER: LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212378

CATALOG NUMBER: LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	31601	31601	31601
5°	70697	29708	21287
10°	277285	26009	16772
15°	601937	21072	14593
20°	897978	15598	13175
25°	1167979	10988	11459
30°	1306594	7394	10023
35°	1175854	4328	8515
40°	959605	2972	7436
45°	550997	2014	6028
50°	161156	1537	5094
55°	18596	1250	4222
60°	3972	1434	3410
65°	1352	1352	2338
70°	1275	1671	1671
75°	1085	2208	1684
80°	0	3292	1618
85°	0	6558	1667



TEST NUMBER: P1212378

CATALOG NUMBER: LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	1.6
10°-20°	400.5	13.7
20°-30°	955.4	32.7
30°-40°	1008.3	34.5
40°-50°	457.2	15.6
50°-60°	40.1	1.4
60°-70°	8.4	0.3
70°-80°	5.5	0.2
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1402.6	47.9
0°-40°	2410.9	82.4
0°-60°	2908.2	99.4
0°-90°	2925.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2925.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	326	326	326	326	326	
5°	727	533	306	235	219	130
15°	6002	2111	210	144	146	1746
25°	10927	2905	103	88	107	4964
35°	9943	802	37	50	72	6140
45°	4022	113	15	28	44	3188
55°	110	18	7	16	25	220
65°	6	6	6	12	10	8
75°	3	3	6	7	4	3
85°	0	3	6	4	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1212378

CATALOG NUMBER: LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2
2.5°	484.7	487.6	474.5	476.0	462.7	468.6	464.1	452.4	443.6	428.9	423.0
5°	727.0	731.5	702.0	693.3	662.5	662.5	649.3	618.4	590.5	556.8	533.2
7.5°	1329.4	1347.0	1258.8	1192.7	1095.7	1072.2	1026.7	921.0	834.2	746.2	680.1
10°	2818.8	2786.5	2604.3	2454.4	2204.7	2112.3	1988.9	1684.8	1405.7	1128.1	910.7
12.5°	4444.8	4549.1	4197.9	4076.2	3680.9	3597.2	3334.3	2837.9	2366.4	1875.7	1440.9
15°	6001.8	6032.6	5725.6	5527.3	5045.5	4936.8	4613.7	4030.5	3396.0	2711.6	2110.8
17.5°	7251.8	7375.2	6924.3	6711.3	6085.5	5910.7	5530.3	4820.8	4114.3	3366.6	2654.3
20°	8710.4	8742.7	8208.0	7798.2	6980.1	6714.2	6258.9	5379.0	4537.4	3683.9	2948.0
22.5°	10036.7	10029.4	9342.0	8763.2	7727.6	7410.4	6847.8	5805.0	4826.7	3824.9	2975.9
25°	10926.9	10950.4	10214.5	9530.1	8259.4	7830.5	7196.0	6026.8	4925.2	3820.5	2905.4
27.5°	11401.3	11377.8	10589.0	9857.5	8454.8	7974.4	7285.6	6034.2	4835.5	3670.7	2693.8
30°	11680.4	11366.1	10524.3	9765.0	8322.6	7829.1	7128.4	5802.0	4537.4	3335.9	2316.4
32.5°	10934.2	10812.2	10079.3	9272.9	7867.2	7378.1	6686.3	5308.4	4064.3	2823.1	1659.9
35°	9942.7	9947.1	9231.8	8478.3	7153.4	6727.4	6013.5	4707.7	3487.1	1962.5	801.9
37.5°	8902.7	8917.5	8237.3	7536.7	6357.3	5909.2	5240.9	4023.2	2508.8	998.8	483.3
40°	7588.1	7618.9	7032.9	6470.4	5381.9	4950.1	4353.6	3044.9	1402.8	558.2	327.6
42.5°	6200.1	6238.2	5718.2	5218.8	4293.5	3938.1	3409.2	1886.0	696.3	361.3	192.4
45°	4021.8	4131.9	3745.6	3535.6	2999.5	2787.9	2225.4	962.1	420.1	211.6	113.2
47.5°	2301.8	2303.2	1977.1	1583.4	1298.5	1129.5	882.7	437.7	245.4	118.9	69.0
50°	1069.3	1095.7	868.2	722.7	517.1	437.7	359.9	236.5	129.3	69.0	42.6
52.5°	311.4	329.0	298.1	270.3	229.1	204.2	174.8	116.0	67.5	41.1	26.4
55°	110.1	117.5	110.1	102.8	92.5	83.7	74.9	55.8	38.3	25.0	17.6
57.5°	45.6	47.0	45.6	44.0	41.1	41.1	36.6	30.9	23.5	16.1	11.7
60°	20.5	22.0	20.5	22.0	20.5	20.5	20.5	22.0	14.7	10.2	8.8
62.5°	8.8	10.2	10.2	10.2	10.2	11.7	11.7	10.2	8.8	7.4	5.9
65°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
67.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
70°	4.5	4.5	4.5	4.5	4.5	4.5	2.9	2.9	4.5	4.5	4.5
72.5°	4.5	4.5	4.5	4.5	2.9	2.9	2.9	2.9	2.9	4.5	4.5
75°	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
77.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.9	2.9	2.9
80°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.9	2.9	2.9
82.5°	0.0	0.0	0.0	1.5	1.5	1.5	1.5	1.5	2.9	2.9	2.9
85°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.9	2.9	2.9
87.5°	0.0	0.0	0.0	0.0	1.5	1.5	1.5	1.5	2.9	2.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212378

CATALOG NUMBER: LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2
2.5°	415.7	402.4	381.9	368.7	362.8	354.0	348.1	333.5	327.6	315.7	311.4
5°	511.1	484.7	453.8	428.9	412.7	395.1	368.7	339.3	324.6	305.5	295.3
7.5°	619.8	562.5	508.2	464.1	443.6	420.1	386.3	340.7	312.9	287.9	273.2
10°	757.9	640.4	555.2	484.7	453.8	423.0	381.9	329.0	293.8	264.4	248.2
12.5°	1081.1	772.6	597.9	496.4	456.9	418.7	367.3	312.9	271.7	238.0	220.4
15°	1555.5	1079.6	712.5	506.8	446.5	399.6	340.7	286.5	243.9	210.1	192.4
17.5°	1975.6	1376.3	871.0	544.9	443.6	377.5	308.4	252.7	211.6	179.2	164.5
20°	2204.7	1532.0	976.8	568.5	430.3	343.8	271.7	218.9	179.2	151.3	138.1
22.5°	2209.2	1523.2	938.6	517.1	378.9	298.1	235.1	185.0	149.8	124.8	114.6
25°	2076.9	1358.7	782.9	406.8	310.0	252.7	196.8	154.2	121.9	102.8	94.0
27.5°	1830.1	1104.6	575.8	293.8	242.3	204.2	158.6	123.4	95.6	83.7	76.4
30°	1439.5	719.7	336.4	218.9	188.0	157.2	120.5	86.7	74.9	66.1	60.2
32.5°	772.6	349.5	235.1	161.6	133.7	110.1	79.4	63.2	54.4	48.5	47.0
35°	403.9	255.6	157.2	102.8	85.1	72.0	54.4	44.0	39.7	36.6	36.6
37.5°	289.4	160.0	99.9	66.1	55.8	45.6	38.3	32.3	29.4	29.4	29.4
40°	171.8	98.4	60.2	42.6	36.6	32.3	27.9	23.5	23.5	23.5	23.5
42.5°	104.3	61.6	42.6	29.4	26.4	23.5	20.5	19.1	17.6	17.6	19.1
45°	64.7	42.6	27.9	22.0	20.5	17.6	16.1	14.7	14.7	14.7	16.1
47.5°	41.1	30.9	20.5	14.7	13.3	11.7	10.2	10.2	11.7	11.7	13.3
50°	30.9	19.1	13.3	10.2	8.8	8.8	7.4	8.8	8.8	10.2	11.7
52.5°	17.6	11.7	8.8	7.4	7.4	5.9	5.9	7.4	7.4	8.8	10.2
55°	11.7	8.8	7.4	5.9	5.9	5.9	5.9	5.9	7.4	7.4	8.8
57.5°	8.8	7.4	5.9	5.9	5.9	4.5	5.9	5.9	5.9	7.4	8.8
60°	7.4	5.9	5.9	5.9	5.9	4.5	4.5	5.9	5.9	7.4	7.4
62.5°	5.9	5.9	5.9	5.9	5.9	4.5	5.9	5.9	5.9	5.9	7.4
65°	4.5	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	7.4
67.5°	4.5	4.5	5.9	5.9	5.9	4.5	5.9	5.9	5.9	5.9	7.4
70°	4.5	4.5	4.5	5.9	5.9	4.5	5.9	5.9	5.9	5.9	5.9
72.5°	4.5	4.5	4.5	5.9	5.9	4.5	5.9	5.9	5.9	5.9	5.9
75°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9
77.5°	4.5	4.5	4.5	4.5	5.9	4.5	5.9	5.9	5.9	5.9	5.9
80°	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9	5.9
82.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9
85°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9	5.9
87.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212378

CATALOG NUMBER: LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2
2.5°	299.6	295.3	286.5	285.0	283.5	277.6	273.2	268.9	268.9	264.4	261.5
5°	277.6	270.3	260.0	255.6	254.1	246.7	240.8	236.5	235.1	230.6	226.2
7.5°	254.1	245.4	233.5	229.1	227.7	220.4	214.5	210.1	207.1	202.7	199.7
10°	229.1	218.9	208.6	204.2	202.7	195.4	190.9	186.6	183.6	180.7	177.8
12.5°	202.7	194.0	183.6	179.2	177.8	171.8	167.4	164.5	163.1	160.0	158.6
15°	176.2	167.4	158.6	155.7	154.2	149.8	146.9	145.5	143.9	143.9	142.4
17.5°	149.8	142.4	135.0	133.7	132.2	129.3	127.8	126.3	127.8	127.8	129.3
20°	124.8	118.9	113.2	113.2	111.7	110.1	110.1	110.1	113.2	114.6	117.5
22.5°	102.8	98.4	94.0	94.0	94.0	94.0	94.0	96.9	99.9	102.8	104.3
25°	85.1	80.8	79.4	79.4	79.4	80.8	82.3	85.1	88.2	91.0	94.0
27.5°	69.0	66.1	66.1	66.1	67.5	69.0	70.6	73.4	77.8	80.8	83.7
30°	55.8	54.4	54.4	55.8	57.3	58.8	61.6	64.7	67.5	70.6	73.4
32.5°	44.0	45.6	45.6	47.0	48.5	49.9	52.9	55.8	58.8	61.6	63.2
35°	36.6	36.6	38.3	39.7	41.1	42.6	45.6	48.5	49.9	52.9	55.8
37.5°	29.4	30.9	32.3	33.8	35.2	36.6	38.3	41.1	42.6	45.6	48.5
40°	25.0	26.4	27.9	29.4	29.4	32.3	32.3	35.2	36.6	39.7	42.6
42.5°	20.5	22.0	23.5	25.0	25.0	26.4	27.9	29.4	32.3	33.8	36.6
45°	16.1	17.6	19.1	20.5	22.0	23.5	23.5	26.4	27.9	29.4	32.3
47.5°	14.7	16.1	17.6	17.6	19.1	20.5	20.5	23.5	25.0	26.4	27.9
50°	11.7	13.3	14.7	16.1	16.1	17.6	19.1	20.5	22.0	23.5	23.5
52.5°	10.2	11.7	13.3	13.3	14.7	16.1	16.1	17.6	19.1	19.1	20.5
55°	10.2	11.7	11.7	13.3	13.3	14.7	14.7	16.1	16.1	17.6	17.6
57.5°	8.8	10.2	10.2	11.7	11.7	13.3	13.3	14.7	14.7	14.7	16.1
60°	8.8	8.8	10.2	10.2	11.7	11.7	11.7	13.3	13.3	13.3	14.7
62.5°	7.4	8.8	8.8	10.2	10.2	10.2	11.7	11.7	11.7	13.3	13.3
65°	7.4	8.8	8.8	10.2	10.2	10.2	10.2	10.2	11.7	11.7	11.7
67.5°	7.4	7.4	8.8	8.8	8.8	8.8	10.2	10.2	10.2	10.2	10.2
70°	7.4	7.4	7.4	8.8	8.8	8.8	8.8	8.8	8.8	8.8	8.8
72.5°	5.9	7.4	7.4	7.4	7.4	8.8	8.8	8.8	8.8	8.8	7.4
75°	5.9	5.9	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
77.5°	5.9	5.9	5.9	7.4	7.4	7.4	7.4	7.4	7.4	5.9	5.9
80°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	4.5
82.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	4.5	4.5	4.5
85°	5.9	4.5	5.9	5.9	5.9	4.5	4.5	4.5	4.5	4.5	2.9
87.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	2.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212378

CATALOG NUMBER: LDSQA4A35935D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	326.2	326.2	326.2	326.2	326.2	326.2	326.2	326.2
2.5°	258.5	255.6	257.0	257.0	254.1	252.7	252.7	254.1
5°	223.2	220.4	221.8	221.8	218.9	217.3	217.3	218.9
7.5°	196.8	194.0	195.4	195.4	192.4	192.4	192.4	192.4
10°	176.2	174.8	174.8	174.8	171.8	173.3	171.8	170.5
12.5°	157.2	157.2	157.2	157.2	155.7	157.2	155.7	155.7
15°	142.4	142.4	143.9	143.9	143.9	145.5	145.5	145.5
17.5°	130.7	132.2	133.7	135.0	135.0	136.7	136.7	136.7
20°	118.9	121.9	123.4	124.8	124.8	127.8	126.3	127.8
22.5°	107.2	110.1	111.7	113.2	114.6	116.0	116.0	117.5
25°	96.9	99.9	101.3	102.8	104.3	107.2	107.2	107.2
27.5°	86.7	89.6	91.0	94.0	95.6	98.4	98.4	98.4
30°	76.4	79.4	80.8	82.3	85.1	88.2	88.2	89.6
32.5°	66.1	70.6	72.0	73.4	76.4	79.4	80.8	80.8
35°	58.8	61.6	63.2	66.1	67.5	72.0	72.0	72.0
37.5°	51.4	54.4	57.3	58.8	60.2	63.2	64.7	66.1
40°	45.6	48.5	49.9	51.4	54.4	57.3	58.8	58.8
42.5°	39.7	42.6	44.0	45.6	47.0	49.9	49.9	49.9
45°	35.2	36.6	38.3	39.7	41.1	42.6	44.0	44.0
47.5°	29.4	32.3	32.3	33.8	35.2	38.3	38.3	39.7
50°	25.0	27.9	27.9	29.4	30.9	32.3	33.8	33.8
52.5°	22.0	23.5	25.0	25.0	26.4	27.9	29.4	29.4
55°	19.1	20.5	20.5	22.0	22.0	23.5	25.0	25.0
57.5°	16.1	17.6	19.1	19.1	19.1	20.5	20.5	22.0
60°	14.7	16.1	16.1	16.1	16.1	17.6	17.6	17.6
62.5°	13.3	13.3	13.3	13.3	13.3	13.3	13.3	13.3
65°	11.7	11.7	11.7	11.7	10.2	10.2	10.2	10.2
67.5°	10.2	10.2	10.2	10.2	8.8	8.8	8.8	8.8
70°	8.8	8.8	8.8	8.8	7.4	7.4	7.4	5.9
72.5°	7.4	7.4	7.4	7.4	7.4	5.9	5.9	5.9
75°	7.4	5.9	5.9	5.9	5.9	5.9	4.5	4.5
77.5°	5.9	5.9	5.9	4.5	4.5	4.5	4.5	4.5
80°	4.5	4.5	4.5	4.5	4.5	2.9	2.9	2.9
82.5°	4.5	2.9	2.9	2.9	2.9	2.9	2.9	2.9
85°	2.9	2.9	2.9	2.9	1.5	1.5	1.5	1.5
87.5°	2.9	1.5	1.5	1.5	1.5	1.5	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)