

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761018

Luminaire Tested: LD6D15D010-EU6DR2015309024-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR2015309024-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1106.7 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761018

CATALOG NUMBER: LD6D15D010-EU6DR2015309024-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P761018

CATALOG NUMBER: LD6D15D010-EU6DR2015309024-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	688288
5°	620965
10°	348516
15°	177161
20°	75008
25°	34624
30°	18332
35°	9870
40°	5277
45°	3121
50°	1819
55°	952
60°	612
65°	440
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3121 cd/sqm

TEST NUMBER: P761018

CATALOG NUMBER: LD6D15D010-EU6DR2015309024-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	448.5	40.5
10°-20°	441.6	39.9
20°-30°	144.3	13.0
30°-40°	49.1	4.4
40°-50°	16.5	1.5
50°-60°	5.0	0.4
60°-70°	1.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.4	93.5
0°-40°	1083.5	97.9
0°-60°	1105.0	99.8
0°-90°	1106.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1106.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6300	
5°	5662	449
15°	1566	442
25°	287	144
35°	74	49
45°	20	17
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761018

CATALOG NUMBER: LD6D15D010-EU6DR2015309024-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6299.5
0.5°	6299.5
1°	6291.6
1.5°	6275.9
2°	6247.3
2.5°	6209.2
3°	6155.3
3.5°	6080.2
4°	5968.5
4.5°	5832.8
5°	5661.7
5.5°	5436.7
6°	5206.2
6.5°	4942.0
7°	4683.4
7.5°	4380.5
8°	4110.1
8.5°	3838.0
9°	3586.7
9.5°	3356.2
10°	3141.3
12.5°	2255.6
15°	1566.2
17.5°	1023.2
20°	645.1
22.5°	417.9
25°	287.2
27.5°	201.9
30°	145.3
32.5°	104.3
35°	74.0
37.5°	51.6
40°	37.0
42.5°	26.9
45°	20.2
47.5°	15.7
50°	10.7
52.5°	6.7
55°	5.0
57.5°	3.9
60°	2.8
62.5°	2.2
65°	1.7



TEST NUMBER: P761018

CATALOG NUMBER: LD6D15D010-EU6DR2015309024-6LBDP1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°		1.1
70°		0.6



(END OF REPORT)