

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761096

Luminaire Tested: LD6D15D010-EU6DR250215IC9024-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR250215IC9024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1143.1 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761096

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9024-6LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P761096

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	473700
5°	441191
10°	314721
15°	185350
20°	115331
25°	63292
30°	28942
35°	10964
40°	4964
45°	2982
50°	1241
55°	800
60°	568
65°	362
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2982 cd/sqm



TEST NUMBER: P761096

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.7	30.2
10°-20°	468.2	41.0
20°-30°	247.8	21.7
30°-40°	61.2	5.4
40°-50°	14.9	1.3
50°-60°	3.9	0.3
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1061.7	92.9
0°-40°	1122.9	98.2
0°-60°	1141.8	99.9
0°-90°	1143.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1143.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4336	
5°	4023	346
15°	1639	468
25°	525	248
35°	82	61
45°	19	15
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761096

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4335.5
2.5°	4264.3
5°	4022.6
7.5°	3537.2
10°	2836.7
12.5°	2144.3
15°	1638.6
17.5°	1277.1
20°	991.9
22.5°	743.9
25°	525.0
27.5°	352.1
30°	229.4
32.5°	139.6
35°	82.2
37.5°	50.3
40°	34.8
42.5°	26.6
45°	19.3
47.5°	11.7
50°	7.3
52.5°	5.3
55°	4.2
57.5°	3.3
60°	2.6
62.5°	2.0
65°	1.4
67.5°	0.6
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)