

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219577

Luminaire Tested: **LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26803)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 25° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3285.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 2.37 / 0.61 / 1.19
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219577

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219577

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75		
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61		
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55		
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50		
8	71	59	52	47	69	59	52	47	58	51	47	57	51	47	55	50	47	45		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	35466	35466	35466
5°	79401	33375	23883
10°	311360	29206	18828
15°	675923	23659	16378
20°	1008349	17505	14794
25°	1311532	12335	12870
30°	1467195	8300	11253
35°	1320383	4884	9556
40°	1077556	3326	8334
45°	618717	2261	6782
50°	180974	1718	5727
55°	20893	1385	4729
60°	4476	1589	3856
65°	1513	1513	2613
70°	1388	1869	1869
75°	1198	2470	1834
80°	0	3682	1785
85°	0	7336	1890



TEST NUMBER: P1219577

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	1.6
10°-20°	449.7	13.7
20°-30°	1072.8	32.7
30°-40°	1132.2	34.5
40°-50°	513.5	15.6
50°-60°	45.0	1.4
60°-70°	9.4	0.3
70°-80°	6.1	0.2
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1575.0	47.9
0°-40°	2707.2	82.4
0°-60°	3265.7	99.4
0°-90°	3285.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3285.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	366	366	366	366	366	
5°	816	599	343	264	246	147
15°	6740	2370	236	162	163	1961
25°	12270	3262	115	99	120	5574
35°	11165	900	41	56	81	6895
45°	4516	127	16	31	50	3580
55°	124	20	8	18	28	247
65°	7	7	7	13	11	9
75°	3	3	7	8	5	3
85°	0	3	7	5	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1219577

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1
2.5°	544.2	547.6	532.8	534.5	519.6	526.1	521.1	507.9	498.2	481.5	475.1
5°	816.5	821.5	788.3	778.5	743.8	743.8	729.0	694.4	663.1	625.0	598.7
7.5°	1492.7	1512.5	1413.6	1339.4	1230.4	1204.1	1153.0	1034.2	936.9	837.8	763.6
10°	3165.2	3128.8	2924.5	2756.2	2475.8	2371.8	2233.3	1891.9	1578.5	1266.8	1022.5
12.5°	4991.1	5108.2	4713.9	4577.1	4133.5	4039.4	3744.1	3186.7	2657.1	2106.2	1618.0
15°	6739.5	6774.1	6429.4	6206.7	5665.7	5543.7	5180.8	4525.9	3813.4	3044.8	2370.2
17.5°	8143.2	8281.6	7775.4	7536.2	6833.5	6637.3	6210.0	5413.3	4620.0	3780.4	2980.4
20°	9781.0	9817.2	9216.9	8756.6	7838.1	7539.5	7028.1	6040.2	5095.1	4136.7	3310.3
22.5°	11270.4	11262.2	10490.3	9840.3	8677.6	8321.2	7689.4	6518.5	5420.0	4295.1	3341.6
25°	12269.9	12296.3	11470.0	10701.4	9274.5	8793.0	8080.5	6767.5	5530.5	4290.2	3262.5
27.5°	12802.8	12776.4	11890.6	11069.1	9494.1	8954.7	8181.1	6775.8	5429.8	4121.8	3025.0
30°	13116.1	12763.1	11818.0	10965.2	9345.5	8791.4	8004.7	6515.2	5095.1	3745.8	2601.1
32.5°	12278.1	12141.4	11318.2	10412.8	8834.3	8285.1	7508.2	5961.0	4563.9	3170.1	1863.9
35°	11164.8	11169.9	10366.6	9520.5	8032.6	7554.4	6752.7	5286.4	3915.7	2203.6	900.5
37.5°	9997.1	10013.6	9249.9	8463.1	7138.6	6635.6	5885.0	4517.7	2817.2	1121.5	542.7
40°	8520.8	8555.5	7897.3	7265.6	6043.4	5558.5	4888.8	3419.3	1575.3	626.9	368.0
42.5°	6962.3	7005.0	6421.2	5860.3	4821.2	4422.1	3828.2	2117.9	781.9	405.7	216.1
45°	4516.1	4639.8	4206.0	3970.2	3368.0	3130.5	2498.9	1080.5	471.7	237.4	127.0
47.5°	2584.5	2586.2	2220.1	1778.1	1458.1	1268.5	991.3	491.6	275.5	133.6	77.5
50°	1200.8	1230.4	974.7	811.4	580.6	491.6	404.1	265.5	145.2	77.5	47.8
52.5°	349.6	369.5	334.8	303.6	257.3	229.3	196.2	130.3	75.8	46.2	29.6
55°	123.7	132.0	123.7	115.4	103.9	94.0	84.2	62.7	42.8	28.0	19.9
57.5°	51.1	52.7	51.1	49.5	46.2	46.2	41.3	34.5	26.3	18.1	13.3
60°	23.1	24.8	23.1	24.8	23.1	23.1	23.1	24.8	16.5	11.4	9.9
62.5°	9.9	11.4	11.4	11.4	11.4	13.3	13.3	11.4	9.9	8.2	6.6
65°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
67.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
70°	4.9	4.9	4.9	4.9	4.9	4.9	3.2	3.2	4.9	4.9	4.9
72.5°	4.9	4.9	4.9	4.9	3.2	3.2	3.2	3.2	3.2	4.9	4.9
75°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
77.5°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	1.7	3.2	3.2	3.2
80°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2
82.5°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	1.7	3.2	3.2	3.2
85°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2
87.5°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219577

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1
2.5°	466.9	452.0	428.8	414.0	407.4	397.5	391.0	374.4	368.0	354.6	349.6
5°	574.0	544.2	509.7	481.5	463.5	443.8	414.0	381.0	364.5	343.2	331.6
7.5°	696.0	631.7	570.6	521.1	498.2	471.7	433.7	382.6	351.3	323.3	306.8
10°	851.0	719.2	623.5	544.2	509.7	475.1	428.8	369.5	329.9	296.9	278.8
12.5°	1213.9	867.6	671.3	557.5	513.0	470.1	412.4	351.3	305.1	267.2	247.3
15°	1746.8	1212.3	800.0	569.0	501.4	448.7	382.6	321.7	273.8	235.9	216.1
17.5°	2218.4	1545.4	978.1	611.9	498.2	423.9	346.4	283.7	237.4	201.2	184.8
20°	2475.8	1720.4	1096.8	638.4	483.2	385.9	305.1	245.6	201.2	169.8	155.1
22.5°	2480.7	1710.4	1054.0	580.6	425.6	334.8	263.8	207.9	168.3	140.2	128.6
25°	2332.3	1525.8	879.1	456.8	348.1	283.7	221.0	173.2	137.0	115.4	105.6
27.5°	2055.1	1240.3	646.6	329.9	272.3	229.3	178.2	138.5	107.2	94.0	85.8
30°	1616.4	808.2	377.7	245.6	211.1	176.5	135.3	97.3	84.2	74.2	67.6
32.5°	867.6	392.6	263.8	181.5	150.0	123.7	89.1	70.9	61.2	54.4	52.7
35°	453.5	286.9	176.5	115.4	95.7	80.8	61.2	49.5	44.6	41.3	41.3
37.5°	324.9	179.8	112.2	74.2	62.7	51.1	42.8	36.4	33.0	33.0	33.0
40°	193.0	110.6	67.6	47.8	41.3	36.4	31.3	26.3	26.3	26.3	26.3
42.5°	117.1	69.3	47.8	33.0	29.6	26.3	23.1	21.5	19.9	19.9	21.5
45°	72.6	47.8	31.3	24.8	23.1	19.9	18.1	16.5	16.5	16.5	18.1
47.5°	46.2	34.5	23.1	16.5	14.9	13.3	11.4	11.4	13.3	13.3	14.9
50°	34.5	21.5	14.9	11.4	9.9	9.9	8.2	9.9	9.9	11.4	13.3
52.5°	19.9	13.3	9.9	8.2	8.2	6.6	6.6	8.2	8.2	9.9	11.4
55°	13.3	9.9	8.2	6.6	6.6	6.6	6.6	6.6	8.2	8.2	9.9
57.5°	9.9	8.2	6.6	6.6	6.6	4.9	6.6	6.6	6.6	8.2	9.9
60°	8.2	6.6	6.6	6.6	6.6	4.9	4.9	6.6	6.6	8.2	8.2
62.5°	6.6	6.6	6.6	6.6	6.6	4.9	6.6	6.6	6.6	6.6	8.2
65°	4.9	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	8.2
67.5°	4.9	4.9	6.6	6.6	6.6	4.9	6.6	6.6	6.6	6.6	8.2
70°	4.9	4.9	4.9	6.6	6.6	4.9	6.6	6.6	6.6	6.6	6.6
72.5°	4.9	4.9	4.9	6.6	6.6	4.9	6.6	6.6	6.6	6.6	6.6
75°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6
77.5°	4.9	4.9	4.9	4.9	6.6	4.9	6.6	6.6	6.6	6.6	6.6
80°	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6	6.6
82.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6
85°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6
87.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1219577

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1
2.5°	336.4	331.6	321.7	320.1	318.2	311.7	306.8	301.8	301.8	296.9	293.5
5°	311.7	303.6	291.9	286.9	285.3	277.1	270.4	265.5	263.8	259.0	254.1
7.5°	285.3	275.5	262.2	257.3	255.7	247.3	240.9	235.9	232.6	227.7	224.2
10°	257.3	245.6	234.2	229.3	227.7	219.3	214.4	209.5	206.2	202.9	199.5
12.5°	227.7	217.7	206.2	201.2	199.5	193.0	188.0	184.8	183.1	179.8	178.2
15°	197.8	188.0	178.2	174.7	173.2	168.3	164.9	163.3	161.6	161.6	160.1
17.5°	168.3	160.1	151.7	150.0	148.4	145.2	143.5	141.9	143.5	143.5	145.2
20°	140.2	133.6	127.0	127.0	125.3	123.7	123.7	123.7	127.0	128.6	132.0
22.5°	115.4	110.6	105.6	105.6	105.6	105.6	105.6	109.0	112.2	115.4	117.1
25°	95.7	90.7	89.1	89.1	89.1	90.7	92.4	95.7	98.9	102.2	105.6
27.5°	77.5	74.2	74.2	74.2	75.8	77.5	79.1	82.4	87.5	90.7	94.0
30°	62.7	61.2	61.2	62.7	64.4	65.9	69.3	72.6	75.8	79.1	82.4
32.5°	49.5	51.1	51.1	52.7	54.4	56.1	59.5	62.7	65.9	69.3	70.9
35°	41.3	41.3	42.8	44.6	46.2	47.8	51.1	54.4	56.1	59.5	62.7
37.5°	33.0	34.5	36.4	38.0	39.6	41.3	42.8	46.2	47.8	51.1	54.4
40°	28.0	29.6	31.3	33.0	33.0	36.4	36.4	39.6	41.3	44.6	47.8
42.5°	23.1	24.8	26.3	28.0	28.0	29.6	31.3	33.0	36.4	38.0	41.3
45°	18.1	19.9	21.5	23.1	24.8	26.3	26.3	29.6	31.3	33.0	36.4
47.5°	16.5	18.1	19.9	19.9	21.5	23.1	23.1	26.3	28.0	29.6	31.3
50°	13.3	14.9	16.5	18.1	18.1	19.9	21.5	23.1	24.8	26.3	26.3
52.5°	11.4	13.3	14.9	14.9	16.5	18.1	18.1	19.9	21.5	21.5	23.1
55°	11.4	13.3	13.3	14.9	14.9	16.5	16.5	18.1	18.1	19.9	19.9
57.5°	9.9	11.4	11.4	13.3	13.3	14.9	14.9	16.5	16.5	16.5	18.1
60°	9.9	9.9	11.4	11.4	13.3	13.3	13.3	14.9	14.9	14.9	16.5
62.5°	8.2	9.9	9.9	11.4	11.4	11.4	13.3	13.3	13.3	14.9	14.9
65°	8.2	9.9	9.9	11.4	11.4	11.4	11.4	11.4	13.3	13.3	13.3
67.5°	8.2	8.2	9.9	9.9	9.9	9.9	11.4	11.4	11.4	11.4	11.4
70°	8.2	8.2	8.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9
72.5°	6.6	8.2	8.2	8.2	8.2	9.9	9.9	9.9	9.9	9.9	8.2
75°	6.6	6.6	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
77.5°	6.6	6.6	6.6	8.2	8.2	8.2	8.2	8.2	8.2	6.6	6.6
80°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	4.9
82.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9	4.9
85°	6.6	4.9	6.6	6.6	6.6	4.9	4.9	4.9	4.9	4.9	3.2
87.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219577

CATALOG NUMBER: LDSQA4A35950D010TE LAR25NF 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	366.1	366.1	366.1	366.1	366.1	366.1	366.1	366.1
2.5°	290.3	286.9	288.6	288.6	285.3	283.7	283.7	285.3
5°	250.7	247.3	249.1	249.1	245.6	244.1	244.1	245.6
7.5°	221.0	217.7	219.3	219.3	216.1	216.1	216.1	216.1
10°	197.8	196.2	196.2	196.2	193.0	194.6	193.0	191.4
12.5°	176.5	176.5	176.5	176.5	174.7	176.5	174.7	174.7
15°	160.1	160.1	161.6	161.6	161.6	163.3	163.3	163.3
17.5°	146.7	148.4	150.0	151.7	151.7	153.4	153.4	153.4
20°	133.6	137.0	138.5	140.2	140.2	143.5	141.9	143.5
22.5°	120.4	123.7	125.3	127.0	128.6	130.3	130.3	132.0
25°	109.0	112.2	113.8	115.4	117.1	120.4	120.4	120.4
27.5°	97.3	100.6	102.2	105.6	107.2	110.6	110.6	110.6
30°	85.8	89.1	90.7	92.4	95.7	98.9	98.9	100.6
32.5°	74.2	79.1	80.8	82.4	85.8	89.1	90.7	90.7
35°	65.9	69.3	70.9	74.2	75.8	80.8	80.8	80.8
37.5°	57.7	61.2	64.4	65.9	67.6	70.9	72.6	74.2
40°	51.1	54.4	56.1	57.7	61.2	64.4	65.9	65.9
42.5°	44.6	47.8	49.5	51.1	52.7	56.1	56.1	56.1
45°	39.6	41.3	42.8	44.6	46.2	47.8	49.5	49.5
47.5°	33.0	36.4	36.4	38.0	39.6	42.8	42.8	44.6
50°	28.0	31.3	31.3	33.0	34.5	36.4	38.0	38.0
52.5°	24.8	26.3	28.0	28.0	29.6	31.3	33.0	33.0
55°	21.5	23.1	23.1	24.8	24.8	26.3	28.0	28.0
57.5°	18.1	19.9	21.5	21.5	21.5	23.1	23.1	24.8
60°	16.5	18.1	18.1	18.1	18.1	19.9	19.9	19.9
62.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9
65°	13.3	13.3	13.3	13.3	11.4	11.4	11.4	11.4
67.5°	11.4	11.4	11.4	11.4	9.9	9.9	9.9	9.9
70°	9.9	9.9	9.9	9.9	8.2	8.2	8.2	6.6
72.5°	8.2	8.2	8.2	8.2	8.2	6.6	6.6	6.6
75°	8.2	6.6	6.6	6.6	6.6	6.6	4.9	4.9
77.5°	6.6	6.6	6.6	4.9	4.9	4.9	4.9	4.9
80°	4.9	4.9	4.9	4.9	4.9	3.2	3.2	3.2
82.5°	4.9	3.2	3.2	3.2	3.2	3.2	3.2	3.2
85°	3.2	3.2	3.2	3.2	1.7	1.7	1.7	1.7
87.5°	3.2	1.7	1.7	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)