

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219581

Luminaire Tested: **LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1219581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26804)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°
Description: PORTFOLIO 4" SQUARE LENSED ADJUSTABLE, SELF-FLANGED, 35° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3347.7 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 2.46 / 0.61 / 1.2
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219581

CATALOG NUMBER: LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219581

CATALOG NUMBER: LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104	110	107	104	102		103	101	99		99	97	96		96	94	93
2	106	100	95	91	103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	91	85	80	97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	71	90	82	76	71		80	74	70		78	73	69		76	72	68
5	86	76	69	64	84	75	68	64		73	67	63		71	66	62		70	65	62
6	80	70	62	57	79	69	62	57		67	61	57		66	60	56		64	59	56
7	75	64	57	52	74	63	56	51		62	56	51		60	55	51		59	54	50
8	70	59	52	47	69	58	51	46		57	51	46		56	50	46		55	50	46
9	66	54	47	42	64	54	47	42		53	46	42		52	46	42		51	45	42
10	62	50	43	38	60	50	43	38		49	42	38		48	42	38		47	42	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	40097	40097	40097
5°	93988	37848	26460
10°	371346	33259	22055
15°	687257	26628	19357
20°	881226	19381	17505
25°	1054354	13746	15520
30°	1121104	9038	13647
35°	1148973	5464	11897
40°	1051771	3541	10218
45°	758953	2480	8385
50°	331339	2004	6963
55°	22852	1672	5827
60°	4166	1589	4805
65°	1513	1513	3415
70°	1388	1869	2323
75°	1198	2470	2470
80°	0	3682	2734
85°	0	7336	1890

TEST NUMBER: P1219581

CATALOG NUMBER: LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	1.8
10°-20°	473.9	14.2
20°-30°	992.0	29.6
30°-40°	1104.3	33.0
40°-50°	633.9	18.9
50°-60°	63.3	1.9
60°-70°	9.9	0.3
70°-80°	6.3	0.2
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1526.2	45.6
0°-40°	2630.5	78.6
0°-60°	3327.7	99.4
0°-90°	3347.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3347.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	414	414	414	414	414	
5°	966	666	389	284	272	177
15°	6852	2736	266	186	193	1937
25°	9864	3765	129	114	145	4467
35°	9715	1150	46	66	101	5932
45°	5540	138	18	36	61	4230
55°	135	20	10	22	34	404
65°	7	5	7	13	15	8
75°	3	3	7	8	7	2
85°	0	3	7	5	2	0
90°	0	0	0	0	0	

TEST NUMBER: P1219581

CATALOG NUMBER: LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9
2.5°	618.5	605.3	592.1	583.9	575.6	587.1	578.9	575.6	552.4	540.9	531.0
5°	966.5	941.7	905.3	875.7	846.0	852.6	829.5	801.5	743.8	702.5	666.3
7.5°	1865.2	1804.2	1692.1	1583.3	1474.4	1454.5	1382.0	1256.7	1095.0	973.0	867.5
10°	3775.0	3590.3	3384.2	3161.5	2900.9	2828.4	2648.7	2308.9	1937.8	1514.0	1207.2
12.5°	5572.6	5488.5	5246.1	4957.5	4675.5	4502.3	4316.0	3755.1	3166.5	2483.7	1913.1
15°	6852.5	6801.4	6588.6	6326.3	6022.8	5910.7	5683.2	5124.1	4380.2	3564.0	2736.0
17.5°	7800.7	7713.3	7490.6	7205.3	6845.8	6750.2	6478.1	5922.3	5150.4	4330.8	3412.1
20°	8547.9	8493.5	8204.9	7861.8	7431.3	7315.9	6997.6	6418.8	5579.3	4708.5	3773.3
22.5°	9219.1	9126.7	8772.1	8363.1	7871.7	7748.0	7393.4	6758.4	5856.2	4886.5	3837.7
25°	9863.9	9723.8	9293.3	8757.3	8180.1	8011.8	7622.7	6949.8	5958.6	4901.5	3765.2
27.5°	10051.9	9981.0	9583.5	8960.1	8292.1	8102.6	7696.8	6992.6	5920.6	4766.2	3504.6
30°	10022.2	9962.9	9631.3	8980.0	8272.5	8072.8	7660.5	6860.7	5699.6	4413.3	3044.4
32.5°	9928.3	9905.2	9504.5	8808.5	8087.7	7870.0	7424.7	6532.4	5285.7	3875.6	2224.8
35°	9715.4	9624.8	9125.1	8470.3	7777.6	7538.4	7035.4	6062.5	4739.8	2821.8	1149.6
37.5°	9092.0	9021.2	8626.9	8053.0	7378.6	7071.8	6540.8	5455.6	3669.5	1604.6	687.6
40°	8316.9	8282.4	7972.2	7459.4	6738.7	6392.4	5815.1	4464.4	2239.6	912.0	453.5
42.5°	7521.9	7512.1	7180.6	6644.6	5862.9	5465.4	4866.9	3011.5	1190.7	550.9	262.2
45°	5539.7	5599.2	5368.2	5046.6	4449.5	4160.8	3384.2	1551.9	686.0	305.1	138.5
47.5°	3885.5	3819.5	3410.6	2848.2	2302.2	1949.4	1474.4	733.8	366.1	160.1	79.1
50°	2198.5	2210.0	1840.5	1489.3	976.2	773.4	587.1	369.3	176.5	84.0	47.8
52.5°	574.0	600.3	517.8	445.2	379.4	308.5	249.0	160.1	84.0	49.5	31.3
55°	135.3	140.2	130.2	122.0	115.4	102.2	90.7	69.3	46.2	31.3	19.9
57.5°	47.8	49.5	47.8	47.8	46.2	44.6	41.3	36.4	28.0	19.9	13.3
60°	21.5	23.1	21.5	23.1	23.1	23.1	23.1	23.1	16.5	11.4	8.2
62.5°	9.9	9.9	9.9	9.9	11.4	11.4	13.3	13.3	9.9	8.2	6.6
65°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	4.9
67.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
70°	4.9	4.9	4.9	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.9
72.5°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
75°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
77.5°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2	3.2
80°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	1.7	3.2	3.2	3.2
82.5°	0.0	0.0	0.0	1.7	1.7	1.7	1.7	1.7	3.2	3.2	3.2
85°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2
87.5°	0.0	0.0	0.0	0.0	1.7	1.7	1.7	1.7	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219581

CATALOG NUMBER: LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9
2.5°	512.8	511.3	493.1	480.0	473.4	463.4	452.0	435.4	417.1	400.8	394.1
5°	623.5	602.0	564.0	532.7	517.8	503.0	476.6	447.0	418.8	389.2	374.4
7.5°	766.9	704.2	630.0	572.3	547.6	522.9	484.8	443.6	405.7	366.1	344.7
10°	963.1	818.1	689.4	597.1	560.7	527.8	473.4	422.1	381.0	338.1	310.0
12.5°	1377.1	1017.5	752.0	608.5	560.7	517.8	452.0	392.5	346.3	301.7	275.4
15°	1983.9	1373.7	889.0	620.2	549.2	494.7	418.8	354.6	305.1	265.5	240.9
17.5°	2473.7	1701.9	1058.8	649.8	534.4	463.4	376.1	308.5	262.2	225.9	206.2
20°	2721.2	1840.5	1136.3	654.8	498.2	413.9	324.9	260.6	219.3	188.0	171.5
22.5°	2716.2	1796.0	1066.9	574.0	437.0	357.9	273.7	214.4	181.5	156.6	143.5
25°	2544.7	1589.8	890.7	458.4	353.0	296.8	222.6	173.2	146.7	128.6	117.1
27.5°	2223.1	1291.3	664.7	339.8	275.4	234.2	173.2	138.5	117.1	103.9	95.7
30°	1744.8	864.2	418.8	252.3	209.5	176.5	133.6	107.1	92.4	80.8	75.8
32.5°	961.5	450.3	282.0	184.8	153.4	128.6	98.9	77.5	67.6	59.3	57.7
35°	531.0	318.2	201.1	123.7	102.2	87.5	67.6	56.1	49.5	46.2	46.2
37.5°	376.1	204.5	120.4	77.5	65.9	57.7	46.2	39.6	38.0	36.4	36.4
40°	225.9	120.4	72.6	51.1	44.6	39.6	34.5	29.6	29.6	28.0	29.6
42.5°	123.7	72.6	49.5	36.4	31.3	29.6	24.8	23.1	23.1	23.1	24.8
45°	74.2	47.8	34.5	26.3	23.1	19.9	18.1	16.5	18.1	18.1	19.9
47.5°	47.8	34.5	23.1	16.5	14.9	13.3	11.4	13.3	13.3	14.9	16.5
50°	33.0	21.5	14.9	9.9	9.9	8.2	9.9	9.9	11.4	13.3	14.9
52.5°	21.5	14.9	9.9	8.2	6.6	6.6	6.6	8.2	9.9	11.4	13.3
55°	13.3	9.9	8.2	6.6	6.6	6.6	6.6	6.6	8.2	9.9	11.4
57.5°	9.9	8.2	6.6	4.9	4.9	4.9	6.6	6.6	8.2	8.2	9.9
60°	6.6	6.6	4.9	4.9	4.9	4.9	4.9	6.6	6.6	8.2	9.9
62.5°	6.6	6.6	4.9	4.9	4.9	4.9	6.6	6.6	6.6	8.2	8.2
65°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	8.2
67.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	8.2
70°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	8.2
72.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6
75°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6
77.5°	3.2	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6
80°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6
82.5°	3.2	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6
85°	3.2	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6	6.6
87.5°	3.2	4.9	4.9	4.9	4.9	4.9	4.9	4.9	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219581

CATALOG NUMBER: LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9
2.5°	385.9	374.4	364.5	367.7	361.2	349.5	346.3	338.1	328.3	326.6	326.6
5°	357.9	339.8	324.9	323.2	316.7	303.6	300.1	291.9	283.7	282.0	280.5
7.5°	323.2	303.6	290.3	286.9	282.0	270.4	268.8	260.6	255.7	252.3	252.3
10°	288.6	270.4	259.0	257.3	254.1	244.1	242.4	235.9	231.0	229.2	227.6
12.5°	255.7	240.9	231.0	229.2	225.9	217.7	216.1	211.1	207.9	206.2	206.2
15°	224.2	211.1	202.8	201.1	199.5	191.4	191.4	188.0	186.4	186.4	188.0
17.5°	193.0	181.5	174.7	173.2	173.2	166.6	168.3	166.6	166.6	166.6	169.8
20°	161.6	151.7	146.7	148.4	145.2	143.5	145.2	145.2	145.2	148.4	153.4
22.5°	135.3	127.0	122.0	123.7	123.7	122.0	123.7	125.3	128.6	133.6	138.5
25°	110.6	103.9	102.2	103.9	103.9	103.9	107.1	110.6	113.8	118.8	123.7
27.5°	89.1	84.0	84.0	85.8	87.5	87.5	92.4	95.7	100.6	105.6	110.6
30°	70.9	69.3	69.3	72.6	72.6	74.2	80.8	84.0	87.5	92.4	97.3
32.5°	56.1	56.1	57.7	61.2	61.2	64.4	69.3	72.6	75.8	80.8	85.8
35°	46.2	47.8	49.5	51.1	52.7	54.4	59.3	62.7	65.9	70.9	74.2
37.5°	38.0	39.6	41.3	44.6	44.6	46.2	51.1	54.4	56.1	61.2	65.9
40°	31.3	33.0	34.5	38.0	38.0	39.6	44.6	46.2	47.8	52.7	57.7
42.5°	26.3	28.0	29.6	31.3	33.0	34.5	38.0	39.6	42.8	46.2	49.5
45°	21.5	23.1	24.8	26.3	28.0	29.6	31.3	34.5	36.4	39.6	42.8
47.5°	18.1	19.9	21.5	23.1	24.8	24.8	28.0	29.6	31.3	34.5	38.0
50°	16.5	18.1	19.9	19.9	21.5	23.1	24.8	26.3	28.0	29.6	33.0
52.5°	13.3	14.9	16.5	18.1	18.1	19.9	21.5	23.1	24.8	26.3	28.0
55°	13.3	13.3	14.9	16.5	16.5	18.1	19.9	21.5	21.5	23.1	24.8
57.5°	11.4	13.3	13.3	14.9	14.9	16.5	18.1	18.1	19.9	19.9	21.5
60°	9.9	11.4	13.3	13.3	13.3	14.9	14.9	16.5	16.5	18.1	18.1
62.5°	9.9	11.4	11.4	13.3	13.3	13.3	14.9	14.9	14.9	16.5	16.5
65°	9.9	9.9	11.4	11.4	11.4	11.4	13.3	13.3	13.3	14.9	14.9
67.5°	8.2	9.9	9.9	9.9	11.4	11.4	11.4	11.4	11.4	13.3	13.3
70°	8.2	8.2	9.9	9.9	9.9	9.9	9.9	11.4	11.4	11.4	11.4
72.5°	8.2	8.2	8.2	8.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9
75°	6.6	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
77.5°	6.6	6.6	6.6	8.2	8.2	8.2	8.2	8.2	8.2	8.2	8.2
80°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
82.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9
85°	6.6	6.6	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
87.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219581

CATALOG NUMBER: LDSQA4A35950D010TE LAR35FL 4LSQAL1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	413.9	413.9	413.9	413.9	413.9	413.9	413.9	413.9
2.5°	319.9	316.7	315.0	319.9	313.4	316.7	315.0	316.7
5°	275.4	272.1	270.4	275.4	268.8	272.1	268.8	272.1
7.5°	247.3	245.6	244.1	247.3	242.4	245.6	244.1	245.6
10°	224.2	222.6	221.0	225.9	221.0	224.2	222.6	224.2
12.5°	204.5	204.5	202.8	206.2	202.8	206.2	204.5	206.2
15°	186.4	188.0	186.4	189.7	188.0	191.4	189.7	193.0
17.5°	171.5	173.2	173.2	178.0	176.5	181.5	179.7	181.5
20°	156.6	158.4	160.1	163.3	163.3	168.3	166.6	169.8
22.5°	141.9	145.2	145.2	150.0	150.0	155.0	155.0	156.6
25°	127.0	131.9	133.6	137.0	138.5	143.5	143.5	145.2
27.5°	115.4	118.8	120.4	125.3	127.0	131.9	131.9	135.3
30°	102.2	107.1	109.0	112.2	113.8	118.8	118.8	122.0
32.5°	90.7	94.0	97.3	100.6	102.2	107.1	107.1	110.6
35°	79.1	84.0	85.8	89.1	92.4	97.3	97.3	100.6
37.5°	69.3	74.2	75.8	79.1	82.4	87.5	87.5	90.7
40°	61.2	65.9	67.6	70.9	72.6	79.1	79.1	80.8
42.5°	54.4	57.7	59.3	62.7	64.4	67.6	67.6	70.9
45°	46.2	49.5	51.1	52.7	56.1	59.3	59.3	61.2
47.5°	39.6	42.8	44.6	46.2	47.8	51.1	51.1	54.4
50°	34.5	36.4	38.0	39.6	41.3	44.6	44.6	46.2
52.5°	29.6	31.3	33.0	34.5	36.4	38.0	39.6	41.3
55°	26.3	28.0	28.0	29.6	31.3	33.0	33.0	34.5
57.5°	23.1	24.8	24.8	24.8	26.3	28.0	28.0	29.6
60°	19.9	21.5	21.5	21.5	23.1	23.1	23.1	24.8
62.5°	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1
65°	14.9	14.9	14.9	14.9	14.9	14.9	13.3	14.9
67.5°	13.3	13.3	13.3	11.4	11.4	11.4	11.4	11.4
70°	11.4	11.4	11.4	9.9	9.9	9.9	8.2	8.2
72.5°	9.9	9.9	9.9	8.2	8.2	8.2	6.6	6.6
75°	8.2	8.2	8.2	8.2	6.6	6.6	6.6	6.6
77.5°	6.6	6.6	6.6	6.6	6.6	6.6	4.9	4.9
80°	6.6	4.9	4.9	4.9	4.9	4.9	4.9	4.9
82.5°	4.9	4.9	4.9	4.9	3.2	3.2	3.2	3.2
85°	3.2	3.2	3.2	3.2	3.2	3.2	1.7	1.7
87.5°	3.2	1.7	1.7	1.7	1.7	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)