

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753458

Luminaire Tested: LD4D75BD010-EU4DR6070959024-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6070959024-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6468.7 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753458

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P753458

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	839374
5°	860008
10°	870396
15°	829167
20°	731077
25°	591315
30°	399976
35°	200434
40°	32505
45°	31831
50°	32466
55°	32955
60°	33871
65°	34643
70°	35460
75°	35883
80°	34606
85°	28833

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 35883 cd/sqm



TEST NUMBER: P753458

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	749.4	11.6
10°-20°	2027.6	31.3
20°-30°	2181.5	33.7
30°-40°	948.3	14.7
40°-50°	159.3	2.5
50°-60°	154.9	2.4
60°-70°	132.5	2.0
70°-80°	88.6	1.4
80°-90°	26.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4958.6	76.7
0°-40°	5906.9	91.3
0°-60°	6221.0	96.2
0°-90°	6468.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6468.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7682	
5°	7841	749
15°	7330	2028
25°	4905	2182
35°	1503	948
45°	206	159
55°	173	155
65°	134	132
75°	85	89
85°	23	27
90°	0	



TEST NUMBER: P753458

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7682.3
2.5°	7898.2
5°	7841.2
7.5°	7859.2
10°	7845.2
12.5°	7683.3
15°	7330.3
17.5°	6856.4
20°	6287.6
22.5°	5678.7
25°	4904.9
27.5°	3923.1
30°	3170.3
32.5°	2443.4
35°	1502.7
37.5°	642.9
40°	227.9
42.5°	210.0
45°	206.0
47.5°	199.0
50°	191.0
52.5°	182.0
55°	173.0
57.5°	164.0
60°	155.0
62.5°	145.0
65°	134.0
67.5°	123.0
70°	111.0
72.5°	98.0
75°	85.0
77.5°	70.0
80°	55.0
82.5°	39.0
85°	23.0
87.5°	8.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)