

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761707

Luminaire Tested: LD6D15D010-EU6DR650215IC9024-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9024-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1067.8 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761707

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9024-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P761707

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9024-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56628
5°	56487
10°	56440
15°	54696
20°	49796
25°	43395
30°	36093
35°	28598
40°	20638
45°	13034
50°	6796
55°	3615
60°	1904
65°	1050
70°	444
75°	474
80°	336
85°	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13034 cd/sqm



TEST NUMBER: P761707

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9024-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	8.6
10°-20°	251.1	23.5
20°-30°	306.9	28.7
30°-40°	249.0	23.3
40°-50°	124.1	11.6
50°-60°	34.6	3.2
60°-70°	7.9	0.7
70°-80°	2.0	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	649.7	60.8
0°-40°	898.7	84.2
0°-60°	1057.4	99.0
0°-90°	1067.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1067.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	970	
5°	964	92
15°	905	251
25°	673	307
35°	401	249
45°	158	124
55°	36	35
65°	8	8
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P761707

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9024-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	969.6
2.5°	968.9
5°	963.5
7.5°	960.4
10°	951.7
12.5°	934.0
15°	904.6
17.5°	858.7
20°	801.2
22.5°	739.0
25°	673.4
27.5°	603.1
30°	535.2
32.5°	468.0
35°	401.1
37.5°	334.3
40°	270.7
42.5°	211.2
45°	157.8
47.5°	110.0
50°	74.8
52.5°	51.6
55°	35.5
57.5°	23.9
60°	16.3
62.5°	11.2
65°	7.6
67.5°	3.8
70°	2.6
72.5°	2.4
75°	2.1
77.5°	1.4
80°	1.0
82.5°	0.7
85°	0.4
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)