

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210736

Luminaire Tested: **LE_4B10D010 EC4B10208027 4LBS1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208027 4LBS1WH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1176.6 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210736

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1WH

Luminous Intensity Polar Plot





TEST NUMBER: P210736

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73		93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64		86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56		79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45		69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41		65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37		61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34		57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210736

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	5.5
10°-20°	167.5	14.2
20°-30°	219.1	18.6
30°-40°	232.0	19.7
40°-50°	216.4	18.4
50°-60°	163.9	13.9
60°-70°	88.8	7.5
70°-80°	23.8	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.3	38.4
0°-40°	683.3	58.1
0°-60°	1063.6	90.4
0°-90°	1176.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1176.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	702	
5°	691	65
15°	599	168
25°	476	219
35°	371	232
45°	282	216
55°	184	164
65°	89	89
75°	21	24
85°	0	0
90°	0	



TEST NUMBER: P210736

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	701.7
2.5°	699.1
5°	691.4
7.5°	674.7
10°	652.7
12.5°	627.0
15°	598.7
17.5°	566.5
20°	538.2
22.5°	506.0
25°	476.4
27.5°	446.7
30°	418.4
32.5°	393.9
35°	370.9
37.5°	347.7
40°	325.7
42.5°	303.8
45°	282.0
47.5°	257.5
50°	233.0
52.5°	208.6
55°	184.1
57.5°	158.3
60°	133.9
62.5°	110.8
65°	88.9
67.5°	68.2
70°	50.2
72.5°	34.8
75°	20.6
77.5°	9.0
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)