

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761036

Luminaire Tested: LD6D15D010-EU6DR2015309027-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR2015309027-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1508.7 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761036

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P761036

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		113	111	109	108		107	106	104		103	102	101		100	99	98
2	111	108	105	102		109	106	104	101		103	101	99		100	99	97		98	96	95
3	108	103	100	97		106	102	99	96		100	97	95		97	95	93		95	93	92
4	105	99	96	93		103	98	95	92		96	93	91		95	92	90		93	91	89
5	102	96	92	89		100	95	91	89		94	90	88		92	89	87		91	88	86
6	99	93	89	86		98	92	88	86		91	87	85		90	87	84		88	86	84
7	96	90	86	83		95	89	86	83		88	85	82		87	84	82		86	84	82
8	94	87	83	81		93	87	83	80		86	83	80		85	82	80		84	82	80
9	91	85	81	78		91	85	81	78		84	80	78		83	80	78		82	80	78
10	89	83	79	76		88	82	79	76		82	78	76		81	78	76		81	78	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	938233
5°	846463
10°	475083
15°	241489
20°	102250
25°	47198
30°	24980
35°	13458
40°	7203
45°	4249
50°	2465
55°	1314
60°	830
65°	595
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4249 cd/sqm



TEST NUMBER: P761036

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	611.4	40.5
10°-20°	602.0	39.9
20°-30°	196.7	13.0
30°-40°	66.9	4.4
40°-50°	22.5	1.5
50°-60°	6.8	0.5
60°-70°	2.3	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1410.1	93.5
0°-40°	1477.0	97.9
0°-60°	1506.3	99.8
0°-90°	1508.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1508.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8587	
5°	7718	611
15°	2135	602
25°	392	197
35°	101	67
45°	28	23
55°	7	7
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761036

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	8587.1
0.5°	8587.1
1°	8576.4
1.5°	8555.0
2°	8516.0
2.5°	8464.0
3°	8390.6
3.5°	8288.1
4°	8135.9
4.5°	7950.9
5°	7717.7
5.5°	7411.1
6°	7096.8
6.5°	6736.6
7°	6384.1
7.5°	5971.2
8°	5602.6
8.5°	5231.8
9°	4889.2
9.5°	4574.9
10°	4282.1
12.5°	3074.7
15°	2134.9
17.5°	1394.7
20°	879.4
22.5°	569.7
25°	391.5
27.5°	275.3
30°	198.0
32.5°	142.2
35°	100.9
37.5°	70.3
40°	50.5
42.5°	36.7
45°	27.5
47.5°	21.4
50°	14.5
52.5°	9.2
55°	6.9
57.5°	5.4
60°	3.8
62.5°	3.1
65°	2.3



TEST NUMBER: P761036

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	1.5
70°	0.8



(END OF REPORT)