

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210827

Luminaire Tested: **LE_4B10D010 EC4B10208030 4LB1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208030 4LB1WH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1041.2 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210827

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LB1WH

Luminous Intensity Polar Plot





TEST NUMBER: P210827

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LB1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210827

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LB1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.9	6.1
10°-20°	184.2	17.7
20°-30°	271.7	26.1
30°-40°	268.1	25.8
40°-50°	164.1	15.8
50°-60°	62.9	6.0
60°-70°	19.7	1.9
70°-80°	5.8	0.6
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.8	49.9
0°-40°	787.9	75.7
0°-60°	1015.0	97.5
0°-90°	1041.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1041.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	671	
5°	671	64
15°	653	184
25°	595	272
35°	435	268
45°	210	164
55°	66	63
65°	18	20
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P210827

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LB1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	671.1
2.5°	672.5
5°	671.1
7.5°	669.7
10°	665.5
12.5°	659.8
15°	652.7
17.5°	644.3
20°	631.5
22.5°	617.4
25°	594.8
27.5°	566.5
30°	531.2
32.5°	487.4
35°	435.1
37.5°	377.2
40°	317.8
42.5°	262.7
45°	210.5
47.5°	163.9
50°	124.4
52.5°	91.9
55°	66.4
57.5°	46.6
60°	33.9
62.5°	25.4
65°	18.3
67.5°	14.2
70°	9.9
72.5°	7.1
75°	5.7
77.5°	2.8
80°	2.8
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)