

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761493

Luminaire Tested: LD6D15D010-EU6DR500215IC9027-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761493  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR500215IC9027-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1550.8 lumens  
Efficiency: N/A  
Efficacy: 98.2 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761493

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9027-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P761493

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9027-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 |  | 106 | 104 | 102 |  | 102 | 101 | 99  |  | 98  | 97  | 97  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  |  | 100 | 98  | 95  |  | 97  | 95  | 93  |  | 95  | 93  | 91  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  |  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  | 88  | 86  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  |  | 90  | 87  | 84  |  | 89  | 85  | 83  |  | 87  | 84  | 82  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 79  |  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 77  |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 79  | 75  |  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  | 76  | 74  |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |
| 8   | 85  | 76  | 71  | 67  | 84  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 69  | 66  |
| 9   | 81  | 73  | 68  | 64  | 80  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 71  | 67  | 64  |  | 70  | 66  | 63  |
| 10  | 78  | 70  | 64  | 61  | 77  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 68  | 64  | 61  |  | 67  | 63  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 273010 |
| 5°  | 270148 |
| 10° | 265694 |
| 15° | 241942 |
| 20° | 201326 |
| 25° | 142907 |
| 30° | 75635  |
| 35° | 30825  |
| 40° | 11453  |
| 45° | 5238   |
| 50° | 2159   |
| 55° | 1124   |
| 60° | 546    |
| 65° | 155    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5238 cd/sqm



TEST NUMBER: P761493

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9027-6LBS1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 232.8  | 15.0      |
| 10°-20°   | 588.4  | 37.9      |
| 20°-30°   | 528.5  | 34.1      |
| 30°-40°   | 165.5  | 10.7      |
| 40°-50°   | 29.0   | 1.9       |
| 50°-60°   | 5.8    | 0.4       |
| 60°-70°   | 0.9    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1349.7 | 87.0      |
| 0°-40°    | 1515.2 | 97.7      |
| 0°-60°    | 1549.9 | 99.9      |
| 0°-90°    | 1550.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1550.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2499 |      |
| 5°  | 2463 | 233  |
| 15° | 2139 | 588  |
| 25° | 1185 | 529  |
| 35° | 231  | 165  |
| 45° | 34   | 29   |
| 55° | 6    | 6    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P761493

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9027-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2498.7 |
| 2.5°  | 2486.3 |
| 5°    | 2463.1 |
| 7.5°  | 2427.6 |
| 10°   | 2394.8 |
| 12.5° | 2289.5 |
| 15°   | 2138.9 |
| 17.5° | 1947.6 |
| 20°   | 1731.5 |
| 22.5° | 1481.4 |
| 25°   | 1185.4 |
| 27.5° | 871.5  |
| 30°   | 599.5  |
| 32.5° | 390.4  |
| 35°   | 231.1  |
| 37.5° | 132.7  |
| 40°   | 80.3   |
| 42.5° | 52.3   |
| 45°   | 33.9   |
| 47.5° | 20.6   |
| 50°   | 12.7   |
| 52.5° | 8.7    |
| 55°   | 5.9    |
| 57.5° | 4.0    |
| 60°   | 2.5    |
| 62.5° | 1.5    |
| 65°   | 0.6    |
| 67.5° | 0.2    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)