

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760871

Luminaire Tested: LD6D15D010-EU6DR1015209024-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR1015209024-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1269.6 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760871

CATALOG NUMBER: LD6D15D010-EU6DR1015209024-6LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P760871

CATALOG NUMBER: LD6D15D010-EU6DR1015209024-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	116	114	113	111	114	112	111	109		108	107	106			104	104	103			98
2	113	110	108	106	111	108	106	104		105	104	102			103	101	100			97
3	111	107	104	102	109	106	103	101		103	101	99			101	99	98			95
4	108	104	101	99	107	103	100	98		101	99	97			99	97	96			94
5	106	102	99	96	105	101	98	96		99	97	95			98	96	94			93
6	104	100	96	94	103	99	96	94		98	95	93			97	94	93			91
7	103	98	95	93	102	97	94	92		96	94	92			95	93	92			90
8	101	96	93	91	100	96	93	91		95	92	91			94	92	90			89
9	100	95	92	90	99	94	92	90		94	91	90			93	91	89			88
10	98	94	91	89	98	93	91	89		93	90	88			92	90	88			87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3020404
5°	1432265
10°	293741
15°	80640
20°	32498
25°	17420
30°	10308
35°	6709
40°	4479
45°	2905
50°	1598
55°	1200
60°	677
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2905 cd/sqm



TEST NUMBER: P760871

CATALOG NUMBER: LD6D15D010-EU6DR1015209024-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	902.8	71.1
10°-20°	244.3	19.2
20°-30°	69.9	5.5
30°-40°	31.9	2.5
40°-50°	14.6	1.2
50°-60°	4.9	0.4
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1217.0	95.9
0°-40°	1249.0	98.4
0°-60°	1268.5	99.9
0°-90°	1269.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1269.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27644	
5°	13059	903
15°	713	244
25°	144	70
35°	50	32
45°	19	15
55°	6	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P760871

CATALOG NUMBER: LD6D15D010-EU6DR1015209024-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	27644.0
0.5°	27405.3
1°	26792.9
1.5°	25612.0
2°	24289.8
2.5°	22543.6
3°	20602.7
3.5°	18724.6
4°	16698.8
4.5°	14833.3
5°	13058.8
5.5°	11450.8
6°	9918.2
6.5°	8570.8
7°	7302.0
7.5°	6218.5
8°	5257.5
8.5°	4415.8
9°	3687.1
9.5°	3131.2
10°	2647.6
12.5°	1262.5
15°	712.9
17.5°	433.4
20°	279.5
22.5°	194.7
25°	144.5
27.5°	106.8
30°	81.7
32.5°	62.8
35°	50.3
37.5°	37.7
40°	31.4
42.5°	25.1
45°	18.8
47.5°	12.6
50°	9.4
52.5°	6.3
55°	6.3
57.5°	3.1
60°	3.1
62.5°	3.1
65°	0.0



TEST NUMBER: P760871

CATALOG NUMBER: LD6D15D010-EU6DR1015209024-6LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	0.0
70°	0.0



(END OF REPORT)