

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761791

Luminaire Tested: LD6D15D010-EU6DR700215IC9027-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR700215IC9027-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1337.7 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761791

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P761791

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20			
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	93	93	93	93	
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85	85	85	
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	78	78	78	78	
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71	71	71	71	71	
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	65	65	65	65	
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	60	60	60	60	
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56	56	56	56	56	
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51	51	51	
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48	48	48	48	48	
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44	44	44	44	44	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115358
5°	115074
10°	114818
15°	114789
20°	113668
25°	106776
30°	95190
35°	75895
40°	50391
45°	30131
50°	15621
55°	8210
60°	2906
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30131 cd/sqm

TEST NUMBER: P761791

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.8	7.5
10°-20°	286.2	21.4
20°-30°	403.7	30.2
30°-40°	348.5	26.1
40°-50°	156.1	11.7
50°-60°	40.9	3.1
60°-70°	2.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.6	59.0
0°-40°	1138.1	85.1
0°-60°	1335.0	99.8
0°-90°	1337.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1337.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1056	
5°	1049	100
15°	1015	286
25°	886	404
35°	569	348
45°	195	156
55°	43	41
65°	0	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761791

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1055.8
2.5°	1054.7
5°	1049.2
7.5°	1044.6
10°	1034.9
12.5°	1026.2
15°	1014.8
17.5°	1001.7
20°	977.6
22.5°	937.9
25°	885.7
27.5°	825.2
30°	754.5
32.5°	668.1
35°	569.0
37.5°	459.7
40°	353.3
42.5°	268.5
45°	195.0
47.5°	134.4
50°	91.9
52.5°	63.4
55°	43.1
57.5°	26.0
60°	13.3
62.5°	4.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)