

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761733

Luminaire Tested: LD6D15D010-EU6DR650215IC9030-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9030-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1224.0 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761733

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9030-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P761733

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9030-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	97	95	94	93	93				
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85				
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78				
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72				
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66				
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61				
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56				
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52				
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49				
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64910
5°	64748
10°	64690
15°	62695
20°	57074
25°	49736
30°	41367
35°	32776
40°	23658
45°	14942
50°	7796
55°	4144
60°	2173
65°	1202
70°	495
75°	564
80°	370
85°	335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14942 cd/sqm

TEST NUMBER: P761733

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9030-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.1	8.6
10°-20°	287.8	23.5
20°-30°	351.8	28.7
30°-40°	285.4	23.3
40°-50°	142.2	11.6
50°-60°	39.7	3.2
60°-70°	9.0	0.7
70°-80°	2.4	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	744.7	60.8
0°-40°	1030.1	84.2
0°-60°	1212.0	99.0
0°-90°	1224.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1224.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1111	
5°	1104	105
15°	1037	288
25°	772	352
35°	460	285
45°	181	142
55°	41	40
65°	9	9
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P761733

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9030-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1111.4
2.5°	1110.6
5°	1104.4
7.5°	1100.8
10°	1090.8
12.5°	1070.6
15°	1036.9
17.5°	984.3
20°	918.3
22.5°	847.2
25°	771.8
27.5°	691.3
30°	613.4
32.5°	536.5
35°	459.7
37.5°	383.1
40°	310.3
42.5°	242.0
45°	180.9
47.5°	126.1
50°	85.8
52.5°	59.1
55°	40.7
57.5°	27.4
60°	18.6
62.5°	12.9
65°	8.7
67.5°	4.4
70°	2.9
72.5°	2.8
75°	2.5
77.5°	1.7
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)