

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761790

Luminaire Tested: LD6D15D010-EU6DR700215IC9027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR700215IC9027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1066.3 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761790

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P761790

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	74	69	88	79	73	69	77	72	68		75	71	67		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	77	66	60	56	75	66	60	56	65	59	55		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131004
5°	127106
10°	123561
15°	121938
20°	113866
25°	85546
30°	60470
35°	21421
40°	11268
45°	11991
50°	12426
55°	12668
60°	12740
65°	12461
70°	11756
75°	10891
80°	9690
85°	7772

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 60°

Luminance: 12740 cd/sqm



TEST NUMBER: P761790

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.3	10.3
10°-20°	299.8	28.1
20°-30°	330.2	31.0
30°-40°	126.2	11.8
40°-50°	59.6	5.6
50°-60°	59.2	5.6
60°-70°	47.4	4.4
70°-80°	27.2	2.6
80°-90°	7.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	739.4	69.3
0°-40°	865.5	81.2
0°-60°	984.3	92.3
0°-90°	1066.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1066.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1199	
5°	1159	109
15°	1078	300
25°	710	330
35°	161	126
45°	78	60
55°	66	59
65°	48	47
75°	26	27
85°	6	7
90°	0	



TEST NUMBER: P761790

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1199.0
2.5°	1186.4
5°	1158.9
7.5°	1135.9
10°	1113.7
12.5°	1094.9
15°	1078.0
17.5°	1037.2
20°	979.3
22.5°	854.4
25°	709.6
27.5°	617.7
30°	479.3
32.5°	309.6
35°	160.6
37.5°	86.7
40°	79.0
42.5°	78.4
45°	77.6
47.5°	75.9
50°	73.1
52.5°	69.8
55°	66.5
57.5°	62.6
60°	58.3
62.5°	53.3
65°	48.2
67.5°	42.5
70°	36.8
72.5°	31.1
75°	25.8
77.5°	20.3
80°	15.4
82.5°	10.8
85°	6.2
87.5°	2.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)