

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761288

Luminaire Tested: LD6D15D010-EU6DR350215IC9035-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR350215IC9035-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1379.1 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761288

CATALOG NUMBER: LD6D15D010-EU6DR350215IC9035-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P761288

CATALOG NUMBER: LD6D15D010-EU6DR350215IC9035-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	414601
5°	404866
10°	364891
15°	283206
20°	160631
25°	62484
30°	23315
35°	12778
40°	8358
45°	5084
50°	3230
55°	2286
60°	1683
65°	905
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5084 cd/sqm



TEST NUMBER: P761288

CATALOG NUMBER: LD6D15D010-EU6DR350215IC9035-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.5	24.6
10°-20°	662.8	48.1
20°-30°	270.3	19.6
30°-40°	64.7	4.7
40°-50°	27.0	2.0
50°-60°	11.2	0.8
60°-70°	3.5	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1272.7	92.3
0°-40°	1337.4	97.0
0°-60°	1375.5	99.7
0°-90°	1379.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1379.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3795	
5°	3691	339
15°	2504	663
25°	518	270
35°	96	65
45°	33	27
55°	12	11
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761288

CATALOG NUMBER: LD6D15D010-EU6DR350215IC9035-6LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3794.6
2.5°	3771.8
5°	3691.4
7.5°	3530.8
10°	3288.9
12.5°	2948.2
15°	2503.7
17.5°	1960.1
20°	1381.5
22.5°	880.9
25°	518.3
27.5°	293.0
30°	184.8
32.5°	129.8
35°	95.8
37.5°	74.1
40°	58.6
42.5°	45.1
45°	32.9
47.5°	24.6
50°	19.0
52.5°	15.1
55°	12.0
57.5°	9.7
60°	7.7
62.5°	5.6
65°	3.5
67.5°	1.3
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)