

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760970

Luminaire Tested: LD6D15D010-EU6DR1515309030-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR1515309030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1481.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760970

CATALOG NUMBER: LD6D15D010-EU6DR1515309030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P760970

CATALOG NUMBER: LD6D15D010-EU6DR1515309030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111	113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105	111	108	106	104		105	103	102		102	101	100		100	98	98
3	110	106	103	101	108	105	102	100		103	100	99		100	99	97		98	97	96
4	108	103	100	98	106	102	99	97		100	98	96		99	97	95		97	95	94
5	106	101	98	95	104	100	97	95		98	96	94		97	95	93		96	94	92
6	104	99	95	93	102	98	95	93		97	94	92		96	93	92		95	93	91
7	102	97	94	91	101	96	93	91		95	93	91		94	92	90		93	91	90
8	100	95	92	90	99	95	92	90		94	91	89		93	91	89		92	90	89
9	99	93	90	88	98	93	90	88		92	90	88		92	89	88		91	89	88
10	97	92	89	87	96	92	89	87		91	89	87		91	88	87		90	88	86

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2270461	2270461	2270461
5°	1334225	1316948	1327375
10°	398209	400999	407129
15°	99052	100980	97862
20°	29636	34316	30266
25°	10446	13305	10579
30°	3841	5054	3901
35°	1924	2171	1859
40°	1214	1335	1214
45°	896	959	896
50°	716	716	716
55°	592	592	592
60°	477	477	477
65°	364	364	364
70°	314	314	314
75°	197	197	257
80°	134	134	134
85°	75	75	75

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 959 cd/sqm



TEST NUMBER: P760970

CATALOG NUMBER: LD6D15D010-EU6DR1515309030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	960.5	64.9
10°-20°	395.1	26.7
20°-30°	78.5	5.3
30°-40°	19.6	1.3
40°-50°	10.3	0.7
50°-60°	7.6	0.5
60°-70°	5.4	0.4
70°-80°	3.1	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1434.1	96.8
0°-40°	1453.7	98.2
0°-60°	1471.6	99.4
0°-90°	1481.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1481.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	20178	20178	20178	20178	20178	
5°	13128	12994	12958	13048	13061	959
15°	1140	1162	1163	1142	1127	391
25°	134	152	171	151	136	70
35°	26	28	30	28	26	18
45°	13	13	14	13	13	10
55°	8	8	8	8	8	8
65°	5	5	5	5	5	5
75°	3	3	3	3	3	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	

TEST NUMBER: P760970

CATALOG NUMBER: LD6D15D010-EU6DR1515309030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	20178.3	20178.3	20178.3	20178.3	20178.3
2.5°	18201.6	18217.0	18223.0	18240.9	18307.5
5°	13128.4	12993.5	12958.4	13048.1	13061.0
7.5°	7776.8	7804.1	7904.1	7926.3	7846.0
10°	4267.7	4302.7	4297.6	4328.3	4363.3
12.5°	2182.5	2155.2	2146.6	2181.7	2133.0
15°	1140.4	1161.7	1162.6	1142.1	1126.7
17.5°	613.3	638.1	679.1	645.8	594.5
20°	362.2	384.4	419.4	392.1	369.9
22.5°	223.8	241.7	266.5	245.2	227.2
25°	134.1	152.1	170.8	151.2	135.8
27.5°	79.4	94.8	106.8	94.0	78.6
30°	51.3	59.8	67.5	58.9	52.1
32.5°	35.9	39.3	42.7	39.3	35.9
35°	26.5	28.2	29.9	28.2	25.6
37.5°	20.5	22.2	23.1	21.4	19.6
40°	17.1	17.9	18.8	17.9	17.1
42.5°	14.5	15.4	15.4	15.4	14.5
45°	12.8	12.8	13.7	12.8	12.8
47.5°	11.1	11.1	12.0	11.1	11.1
50°	10.3	10.3	10.3	10.3	10.3
52.5°	9.4	9.4	9.4	9.4	9.4
55°	8.5	8.5	8.5	8.5	8.5
57.5°	7.7	7.7	7.7	7.7	7.7
60°	6.8	6.8	6.8	6.8	6.8
62.5°	6.0	6.0	6.0	6.0	6.0
65°	5.1	5.1	5.1	5.1	5.1
67.5°	5.1	5.1	5.1	5.1	5.1
70°	4.3	4.3	4.3	4.3	4.3
72.5°	3.4	3.4	3.4	3.4	3.4
75°	2.6	2.6	2.6	2.6	3.4
77.5°	2.6	2.6	2.6	2.6	2.6
80°	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7
85°	0.9	0.9	0.9	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)