

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761740

Luminaire Tested: LD6D15D010-EU6DR650215IC9035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1356.4 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761740

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P761740

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145918
5°	146036
10°	151186
15°	151438
20°	139423
25°	118796
30°	90939
35°	64250
40°	37925
45°	15390
50°	5575
55°	3105
60°	1770
65°	982
70°	1022
75°	802
80°	818
85°	752

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15390 cd/sqm



TEST NUMBER: P761740

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.6	9.5
10°-20°	371.0	27.3
20°-30°	445.1	32.8
30°-40°	299.1	22.1
40°-50°	89.5	6.6
50°-60°	15.8	1.2
60°-70°	4.5	0.3
70°-80°	2.2	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	944.6	69.6
0°-40°	1243.7	91.7
0°-60°	1349.0	99.5
0°-90°	1356.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1356.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1336	
5°	1332	129
15°	1339	371
25°	985	445
35°	482	299
45°	100	90
55°	16	16
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P761740

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1335.5
2.5°	1341.2
5°	1331.5
7.5°	1351.6
10°	1362.7
12.5°	1360.0
15°	1338.8
17.5°	1286.8
20°	1199.1
22.5°	1095.8
25°	985.4
27.5°	860.7
30°	720.8
32.5°	594.0
35°	481.7
37.5°	370.6
40°	265.9
42.5°	173.7
45°	99.6
47.5°	52.8
50°	32.8
52.5°	22.7
55°	16.3
57.5°	11.7
60°	8.1
62.5°	5.3
65°	3.8
67.5°	3.4
70°	3.2
72.5°	2.5
75°	1.9
77.5°	1.7
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.4
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)