

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761350

Luminaire Tested: LD6D15D010-EU6DR400215IC9030-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761350
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR400215IC9030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1530.8 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761350

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P761350

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96						
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88						
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84						
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81						
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77						
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74						
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72						
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69						
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	389427
5°	387537
10°	366300
15°	311406
20°	212244
25°	88560
30°	27844
35°	12938
40°	7160
45°	3291
50°	1598
55°	876
60°	459
65°	155
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3291 cd/sqm



TEST NUMBER: P761350

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.9	21.6
10°-20°	739.1	48.3
20°-30°	370.0	24.2
30°-40°	67.8	4.4
40°-50°	18.7	1.2
50°-60°	4.4	0.3
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1439.0	94.0
0°-40°	1506.8	98.4
0°-60°	1530.0	99.9
0°-90°	1530.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1530.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3564	
5°	3533	330
15°	2753	739
25°	735	370
35°	97	68
45°	21	19
55°	5	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761350

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3564.2
2.5°	3559.0
5°	3533.4
7.5°	3451.7
10°	3301.6
12.5°	3067.6
15°	2753.0
17.5°	2343.8
20°	1825.4
22.5°	1244.5
25°	734.6
27.5°	388.3
30°	220.7
32.5°	142.6
35°	97.0
37.5°	69.3
40°	50.2
42.5°	34.4
45°	21.3
47.5°	13.5
50°	9.4
52.5°	6.6
55°	4.6
57.5°	2.9
60°	2.1
62.5°	1.3
65°	0.6
67.5°	0.4
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)