

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761071

Luminaire Tested: LD6D15D010-EU6DR2015309040-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR2015309040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1479.6 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761071

CATALOG NUMBER: LD6D15D010-EU6DR2015309040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P761071

CATALOG NUMBER: LD6D15D010-EU6DR2015309040-6LB DP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100			
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97			
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94			
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91			
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88			
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85			
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83			
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81			
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79			
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77			
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	920183
5°	830176
10°	465941
15°	236852
20°	100274
25°	46293
30°	24501
35°	13205
40°	7060
45°	4172
50°	2414
55°	1276
60°	809
65°	569
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4172 cd/sqm



TEST NUMBER: P761071

CATALOG NUMBER: LD6D15D010-EU6DR2015309040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	599.6	40.5
10°-20°	590.4	39.9
20°-30°	192.9	13.0
30°-40°	65.7	4.4
40°-50°	22.1	1.5
50°-60°	6.6	0.4
60°-70°	2.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1383.0	93.5
0°-40°	1448.6	97.9
0°-60°	1477.3	99.8
0°-90°	1479.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1479.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8422	
5°	7569	600
15°	2094	590
25°	384	193
35°	99	66
45°	27	22
55°	7	7
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761071

CATALOG NUMBER: LD6D15D010-EU6DR2015309040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8421.9
0.5°	8421.9
1°	8411.4
1.5°	8390.4
2°	8352.2
2.5°	8301.2
3°	8229.2
3.5°	8128.7
4°	7979.4
4.5°	7798.0
5°	7569.2
5.5°	7268.5
6°	6960.3
6.5°	6607.0
7°	6261.3
7.5°	5856.3
8°	5494.9
8.5°	5131.1
9°	4795.2
9.5°	4486.9
10°	4199.7
12.5°	3015.5
15°	2093.9
17.5°	1367.9
20°	862.4
22.5°	558.7
25°	384.0
27.5°	270.0
30°	194.2
32.5°	139.5
35°	99.0
37.5°	69.0
40°	49.5
42.5°	36.0
45°	27.0
47.5°	21.0
50°	14.2
52.5°	9.0
55°	6.7
57.5°	5.2
60°	3.7
62.5°	3.0
65°	2.2



TEST NUMBER: P761071

CATALOG NUMBER: LD6D15D010-EU6DR2015309040-6LBDP1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	1.5
70°	0.7



(END OF REPORT)