

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761502

Luminaire Tested: LD6D15D010-EU6DR500215IC9030-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR500215IC9030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1521.2 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761502

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P761502

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95						
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90						
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85						
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80						
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76						
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72						
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69						
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65						
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62						
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	267798
5°	264993
10°	260635
15°	237327
20°	197478
25°	140182
30°	74197
35°	30238
40°	11225
45°	5145
50°	2108
55°	1105
60°	546
65°	155
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5145 cd/sqm



TEST NUMBER: P761502

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.4	15.0
10°-20°	577.1	37.9
20°-30°	518.4	34.1
30°-40°	162.3	10.7
40°-50°	28.4	1.9
50°-60°	5.7	0.4
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1323.9	87.0
0°-40°	1486.2	97.7
0°-60°	1520.3	99.9
0°-90°	1521.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1521.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2451	
5°	2416	228
15°	2098	577
25°	1163	518
35°	227	162
45°	33	28
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761502

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2451.0
2.5°	2438.8
5°	2416.1
7.5°	2381.4
10°	2349.2
12.5°	2245.8
15°	2098.1
17.5°	1910.4
20°	1698.4
22.5°	1453.1
25°	1162.8
27.5°	854.9
30°	588.1
32.5°	382.9
35°	226.7
37.5°	130.2
40°	78.7
42.5°	51.2
45°	33.3
47.5°	20.2
50°	12.4
52.5°	8.5
55°	5.8
57.5°	4.0
60°	2.5
62.5°	1.4
65°	0.6
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)