

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761525

Luminaire Tested: LD6D15D010-EU6DR500215IC9040-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR500215IC9040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1571.7 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761525

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P761525

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	109	107		112	110	108	106		106	104	102			102	101	99			98
2	109	105	101	98		107	103	100	97		100	98	95			97	95	93			95
3	105	99	95	91		103	98	94	90		95	92	89			93	90	88			91
4	100	94	89	85		99	93	88	85		90	87	84			89	85	83			87
5	96	89	84	80		95	88	83	79		86	82	79			85	81	78			83
6	92	84	79	75		91	83	79	75		82	78	74			81	77	74			79
7	88	80	75	71		87	79	74	71		78	74	71			77	73	70			76
8	85	76	71	67		84	76	71	67		75	70	67			74	70	67			73
9	81	73	68	64		80	72	67	64		71	67	64			71	67	64			70
10	78	70	64	61		77	69	64	61		68	64	61			68	64	61			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276692
5°	273789
10°	269278
15°	245211
20°	204036
25°	144836
30°	76657
35°	31238
40°	11610
45°	5315
50°	2176
55°	1143
60°	568
65°	155
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5315 cd/sqm



TEST NUMBER: P761525

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.0	15.0
10°-20°	596.3	37.9
20°-30°	535.6	34.1
30°-40°	167.7	10.7
40°-50°	29.4	1.9
50°-60°	5.9	0.4
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1367.9	87.0
0°-40°	1535.6	97.7
0°-60°	1570.8	99.9
0°-90°	1571.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1571.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2532	
5°	2496	236
15°	2168	596
25°	1201	536
35°	234	168
45°	34	29
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761525

CATALOG NUMBER: LD6D15D010-EU6DR500215IC9040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2532.4
2.5°	2519.8
5°	2496.3
7.5°	2460.5
10°	2427.1
12.5°	2320.4
15°	2167.8
17.5°	1973.9
20°	1754.8
22.5°	1501.4
25°	1201.4
27.5°	883.3
30°	607.6
32.5°	395.6
35°	234.2
37.5°	134.5
40°	81.4
42.5°	52.9
45°	34.4
47.5°	20.9
50°	12.8
52.5°	8.8
55°	6.0
57.5°	4.1
60°	2.6
62.5°	1.5
65°	0.6
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)