

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761730

Luminaire Tested: LD6D15D010-EU6DR650215IC9030-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761730  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR650215IC9030-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1196.0 lumens  
Efficiency: N/A  
Efficacy: 75.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761730

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9030-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P761730

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9030-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 92  | 97  | 93  | 90  |  | 94  | 91  | 88  |  | 91  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 86  | 82  |  | 87  | 84  | 81  |  | 85  |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 84  | 79  | 75  |  | 82  | 77  | 74  |  | 80  |
| 5   | 90  | 81  | 74  | 70  | 88  | 80  | 74  | 69  | 78  | 73  | 69  |  | 76  | 72  | 68  |  | 75  |
| 6   | 85  | 75  | 69  | 64  | 83  | 74  | 68  | 64  | 73  | 67  | 63  |  | 71  | 67  | 63  |  | 70  |
| 7   | 80  | 70  | 64  | 59  | 79  | 69  | 63  | 59  | 68  | 63  | 59  |  | 67  | 62  | 58  |  | 66  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  |  | 63  | 58  | 54  |  | 62  |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 51  |  | 59  | 54  | 50  |  | 58  |
| 10  | 68  | 58  | 52  | 47  | 67  | 57  | 51  | 47  | 57  | 51  | 47  |  | 56  | 51  | 47  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 63421 |
| 5°  | 63264 |
| 10° | 63207 |
| 15° | 61256 |
| 20° | 55769 |
| 25° | 48602 |
| 30° | 40423 |
| 35° | 32027 |
| 40° | 23116 |
| 45° | 14603 |
| 50° | 7614  |
| 55° | 4053  |
| 60° | 2126  |
| 65° | 1175  |
| 70° | 495   |
| 75° | 542   |
| 80° | 370   |
| 85° | 335   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14603 cd/sqm



TEST NUMBER: P761730

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9030-6LBS1B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 102.7  | 8.6       |
| 10°-20°   | 281.2  | 23.5      |
| 20°-30°   | 343.7  | 28.7      |
| 30°-40°   | 278.9  | 23.3      |
| 40°-50°   | 139.0  | 11.6      |
| 50°-60°   | 38.8   | 3.2       |
| 60°-70°   | 8.8    | 0.7       |
| 70°-80°   | 2.3    | 0.2       |
| 80°-90°   | 0.6    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 727.6  | 60.8      |
| 0°-40°    | 1006.6 | 84.2      |
| 0°-60°    | 1184.3 | 99.0      |
| 0°-90°    | 1196.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1196.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1086 |      |
| 5°  | 1079 | 103  |
| 15° | 1013 | 281  |
| 25° | 754  | 344  |
| 35° | 449  | 279  |
| 45° | 177  | 139  |
| 55° | 40   | 39   |
| 65° | 8    | 9    |
| 75° | 2    | 2    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P761730

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9030-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1085.9 |
| 2.5°  | 1085.2 |
| 5°    | 1079.1 |
| 7.5°  | 1075.5 |
| 10°   | 1065.8 |
| 12.5° | 1046.0 |
| 15°   | 1013.1 |
| 17.5° | 961.8  |
| 20°   | 897.3  |
| 22.5° | 827.7  |
| 25°   | 754.2  |
| 27.5° | 675.5  |
| 30°   | 599.4  |
| 32.5° | 524.2  |
| 35°   | 449.2  |
| 37.5° | 374.4  |
| 40°   | 303.2  |
| 42.5° | 236.5  |
| 45°   | 176.8  |
| 47.5° | 123.2  |
| 50°   | 83.8   |
| 52.5° | 57.8   |
| 55°   | 39.8   |
| 57.5° | 26.8   |
| 60°   | 18.2   |
| 62.5° | 12.6   |
| 65°   | 8.5    |
| 67.5° | 4.3    |
| 70°   | 2.9    |
| 72.5° | 2.7    |
| 75°   | 2.4    |
| 77.5° | 1.6    |
| 80°   | 1.1    |
| 82.5° | 0.8    |
| 85°   | 0.5    |
| 87.5° | 0.3    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9







— 0°-180°







(END OF REPORT)