

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761675

Luminaire Tested: LD6D15D010-EU6DR600215IC9040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761675
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR600215IC9040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1519.4 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761675

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P761675

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197161
5°	202005
10°	204441
15°	194762
20°	171723
25°	138892
30°	93954
35°	47071
40°	7645
45°	7479
50°	7632
55°	7734
60°	7954
65°	8144
70°	8338
75°	8401
80°	8117
85°	6770

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 8401 cd/sqm



TEST NUMBER: P761675

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.0	11.6
10°-20°	476.3	31.3
20°-30°	512.4	33.7
30°-40°	222.7	14.7
40°-50°	37.4	2.5
50°-60°	36.4	2.4
60°-70°	31.1	2.0
70°-80°	20.8	1.4
80°-90°	6.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.7	76.7
0°-40°	1387.4	91.3
0°-60°	1461.2	96.2
0°-90°	1519.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1519.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1804	
5°	1842	176
15°	1722	476
25°	1152	512
35°	353	223
45°	48	37
55°	41	36
65°	32	31
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P761675

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1804.5
2.5°	1855.2
5°	1841.8
7.5°	1846.0
10°	1842.7
12.5°	1804.7
15°	1721.8
17.5°	1610.5
20°	1476.9
22.5°	1333.9
25°	1152.1
27.5°	921.5
30°	744.7
32.5°	573.9
35°	352.9
37.5°	151.0
40°	53.6
42.5°	49.3
45°	48.4
47.5°	46.8
50°	44.9
52.5°	42.7
55°	40.6
57.5°	38.5
60°	36.4
62.5°	34.0
65°	31.5
67.5°	28.9
70°	26.1
72.5°	23.0
75°	19.9
77.5°	16.4
80°	12.9
82.5°	9.2
85°	5.4
87.5°	1.9
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)