

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761058

Luminaire Tested: LD6D15D010-EU6DR2015309035-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761058
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR2015309035-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1640.4 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761058

CATALOG NUMBER: LD6D15D010-EU6DR2015309035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P761058

CATALOG NUMBER: LD6D15D010-EU6DR2015309035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1020157
5°	920375
10°	516566
15°	262574
20°	111168
25°	51321
30°	27163
35°	14632
40°	7830
45°	4620
50°	2686
55°	1429
60°	918
65°	646
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4620 cd/sqm



TEST NUMBER: P761058

CATALOG NUMBER: LD6D15D010-EU6DR2015309035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	664.8	40.5
10°-20°	654.6	39.9
20°-30°	213.8	13.0
30°-40°	72.8	4.4
40°-50°	24.5	1.5
50°-60°	7.4	0.4
60°-70°	2.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1533.2	93.5
0°-40°	1606.0	97.9
0°-60°	1637.9	99.8
0°-90°	1640.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1640.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9337	
5°	8392	665
15°	2321	655
25°	426	214
35°	110	73
45°	30	24
55°	8	7
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761058

CATALOG NUMBER: LD6D15D010-EU6DR2015309035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9336.9
0.5°	9336.9
1°	9325.3
1.5°	9302.0
2°	9259.6
2.5°	9203.1
3°	9123.3
3.5°	9011.8
4°	8846.4
4.5°	8645.2
5°	8391.6
5.5°	8058.2
6°	7716.5
6.5°	7324.9
7°	6941.6
7.5°	6492.6
8°	6091.9
8.5°	5688.6
9°	5316.1
9.5°	4974.4
10°	4656.0
12.5°	3343.2
15°	2321.3
17.5°	1516.5
20°	956.1
22.5°	619.4
25°	425.7
27.5°	299.3
30°	215.3
32.5°	154.6
35°	109.7
37.5°	76.5
40°	54.9
42.5°	39.9
45°	29.9
47.5°	23.3
50°	15.8
52.5°	10.0
55°	7.5
57.5°	5.8
60°	4.2
62.5°	3.3
65°	2.5



TEST NUMBER: P761058

CATALOG NUMBER: LD6D15D010-EU6DR2015309035-6LBDP1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	1.7
70°	0.8



(END OF REPORT)